



FX Series All Metal Hose

The corrosion resistant all metal hose designed
for high pressure & high temperature applications

Swagelok Columbus|Charleston

Swagelok®



Configurable. Local. Reliable.

Our expert operators and strict process control in manufacturing results in unmatched quality and consistency that customers can count on. Our products are backed by the Swagelok Limited Lifetime Warranty, proving our dedication and commitment to quality and our customers.

All FX hoses built are also provided with a Canadian Registration Number, proving that their temperature and pressure ratings have been tested to ensure consistent quality, safety, and performance standards.

Our FX Series All Metal Hose

Features

- High-pressure corrosion resistant all-metal hose
- 316L Stainless steel annular convoluted core
- Size ranging from 1/4 to 2 inch
- Working pressures from vacuum to 6000 psig (413 bar)
- Temperature rating from -200°C to 537°C (-325°F to 1000°F)

Benefits

- Double braid layers of 321 stainless steel promotes hose pressure containment
- End connections welded in accordance with ASME Boiler and Pressure Vessel Code Section IX
- Standard and custom assemblies available
- Optional hose covers, hose tags and additional leak tests available
- CRN Certified

Available end connections

Swagelok Tube Adapters



Swagelok Tube Fittings



Female VCO O-Ring Face Seal Fittings



SAE 37° (JIC) Female Swivel



Female Pipe Threads, NPT



Male Pipe Threads, NPT



High pressure applications

- Chemical
- Compressed gasses
- Cryogenic
- Hydrogen and fuel cell
- Marine
- Oil and gas
- Power
- Pulp and paper

Let's get started today.

Visit columbus.swagelok.com to learn more or contact us today - Columbus, OH (614)-212-7766 Charleston, WV: (304) 744-3461

Email: info@scioto.swagelok.com (OH) info.cvf@swagelok.com (WV)

© 2020 Swagelok Columbus|Charleston and © 2020 Swagelok Company