

CRN Statutory Declaration Log
Revision: 20-Jan-2022

n/a = not available

PRODUCT DESCRIPTION	LIMITING EXPIRY DATE	NATIONAL CRN	EXAMPLE PART NUMBER	SASKATCHEWAN (.3)	
				CRN	Expiry
FILTERS					
Filters (F, TF, FW, FC Series)	29-Apr-2029	0E21343.5C	SS-4FW-2	CSA-0E21343.56	4/29/29
B-TF4 w/PS--57314 (for gas distribution systems)	6-Apr-2031	0E23159.5C	B-4TF4-57314	0E23159.53	4/6/31
Genie Filters Supreme and Avenger	11-Jan-2026	0E07663.2C		0E7663.23	1/11/26
FITTINGS-CONE AND THREAD IPT					
Cone and Thread (IPT) Fittings	1-Mar-2026	0A18288.5C	SS-4FK0-1-4	CSA-0A18288.56	3/1/26
FITTINGS-FACE SEAL VCO & VCR					
VCO O-Ring Face Seal Fittings	10-Feb-2030	0A22161.5C	SS-4-VCO-1-2	0A22161.53	2/10/30
VCR Metal Gasket Face Seal Fittings	4-Oct-2029	0A21839.5C	SS-4-VCR-6-200	CSA-0A21839.56	10/4/29
FITTINGS-PIPE					
Pipe Fittings (Stainless Steel)	12-Jan-2031	0A22932.5C	SS-2-HRN-1	0A22932.53	1/12/31
Pipe Fittings (Brass)	17-Jun-2030	0A22505.5C	B-2-HRN-1	0A22505.53	6/17/30
FITTINGS-PLASTIC					
PFA Tube Fittings	13-Jul-2025	0A06054.5C	PFA-220-1-2	CSA-0A06054.56R2	9/7/25
FITTINGS-TUBE					
Tube Fittings (Stainless Steel)	24-Jan-2029	0A21025.5C	SS-100-1-2	CSA-0A21025.56	1/24/29
Tube Fittings (Carbon Steel)	2-Aug-2029	0A21661.5C	S-1210-1-8	CSA-0A21661.56	8/2/29
Tube Fittings (Brass)	13-May-2029	0A21395.5C	B-810-3	CSA-0A21395.56	5/13/29
Tube Fittings (Carbon Steel, MoS2 Coated- ZSML)	25-Jun-2031	See territory for CRN	S-1210-1-8ZSML	N/A	
Tube Fittings (Alloy 276, HC- a.k.a. "Hastelloy™")	2-Mar-2030	0A22214.5C	HC-100-1-2	0A22214.53	3/2/30
Tube Fittings (Alloy 400, M- a.k.a. "Monel™")	10-Jun-2029	0A21487.5C	M-100-1-2	CSA-0A21487.56	6/10/29
Tube Fittings (Alloy 600, INC- a.k.a. "Inconel™")	8-Apr-2030	0A22314.5C	INC-100-1-2	0A22314.53	4/8/30
Tube Fittings (Alloy 625)	11-Apr-2027	0A19311.5C	625-400-1-4	CSA-0A19311.56	4/11/27
Tube Fittings (Alloy 825)	1-Jun-2031	0A23291.5C	825-400-6	0A23291.53	6/1/31
Tube Fittings (2507)	10-Jun-2029	0A21486.5C	2507-400-1-4	CSA-0A21486.56	6/10/29
Fittings for Heavy Wall Tubing (Sno-Trik)	6-Apr-2030	0A22318.5C	SS-440-6	0A22318.53	4/6/30
Tube Fittings (Titanium)	1-Mar-2030	0A22212.5C	TI-100-1-2	0A22212.53	3/1/30
FK Tube Fittings (Medium Pressure- 15ksi)	7-Jun-2031	0A23299.5C	SS-4FK0-1-4	0A23299.53	6/7/31
Dielectric Fittings	25-Jul-2023	See territory for CRN		N/A	
810+1210 Tube Fittings to 8STH end (special)	22-Jun-2026	0A18544.5C		CSA-0A18544.56	7/22/26
Tube Fittings with ANSI Flange Adapters (SS)	9-Jun-2027	0A17712.2C	SS-400-F8-150	0A17712.23	6/9/27
ETOP Tube Fittings with ANSI Flange Adapter 625-600-F8-150	18-Jan-2029	See territory for CRN	625-600-F8-150	N/A	
ETOP Tube Fittings with ANSI Flange Adapters (M- Class 2500)	18-Oct-2029	See territory for CRN	M-810-F8-2500	N/A	
FITTINGS-WELD					
High Purity Weld Fittings	4-Oct-2029	0A21840.5C	316L-2TB7-4	CSA-0A21840.56	10/4/29
Industrial Weld Fittings	4-May-2030	0A22391.5C	SS-4-TSW-1-4	0A22391.53	5/4/30
FLOW METERS (VARIABLE AREA)					
M1, M2 VAF Variable Area Flowmeters	14-Apr-2031	0F21398.2C	VAF-M1-01M-1-1	0F21398.26	4/14/31
M4, M4H VAF Variable Area Flowmeters	3-Jan-2028	0F23192.5C	VAF-M4-1-1-01M-1A-F	0F23192.53	1/3/2028
GAUGES, TRANSDUCERS, PROBES					
Gauges and Transducers	20-Mar-2030	0F02026.2C	PGI-63B-BC.6-CASX	0F02026.23	3/20/30
SPR Retractable Probe	2-Aug-2022	0H2915.5C		N/A	
SPW Welded Probes	1-Mar-2022	See territory for CRN	SS-SPW-A3E6-P08	N/A	
PTX Transducers	1-Mar-2026	0F18289.5C	SS-PTX-D-G250-S4-K	0F18289.56	3/1/26
HOSES AND HOSE CONNECTORS					
Medium Pressure Hose (FJ Series)	15-Aug-2028	See territory for CRN	SS-FJ4TA4SL4-28	CSA-0D20616.56	8/15/28
Low Pressure Metal Flexible Hose (FL Series)	15-Sep-2029	0D21780.5C	SS-FL4TA4TA4-28	0D21780.56	9/15/29
High Pressure Metal Flexible Hose (FM Series)	15-Sep-2029	0D21781.5C	SS-FM8TA8PM8-43	0D21781.53	9/15/29
FX Metal Flexible Hose	11-Jul-2028	0D20522.5C	SS-FX8TA8PM8-43	CSA-0D20522.56	7/11/28
Multipurpose Push-On Hose (PB Series)	1-May-2029	0D21357.5C	SS-PB4TA4TA4-43	CSA-0D21357.5	5/1/29
PTFE Lined Stainless Steel Braided Hose (TH and TC Series) <i>and Crimped assemblies</i>	14-May-2030	0D22419.5C ADD1	SS-TH8TA8PM8-43	0D22419.52 (ADD1)	5/14/30
Thermoplastic Hose (7R, 8R, 7N, 8N and 7P Series)	16-Dec-2030	0D22889.5C	SS-7R4TA4TA4-43	0D22889.53	12/16/30
BT Series ("Coreflex") Hose	31-Aug-2030	0D22655.5C	SS-BT8TA8KC16-28	0D22655.53	8/31/30
CT Series ("Coreflex") Hose	14-Oct-2030	0D22736.5C	SS-CT8TA8KC16-28	0D22736.53	10/14/30
FC Series ("Coreflex") Hose	14-Oct-2030	0D22735.5C	SS-FC8TA8KC16-28	0D22735.53	10/16/30
NC Series ("Coreflex") Hose	31-Aug-2030	0D22658.5C	SS-NC8TA8KC16-28	0D22658.53	10/7/30
ST Series ("Coreflex") Hose	16-Oct-2030	0D22750.5C	SS-ST8TA8KC16-28	0D22750.53	10/16/30
Coreflex UT Series Hose (incl. Megafang design)	16-Oct-2030	0D22747.5C	SS-UT8TA8KC16-28	0D22747.53	10/16/30
W Series ("Coreflex") Hose	21-Dec-2025	0D14205.5C	SS-WC6TA6TA6-225	CSA-0D14205.56R1	12/21/25
X Series ("Coreflex") Hose	16-Oct-2030	0D22748.5C	SS-XT8TA8KC16-28	0D22748.53	10/16/30
MANIFOLDS					
VB03, VB04 Process DBBs (SS)	29-Jul-2026	0C18622.5C	VB0301CAD1C13CA	CSA-0C18622.56	7/29/26
VB04 (ETOP Special)	29-Jul-2026	0C18622.5C		CSA-0C18622.56ADD1	7/29/26
MN Series Monoflange Valves (SS)	11-Apr-2028	0C18486.2C	MN0201SAA1AC A A	0C18486.23	4/11/28
MN03 ETOP Special	19-Jan-2026	See territory for CRN		N/A	
V Series Manifolds (V2, V3, V5 Instrument Manifolds & V2, V3 Compact Body Manifolds)	18-Nov-2028	0C20864.5C	SS-V3NBF8	CSA-0C20864.56	11/18/28
VE Series Direct Mount Manifolds	16-Nov-2029	See territory for CRN	SS-VE3VF8-FL	N/A	
VN01 Series Double Block and Bleeds	14-Aug-2025	0C17881.5C	VN0102SAA1A1CCX-P0059	CSA-0C17881.56	8/14/25
QUICK COUPLINGS					
QC, QF, QM, QTM Series Quick-Connects	1-May-2029	0A21361.5C	SS-QC4-B-400	CSA-0A21361.56	5/1/29
REGULATORS					
Swagelok K Series Regulators (KPR, KCY, KCM, KLF, KHf, KCP, KPP, KPF, KHP, KHR, KBP, KFB, KCB, KPB, KHB, KEV, & KSV Series)	13-Sep-2023	0C16304.5C	KPR1A1C3CA10A00	CSA-0C16304.56	9/13/23
Swagelok RHPs Series Regulators (RSN2, RSN4, RSN6, RSN8, BSN4, BSN6, BSN8, RDN6, RDN8, LRSN4 Series)	10-Feb-2022	See territory for CRN	RSN2-02-1-VVK	CSA-0C15099.56	2/10/22
Swagelok RHPs Series Regulators (BS6, LRS4 Series)	5-Jan-2032	See territory for CRN			
Swagelok RHPs Series Regulators (RS, RSH, RD, RDH, BS Series)	24-Jun-2025	See territory for CRN	RSN2-02-1-VVK	N/A	
THERMOWELLS					
TWF, TWT, TWW Series R1 Thermowells	11-Sep-2024	0H12871.5C	TWT-008-T-1-N-4.50	0H12871.56R1	9/11/24
VALVES-BALL SHUT OFF					
40G Series Ball Valves	22-Jan-2025	0C6054.5C	SS-43GF4	CSA-0C6054.56ADD13	1/22/25
40 series Ball Valves	22-Feb-2029	0C21141.5C	SS-43F4	CSA-021141.56	2/22/29
60 series Ball Valves	22-Feb-2029	0C21138.5C	SS-63TF4	CSA-0C21138.56	2/22/29
83, G83 Series Multi-Service Trunnion Ball Valves	13-May-2029	0C21397.5C	SS-83KF4	CSA-0C21397.56	5/13/29
H83 Series Multi-Service Trunnion Ball Valves	1-May-2029	0C21354.5C	SS-H83PF4	CSA-0C21354.56	5/1/29
AFS Series Ball Valve	3-Jun-2024	0C16922.5C	SS-AFSS6	CSA-0C16922.56	6/3/24
Steam Trap Mount (Integrated test stand)	28-Aug-2025	0H6054.5C	SS-TVL1-T-S8-H1-SX	CSA-0H6054.56R4	8/28/25
FKB Medium Pressure (15ksi) Ball Valves	29-Nov-2022	See territory for CRN	SS-6FKBF4	CSA-0C15674.56	11/29/22
GB General Service Ball Valves	7-Jul-2030	0C20808.2C	SS-8GBS6	0C20808.23	7/7/30
SK Series Multipurpose Ball Valves	17-Oct-2026	0C18853.5C	SS-4SKPS4	CSA-0C18853.56	10/17/26

PRODUCT DESCRIPTION	LIMITING EXPIRY DATE	NATIONAL CRN	EXAMPLE PART NUMBER	CRN	Expiry
VALVES-BELLOWS SHUT OFF					
B Series Bellows Sealed Valves	22-Jan-2029	0C21018.5C	SS-(4,6,8,10,12)BG-TW	CSA-0C21018.56	1/22/29
H & HK Series Bellows Sealed Valves	6-May-2030	0C22395.5C	SS-4H	0C22395.56	5/6/30
U Series Bellows Sealed Valves	22-Feb-2029	0C21140.5C	SS-(4,6,8,10,12)UW	CSA-0C21140.5	2/22/29
VALVES-CHECK / RELIEF					
50 Series Lift Check Valves (SS)	15-Sep-2029	0C21782.5C	SS-(53,56,58)F4	0C21782.56	9/15/29
50 Series Lift Check Valves (M)	14-Aug-2024	0C17882.5C	M-(53,56,58)F4	CSA-0C17882.56	8/14/25
ETOP 50 Series Lift Check Valves: INC-58S12, INC-58S16	24-Dec-2028	See territory for CRN	INC-58S12, INC-58S16	N/A	
BV Series Bleed + P Series Purge Valves	17-Jun-2030	0C22506.5C	SS-BVM2	0C22506.53	6/17/30
C, CA Series Poppet Check Valves	18-Nov-2028	0C20863.5C	SS-(2,4,6,8,12,16)C-10	CSA-0C20863.5	11/18/28
CH Series Compact Check Valves	24-Apr-2028	0C20294.5C	SS-CHS8-10	0C20294.56	4/24/28
CP, CPA Series Check Valves	5-Jul-2029	0C21554.5C	SS-(4,8)CP2-1	CSA-0C21554.56	7/5/29
CW Series Welded Check Valve	17-Dec-2025	0C18133.5C		CSA-0C18133.56	12/17/25
KVV Series Regulator Relief Valve	19-Jan-2032	See territory for CRN		N/A	
R Series Proportional Relief Valves	8-Jan-2029	0C19221.2C	SS-RL3S4	0C19223.23	3/7/29
XS Series Industrial Excess Flow Valves	24-Apr-2028	0C20290.5C	SS-XSM8S8	0C20290.56	4/24/28
VALVES-DIAPHRAGM SHUT OFF					
DP & DPH Series Diaphragm Valves	31-Jul-2022	See territory for CRN	6LVV- DPBW4-P	N/A	
VALVES-GAUGE ROOT					
6PN Series Gauge Valves	21-Jan-2030	0C22125.5C	SS-6PNBGM8-F8	0C22125.56	1/21/30
VALVES-IPT					
IPT Check, Double Block & Bleed, Needle Valves	8-Jan-2026	0C18171.5C		CSA-0C18171.56	1/8/26
VALVES-NEEDLE SHUT OFF					
6DB Series Instrumentation Blowdown Valves	18-Nov-2028	0C20862.5C	SS-6DBF4	CSA-0C20862.56	11/18/28
D Series Non-Rotating Stem Needle Valve	27-Feb-2030	0C22209.5C	SS-(0,14,16)DM4	0C22209.53	2/27/30
GU Series General Utility Needle Valve	2-Mar-2026	0C6054.5C	SS-4GUF4	CSA-0C18297.56	3/2/26
JB, JN Series Screwed Bonnet Needle Valves	1-Apr-2030	0C22305.5C	SS-(2,4,6,8)JB	0C22305.53	4/1/30
N,HN Series Severe Service Union Bonnet Needle Valves	18-Nov-2028	0C20862.5C	SS-(3,6,12)NBF4	CSA-0C20862.56	11/18/28
O, 1, 18, 20, & 26 Series Integral Bonnet Needle Valves	10-Mar-2030	0C22234.5C	SS-(0,1,18)RM4	0C22234.53	3/10/30
1RP Series Compact Gauge Valve	10-Feb-2022	0C15099.5C	SS-1RPS8	CSA-0C15099.56	2/10/22
High Pressure Needle Valves (Sno-Trik)	28-Sep-2030	0C22706.5C	SS-(410,445,645,945)-FP	0C22706.53	9/28/30
G Series Toggle Valves	11-Dec-2020	See territory for CRN	SS-(0,1)GF4	0C22960.53	1/20/31
VALVES-PLUG SHUT OFF					
4P and 5P Series Rising Plug Valves	10-Jan-2029	0C20984.5C	SS-(4,5)PDF4	0C20984.53	1/10/29
P4T & P6T Series Plug Valves	10-Apr-2028	0C20227.5C	SS-(2,4,6,8,10)P4T	CSA-0C20227.56	4/10/28
PFA 43 Series Plug Valves	11-Sep-2024	0C17125.5C	PFA-43S4	CSA-0C17125.56	9/11/24
VALVES-REGULATING					
31 Series Union Bonnet Metering Valves S, M, L Series Metering Valves	22-Jun-2030	0C22514.5C	SS-31RF4 SS-(4,6)L	0C22514.53	6/22/30
VALVES-SPECIAL ALLOY					
Special Alloy 60, 83, BV, CH, N-HN valves	14-Nov-2026	See territory for CRN	n/a	CSA-0C18924.56	11/14/26
VALVES-SURFACE MOUNT & SAMPLING VALVE					
MPC Modular Platform Components, including PSV Pneumatically Actuated Switching Valve, SSV Series Stream Selector Valve	23-Sep-2030	0H22699.54	SS-MPC-42T-2	0H22699.53	9/23/30
PrESS MODULES					
Fluid Distribution Header (FDH1, FDH2) All other components-refer to CRNs listed above	31-Jan-2028	0H20020.5C	FDH1-CB-C0-A0-C0-0	0H20020.56	1/31/28