

Swagelok Northwest (US) Serving Alaska, Oregon, Washington, and the Idaho Panhandle:

We'll Help You Get the Job Done.

SERVICES & SOLUTIONS

SWAGELOK® CUSTOM SOLUTIONS

CAD Service/Design Support
General Industrial Assemblies
High Purity Assemblies Class
100 Clean Room

EVALUATION & ADVISORY SERVICES

Hose Advisory Services
Compressed Gas Leak Detection

TECHNICAL SUPPORT

Browse Products/Download Data Sheets
Download Product Catalogs
Email Technical Support
Cv Online Calculator Tool
Flow Curve Generator Tool
Download CAD Drawings
Download Product Certifications
Rent Tools

TRAINING AND EDUCATION

Tube Fitting Installation (Half Day) Tube Bending (Half Day)
Orbital Weld Training (Full Day)
Tube Fitting Safety Installation Seminar
Valve Selection Seminar
VCR® Safety Installation Seminar
Thread Identification Seminar Regulator Selection Seminar

PRODUCT CATALOG QUICK LINKS

FILTERS

[Coalescing Filters](#)
[High-purity Filters](#)
[Particulate Filters: Inline and Tee Type](#)

FITTINGS

[Swagelok® Tube Fittings \(1/16"- 2"\)](#)
[B Type VCO® L-Ring Face Seal Fittings](#)
[Dielectric Fittings](#)
[Flange to Swagelok Tube Fitting](#)
[PFA Fine Thread Flare Fittings](#)
[Pipe Fittings](#)
[Vacuum Fittings](#)
[VCO® O-ring Face Seal](#)
[VCR® Metal Gasket Face Seal](#)
[Weld Fittings](#)

HOSES AND FLEXIBLE TUBING

[313 SS Core Hoses, SS Braid](#)
[Hose And Flexible Tubing End Connections](#)
[Nylon Core Hose, Fiber Braid Reinforced](#)
[PFA Core Hose, 302 SS Braid Reinforced](#)
[PFA Flexible Tubing](#)
[Polyethylene Core, Fiber Braid Reinforced](#)
[PTFE Core Hose, Convuluted or Smooth Bore](#)
[Rubber Core Hose, Rayon Fiber Reinforced](#)
[Vacuum Flexible Tubing Convuluted 316 SS](#)
[Vinyl Flexible Tubing](#)
[Hose Accessories](#)

LEAK DETECTORS, LUBRICANTS, SEALANTS

[Heat Exchanger Tube Plugs](#)
[Lubricants \(Goop®\)](#)
[Sealants \(PTFE Tape, SWAK®, PTFE-Free\)](#)
[Snoop® Liquid Leak Detector](#)

MEASUREMENT DEVICES

[Flow Sensors](#)
[Pressure Gauges](#)
[Pressure Transducers](#)
[Thermometers](#)
[Thermowells](#)
[Variable Area Flowmeters](#)

MINIATURE MODULAR SYSTEMS

[Analytical, Modular Platform Components](#)
[Ultrahigh-Purity Integrated Gas Components](#)

PRE-ENGINEERED SUBSYSTEMS

[Calibration and Switching Modules](#)
[Fast Loop Modules](#)
[Field Station Modules](#)
[Fluid Distribution Headers](#)
[Sample Probe Modules](#)

QUICK CONNECTS

[Full-Flow](#)
[Instrumentation](#)
[Miniature](#)
[PTFE-Sealed](#)

REGULATORS

[Back-Pressure, Dome-Loaded](#)
[Back-Pressure, Spring-Loaded](#)
[Pressure-Reducing, Dome-Loaded](#)
[Pressure-Reducing, Spring-Loaded](#)
[Specialty](#)

SAMPLE CYLINDERS

[Miniature Sample Cylinders](#)
[Single & Double Ended Cylinders](#)

TOOLS AND ACCESSORIES

[Tube Benders](#)
[Tube Cutter](#)
[Deburring Tool](#)
[Hydraulic Swaging Units](#)
[Inspection Gauges](#)
[Lubricants](#)
[Orbital Welding System](#)
[Sealants](#)
[Wrenches](#)

TUBING AND TUBE SUPPORTS

[304 304L and 316 316L Seamless](#)
[304/304L Welded](#)
[316L Titanium Alloyed](#)
[Insulated Tubing](#)
[Jacketed Tubing](#)
[Multijacketed Tubing](#)
[Support Systems](#)

VALVES AND MANIFOLD VALVES

[Ball Valves](#)
[Bellows-Sealed Valves](#)
[Bleed and Purge Valves](#)
[Check Valves](#)
[Diaphragm-Sealed](#)
[Excess Flow](#)
[2-, 3- And 5-Way Manifolds](#)
[Metering Valves](#)
[Needle, Shutoff and Regulating](#)
[Quarter-turn Plug](#)
[Relief Valves](#)
[Sample Stream Select Actuated](#)
[Valve Locks](#)

Swagelok Northwest

(800) 858-0808

info@nwus.swagelok.com

The Swagelok logo is written in a stylized, blue, cursive-like font. The 'S' is large and loops around the 'w'. The 'g' is also stylized, and the 'l' is tall. The 'o' is a simple circle, and the 'k' is short and ends in a small hook. A registered trademark symbol (®) is at the end.