



CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

No. : 2008010604293593

NAME AND ADDRESS OF THE APPLICANT

Swagelok Company
29500 Solon Road Solon, Ohio 44139-3492

NAME AND ADDRESS OF THE MANUFACTURER

Swagelok Company
29500 Solon Road Solon, Ohio 44139-3492

NAME AND ADDRESS OF THE FACTORY

Swagelok Company
29495 F.A. Lennon Drive Solon, Ohio, 44139-3933

NAME, MODEL AND SPECIFICATION

TIG Welding System
SWS-M200 (1~220V, 200A, X=25%)

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB15579.1-2013 GB/T8118-2010中6.15和6.16

This is to certify that the above mentioned products have met the requirements of implementation rules for compulsory certification(REF NO. CNCA-C06-01:2014).

Date of issue: Sep.07, 2015 Date of expiry: Sep. 07, 2020

Validity of this certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

Date of original certification: Sep.12, 2008

This certificate can be verified through CNCA's website: www.cnca.gov.cn



President:

Wang Kejiao

CHINA QUALITY CERTIFICATION CENTRE

Section 9, No.188, Nansihuan Xilu, Beijing 100070 P.R.China

<http://www.cqc.com.cn>



Q 1221920



中国国家强制性产品认证证书

变更结论 Modification Approval

证书编号 Certificate No. : 2008010604293593

申请编号 Application No. : A2020CCC0604-3424770

申请人(委托人) Applicant: Swagelok 公司 / Swagelok Company

证书编号 Certificate No.(变更前 Original): 2008010604293593

变更产品名称: TIG 焊接系统

Name of Product Modified: TIG Welding System

变更情况 Situation of Modification (见下表 See table below) :

序号	项目 Item	变更前 Original	变更后 Present
1	1. 聚氯乙烯绝缘软电缆 电线制造商的变更;	1. 聚氯乙烯绝缘软电缆 型 号: 60227 IEC 53(RVV) 技术参数: 300/500V 3×1.5mm ² 制造商: 费勒 有限公司	1. 聚氯乙烯绝缘软电缆 型 号: 60227 IEC 53(RVV) 技术参数: 300/500V 3×1.5mm ² 制造商: Interpower Corporation
2	2. 电线组件型号及制造 商的变更;	2. 用于冷条件下 I 类设备的 16A 250V 连接器 型号: C19、C19W、C19L 技术参数: 16A 250VAC (配 60227 IEC 53 3×1.5mm ²) 制造商: 费 勒有限公司	2. 电线组件 型号: 081 (黑色) +068 (黑色) 081 (灰色) +068 (灰 色) 081 (黑色) +069 (黑色) 081 (灰色) +069 (灰色) 081 (黑 色) +070 (黑色) 081 (灰色) +070 (灰色) 技术参数: 16A 250V~ (配 60227 IEC 53 3×1.5mm ²) 制 造商: Interpower Corporation
3	3. 单相两极带接地不可 拆线插头型号及制造 商的变更。	3. 单相两极带接地不可拆线插头 型 号: PRC/3/16 技术参数: 16A 250VAC (配 60227 IEC 53 3×1.5mm ²) 制造商: 费勒有限公司	3. 单相两极带接地不可拆线插头 型号: 081 (黑色); 081 (灰色) 技术参数: 16A 250V~ (配 60227 IEC 53 3×1.5mm ²) 制造商: Interpower Corporation

第 1 页 / 共 2 页



主任: 陆楠



中国质量认证中心



中国国家强制性产品认证证书

变更结论 Modification Approval

证书编号 Certificate No. : 2008010604293593

现批准以上变更。

Above Modification is approved. The present will replace the original.

批准日期 (Date) : 2020 年 04 月 09 日

第 2 页 / 共 2 页



主任: 陆楠



中国质量认证中心