


Instrumentation Quick-Connects, QC Series

Warning: System pressure must not exceed 250 psig (17.2 bar) at 70°F (20°C) when coupling and uncoupling this product. When uncoupling single-end shutoff quick-connects, system pressure on stem side will vent to atmosphere.


To Couple:

Align stem with body. Push stem into body until it clicks.



To Uncouple:

Pull body sleeve toward stem.



Good Practices for Operation of Swagelok Quick-Connects

- Use filters ahead of quick-connects.
- Use body and stem protectors or dust caps on uncoupled bodies and stems.
- Align bodies and stems when coupling or uncoupling.
- Couple and uncouple quick-connects at room temperature.
- Couple and uncouple quick-connects during system cleaning operations.
- Support hanging hoses or other equipment to prevent side load.
- Re-lubricate stem seal O-rings periodically.

Caution:

- Do not rotate while coupled.
- Do not insert foreign objects into uncoupled bodies or stems

See the *Swagelok Quick-Connects* catalog for coupled pressure rating information.

MS-CRD-QC1 Swagelok—TM Swagelok Company Printed in U.S.A., CP April 2002. R0