

General-Purpose

IMAGE NOT
AVAILABLE

Part No.


RSN4-02-3-VVV


Part Description

316L Stainless Steel General Purpose Spring Loaded PR Regulator, 0 to 203 psig (14 bar), 1015 psig (70 bar) Inlet, 1/2 in. FNPT, Fluorocarbon FKM Seat Seal

Specifications

General	
Body Material	316L Stainless Steel
Cleaning Process	Standard Cleaning and Packaging (SC-10)
Maximum Inlet Pressure	1015 psig (70 bar)
Outlet Range	0 to 203 psig (14 bar)
Port Type	1/2 in. Female NPT
UNSPSC (AirLiquide)	C2302-99

 The complete catalog contents must be reviewed to ensure that the system designer and user make a safe product selection. When selecting products, the total system design must be considered to ensure safe, trouble-free performance. Function, material compatibility, adequate ratings, proper installation, operation, and maintenance are the responsibilities of the system designer and user.

 Warning: Do not mix/interchange Swagelok products or components not governed by industrial design standards, including Swagelok tube fitting end connections, with those of other manufacturers.