

General-Purpose

IMAGE NOT
AVAILABLE

Part No.

RSN6-02-2-EEE

Part Description

316L Stainless Steel General Purpose Spring Loaded PR Regulator, 0 to 101 psig (7 bar), 1015 psig (70 bar) Inlet, 3/4 in. FNPT, EPDM Seat Seal

Specifications

General	
Body Material	316L Stainless Steel
Cleaning Process	Standard Cleaning and Packaging (SC-10)
Maximum Inlet Pressure	1015 psig (70 bar)
Outlet Range	0 to 101 psig (7 bar)
Port Type	3/4 in. Female NPT

! The complete catalog contents must be reviewed to ensure that the system designer and user make a safe product selection. When selecting products, the total system design must be considered to ensure safe, trouble-free performance. Function, material compatibility, adequate ratings, proper installation, operation, and maintenance are the responsibilities of the system designer and user.

⚠ Warning: Do not mix/interchange Swagelok products or components not governed by industrial design standards, including Swagelok tube fitting end connections, with those of other manufacturers.