

VCO® O-Ring Bodies, Straight



Part No.

SS-4-VCO-6-400

Part Description

316 Stainless Steel VCO O-Ring Face Seal Fitting, Swagelok Tube Fitting Connector, 1/4 in. VCO Fitting x 1/4 in. Tube OD

Specifications

General	
Body Material	316 Stainless Steel
Body Type	Union /Reducing Union
Cleaning Process	Standard Cleaning and Packaging (SC-10)
Connection 1 Size	1/4 in.
Connection 1 Type	VCO® O-Ring Face Seal Fitting
Connection 2 Size	1/4 in.
Connection 2 Type	Swagelok® Tube Fitting
eClass (4.1)	37020713
eClass (5.1.4)	37020590
eClass (6.0)	37020500
eClass (6.1)	37020590
Lubricant	Dow Corning 111
Series	VCO O-Ring Face Seal Fittings
UNSPSC (10.0)	40142610
UNSPSC (11.0501)	40142613
UNSPSC (13.0601)	40183107
UNSPSC (15.1)	40183107
UNSPSC (17.1001)	31160000
UNSPSC (4.03)	31163100
UNSPSC (PGE)	401753AN
UNSPSC (SEQIRUS)	M4170
UNSPSC (SWG01)	31163100

! The complete catalog contents must be reviewed to ensure that the system designer and user make a safe product selection. When selecting products, the total system design must be considered to ensure safe, trouble-free performance. Function, material compatibility, adequate ratings, proper installation, operation, and maintenance are the responsibilities of the system designer and user.

⚠ Warning: Do not mix/interchange Swagelok products or components not governed by industrial design standards, including Swagelok tube fitting end connections, with those of other manufacturers.