



STATUTORY DECLARATION Registration of Fittings

In this space, show facsimile of manufacturer's logo or trademark as it will appear on the fitting.

Swagelok

1, _	David H. Peace	Cwadelok
	Vice President of Engineering	
(con	mpany title, e.g. vice president, plant manager, chief engineer) (must be in a position of authority)	_
of	Swagelok Company	
	(name of manufacturer)	
loca	ated at Headquarters: 29500 Solon Road, Solon, Ohio 44139-3492 (See Attachment A)
	(plant address)	
do so (che	solemnly declare that the fittings listed hereunder, which are subject to the Safety Codes Aceck one)	Act
\boxtimes	comply with the requirements of ASME B31.1 and ASME B31.3 which specified of recognized North American Standard)	ecifies the dimensions,
	materials of construction, pressure/temperature ratings and identification marking of	the fittings, or
	are not covered by the provisions of a recognized North American standard and are the	herefore manufactured to
	comply with as supported by the attached data wh	ich identifies the dimensions,
	materials of construction, pressure/temperature ratings and the basis for such ratings,	
	for identification.	
I furt	ther declare that the manufacture of these fittings is controlled by a quality control progra	am which has been verified by the
		nufacture of these fittings to the
	ed standard. The fittings covered by this declaration, for which I seek registration, are	
	apport of this application, the following information, calculations and/or test data are attack	ched:
150	9001:2008 Certificate, Support Documents, Attachment B, Catalog Information	
DEC	CLARED before me at Solon in the State of	Shii
this _	day of October , 2013	
(print	it) LOREA SARVER (Month) (Year) Lori A. Sarver, Notary Public	
100	State of Ohio, Summit County (Signature o	f Applicant)
(sign)	(A Commissioner for Oaths)	
For C	Office Use Only	
To the	ne best of my knowledge and belief, the application meets the requirements of the Safety Clause 4.2, and is accepted for registration in Category	Codes Act and CSA Standard
	stration Number: 0 C 1 5 7 4 1 2 heleke	Ao
Date 1	Registered:JUN 2 4 2015 (For the Administrate Expiry Date	or/Chief Inspector of Alberta) ee: 100-24-2025

The information you provide is necessary only for the administration of the programs as required by the Alberta Safety Codes Act and Regulations in the Boiler Discipline.

Attachment B. Scope for Swagelok RHPS Series Pressure Regulators (RS, RSH, RD, RDH and BS) (Category C)

Product Scope

This document represents the scope of the Swagelok RHPS Series Pressure Regulators (RS, RSH, RD, RDH and BS) covered by this submission for CRN approval. The Swagelok RHPS Series Pressure Regulators (RS, RSH, RD, RDH and BS) were designed and evaluated in accordance with ASME B31.1 for unlisted components and ASME B31.3 for unlisted components.

Note:

The temperature ratings in the table below in most cases exceed those shown in the product catalog. The pressure retaining components are designed to be safe at the temperature rating as demonstrated in the Code Compliance Summary, but the Swagelok factory must be consulted to determine which seat and seal materials listed in the Typical Product Characteristics section below are suitable for use at this temperature.

Summary Table

0015741.2

#	sure g ent	Main			Maximum R	ated Pressu	re	
Product Series	Main Pressure Bearing Component	Pressure Bearing Material	Port Connections and Sizes	At ambient temperature		At maximum temperature		Design Code of Construction
	Mai	Material		Inlet	Outlet	Inlet	Outlet	
RS6	Body	Stainless Steel (UNS S31603 / ASTM A479)	Female NPT 3/4" Female ISO/BSP 3/4" ASME B16.5 Flange 3/4"	1015 psi @ 100 °F	406 psi @ 100 °F	1015 psi @ 302 °F	406 psi @ 302 °F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted
RS10	Body	Stainless Steel (UNS S31603 / ASTM A479)	Female NPT 1" Female ISO/BSP 1" ASME B16.5 Flange 1"	1015 psi @ 100 °F REGISTRAT	290 psi @ 100 °F	Lucian	TTINGS 5 290 psi 0 302 F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
RS15	Body	Stainless Steel (UNS S31603 / ASTM A479)	Female NPT 1-1/12" Female ISO/BSP 1-1/2" ASME B16.5 Flange 1-1/2"	T1015 psi F @ 100 °F UN 2	290 psi @ 100 °F	1015 psi @ 302 °F	290/psi 0 302/FF 0 DEDOVIC N SURVEYOR	ASME B31.1 Compodents) and ASME B31.3 (Unlisted Components)
RS20	Body	Stainless Steel (UNS S31603 / ASTM A479)	Female NPT 2" Female ISO/BSP 2" ASME B16.5 Flange 2"	1015 psi @ 100 °F	290 psi @ 100 °F	1015 psi @ 302 °F	290 psi @ 302 ^º F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
RSH2	Body	Stainless Steel (UNS S31603 / ASTM A479)	Female NPT 1/4"	6800 psi @ 100 ⁰ F	4500 psi @ 100 ⁰ F	6800 psi @ 302 ⁰ F	4500 psi @ 302 ⁰ F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)

+	sure	Main			Maximum Rated Pressure					
Product Series	Main Pressure Bearing Component	Pressure Bearing Material	Port Connections and Sizes	At ambient temperature		At maximum temperature		Design Code of Construction		
	Mai	Material		Inlet	Outlet	Inlet	Outlet	Construction		
RSH4	Body	Stainless Steel (UNS S31603 / ASTM A479)	Female ISO/BSP 1/2"	5800 psi @ 100 ⁰ F	4900 psi @ 100 °F	5800 psi @ 302 °F	4900 psi @ 302 °F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)		
RSH6	Body	Stainless Steel (UNS S31603 / ASTM A479)	Female NPT 3/4" Female ISO/BSP 3/4" ASME B16.5 Flange 3/4"	5800 psi @ 100 °F	5800 psi @ 100 °F	5800 psi @ 302 ⁰ F	5800 psi @ 302 ⁰ F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)		
RSH8	Body	Stainless Steel (UNS S31603 / ASTM A479)	Female NPT 1" Female ISO/BSP 1" ASME B16.5 Flange 1"	5800 psi @ 100 °F	5700 psi @ 100 °F	5800 psi @ 302 °F	5700 psi @ 302 °F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)		
RSH10	Body	Stainless Steel (UNS S31603 / ASTM A479)	Female NPT 1" Female ISO/BSP 1" ASME B16.5 Flange 1"	5800 psi @ 100 °F	3625 psi @ 100 °F	5800 psi @ 302 °F	3625 psi @ 302 °F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)		
RSH15	Body	Stainless Steel (UNS S31603 / ASTM A479)	Female NPT 1-1/12" Female ISO/BSP 1-1/2"	5800 psi @ 100 °F	3625 psi @ 100 °F	5800 psi @ 302 °F	3625 psi @ 302 ⁰ F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)		
RSH15	Body	Stainless Steel (UNS S31603 / ASTM A479)	ASME B16.5 Flange 1-1/2"	5700 psi @ 100 °F	1 5 7 3625 psi @ 100 °F	5700 psi @ 100 °F	3625 psi @ 302 °F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)		
RSH20	Body	Stainless Steel (UNS S31603 / ASTM A479)	Female NPT 2" Female ISO/BSP 2"	5800 psi @ 100 °F	290 psi @ 100 °F	4400 psi @ 302 °F	290 psi @ 302 °F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)		
RSH20	Body	Stainless Steel (UNS S31603 / ASTM A479)	ASME B16.5 Flange 2"	5500 psi @ 100 °F	290 psi @ 100 °F	5500 psi @ 100 °F	290 psi @ 302 °F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)		

	ure				Maximum R	ated Pressu	re	
Product Series	Main Pressure Bearing Component	Main Pressure Bearing	Port Connections and Sizes	At ambient temperature		At maximum temperature		Design Code of Construction
	Mair	Material		Inlet	Outlet	Inlet	Outlet	- Construction
RD2	Body	Stainless Steel (UNS S31603 / ASTM A479)	Female NPT 1/4"	5800 psi @ 100 °F	4500 psi @ 100 °F	5800 psi @ 302 °F	4500 psi @ 302 °F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
RD6DP	Body	Stainless Steel (UNS S31603 / ASTM A479)	Female NPT 3/4" Female ISO/BSP 3/4" ASME B16.5 Flange 3/4"	1015 psi @ 100 °F	1015 psi @ 100 °F	1015 psi @ 302 °F	1015 psi @ 302 °F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
RD10	Body	Stainless Steel (UNS S31603 / ASTM A479)	Female NPT 1" Female ISO/BSP 1" ASME B16.5 Flange 1"	1015 psi @ 100 °F	1015 psi @ 100 °F	1015 psi @ 302 °F	1015 psi @ 302 °F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
RD15	Body	Stainless Steel (UNS S31603 / ASTM A479)	Female NPT 1-1/12" Female ISO/BSP 1-1/2" ASME B16.5 Flange 1- 1/2"	1015 psi @ 100 °F	1015 psi @ 100 °F	1015 psi @ 302 °F	1015 psi @ 302 °F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
RD20	Body	Stainless Steel (UNS S31603 / ASTM A479)	Female NPT 2" Female ISO/BSP 2" ASME B16.5 Flange 2"	1015 psi @ 100 °F	1015 psi @ 100 °F	1015 psi @ 302 °F	1015 psi @ 302 °F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
RD25	Body	Stainless Steel (UNS S31603 / ASTM A479)	Female NPT 2-1/2" Female ISO/BSP 2-1/2" ASME B16.5 Flange 2- 1/2"	0 C 1015 psi @ 100 °F	1 5 7 1015 psi @ 100 °F	4 1 1015 psi @ 302 °F	2 1015 psi @ 302 °F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
RD30	Body	Stainless Steel (UNS S31603 / ASTM A479)	ASME B16.5 Flange 3"	1015 psi @ 100 °F	1015 psi @ 100 ⁰ F	1015 psi @ 302 ⁰ F	1015 psi @ 302 ⁰ F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
RD40	Body	Stainless Steel (UNS S31603 / ASTM A479)	ASME B16.5 Flange 4*	1015 psi @ 100 ⁰ F	1015 psi @ 100 ⁰ F	1015 psi @ 302 °F	1015 psi @ 302 °F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)

Product Series	ure		Port Connections and Sizes	Maximum Rated Pressure					
	Main Pressure Bearing Component	Main Pressure Bearing		0.000	At ambient temperature		ximum erature	Design Code of Construction	
	Mair	Material		Inlet	Outlet	Inlet	Outlet	Construction	
RDH6	Body	Stainless Steel (UNS S31603 / ASTM A479)	Female NPT 3/4" Female ISO/BSP 3/4" ASME B16.5 Flange 3/4"	5800 psi @ 100 °F	5800 psi @ 100 °F	5800 psi @ 302 °F	5800 psi @ 302 °F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)	
RDH6DP	Body	Stainless Steel (UNS S31603 / ASTM A479)	Female NPT 3/4" Female ISO/BSP 3/4" ASME B16.5 Flange 3/4"	5800 psi @ 100 °F	3335 psi @ 100 °F	5800 psi @ 302 °F	3335 psi @ 302 °F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)	
RDH8	Body	Stainless Steel (UNS S31603 / ASTM A479)	Female NPT 1" Female ISO/BSP 1" ASME B16.5 Flange 1"	5800 psi @ 100 °F	5700 psi @ 100 °F	5800 psi @ 302 °F	5700 psi @ 302 °F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)	
RDH10	Body	Stainless Steel (UNS S31603 / ASTM A479)	Female NPT 1" Female ISO/BSP 1" ASME B16.5 Flange 1"	5800 psi @ 100 °F	3625 psi @ 100 °F	5800 psi @ 302 °F	3625 psi @ 302 °F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)	
RDH15	Body	Stainless Steel (UNS S31603 / ASTM A479)	Female NPT 1-1/12" Female ISO/BSP 1-1/2"	5800 psi @ 100 °F	3400 psi @ 100 °F	5800 psi @ 302 ⁰ F	3400 psi @ 302 ⁰ F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)	
RDH15	Body	Stainless Steel (UNS S31603 / ASTM A479)	ASME B16.5 Flange 1- 1/2"	5700 psi @ 100 °F	3625 psi @ 100 °F	5700 psi @ 100 °F	3625 psi @ 302 °F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)	
RDH20	Body	Stainless Steel (UNS S31603 / ASTM A479)	Female NPT 2" Female ISO/BSP 2"	5800 psi @ 100 ⁰ F	2900 psi @ 100 ⁰ F	5800 psi @ 100 ⁰ F	2900 psi @ 302 ⁰ F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)	
RDH20	Body	Stainless Steel (UNS S31603 / ASTM A479)	ASME B16.5 Flange 2"	5500 psi @ 100 °F	2900 psi @ 100 °F	5500 psi @ 100 ⁰ F	2900 psi @ 302 °F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)	

The products shown in the table below are a part of the above product families and were previously registered under CRN registration number 0C15099.5C

	ure at	Main Pressure Bearing						
Product Series	Main Pressure Bearing Component		Port Connections and Sizes	At ambient temperature		At maximum temperature		Design Code of Construction
a . **	Mat Go	Material		Inlet	Outlet	Inlet	Outlet	Constitution
RDH25	Body	Stainless Steel (UNS S31603 / ASTM A479)	ASME B16.5 Flange 2-1/2"	4060 psi @ 100 °F	2900 psi @ 100 ⁰ F	4060 psi @ 100 °F	2900 psi @ 302 °F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
RDH30	Body	Stainless Steel (UNS S31603 / ASTM A479)	ASME B16.5 Flange 3"	4060 psi @ 100 °F	1900 psi @ 100 °F	4060 psi @ 100 °F	1900 psi @ 302 °F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
RDH40	Body	Stainless Steel (UNS S31603 / ASTM A479)	ASME B16.5 Flange 4"	4040 psi @ 100 °F	1900 psi @ 100 °F	4040 psi @ 100 °F	1900 psi @ 302 °F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
BS10	Body	Stainless Steel (UNS S31603 / ASTM A479)	Female NPT 1" Female ISO/BSP 1" ASME B16.5 Flange 1"	1015 psi @ 100 °F	290 psi @ 100 °F	1015 psi @ 302 °F	290 psi @ 302 ⁰ F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
RS2	Body	Stainless Steel (UNS S31603 / ASTM A479)	Female NPT 1/4"	5800 psi @ 100 °F	4500 psi @ 100 °F	5800 psi @ 302 °F	4500 psi @ 302 °F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
RS4	Body	Stainless Steel (UNS S31603 / ASTM A479)	Female NPT 1/2" Female ISO/BSP 1/2" ASME B16.5 Flange 1/2"	1015 psi @ 100 °F	406 psi @ 100 ^p F	1015 psi @ 302 [©] F	406 psi @ 302 ⁰ F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
RS8	Body	Stainless Steel (UNS S31603 / ASTM A479)	Female NPT 1" Female tSO/BSP 1" ASME B16.5 Flange 1"	1015 psi @ 100 ⁰ F	406 psi @ 100 ⁰ F	1015 psi @ 302 °F	406 psi @ 302 ⁰ F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
RD6	Body	Stainless Steel (UNS S31603 / ASTM A479)	Female NPT 3/4" Female ISO/BSP 3/4" ASME B16.5 Flange 3/4"	1015 psi @ 100 [®] F	1015 psi @ 100 ^⁰ F	1015 psl @ 302 °F	1015 psi @ 302 ⁰ F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)

	ure			,	Maximum Rated Pressure				
Product Series	Main Pressure Bearing Component	Main Pressure Bearing	re Port Connections and	At ambient temperature		At maximum temperature		Design Code of Construction	
	Main	Material		Inlet	Outlet	Inlet	Outlet		
RD8	Body	Stainless Steel (UNS S31603 / ASTM A479)	Female NPT 1" Female ISO/BSP 1" ASME B16.5 Flange 1"	1015 psi @ 100 °F	1015 psi @ 100 °F	1015 psi @ 302 °F	1015 psi @ 302 °F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)	
BS4	Body	Stainless Steel (UNS S31603 / ASTM A479)	Female NPT 1/2" Female ISO/BSP 1/2" ASME B16.5 Flange 1/2"	1015 psi @ 100 °F	406 psi @ 100 °F	1015 psi @ 302 °F	406 psi @ 302 ⁰ F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)	
BS8	Body	Stainless Steel (UNS S31603 / ASTM A479)	Female NPT 1" Female ISO/BSP 1" ASME B16.5 Flange 1"	1015 psi @ 100 °F	203psi @ 100 °F	1015 psi @ 302 ⁰ F	203 psi @ 302 ⁰ F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)	

Product Illustration



RS(H)2



RS(H)4, 6, 8



RS(H)10, 15, 20

0015741.2



RD2



RD(H)6, 8



RD(H)6DP



Typical Product Characteristics:

Some of the product options listed below affect the pressure-temperature ratings shown in the Summary Table, but in all cases the ratings are less than those shown in the Summary Table. All of the following options are within the scope of this registration:

- Body Seal Materials: FKM, Nitrile, EPDM, FFKM, HNBR
- Diaphragm Materials: FKM, Nitrile, EPDM, FFKM, HNBR, PTFE, 316SS
- Piston Seal Materials: FKM, Nitrile, EPDM, FFKM, HNBR
- Seat Materials: FKM, Nitrile, EPDM, FFKM, HNBR, PCTFE, PEEK, Polyurethane

Some of the product options listed below do not affect the pressure-temperature ratings shown in the Summary Table. All of the following options are within the scope of this registration:

Handle Type
Cleaning options
Panel Mounting
Feedback Loops
Handle color
Anti-tamper
Laser Etching
ASTM G93 cleaning
NACE Components
External Feedback
External Feedback to the Pilot

OC15741.2

Quality System

The Swagelok Company quality system complies with the requirements of BS EN ISO 9001:2008. The Swagelok Company maintains British Standards Institution Certificate of Registration Number FM 01729, which applies to all locations listed on the Certificate. The Swagelok RHPS Series Pressure Regulators (RS, RSH, RD, RDH and BS) are manufactured and assembled at Swagelok Company locations in Solon, Ohio and Tromode, Isle of Man, British Isles.

References

The product catalog does not represent the full scope of registration, but rather details some of the most common options.

RHPS Series Pressure Regulator Catalog MS-02-430, R1