



11/6/2020

TSSA
345 Carlingview Drive
Toronto, Ontario M9W 6N9
CA

Dear Cecylia Garbacz

Re: Reciprocal CRN Registration in Manitoba

Your application indicates that a CRN has been received in another Canadian Jurisdiction, and therefore your CRN has been registered in Manitoba as follows:

File Number: 74-R1055
CRN: 0D22748.54
Scope: Crimped Swagelok X Series PTFE-Attachment A and B
Manufacturer: SWAGELOK
Expiry Date: 16/Oct/30

Please find attached invoice for registration.

As indicated by the Regulatory Reconciliation and Cooperation Table and the Reconciliation Agreement for the Canadian Registration Number (CRN) for Pressure Equipment, a CRN issued in any Canadian Jurisdiction will be accepted for use in Manitoba.

In accordance with Steam and Pressure Plants Regulation and CSA B51, it is the manufacturer's responsibility to file a Manufacturers Data Report, including partial data reports, with our office, prior to shipping pressure equipment to Manitoba.

Please contact me directly via email at Cheryl.Lashek@gov.mb.ca for any questions or concerns.

Cheryl Lashek, P.Eng
Director, ITSM
Inspection and Technical Services
Office of the Fire Commissioner
508 - 401 York Avenue, Winnipeg Manitoba R3C 0P8
T (204) 945-3507 | F (204) 948-2309



Technical Standards and Safety Authority
 345 Carlingview Drive
 Toronto, Ontario M9W 6N9
 www.tssa.org

Show facsimile of manufacturer's logo or trademark, as it will appear on the fitting, in the space below

Swagelok

STATUTORY DECLARATION Registration of Fittings

I, Joel Feldman, Vice President of Engineering
(Name and Position, e.g. President, Plant Manager, Chief Engineer)

of Swagelok Company
(Name of Manufacturer)

Located at 29500 Solon Road, Solon, Ohio 44139 USA (440) 248-4600 (440) 349-5970
(Plant Address) (Telephone No.) (Fax No.)

- do solemnly declare that the fittings listed hereunder, which are subject to the *Technical Standards and Safety Act*, Boilers and Pressure Vessels Regulation, comply with all of the requirements of Association for Rubber Products Manufacturers (ARPM) Hose Handbook
(Title of recognized North American Standard)
 which specifies the dimensions, materials of construction, pressure/temperature ratings, identification marking the fittings and service;
- or are not covered by the provisions of a recognized North American standard and are therefore manufactured to comply with as supported by the attached data which identifies the dimensions, material of construction, pressure/temperature ratings and the basis for such ratings, the marking of the fitting for identification and service.

I further declare that the manufacture of these fittings is controlled by a quality system meeting the requirements of ISO 9001:2015 which has been verified by the following authority, BSI.

The items covered by this declaration, for which I seek registration, are category D. Hose type fittings. In support of this application, the following information and/or test data are attached as follows:
ISO 9001:2015 Certificate, Attachment A, Attachment B, Catalog Information and other Support Documents
(drawings, calculations, test reports, etc.)

Declared before me at _____ in the _____ of _____
 the _____ day of _____ AD 20_____.

Commissioner for Oaths:

Unable to get a notary signature or seal due to COVID-19 situation - September 17, 2020
(Printed name) (Signature)

Joel C. Feldman
(Signature of Declarer)

FOR OFFICE USE ONLY

To the best of my knowledge and belief, the application meets the requirements of the *Technical Standards and Safety Act*, Boilers and Pressure Vessels Regulation, and CSA Standard B51 and is accepted for registration in Category D.

CRN: 0D22748.5
 Registered by: [Signature]
 Dated: OCTOBER 16, 2020



This Document has been digitally signed. The stamp size has been optimized for 11 x 17 documents

Technical Standards and Safety Authority	Boilers and Pressure Vessels Safety Program
REGISTERED	
C.R.N.: 0D22748.5	
Signed: <u>[Signature]</u>	
Date: October 16, 2020.	

NOTE: This registration expires on: OCTOBER 16, 2030 For scope of registration see the stamped attachment A and B

**Information provided in this application is releasable under the Freedom of Information and Privacy Protection Act and may be disclosed upon request.*



Attachment B: Scope of Registration for Crimped Swagelok X Series PTFE Hose Assemblies (Category D)

This document represents the scope of the Swagelok Coreflex XC and XT hose (X Series) and crimped assemblies covered by this submission for CRN approval. These products have been evaluated in accordance with the Association for Rubber Products Manufacturers (ARPM) Hose Handbook.

Summary Table


X Series Hose Size	Maximum Pressure (psig)			Pressure Retaining Material	End Connections and Sizes	Design Code of Construction
	At Minimum Temp. (-65°F)	Room temperature (0°-100°F)	At Maximum Temp. (450°F)			
1/4"	3500	3500	3075	Core Smooth bore PTFE (XT Series) OR Smooth bore carbon black filled PTFE (XC Series) Braid Fiber braid reinforcement AND 304 SS Braid Reinforcement End Connections 316 SS Crimp on Collar 300 series SS	Swagelok Tube Fitting [SL, SM] 1/8" – 2" (3-50mm)	Association for Rubber Products Manufacturers (ARPM) Hose Handbook
3/8"	3000	3000	1675		Male & Female NPT Tapered Pipe Fitting [PM, PF] 1/8" – 2" Male & Female ISO/BSP Tapered (ISO 7) Pipe Threads [MT, FT] 1/4" – 1"	
1/2"	1800	1800	1665		Male 37° JIC & Female 37° JIC with female swivel nut [AN, AS] 1/4" – 2"	
3/4"	1250	1250	900		Tube Butt Welds [TB] 1/2" – 1" Female VCO O-ring Face seal Fitting [VF] 1/8" – 2" Female VCR Metal Gasket Face seal Fitting [RF] 1/8" – 2"	
1"	1000	1000	895		Male ISO/BSP Parallel Threads W/ 60° Male cone (ISO 228) [MS] 1/4" – 1" Female ISO/BSP Parallel Threads (ISO 228) [FS] 1/4" – 1"	

Product Description

XT series is standard Swagelok virgin PTFE-lined hose with a fiber braid reinforcement and 304 stainless steel reinforcement with a silicone cover. The XC series consist of the same construction but has Swagelok carbon black filled virgin PTFE liner. The 1 inch nominal ID hose for both XT and XC series is constructed with two stainless steel braids and no fiber braid. All X Series hoses undergo production testing in accordance with ASTM D380 "Test Methods for Rubber Hose" (version current to hose production date).

Configurations

All end connection inserts are crimped onto the hose using crimp collars.



Product Options:

Additional options that do not affect pressure and/or temperature ratings may be made available and are within the scope of this approval. Examples of these would include, but not limited to, the following:

Cover Options

- Armor guard - Interlocking, flexible 302 stainless steel.
- Fire jacket - Woven fiberglass coated with specially compounded aerospace-grade silicone rubber
- Spiral guard - Helical HDPE plastic

Tag and Marking Options

- Mat tag - Polyester tag with customer-specified text
- Lanyard tag - Stainless steel tag with customer-specified text

End Connection Seals or Sealants Options

- VCO – O-rings
- Pipe Thread ends – thread sealant

Quality System

The Swagelok Company quality system complies with the requirements of ISO 9001:2015. The Swagelok Company maintains BSI Certificate of Registration Number FM 01729, which applies to all locations listed on the Certificate.

References

The product catalog does not represent the full scope of the registration but rather details some of the most common options. Hose Assemblies, Bulk Hose, and End Connections Product Catalog MS-01-180.

Attachment A. Swagelok Manufacturing Locations

This document lists the Swagelok locations where end item or component level manufacturing activities take place.

Swagelok Company 29500 Solon Road Solon, Ohio 44139 USA	Swagelok Company (Falon 1) 348 Bishop Road Highland Heights, Ohio 44143 USA
Swagelok Company (Highland) 318 Bishop Road Highland Heights, Ohio 44143 USA	Swagelok Company (Falon 2) 358 Bishop Road Highland Heights, Ohio 44143 USA
Swagelok Company (OFC) 29495 F.A. Lennon Drive Solon, Ohio 44139 USA	Swagelok Company (HPF) 6050 Cochran Road Solon, Ohio 44139 USA
Swagelok Company (Atlantic) 26651 Curtiss Wright Parkway Willoughby Hills, Ohio 44092 USA	Swagelok Company (Snow Metal) 6060 Cochran Road Solon, Ohio 44139 USA
Swagelok Company (Micro) 26653 Curtiss Wright Parkway Willoughby Hills, Ohio 44092 USA	Swagelok Company (Alfred) 29500 Ambina Drive Solon, Ohio 44139
Swagelok Hose Services Company (SHSC) 29900 Solon Industrial Parkway Solon, Ohio 44139	Swagelok Company (Strongsville) 15400 Foltz Road Strongsville, Ohio 44119
Swagelok (China) Fluid System Technologies Ltd. Changshu Export Process Zone Changshu Economic Development Zone Changshu, Jiangshu 215513 China	Swagelok Limited Ballafletcher Road Tromode IM4 4RA Isle of Man