UNIFORM STATUTORY DECLARATION FORM FOR THE REGISTRATION OF FITTING DESIGNS

NEW BRUNSWICK NUNAVUT

NOVA SCOTIA YUKON PRINCE EDWARD ISLAND NORTHWEST TERRITORIES

NEWFOUNDLAND AND LABRADOR

MANUFACTURERS NAME: Swagelok Company	
MANUFACTURERS ADDRESS: 29500 Solon Road, Solon, Ohio 44139 USA	
PLANT LOCATIONS: Headquarters: 29500 Solon Road, Solon, Ohlo 44139 USA (See Att	achment A)
CATEGORY OF FITTINGS TO BE REGISTERED. CIRCLE ONE CATEGORY ONLY	TITLE OF THE STANDARD OF CONSTRUCTION
A Pipe fittings, including couplings, tees, elbows, Ys, plugs, unions, pipe caps, or reducers Planges: all flanges (C) Valves: all fine valves (E) Expansion joints, flexible connections, and hose assemblies: all types (E) Strainers, fitters, separators, and steam traps (E) Measuring devices, including pressure gauges, level gauges, sight glasses, levels, or pressure transmitters (E) Certified capacity-rated pressure relief devices acceptable as primary over pressure protection on boliers, pressure vessels, piping and furable plugs (E) Pressure retaining components that do not fall into one of the above categories (E) Nuclear components: Class 1 (Class 2 (Class 3 (I), (Meeting AECB or ASME requirements)	ASME B31.1 for unlisted components, ASME B31.3 for unlisted components
SHOW MANUFACTURERS NAME, TRADEMARK, OR LOGO AS IT WILL APPEAR ON THE PRODUCT	TYPE OF CONTINUCTION
Swagelok	FORGED CI WELDED CI WROUGHT 30 CAST CI OTHER CI OFFICE CITHER
LIST OF SUPPORTING DOCUMENTATION AND IDENTIFICATION OF THE ACTUAL ITEMS TO BE REC	USTEDER.
responsibility for the quality of the end product do solemnly declare that the information contained my knowledge represents the product for which registration is sought. The dimensions, malerials emperature ratings, and identification markings are in accordance with the herein named standar nanufacture of those fittings is regulated by a Quality Control Program which extends to each place in part and has been verified by BSI as being suitable for the eclaration conscientiously believing it to be true, and knowing that it is of the same force and effecting that it is of the control Program which extends to each place in part and has been verified by BSI as being suitable for the eclaration conscientiously believing it to be true, and knowing that it is of the same force and effecting that the product of the same force and effecting that the product of the same force and effecting that the product of the same force and effecting that the product of the same force and effecting the product of the same force and effecting that the product of the same force and effecting the product of the same force and effecting the product of the same force and effecting that the product of the same force and effecting the product of the	of construction, pressure ds. I further declare that the nt where fabrication occurs in whole
eclared before me at Unable to get a notary signature THIS	SPACE FOR THE
or court care to co i and and	CIAL SEAL
ommissioner of Oaths r Notary Public: (sign) <u>situation - August 27, 2020</u> (Affix Official seal to the right)	
This registration must be revalidated after ten (10) years from the date of	as continued
CRN: 0C22706.5	16300
FID#: 1214	
ino-Trik 410 (B31.1, B31.3), 445, 645 and 945 (B31.3 Northwell)	The state of the s
2. Each category shall be supported with two Statutory Declaration IINDER THE	STERED AUTHORITY OF
responsibility for the quality of the end product. 4. Quality control programs shall be resubmitted for validation at a maximum interval of five (5) years. CRN expires Sept.28th, 2030 - DG SIGNED	AND PRESSURE SEL ACT. 22706.5
responsibility for the quality of the end product. 4. Quality control programs shall be resubmitted for validation C.R.N. OC.	AND PRESSURE SELACT. 22706-5



Canadian Registration Number Submittal
Category C: Swagelok Sno-Trik High Pressure Needle Valves

Attachment B. Scope of CRN Registration for Swagelok Sno-Trik 410, 445, 645 and 945 Series High-Pressure Needle Valves (Category C)

This document represents the scope of the Sno-Trik 410, 445, 645 and 945 Series High-Pressure Needle Valves covered by this submission for CRN approval. The 410 Series Valves were designed and evaluated in accordance with ASME B31.1 for unlisted components and ASME B31.3 for unlisted components, while the 445, 645 and 945 High-Pressure Needle Valves were designed and evaluated in accordance with ASME B31.3 Chapter IX for unlisted components.

Summary Table

Product Series	Main Pressure Bearing Component	Main Pressure			um Rated ire (psig)	Design Code
		Bearing Material (Standard)	Port Connections and Sizes	At -65 to 100°F	At maximum temperature	of Construction
410	Body	316 SS (ASTM A479)	Female NPT 1/4"	15,000	6085 @ 850°F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
445	Body	316 SS (ASTM A479)	Swagelok straight thread high-pressure Female 9/16"	45,000	33,400 @ 450°F	
			Medium Pressure 1/4"	20,000	18,600 @ 450°F	
645	Body	316 SS (ASTM A479)	Swagelok straight thread high-pressure Female 3/4	45,000	33,400 @ 450°F	ASME B31.3 Chapter IX
			Medium Pressure 3/8"	20,000	18,600 @ 450°F	(Unlisted Components)
945	Body	316 SS (ASTM A479)	Swagelok straight thread high-pressure Female 1-1/8	45,000	33,400 @ 450°F	
			Medium Pressure 1/2"	20,000	18,600 @ 450°F	

THIS IS PART OF CRN

Date: August 13, 2020

Page 1 of 2

0C22706.5

Technical Standards and Safety Authority
Boilers and Pressure Vessels Safety
Program



Canadian Registration Number Submittal
Category C: Swagelok Sno-Trik High Pressure Needle Valves

Product Illustration



THIS IS PART OF CRN 0C22706.5

Date: August 13, 2020

Page 2 of 2

Technical Standards and Safety Authority

Boilers and Pressure Vessels Safety

Program

Typical Product Characteristics:

Some of the product options listed below affect the pressure-temperature ratings shown in the Summary Table, but in all cases the ratings are equal to or less than those shown in the Summary Table. All of the following options are within the scope of this registration:

Stem Material

440C SS S17400 SS

Stem Seal Material

Glass-Filled PTFE Grafoil

Quality System

The Swagelok Company quality system complies with the requirements of ISO 9001:2015. The Swagelok Company maintains BSI Certificate of Registration Number FM 01729, which applies to all locations listed on the Certificate.

References

The product catalog does not represent the full scope of registration, but rather details some of the most common options.

 Medium and High-Pressure Fittings, Tubing, Valves and Accessories Catalog MS-02-472, Rev M

THIS IS PART OF CRN 0C22706.5

Technical Standards and Safety Authority
Boilers and Pressure Vessels Safety
Program

Attachment A. Swagelok Manufacturing Locations

This document lists the Swagelok locations where end item or component level manufacturing activities take place.

Swagelok Company	Swagelok Company (Falon 1)
29500 Solon Road	348 Bishop Road
Solon, Ohio 44139	Highland Heights, Ohio 44143
USA	USA
Swagelok Company (Highland)	Swagelok Company (Falon 2)
318 Bishop Road	358 Bishop Road
Highland Heights, Ohio 44143	Highland Heights, Ohio 44143
USA	USA
Swagelok Company (OFC)	Swagelok Company (HPF)
29495 F.A. Lennon Drive	6050 Cochran Road
Solon, Ohio 44139	Solon, Ohio 44139
USA	USA
Swagelok Company (Atlantic)	Swagelok Company (Snow Metal)
26651 Curtiss Wright Parkway	6060 Cochran Road
Willoughby Hills, Ohio 44092	Solon, Ohio 44139
USA	USA
Swagelok Company (Micro) 26653 Curtiss Wright Parkway Willoughby Hills, Ohio 44092 USA	Swagelok Company (Alfred) 29500 Ambina Drive Solon, Ohio 44139
Swagelok Hose Services Company (SHSC)	Swagelok Company (Strongsville)
29900 Solon Industrial Parkway	15400 Foltz Road
Solon, Ohio 44139	Strongsville, Ohio 44119
Swagelok (China) Fluid System Technologies Ltd. Changshu Export Process Zone Changshu Economic Development Zone Changshu, Jiangshu 215513 China	Swagelok Limited Ballafletcher Road Tromode IM4 4RA Isle of Man