Diaphragm Valves



LD Series


- Working pressures up to 300 psig (20.6 bar)
- Shutoff, bulk-gas distribution, and isolation service
- Cast, forged, and bar stock stainless steel body material
- 1/4 to 1 in. and 12 to 25 mm end connections



Features

- No springs or threads in wetted areas enable cleaner operation.
- Contoured flow passages allow high flow.
- Tied diaphragm design provides positive stem retraction.

Replaceable Diaphragm/Stem Subassembly



Welded Diaphragm Construction

- Diaphragms are welded to stem to prevent leakage.
- Three diaphragms offer optimum combination of strength, flexibility, and cycle life.
- Design provides all-metal fluid containment.

Unique Stem Tip Design

- PCTFE stem tip insert promotes leak-tight shutoff.
- Compensating stem tip helps prevent damage from overtightening.

Body Construction

Cast (1/2 and 1 in. Sizes)


- Machined wetted surfaces in body are finished to an average of 20 μin. (0.51 μm) R_a.
- Optional electropolished body exteriors (ELD series) are available.
- Optional tube extension interiors electropolished to an average of 10 μin. (0.25 μm) R_a are available.

Forged (1/2 in. Size)


- Design results in compact size, lower internal volume.
- Wetted surfaces are electropolished to an average of 5 μin. (0.13 μm) R_a.

Bar Stock (1/2 and 1 in. Sizes)

- Valve and tubular shapes are combined into one integrated, compact component.
- Block bodies permit compact layout of bulk gas systems.
- Wetted surfaces are electropolished to an average of 5 μ in. (0.13 μ m) R_a .



Materials of Construction



Cast-body 1/2 in. size shown.

Testing

SC-11 Process

Every LD series diaphragm valve processed in accordance with Swagelok® *Special Cleaning and Packaging (SC-11)* catalog, $\underline{\text{MS-}06-63}$ is helium leak tested to a maximum leak rate of 4×10^{-9} std cm³/s.

SC-01 Process

Every LD series diaphragm valve processed in accordance with Swagelok *Ultrahigh-Purity Process Specification (SC-01)* catalog, MS-06-61 is helium leak tested to a maximum leak rate of 1 \times 10⁻⁹ std cm³/s.

			Valve Body			
		Cast	Forged	Bar Stock		
	Component	Material Grade/ASTM Specification				
1	Handle	Polyest	er with 316 S	S insert		
	Handle set screw		Alloy steel			
2	Bonnet nut	Silver-	plated 316 SS	S/A479		
3	Thrust washer		Bronze			
	Actuator bearing (1 in. size)	High-carbon chrome steel	_	High-carbon chrome steel		
4	Actuator		416 SS/A582			
5	Spring washer		Alloy steel			
6	Bonnet		316 SS/A479			
	Thrust washer (1 in. size)	Bronze				
	Bonnet bearing (1 in. size)					
7	Upper stem		316 SS/A479			
8	Clamp ring		Brass/B16			
9	Diaphragm/stem subassembly	See individ	dual compone	ents below		
	9a Diaphragms (3)		316L SS/A240)		
	9b Stem		316L SS/A479	9		
	9c Compression ring		Virgin PTFE			
	9d Inner ring		316L SS/A479	9		
	9e Stem tip insert		PCTFE			
	9f Outer ring	:	316L SS/A479	9		
10	Gasket	PTFE-c	oated 316L S	S/A240		
11	Body	CF3M/ A351	316L SS/ A182	316L SS/ A479		
Swagelok tube fitting and pipe end connections		316 SS/ A479 – –				
VCF	[®] fitting end connections	316 SS/A479				
Tube	e extensions		316 SS/A269			
	Lubricant		n disulfide-bas roleum lubric			

Wetted components listed in italics.

Cleaning and Packaging

Cast-Body Valves

All LD series cast-body diaphragm valves are cleaned and packaged in accordance with Swagelok *Special Cleaning and Packaging (SC-11)* catalog, <u>MS-06-63</u> to ensure compliance with product cleanliness requirements stated in ASTM G93 Level C. Cleaning and packaging in accordance with Swagelok *Ultrahigh-Purity Process Specification (SC-01)* catalog, <u>MS-06-61</u> is available as an option for ELD series cast-body valves.

Forged-Body and Bar Stock Valves

All LD series forged-body and bar stock diaphragm valves are manufactured, cleaned, and packaged in accordance with Swagelok *Ultrahigh-Purity Process Specification (SC-01)* catalog, MS-06-61. Cleaning in accordance with Swagelok *Special Cleaning and Packaging (SC-11)* catalog, MS-06-63 to ensure compliance with product cleanliness requirements stated in ASTM G93 Level C is available as an option.



Pressure-Temperature Ratings

Valve Body	Cast	Forged and Bar Stock			
Temperature, °F (°C)	Working Pressure, psig (bar)				
-20 (-28) to 100 (37)	300 (20.6)	300 (20.6)			
200 (93)	265 (18.2)	255 (17.5)			
300 (148)	240 (16.5)	230 (15.8)			

Process Specifications

Series	Wetted Surface Roughness Average (<i>R_a</i>) μin. (μm) avg	Swagelok Process Specification
LD cast body	20 (0.51)—body machined surfaces	SC-11
ELD cast body	20 (0.51)—body machined surfaces; 10 (0.25)—tube extensions	SC-11
Forged body	5 (0.13)—P process	SC-01
Bar stock body	5 (0.13)—P process	SC-01

Flow Data at 70°F (20°C)

1/2 in. Size

0.500 in. (12.7 mm) orifice, 2.8 C_{ν}


Pressure Drop to Atmosphere (Δp) psi (bar)	Air Flow std ft ³ /min (std L/min)	Water Flow U.S. gal/min (L/min)
10 (0.68)	31 (870)	9 (34)
50 (3.4)	84 (2300)	20 (75)
100 (6.8)	148 (4100)	28 (100)

1 in. Size


1.125 in. (28.6 mm) orifice, 13 C_{ν}

Pressure Drop to Atmosphere (Δp) psi (bar)	Air Flow std ft³/min (std L/min)	Water Flow U.S. gal/min (L/min)
10 (0.68)	140 (3900)	41 (150)
50 (3.4)	390 (11 000)	92 (340)
100 (6.8)	690 (19 500)	130 (490)

Flow Coefficient at Turns Open



Flow Coefficient at Turns Open



Ordering Information and Dimensions


Dimensions, in inches (millimeters), are for reference only and are subject to change.

Cast-Body Valves

Select an ordering number. To order optional cleaning and packaging in accordance with Ultrahigh-Purity Process Specification (SC-01) catalog, MS-06-61, for ELD series valves, add -DU to the ordering number.

Example: 6L-ELD8-BBXX-DU


LD8 Series



End Cor	nnections	Ordering	Α	
Туре	Size	Number	in. (mm)	
	1/2 in.	6L-LD8-BBXX		
Swagelok	1/2 111.	6L-ELD8-BBXX	5.30 (135)	
tube fitting	10	6L-LD8-DDXX		
	12 mm	6L-ELD8-DDXX		
Male VCR fitting	1/2 in.	6L-ELD8-CCXX	4.58 (116)	
Female NPT	1/2 in.	6L-LD8-EEXX	F C1 (4.40)	
Female ISO ^①	1/2 in.	6L-LD8-FFXX	5.61 (142)	
	$1/2 \times 0.049$ in.	6L-ELD8-11XX	8.82 (224)	
Tube extension,	3/4 imes 0.065 in.	6L-ELD8-22XX	8.79 (223)	
3 in. (76.2 mm) long	12 × 1 mm	6L-ELD8-33XX	8.82 (224)	
	18 × 1.5 mm	6L-ELD8-55XX	8.79 (223)	

Dimensions shown with Swagelok tube fitting nuts finger-tight.

LD16 Series



End Cor	nnections	Ordering	Α			
Туре	Size	Number	in. (mm)			
	3/4 in.	6L-LD16-AAXX	0.00 (040)			
l	3/4 III.	6L-ELD16-AAXX	8.28 (210)			
Swagelok tube fitting	1 in.	6L-LD16-BBXX	9.46 (015)			
l tabo inting		6L-ELD16-BBXX	8.46 (215)			
	25 mm	6L-LD16-EEXX	8.63 (219)			
Tube extension.	4 × 0 005 :-	6L-LD16-55XX				
3 in. (76.2 mm)	1×0.065 in.	6L-ELD16-11XX	10.9 (277)			
long	23 × 1.5 mm	6L-ELD16-33XX				

Cast-Body Valves with Purge Ports

Replace XX with BB for 1/4 in. integral male VCR fitting inlet and outlet purge ports.

Example: 6L-ELD8-BBB

Replace XX with BX for 1/4 in. integral male VCR fiting inlet purge port and no

outlet purge port.

Example: 6L-ELD8-BBBX

Replace XX with XB for no inlet purge port and 1/4 in. integral male VCR fiting


outlet purge port.

Example: 6L-ELD8-BBXB


Purge Ports

Purge Port End	Dimensions, in. (mm)					
Connections	Α	В				
LD8 Series						
None		0.88 (22.4)				
1/4 in. male VCR fittings	1.83 (46.5)	1.69 (42.9)				
LD1	6 Series					
None		1.35 (34.3)				
1/4 in. male VCR fittings	3.40 (86.4)	2.16 (54.9)				





Integral male VCR fittings





① See specifications ISO 7/1, BS EN 10226-1, DIN-2999, JIS B0203.


Ordering Information and Dimensions

Dimensions, in inches (millimeters), are for reference only and are subject to change.

Forged-Body Valves

Select an ordering number. To order optional cleaning in accordance with Swagelok *Special Cleaning and Packaging (SC-11)* catalog, MS-06-63, to ensure compliance with product cleanliness requirements stated in ASTM G93 Level C, remove **-P** from the ordering number.

Example: 6L-ELD8-VVX



End Cor	nections	Ordering	A in. (mm)	
Туре	Size	Number		
Tube	3/8 imes 0.035 in.	6L-ELD8-VVX-P	0 00 (70 0)	
		6L-ELD8-WWX-P	2.88 (73.2)	
Tube extension.	3/8 imes 0.035 in.	6L-ELD8-33X-P	0.06 (005)	
3 in. (76.2 mm)	1/2 imes 0.049 in.	6L-ELD8-11X-P	8.86 (225)	
long	3/4 imes 0.065 in.	6L-ELD8-22X-P	10.0 (254)	
Rotatable male VCR fitting	1/2 in.	6L-ELD8-66X-P	5.43 (138)	
Female VCR fitting	1/2 in.	6L-ELD8-77X-P	4.09 (104)	

Forged-Body Valves with Purge Ports

Replace **X** with **M** for 1/4 in. rotatable male VCR fitting inlet and outlet purge ports.

Example: 6L-ELD8-11**M**-P Replace **X** with **MX** for 1/4 in. integral male VCR fiting inlet purge port and no outlet purge port.

Example: 6L-ELD8-11**MX**-P Replace **X** with **XM** for no inlet purge port and 1/4 in. integral male VCR fiting outlet purge port.

Example: 6L-ELD8-11XM-P

Rotatable male VCR fitting 0.76 (19.3) 1.35 Protective cap (62.2) 1.98 (50.3)

Bar Stock-Body Distribution Valves


- Valves eliminate need for tee and cross fittings.
- Branches contain shutoff valves.
- Main line and branches are in same plane.
- Purge ports are 1/4 in. rotatable male VCR fittings.

Select an ordering number. To order optional cleaning in accordance with Swagelok *Special Cleaning and Packaging (SC-11)* catalog, MS-06-63, to ensure compliance with product cleanliness requirements stated in ASTM G93 Level C, remove **P** from the ordering number.

Example: 6L-LDE-2B1-A

Double Horizontal Tee

Terminates main line in body.



Tubin	g Size		Ordering
Main	Branch	Series	Number
	$1/2 \times 0.049$ in.		6L-LDE-2B1P-A
3/4 imes 0.065 in.	1/2 in. rotatable male VCR fitting	LD8	6L-LDE-2H1P-A

9.38

(238)

Length of main and branch line tubing is 3 in. (76.2 mm).




Ordering Information and Dimensions

Dimensions, in inches (millimeters), are for reference only and are subject to change.

Single Horizontal Cross

Directs main line flow through body.





Tubing Size Ordering Main **Branch Series** Number 6L-LDA-1A1P-A $1/4\times0.035$ in. $1/2 \times 0.049$ in. 6L-LDA-1B1P-A 1/4 in. rotatable $1/2 \times 0.049$ in. 6L-LDA-1L1P-A male VCR fitting 1/2 in. rotatable 6L-LDA-1H1P-A male VCR fitting LD8 6L-LDA-2B1P-A $1/2 \times 0.049$ in. $3/4 \times 0.065$ in. 1/2 in. rotatable 6L-LDA-2H1P-A male VCR fitting 6L-LDA-3B1P-A $1/2 \times 0.049$ in. 1×0.065 in. 1/2 in. rotatable 6L-LDA-3H1P-A male VCR fitting


Length of main and branch line tubing is 3 in. (76.2 mm).

Double Horizontal Cross

Directs main line flow through body.







Tubin	g Size		Ordering
Main	Branch	Series	Number
	1/2 × 0.049 in.		6L-LDC-1B1P-A
$1/2 \times 0.049$ in.	1/2 in. rotatable male VCR fitting		6L-LDC-1H1P-A
	1/2 × 0.049 in.		6L-LDC-2B1P-A
3/4 × 0.065 in.	1/2 in. rotatable male VCR fitting	LD8	6L-LDC-2H1P-A
	1/2 × 0.049 in.		6L-LDC-3B1P-A
1×0.065 in.	1/2 in. rotatable male VCR fitting		6L-LDC-3H1P-A

Length of main and branch line tubing is 3 in. (76.2 mm).




Dimensions are for reference only and are subject to change.

Bar Stock-Body Isolation Valves

- Valves provide shutoff service for bulk gas distribution systems.
- Purge ports are 1/4 in. rotatable male VCR fittings.

Select an ordering number. To order optional cleaning in accordance with Swagelok Special Cleaning and Packaging (SC-11) catalog, MS-06-63, to ensure compliance with product cleanliness requirements stated in ASTM G93 Level C, remove P from the ordering number.

Example: 6L-LDF-1B1-A



Tubing Size		Ordering		Dimensions, in. (mm)								
Inlet	Outlet	Number	Series	Α	В	С	D	E	F	G	Н	J
1/2 × 0.049 in.	1/2 × 0.049 in.	6L-LDF-1B1P-A	1.00	8.28 (210)	2.33 (59.2)	2.00	1.63	0.62 (15.7)	1.53 (38.9)	3.30 (83.8)		2.25
3/4 imes 0.065 in.	3/4 imes 0.065 in.	6L-LDF-2C1P-A	LD8	8.42 (214)	2.45 (62.2)	(50.8)	(41.4)			3.42	(86.9)	(57.2)
$3/4 \times 0.065$ in.	3/4 imes 0.065 in.	6L-LDS-2C1P-Q	LD16	9.46	3.50	2.69	3.00	0.61	2.63	5.31	(12E)	4.00
1 imes 0.065 in.	1 × 0.065 in.	6L-LDS-3D1P-Q		(240)	(88.9)	(68.3)	(76.2)	(15.5)	(66.8)	3.31	(133)	(102)

Length of main and branch line tubing is 3 in. (76.2 mm).

Accessories

Diaphragm/Stem Subassembly-Kit

Includes replacement diaphragm/stem subassembly, gasket, and instructions.

Ordering numbers:

6L-3K-LD8 for LD8 series: 6L-3K-LD16 for LD16 series.

Gasket Kit

Includes replacement gasket and instructions.

Ordering numbers:

6L-8K-LD8 for LD8 series; 6L-8K-LD16 for LD16 series.

Colored Handles

Green handles are standard.

Cast-Body Valves

For colored handles, add a dash and a handle color designator to the ordering number.

Example: 6L-LD8-BBXX-BL

Forged-Body Valves

For colored handles, insert a handle color designator in the ordering number.

Example: 6L-ELD8-VVXBL-P

Bar Stock-Body Valves

For colored handles, replace A or Q in the ordering number with a handle color designator.

Examples: 6L-LDE-2B1P-C 6L-LDS-2C1P-S

	Designators		
Handle	Cast and Forged Valves	Bar Stock Valves	
Color		LD8	LD16
Blue	BL	С	S
Black	BK	В	R
Brown	BW	J	Υ
Gold	GD	G	W
Orange	OG	L	1
Pink	PN	K	Z
Purple	PR	F	V
Red	RD	D	Т
Silver	IV	М	2
White	WH	Н	Х
Yellow	YW	Е	U

Oxygen Service Hazards

For more information about hazards and risks of oxygenenriched systems, refer to Oxygen System Safety Technical Report, MS-06-13.

⚠ WARNING

Do not mix/interchange Swagelok products or components not governed by industrial design standards, including Swagelok tube fitting end connections, with those of other manufacturers.

To increase service life, ensure proper valve performance, and prevent leakage, apply only as much torque as is required to achieve positive shutoff.



Introduction

Since 1947, Swagelok has designed, developed, and manufactured high-quality, general-purpose and specialty fluid system products to meet the evolving needs of global industries. Our focus is on understanding our customers' needs, finding timely solutions, and adding value with our products and services.

We are pleased to provide this global edition of the book-bound *Swagelok Product Catalog*, which compiles more than 100 separate product catalogs, technical bulletins, and reference documents into one convenient, easy-to-use volume. Each product catalog is up to date at the time of printing, with its revision number shown on the last page of the individual catalog. Subsequent revisions will supersede the printed version and will be posted on the Swagelok website and in the Swagelok electronic Desktop Technical Reference (eDTR) tool.

For more information, visit your Swagelok website or contact your authorized Swagelok sales and service representative.

Warranty Information

Swagelok products are backed by The Swagelok Limited Lifetime Warranty. For a copy, visit swagelok.com or contact your authorized Swagelok representative.

Safe Product Selection

When selecting a product, the total system design must be considered to ensure safe, trouble-free performance. Function, material compatibility, adequate ratings, proper installation, operation, and maintenance are the responsibilities of the system designer and user.

⚠ WARNING

Do not mix/interchange Swagelok products or components not governed by industrial design standards, including Swagelok tube fitting end connections, with those of other manufacturers.

Not all trademarks listed below apply to this catalog. Swagelok, Cajon, Ferrule-Pak, Goop, Hinging-Colleting, IGC, Kenmac, Micro-Fit, Nupro, Snoop, Sno-Trik, SWAK, VCO, VCR, Ultra-Torr, Whitey-TM Swagelok Company 15-7 PH—TM AK Steel Corp. AccuTrak, Beacon, Westlock-TM Tyco International Services Aflas-TM Asahi Glass Co., Ltd. Alleima-TM Alleima ASCO, El-O-Matic—TM Emersor AutoCAD-TM Autodesk, Inc. CSA-TM Canadian Standards Association Crastin, DuPont, Kalrez, Krytox, Teflon, Viton-TM E.I. duPont Nemours and Company DeviceNet-TM ODVA Dyneon, Elgiloy, TFM—TM Dyneon Elgiloy—TM Elgiloy Specialty Metals Festo—TM Festo SE & Co. KG FM-TM FM Global Grafoil-TM GrafTech International Holdings, Inc. Honeywell, MICRO SWITCH-TM Honeywell MAC-TM MAC Valves
Microsoft, Windows-TM Microsoft Corp. NACE—TM NACE International PH 15-7 Mo, 17-7 PH-TM AK Steel Corp picofast-Hans Turck KG Pillar-TM Nippon Pillar Packing Company, Ltd. Raychem—TM Tyco Electronics Corp. Sandvik, SAF 2507—TM Sandvik AB Simriz-TM Freudenberg-NOK SolidWorks-TM SolidWorks Corporation UL-Underwriters Laboratories Inc. Xylan-TM Whitford Corporation © 2022 Swagelok Company