




KPRREG $\frac{1}{1}$ - $\frac{M}{2}$ - $\frac{IR}{3}$ - $\frac{320}{4}$ - $\frac{1000}{5}$ - $\frac{H}{6}$ - $\frac{F}{7}$

1 - REGULATOR CONTROL RANGE

- 1 0-100 PSIG
- 5 0-500 PSIG

2 - MOUNTING OPTION

- 0 NO MOUNTING
- M WALL MOUNT PANEL INCLUDED

3 - VALVE OPTIONS

- 0 NO VALVES
- R RELIEF VALVE ONLY (ITEM#3A)
- IR ISOLATION VALVE (ITEM#3B) AND RELIEF VALVE (ITEM#3A)

4 - CGA CONNECTION

- 000 NO CGA
- 320 CGA320 NUT AND NIPPLE (CO2)
- 580 CGA580 NUT AND NIPPLE (Ar, He, Kr, Ne, Xe, CF4)
- 590 CGA590 NUT AND NIPPLE (Air, SF6)

5 - OUTLET GAUGE

- 0160 PGI C SERIES 0-160PSIG GAUGE (0-100 PSIG CONTROL RANGE REGULATOR ONLY)
- 1000 PGI C SERIES 0-1000PSIG (0-500 PSIG CONTROL RANGE REGULATOR ONLY)

6 - HOSE

- 0 NO HOSE
- H 1/4" DIA X 36" LONG T SERIES PTFE HOSE (1/4" TA X 1/4" FNPT ENDS)

7 - FILTER

- 0 NO FILTER
- F TF SERIES FILTER, 7 MICRON

NOTES:

- REGULATOR INLET 3600PSIG
- INLET GAUGE (ITEM#8) 0-5000PSIG
- ISOLATION VALVE CANNOT BE ORDERED WITHOUT RELIEF VALVE
- RELIEF VALVE SIZED FOR SELECTED REGULATOR CONTROL RANGE
- 25micron FILTER INCLUDED INSIDE REGULATOR INLET PORT

CONCEPT DRAWING

Swagelok