

Some Special Specialties

Swagelok premium-quality, leak-tight **Special Application/Alloy Valves** are your proven and trusted performers for ultra-reliable economy and productivity in even the most challenging fluid-system applications and operating environments...

FIRE SERIES

Ball Valves A60T

Available in stainless steel or carbon steel, for temperatures up to 400°F and working pressures up to 2200 psig. Offered in our 63, 65, 67, and 68 series sizes – and all meet API Standard 607 and our own specially developed Fire Test specification involving valve exposure to uneven heating.



ALTERNATIVE FUEL SERVICE

Ball Valves

Our AFS components, with 316 stainless steel bodies, are ideal for high-pressure/high-flow applications – up to 6000 psig, with flow coefficients from 4.0 to 13.8. Can be manually or pneumatically activated.



Features include a heavy-duty directional handle that enables quarter-turn actuation; a PTFE-coated stainless steel floating-ball design that provides consistent, low-actuation torque; and our patented seat-loading technology for optimum integrity in low OR high pressures. Fully compatible with hydrogen and CNG.

60 SERIES

Special Alloy On-Off Ball Valves

Available in 3/8" to 1" sizes, in Alloy 625, Alloy 825, Alloy 2507 Super Duplex Stainless Steel, and 6-Moly. Features include a compensating seat design, live-loaded/two-piece stem packing, and quarter-turn actuation.



83 SERIES

Special Alloy Trunnion Ball Valves

Available in Alloy 2507, 6-Moly, Alloy 625, and Alloy 825. For working pressures up to 6000 psig, with flow coefficients from 0.75 to 1.6. Low operating torque due to spring-loaded seats. Exceptional performer in both low and high pressures. Unique trunnion ball prevents blowouts.



For complete details concerning all Swagelok Valves and industry-leading Componentry, contact:

Zach Barefoot,
Manager –
Business Development



zach.barefoot@swagelok.com

412.761.3212

Put our team alongside yours



**WE DELIVER
DIFFERENCE-MAKING
SOLUTIONS:**

Products | Strategic Support Services | Application Know-How



The Brand. The Inventory. The Expertise.

WE'RE YOUR SWAGELOK FLUID-SYSTEM SOLUTIONS PROVIDER



Industry-Best Componentry



Masterful Custom Fabrication



Expert Safety Training



Extensive Energy Evaluations



Unparalleled Application Knowledge




Comprehensive Hose Advisories





Proven Inventory Management Support



Genuine Swagelok Tool Rentals



WE CAN HELP YOU SAVE TIME, MONEY, AND WORRY:



Swagelok Pittsburgh | Tri-State Area
49 Meade Avenue, Pittsburgh, PA 15202
412.761.3212

All service marks and trademarks shown are owned and registered by Swagelok Company. © 2025 Swagelok Company. www.swagelok.com

You are receiving this email as a valued contact of Swagelok Pittsburgh | Tri-State Area.