

# Sample Cylinders, Accessories, and Outage Tubes



## Features

- Sizes from 10 to 3785 cm<sup>3</sup> (1 gal)
- Working pressures up to 5000 psig (344 bar)
- 304L and 316L stainless steel and alloy 400

## Sample Cylinders

### Features

- Body made of seamless tubing provides consistent wall thickness, size, and capacity.
- Smooth internal neck transition allows easy cleaning and eliminates trapped fluids.
- Cold-formed female NPT threads provide greater strength.
- Heavy-wall end connections provide strength and resist flaring.
- Swagelok® DOT sample cylinders conform to 49 CFR Part 178, "Specifications for Packagings."

### Single-Ended Cylinders

- 150, 300, and 500 cm<sup>3</sup> sizes meet a variety of sampling needs.
- 304L stainless steel construction resists intergranular corrosion.
- Full-penetration gas tungsten arc-weld construction provides leak-tight sample containment.

### Testing

**DOT-4B 500** cylinders are hydrostatically proof tested at 1000 psig (69 bar) minimum.



### Double-Ended Cylinders

- Sizes from 40 to 3785 cm<sup>3</sup> (1 gal)
- Working pressures up to 5000 psig (344 bar)
- 304L and 316L stainless steel materials resist intergranular corrosion.

### Testing

Each DOT cylinder is hydrostatically tested to at least 5/3 the working pressure.

**DOT-3E 1800** cylinders are hydrostatically proof tested at 3050 psig (210 bar). One cylinder of each lot is burst tested.

**DOT-3A 1800 and 5000** cylinders are marked with a serial number. Volumetric expansion of each cylinder during hydrostatic testing must be within the limits set by DOT Specification 3A.

**DOT-3A 1800** cylinders are hydrostatically proof tested at 3000 psig (206 bar) minimum.

**DOT-3A 5000** cylinders are hydrostatically proof tested at 8500 psig (586 bar) minimum.

**DOT-SP7458 1800** cylinders are hydrostatically proof tested at 3000 psig (206 bar).

**⚠ It is the responsibility of the party filling the cylinder to have it retested by an approved facility, at the required intervals.**

## Pressure-Temperature Ratings

Ratings up to 100°F (37°C) are determined by DOT code. Ratings limited to 300°F (148°C) max with PTFE internal coating. Ratings may be limited by individual country government regulations.

| Material              | 316L SS                      | 316L SS, 304L SS | 304L SS     | Alloy 400       | 316 SS      | 304L SS    |
|-----------------------|------------------------------|------------------|-------------|-----------------|-------------|------------|
| Specification         | DOT-3A 5000                  | DOT-3E 1800      | DOT-3A 1800 | DOT-SP7458 1800 | None        | DOT-4B 500 |
| Temperature, °F (°C)  | Working Pressure, psig (bar) |                  |             |                 |             |            |
| -65 (-53) to 100 (37) | 5000 (344)                   | 1800 (124)       | 1800 (124)  | 1800 (124)      | 1000 (68.9) | 500 (34.4) |
| 200 (93)              | 3960 (272)                   | 1360 (93.7)      | 1360 (93.7) | 1580 (108)      | 840 (57.8)  | 500 (34.4) |
| 300 (148)             | 3570 (245)                   | 1230 (84.7)      | 1230 (84.7) | 1490 (102)      | 760 (52.3)  | 500 (34.4) |
| 400 (204)             | 3290 (226)                   | 1130 (77.8)      | 1130 (77.8) | 1430 (98.5)     | 700 (48.2)  | 500 (34.4) |
| 500 (260)             | 3060 (210)                   | 1050 (72.3)      | 1050 (72.3) | 1420 (97.8)     | 650 (44.7)  | 500 (34.4) |
| 600 (315)             | 2920 (201)                   | 1000 (68.9)      | 1000 (68.9) | 1420 (97.8)     | 620 (42.7)  | 500 (34.4) |
| 650 (343)             | 2870 (197)                   | 980 (67.5)       | 980 (67.5)  | 1420 (97.8)     | 610 (42.0)  | 500 (34.4) |
| 700 (371)             | 2810 (193)                   | 970 (66.8)       | 970 (66.8)  | 1420 (97.8)     | 590 (40.6)  | 500 (34.4) |
| 750 (398)             | 2750 (189)                   | 950 (65.4)       | 950 (65.4)  | 1410 (97.1)     | 580 (39.9)  | 500 (34.4) |
| 800 (426)             | 2700 (186)                   | 930 (64.0)       | 930 (64.0)  | —               | 570 (39.2)  | 500 (34.4) |
| 850 (454)             | 2640 (181)                   | —                | —           | —               | 560 (38.5)  | —          |

## Transportable Pressure Equipment Directive (TPED)

The Transportable Pressure Equipment Directive (TPED) provides requirements relating to the design, manufacture, and testing of transportable pressure vessels and accessories, including sample cylinders and rupture discs. The intent of the directive is to provide a uniform level of product safety throughout the European Union countries.

For information about TPED-compliant Swagelok products, see the *Swagelok Products Compliant with the Transportable Pressure Equipment Directive* catalog, [MS-02-193](#).


## Sample Cylinders

### Ordering Information, Technical Data, and Dimensions


Select an ordering number.

Dimensions are for reference only and are subject to change.

#### Single-Ended Cylinders



#### Double-Ended Cylinders



| Material Grade/<br>Cylinder<br>Specification | Pressure<br>Rating<br>psig (bar) | Internal<br>Volume<br>cm <sup>3</sup> ± 5 % | P<br>in.    | Ordering<br>Number | Dimensions, in. (mm) |             |             | Weight<br>lb (kg) |  |
|--|----------------------------------|---|-------------|--------------------|----------------------|-------------|-------------|-------------------|--|
|  |                                  |   |             |                    | A                    | B           | T           |                   |  |
| <b>Single-Ended</b>                          |                                  |   |             |                    |                      |             |             |                   |  |
| 304L SS/<br>DOT-4B 500                       | 500<br>(34.4)                    | 150   | 1/4         | 304L-05SF4-150     | 2.00 (50.8)          | 4.88 (124)  | 0.093 (2.4) | 1.1 (0.50)        |  |
|  |                                  | 300   |             | 304L-05SF4-300     |                      | 8.62 (219)  |             | 1.8 (0.82)        |  |
|  |                                  | 500   |             | 304L-05SF4-500     |                      | 13.6 (345)  |             | 2.7 (1.2)         |  |
| <b>Double-Ended</b>                          |                                  |   |             |                    |                      |             |             |                   |  |
| 304L SS/<br>DOT-3E 1800                      | 1800<br>(124)                    | 40  | 1/8         | 304L-HDF2-40       | 1.25 (31.8)          | 3.88 (98.6) | 0.070 (1.8) | 0.31 (0.14)       |  |
|  |                                  | 50  | 1/4         | 304L-HDF4-50       | 1.50 (38.1)          | 3.75 (95.2) | 0.093 (2.4) | 0.38 (0.17)       |  |
|  |                                  | 75  |             | 304L-HDF4-75       |                      | 4.94 (125)  |             | 0.62 (0.28)       |  |
|  |                                  | 150   |             | 304L-HDF4-150      | 2.00 (50.8)          | 5.25 (133)  |             | 0.94 (0.43)       |  |
|  |                                  | 300   |             | 304L-HDF4-300      |                      | 8.94 (227)  |             | 1.6 (0.73)        |  |
|  |                                  | 400   |             | 304L-HDF4-400      |                      | 11.4 (290)  |             | 2.1 (0.95)        |  |
|  |                                  | 500   |             | 304L-HDF4-500      |                      | 13.8 (351)  |             | 2.6 (1.2)         |  |
| 1000   | 1/4                              | 304L-HDF4-1000                              | 3.50 (88.9) | 10.9 (277)         |                      | 0.180 (4.6) |             | 6.5 (2.9)         |  |
| 1000   | 1/2                              | 304L-HDF8-1000                              |             |                    |                      |             |             |                   |  |
| 304L SS/<br>DOT-3A 1800                      | 1800<br>(124)                    | 2250  | 1/4         | 304L-HDF4-2250     | 4.00 (102)           | 17.2 (437)  | 0.206 (5.2) | 14 (6.4)          |  |
|  |                                  | 2250  | 1/2         | 304L-HDF8-2250     |                      | 26.7 (678)  |             | 21 (9.5)          |  |
|  |                                  | 3785<br>(1 gal)                             | 1/4         | 304L-HDF4-1GAL     |                      |             |             |                   |  |
|  |                                  | 3785<br>(1 gal)                             | 1/2         | 304L-HDF8-1GAL     |                      |             |             |                   |  |
| 316L SS/<br>DOT-3E 1800                      | 1800<br>(124)                    | 150   | 1/4         | 316L-HDF4-150      | 2.00 (50.8)          | 5.25 (133)  | 0.093 (2.4) | 0.94 (0.43)       |  |
|  |                                  | 300   |             | 316L-HDF4-300      |                      | 8.94 (227)  |             | 1.6 (0.73)        |  |
|  |                                  | 500   |             | 316L-HDF4-500      |                      | 13.8 (351)  |             | 2.6 (1.2)         |  |
| 316L SS/<br>DOT-3A 5000                      | 5000<br>(344)                    | 150   |             | 316L-50DF4-150     | 1.90 (48.2)          | 8.00 (203)  | 0.240 (6.1) | 3.0 (1.4)         |  |
|  |                                  | 300   |             | 316L-50DF4-300     |                      | 14.5 (368)  |             | 5.6 (2.5)         |  |
|  |                                  | 500   |             | 316L-50DF4-500     |                      | 23.5 (597)  |             | 9.1 (4.1)         |  |
| Alloy 400/<br>DOT-<br>SP7458 1800            | 1800<br>(124)                    | 150   |             | M-HDF4-150         | 2.00 (50.8)          | 5.25 (133)  | 0.093 (2.4) | 0.94 (0.43)       |  |
|  |                                  | 300   |             | M-HDF4-300         |                      | 8.94 (227)  |             | 1.8 (0.82)        |  |
|  |                                  | 500   |             | M-HDF4-500         |                      | 13.8 (351)  |             | 2.9 (1.3)         |  |

## Overpressure Protection

Compressed gas cylinders must be equipped with pressure relief devices in accordance with United States DOT regulations and CGA S-1.1. The CGA standard lists devices that can be used with specific gases. It also contains information on other types of pressure relief devices.

- ⚠ **Be sure to use the correct pressure-relief device for the gas being used.**
- ⚠ **Proper filling of the cylinder according to DOT specifications, or other local regulations, is critical in preventing overpressurization.**

## Rupture Disc Units

Swagelok rupture disc units protect sample cylinders from overpressurization by venting the cylinder contents to atmosphere. The rupture disc is welded to a body that is threaded into a valve body or a rupture disc tee and sealed by an elastomer O-ring. The rupture disc can be easily replaced without removing the valve or the tee from the cylinder.



### Materials of Construction

| Component        | Material Grade/ASTM Specification |
|------------------|-----------------------------------|
| Body, inlet ring | 316L/A479 or A213                 |
| O-ring           | Fluorocarbon FKM                  |
| Rupture disc     | Alloy 600/B168                    |

### Ordering Information

| Nominal Burst Pressure at 70°F (20°C)      | Ordering Number |
|--|-----------------|
| 2850 psig ± 150 psig<br>196 bar ± 10.3 bar | SS-RDK-16-2850  |
| 1900 psig ± 100 psig<br>130 bar ± 6.8 bar  | SS-RDK-16-1900  |

## Nonrotating-Stem Needle Valves with Rupture Disc Units



### Ordering Information and Dimensions

| End Connections                              |                    | Flow Pattern | Valve Ordering Number | Orifice in. (mm) |
|--|--------------------|--------------|-----------------------|------------------|
| Inlet  | Outlet             |              |                       |                  |
| <b>With 2850 psig (196 bar) Rupture Disc</b> |                    |              |                       |                  |
| 1/4 in. male NPT                             | 1/4 in. female NPT | Straight     | SS-16DKM4F4-2         | 0.218 (5.5)      |
|  |                    | Angle        | SS-16DKM4F4-A-2       |                  |
| 1/2 in. male NPT                             |                    |              |                       |                  |
| <b>With 1900 psig (130 bar) Rupture Disc</b> |                    |              |                       |                  |
| 1/4 in. male NPT                             | 1/4 in. female NPT | Straight     | SS-16DKM4-F4-1        | 0.218 (5.5)      |
|  |                    | Angle        | SS-16DKM4-F4-A-1      |                  |
| 1/2 in. male NPT                             |                    |              |                       |                  |

Dimensions are for reference only and are subject to change.

Refer to *Nonrotating-Stem Needle Valves* catalog, [MS-01-42](#), for additional information. Other Swagelok valves are available for use with sample cylinders. Contact your authorized Swagelok sales and service representative for details.


Swagelok

## Rupture Disc Precautions

- Do not use rupture disc devices in a location where the release of the cylinder contents might create a hazard. The rupture disc vents to the atmosphere through six radial holes in the body. Pressure is released suddenly with a loud noise, and gases escape at high velocity.
- Know the burst pressure. (This rating is marked on the end face of the rupture disc unit, as required by CGA S-1.1.)
- Be sure the maximum burst pressure does not exceed the cylinder test pressure.
- Be sure the minimum burst pressure is at least 40 % higher than the cylinder filling pressure.
- Inspect rupture discs regularly. The strength of rupture discs deteriorates with time due to temperature, corrosion, and fatigue. Pulsating pressure, vacuum/pressure cycling, heat, and corrosive fluids and atmospheres can reduce the disc's burst pressure.
- Do not use rupture discs to protect vessels with volumes greater than 3 gal (11 355 cm<sup>3</sup>) for compressed gases or 1 1/2 gal (5677 cm<sup>3</sup>) for liquefied gases.
- Provide suitable means to isolate the sample cylinder from the system in case the rupture disc bursts while taking a sample.
- In cylinders with liquefied gases, a small temperature increase during transportation or storage will cause the liquid to expand and may cause the rupture disc to release its contents. See local regulations and other appropriate guidelines for safe filling limits for your application.

## Rupture Disc Tees

These compact assemblies are designed for use with various Swagelok valves. Tees are made of 316 stainless steel. Each tee includes a rupture disc unit.



Dimensions are for reference only and are subject to change.

### Ordering Information and Dimensions

| End Connections                              |                    | Ordering Number | Dimensions, in. (mm) |             |             |             |
|--|--------------------|-----------------|----------------------|-------------|-------------|-------------|
| Inlet  | Outlet             |                 | A                    | B           | C           | D           |
| <b>With 2850 psig (196 bar) Rupture Disc</b> |                    |                 |                      |             |             |             |
| 1/4 in. male NPT                             | 1/4 in. female NPT | SS-RTM4-F4-2    | 1.88 (47.7)          | 1.06 (26.9) | 0.94 (23.9) | 0.50 (12.7) |
| 1/2 in. male NPT                             |                    | SS-RTM8-F4-2    | 2.19 (55.6)          | 1.22 (31.0) | 1.19 (30.2) | 0.56 (14.2) |
| <b>With 1900 psig (130 bar) Rupture Disc</b> |                    |                 |                      |             |             |             |
| 1/4 in. male NPT                             | 1/4 in. female NPT | SS-RTM4-F4-1    | 1.88 (47.7)          | 1.06 (26.9) | 0.94 (23.9) | 0.50 (12.7) |
| 1/2 in. male NPT                             |                    | SS-RTM8-F4-1    | 2.19 (55.6)          | 1.22 (31.0) | 1.19 (30.2) | 0.56 (14.2) |

## Options

### PTFE Coating

Internal cylinder surfaces can be coated with PTFE to provide a nonstick surface, which aids in cleaning. To order, add **-T** to the cylinder ordering number.

Example: 304L-HDF4-300-**T**

### Electropolishing

Electropolishing provides a clean internal surface with a high degree of passivation. To order, add **-EP** to the cylinder ordering number.

Example: 304L-HDF4-300-**EP**

## Accessories

### End Caps

End caps protect valves from damage. Each cap threads onto a neck ring that has been peened to the cylinder neck. End caps are made from plated carbon steel and are available for use on 2250 and 3785 cm<sup>3</sup> (1 gal) cylinders. Swagelok angle-pattern valves can be used on cylinders with end caps.

To order, add **-C** to the cylinder ordering number.

Example: 304L-HDF8-2250-**C**



### Carrying Handle

This accessory provides a convenient way to carry sample cylinders. The handle is made from 304 stainless steel and is available for use on 300 cm<sup>3</sup> and larger cylinders.

To order a sample cylinder to be shipped with a carrying handle, add **-H** to the cylinder ordering number.


Example: 304L-HDF4-300-**H**

To order a carrying handle as a separate component, use one of the following ordering numbers:

| Cylinder OD<br>in. (mm) | Ordering<br>Number |
|-------------------------|--------------------|
| 1.9, 2<br>(48.2, 50.8)  | MS-5K-CY-2"        |
| 3.5, 4<br>(88.9, 102)   | MS-5K-CY-4"        |

### Caps and Plugs

Caps and plugs protect Swagelok tube fitting or NPT end connections on valves during cylinder transport. Contact your authorized Swagelok representative for details.



### Ordering Multiple Options and Accessories

Add designators in *alphabetical* order.

Examples: 304L-HDF8-2250-**C-H** for a sample cylinder with end caps and carrying handle  
304L-HDF4-300-**H-T** for a sample cylinder with carrying handle and internal PTFE coating.


## Outage Tubes

### Features

- Made from 316 stainless steel or alloy 400 tubing
- Offered in 1/4 or 1/2 in. NPT sizes
- Marked “Outage Tube” for identification

### Construction

Outage tubes are welded to the male inlet end of an adapter or tee. This adapter or tee is then threaded into the female port of a sample cylinder.



Outage tubes can also be welded directly to the male inlet of a Swagelok nonrotating stem needle valve. The valve is then threaded into the female port of a sample cylinder.

### Tube Length



Outage tube length ( $L$ ) is measured from the end of the pipe fitting to the end of the tube. Standard tube length is 10.4 in. (26.4 cm). Tubing can be cut to a desired length; instructions are included.

### Purpose

Outage tubes provide a vapor space of the desired volume in cylinders containing liquefied gases, so that liquid in the cylinder can expand if the temperature increases. Without enough vapor space, a small temperature increase can cause the liquid to expand and increase the pressure dramatically.


See local regulations and other appropriate guidelines for safe filling limits for your application.

### Use

Outage is the vapor space in the cylinder expressed as a percentage of the total volume of the cylinder.

$$\% \text{ outage} = (\text{vapor space} / \text{total volume}) \times 100$$

The cylinder is held vertically with the outage tube at the top, as shown. The length of the outage tube determines the amount of vapor space. Sampling methods and the use of the outage tube are described in technical publications such as ASTM D1265, *Standard Practice for Sampling Liquefied Petroleum (LP) Gases (Manual Method)*.



## Outage Tubes

### Ordering Information

#### Adapters with Outage Tubes

Select an adapter ordering number.

For alloy 400 material, replace **SS** with **M**.

Example: **M-DTM4-F4-104**

| End Connections  |                    | Adapter Ordering Number | Tube Length<br>in. (cm) | Tube OD  |
|------------------|--------------------|-------------------------|-------------------------|----------|
| Inlet            | Outlet             |                         |                         |          |
| 1/4 in. male NPT | 1/4 in. female NPT | SS-DTM4-F4-104          | 10.4<br>(26.4)          | 5/16 in. |
| 1/2 in. male NPT | 1/4 in. female NPT | SS-DTM8-F4-104          |                         | 1/2 in.  |

#### Nonrotating Stem Needle Valves with Outage Tubes

Select a valve ordering number.

For alloy 400 material, replace **SS** with **M**.

Example: **M-14DKM4-104**

| End Connections  |                    | Valve Ordering Number | Tube Length<br>in. (cm) | Tube OD  |
|------------------|--------------------|-----------------------|-------------------------|----------|
| Inlet            | Outlet             |                       |                         |          |
| 1/4 in. male NPT |                    | SS-14DKM4-104         | 10.4<br>(26.4)          | 5/16 in. |
| 1/4 in. male NPT | 1/4 in. female NPT | SS-16DKM4-F4-104      |                         | 1/2 in.  |

Valves do not include rupture disc units. Contact your authorized Swagelok representative for information about valves with outage tubes and rupture disc units.

#### Factory-Cut Tube Lengths

Follow the example below to determine how to order outage tubes cut at the factory to a length other than 10.4 in. (26.4 cm).

Sample cylinder ordering number is 304L-HDF4-150.

Outage required is 30 %.

See **Outage Tube Lengths** table at right:

- Find 304L-HDF4-150, the cylinder ordering number.
- Read across to the 30 % column.
- Tube length is 1.79 in.
- Designator is 018.
- Replace **104** in the outage tube adapter or valve ordering number with **018**.

Examples: **SS-DTM4-F4-018**  
**SS-16DKM4-F4-018**

#### Caution:

**Tolerances on cylinder volume, dimensions, and thread fit can change the outage obtained by as much as 20 %. To obtain an exact outage, each outage tube and cylinder assembly should be calibrated by a suitable method.**

### Outage Tube Lengths

| Tube OD    | Cylinder Ordering Number | Minimum Outage, % |      |      |       |       |
|------------|--------------------------|-------------------|------|------|-------|-------|
|            |                          | 10                | 20   | 30   | 40    | 50    |
|            |                          | Tube Length, in.  |      |      |       |       |
| Designator |                          |                   |      |      |       |       |
| 1/4 in.    | 304L-HDF2-40             | 0.87              | 1.11 | 1.35 | 1.59  | 1.84  |
|            |                          | 009               | 011  | 014  | 016   | 018   |
| 5/16 in.   | 304L-HDF4-50             | 0.85              | 1.07 | 1.28 | 1.50  | 1.71  |
|            |                          | 009               | 011  | 013  | 015   | 017   |
|            | 304L-HDF4-75             | 1.02              | 1.34 | 1.66 | 1.98  | 2.31  |
|            |                          | 010               | 013  | 017  | 020   | 023   |
|            | 304L-HDF4-150            | 1.12              | 1.45 | 1.79 | 2.13  | 2.46  |
|            |                          | 011               | 015  | 018  | 021   | 025   |
|            | 304L-HDF4-300            | 1.65              | 2.32 | 2.99 | 3.67  | 4.34  |
|            |                          | 017               | 023  | 030  | 037   | 043   |
|            | 304L-HDF4-400            | 2.00              | 2.90 | 3.79 | 4.69  | 5.59  |
|            |                          | 020               | 029  | 038  | 047   | 056   |
|            | 304L-HDF4-500            | 2.26              | 3.38 | 4.50 | 5.62  | 6.74  |
|            |                          | 023               | 034  | 045  | 056   | 067   |
|            | 304L-HDF4-1000           | 2.31              | 3.06 | 3.81 | 4.56  | 5.31  |
|            |                          | 023               | 031  | 038  | 046   | 053   |
|            | 304L-HDF4-2250           | 3.30              | 4.59 | 5.88 | 7.17  | 8.46  |
|            |                          | 033               | 046  | 059  | 072   | 085   |
|            | 304L-HDF4-1GAL           | 4.62              | 6.79 | 8.96 | 11.14 | 13.31 |
|            |                          | 046               | 068  | 090  | 111   | 133   |
| 1/2 in.    | 304L-HDF8-1000           | 2.21              | 2.96 | 3.71 | 4.46  | 5.21  |
|            |                          | 022               | 030  | 037  | 045   | 052   |
|            | 304L-HDF8-2250           | 3.20              | 4.49 | 5.78 | 7.07  | 8.36  |
|            |                          | 032               | 045  | 058  | 071   | 084   |
|            | 304L-HDF8-1GAL           | 4.52              | 6.69 | 8.86 | 11.04 | 13.21 |
|            |                          | 045               | 067  | 089  | 110   | 132   |
| 5/16 in.   | 316L-HDF4-150            | 1.12              | 1.45 | 1.79 | 2.13  | 2.46  |
|            |                          | 011               | 015  | 018  | 021   | 025   |
|            | 316L-HDF4-300            | 1.65              | 2.32 | 2.99 | 3.67  | 4.34  |
|            |                          | 017               | 023  | 030  | 037   | 043   |
|            | 316L-HDF4-500            | 2.26              | 3.38 | 4.50 | 5.62  | 6.74  |
|            |                          | 023               | 034  | 045  | 056   | 067   |
|            | M-HDF4-150               | 1.12              | 1.45 | 1.79 | 2.13  | 2.46  |
|            |                          | 011               | 015  | 018  | 021   | 025   |
|            | M-HDF4-300               | 1.65              | 2.32 | 2.99 | 3.67  | 4.34  |
|            |                          | 017               | 023  | 030  | 037   | 043   |
|            | M-HDF4-500               | 2.26              | 3.38 | 4.50 | 5.62  | 6.74  |
|            |                          | 023               | 034  | 045  | 056   | 067   |
|            | 304L-05SF4-150           | 1.09              | 1.43 | 1.77 | 2.12  | 2.46  |
|            |                          | 010               | 014  | 018  | 021   | 025   |
|            | 304L-05SF4-300           | 1.59              | 2.27 | 2.96 | 3.65  | 4.34  |
|            |                          | 016               | 023  | 030  | 037   | 043   |
|            | 304L-05SF4-500           | 2.16              | 3.30 | 4.45 | 5.60  | 6.74  |
|            |                          | 022               | 033  | 045  | 056   | 067   |
|            | 316L-50DF4-150           | 1.62              | 2.17 | 2.71 | 3.26  | 3.81  |
|            |                          | 016               | 022  | 027  | 033   | 038   |
|            | 316L-50DF4-300           | 2.74              | 3.84 | 4.93 | 6.03  | 7.12  |
|            |                          | 027               | 038  | 049  | 060   | 071   |
|            | 316L-50DF4-500           | 4.39              | 6.21 | 8.04 | 9.86  | 11.68 |
|            |                          | 044               | 062  | 080  | 099   | 117   |

## Miniature Sample Cylinders

Miniature sample cylinders with 3/8 in. Swagelok tube adapter end connections allow transport of low volumes of fluids. The tube adapter ends can be connected to 3/8 in. Swagelok tube fittings or welded to 1/4 or 3/8 in. tubing.


### Features

- Single-ended or double-ended designs
- Corrosion-resistant 316/316L stainless steel construction
- Pressure rating of 1000 psig (68.9 bar)
- Sizes include 10, 25, and 50 cm<sup>3</sup> capacities
- Smooth internal port transition for easy cleaning
- Volume is closely controlled
- Full-penetration butt weld construction

### Ordering Information and Dimensions

Select an ordering number.

Dimensions, in inches (millimeters), are for reference only and are subject to change.



| Cylinder Model | Internal Volume cm <sup>3</sup> | Volume Tolerance | Ordering Number | Pressure Rating psig (bar) | A in. (mm)  | Average Weight oz (g) |
|----------------|---------------------------------|------------------|-----------------|----------------------------|-------------|-----------------------|
| Single-ended   | 10                              | ± 10 %           | SS-4CS-TW-10    | 1000 (68.9)                | 2.19 (55.6) | 2.2 (62)              |
|                | 25                              | ± 5 %            | SS-4CS-TW-25    |                            | 3.69 (93.7) | 3.2 (91)              |
|                | 50                              |                  | SS-4CS-TW-50    |                            | 6.25 (159)  | 5.6 (159)             |
| Double-ended   | 10                              | ± 10 %           | SS-4CD-TW-10    |                            | 2.75 (69.8) | 1.9 (54)              |
|                | 25                              | ± 5 %            | SS-4CD-TW-25    |                            | 4.25 (108)  | 3.3 (94)              |
|                | 50                              |                  | SS-4CD-TW-50    |                            | 6.81 (173)  | 5.1 (145)             |

Existing DOT and TC specifications do not cover miniature cylinders of this size, construction, and pressure rating.

## Additional Products

### N Series Needle Valves

Swagelok N series severe-service union-bonnet needle valves can handle working pressures up to 6000 psig (413 bar) and are available in straight and angle patterns.

Refer to *Severe-Service Union-Bonnet Needle Valves—N Series and HN Series* catalog, [MS-01-168](#), for additional information.



### Quick-Connects

Swagelok quick-connects are available in single- and double-end shutoff stem models and can be keyed to prevent accidental intermixing of different lines in multifluid or multipressure systems.

Refer to *Quick-Connects* catalog, [MS-01-138](#), for additional information.



#### ⚠ WARNING

Do not mix/interchange Swagelok products or components not governed by industrial design standards, including Swagelok tube fitting end connections, with those of other manufacturers.



## Introduction

Since 1947, Swagelok has designed, developed, and manufactured high-quality, general-purpose and specialty fluid system products to meet the evolving needs of global industries. Our focus is on understanding our customers' needs, finding timely solutions, and adding value with our products and services.

We are pleased to provide this global edition of the book-bound *Swagelok Product Catalog*, which compiles more than 100 separate product catalogs, technical bulletins, and reference documents into one convenient, easy-to-use volume. Each product catalog is up to date at the time of printing, with its revision number shown on the last page of the individual catalog. Subsequent revisions will supersede the printed version and will be posted on the Swagelok website and in the Swagelok electronic Desktop Technical Reference (eDTR) tool.

For more information, visit your Swagelok website or contact your authorized Swagelok sales and service representative.

## Warranty Information

Swagelok products are backed by The Swagelok Limited Lifetime Warranty. For a copy, visit [swagelok.com](http://swagelok.com) or contact your authorized Swagelok representative.

### Safe Product Selection

**When selecting a product, the total system design must be considered to ensure safe, trouble-free performance. Function, material compatibility, adequate ratings, proper installation, operation, and maintenance are the responsibilities of the system designer and user.**

### WARNING

**Do not mix/interchange Swagelok products or components not governed by industrial design standards, including Swagelok tube fitting end connections, with those of other manufacturers.**

Not all trademarks listed below apply to this catalog.  
Swagelok, Cajon, Ferrule-Pak, Goop, Hinging-Colleting, IGC, Kenmac, Micro-Fit, Nupro, Snoop, Sno-Trik, SWAK, VCO, VCR, Ultra-Torr, Whitey—TM Swagelok Company  
15-7 PH—TM AK Steel Corp.  
AccuTrak, Beacon, Westlock—TM Tyco International Services  
Atlas—TM Asahi Glass Co., Ltd.  
ASCO, El-O-Matic—TM Emerson  
AutoCAD—TM Autodesk, Inc.  
CSA—TM Canadian Standards Association  
Crastin, DuPont, Kalrez, Krytox, Teflon, Viton—TM E.I. duPont  
Nemours and Company  
DeviceNet—TM ODVA  
Dyneon, Elgiloy, TFM—TM Dyneon  
Elgiloy—TM Elgiloy Specialty Metals  
FM—TM FM Global  
Grafoil—TM GrafTech International Holdings, Inc.  
Honeywell, MICRO SWITCH—TM Honeywell  
MAC—TM MAC Valves  
Microsoft, Windows—TM Microsoft Corp.  
NACE—TM NACE International  
PH 15-7 Mo, 17-7 PH—TM AK Steel Corp  
picofast—Hans Turck KG  
Pillar—TM Nippon Pillar Packing Company, Ltd.  
Raychem—TM Tyco Electronics Corp.  
Sandvik, SAF 2507—TM Sandvik AB  
Simriz—TM Freudenberg-NOK  
SolidWorks—TM SolidWorks Corporation  
UL—Underwriters Laboratories Inc.  
Xylan—TM Whitford Corporation  
© 2022 Swagelok Company