UNIFORM STATUTORY DECLARATION FORM FOR THE REGISTRATION OF FITTING DESIGNS

NEW BRUNSWICK NUNAVUT

March 1

NOVA SCOTIA YUKON PRINCE EDWARD ISLAND NORTHWEST TERRITORIES

NEWFOUNDLAND AND LABRADOR

MANUFACTURERS NAME: Suggetate Communication	
MANUFACTUREDS ADDRESS	
PLANT LOCATIONS: Headquarters: 29500 Solon Road, Solon, Ohio 44139-3492 (See At	ta object (A)
CATEGORY OF FITTINGS TO BE REGISTERED, CIRCLE ONE CATEGORY ONLY	ITLE OF THE STANDAND OF CONSTRUCTION
A Pipe littings, including couplings, tees, albaws, Ye, plugs, unions, pipe caps, or reducers E Flanges; all line valves C Valves: all line valves D Expension joints, flexible connections, and hose assemblies; all types E Strainers, fliters, separators, and attent traps F Messuring devices, including pressure gauges, level gauges, sight gisses, levels, or pressure transmitters C Certified capacity-rated pressure relief devices acceptable as primary over pressure protection on boilers, pressure yearsile, boiled and forbing phone	ASME B31.1 & ASME B31.3 Unlisted Components
H Pressure retaining components that do not fall into one of the above categories	
N Nuclear components: Class 1 🗆 Class 2 🗆 Class 3 🗀, (Meeting AECB or ASME requirements) SHOW MANUFACTURERS NAME, TRADEMARK, OR LOGO AS IT WILL APPEAR ON THE PRODUCT	
Swagelok	TYPE OF CONSTRUCTION FORGED THE DESCRIBE OTHER DESCRIBE OTHER:
LIST OF SUPPORTING COCUMENTATION AND IDENTIFICATION OF THE ACTUAL ITEMS TO BE REC	13TER#D:
ISO 9001:2008 Quality System Certificate, Support Documents, Attachment B, Catalog Informs	
DECLARATION: David H. Peace	of in this form is true and to the best of sol construction, pressure rds. I further declare that the sol where fabrication occurs in whole
Signature of Declarer:	
This Of day of Workfey AD 2013 OFFI	SPACE FOR THE CIAL SEAL
Commissioner of Oaths or Notery Public: (sign) Lori A. Sarver, Notery Public State of Ohio, Summit County ARtic Official Seaf-to the right) My Commission Expires April 13, 26	nts
This space for Regulatory Authority use	
This registration must be revalidated after ten (10) years from the date of	三
CRN: 0C15741.2	. Newforkingaud Labration
FID#: 1214	Service NL
Notes: 1. All fittings shall be registered in the name of the Manufacturer. 2. Each category shall be supported with two Statutory Declaration forms and one copy of supporting documentation.	Registered 0C15741-20 Date 15/10/09 Engineering and Inspection Sprices Registered by K.
3. The declaration shall be made by the person having full authority and responsibility for the quality of the end product. 4. Quality control programs shall be resubmitted for validation at a meximum interval of five (5) years.	UNDER THE AUTHOUT LETHE PUCLIC SAFEDY AT AND THE BOLLER, PRESSURE TESCEL AND COMPRESSED CAS REQUEATIONS

Attachment B. Scope for Swagelok RHPS Series Pressure Regulators (RS, RSH, RD, RDH and BS) (Category C)

Product Scope

This document represents the scope of the Swagelok RHPS Series Pressure Regulators (RS, RSH, RD, RDH and BS) covered by this submission for CRN approval. The Swagelok RHPS Series Pressure Regulators (RS, RSH, RD, RDH and BS) were designed and evaluated in accordance with ASME B31.1 for unlisted components and ASME B31.3 for unlisted components.

Note:

The temperature ratings in the table below in most cases exceed those shown in the product catalog. The pressure retaining components are designed to be safe at the temperature rating as demonstrated in the Code Compliance Summary, but the Swagelok factory must be consulted to determine which seat and seal materials listed in the Typical Product Characteristics section below are suitable for use at this temperature.

Summary Table

0015741.2

#	sure g ent	Main						
Product Series	Main Pressure Bearing Component	Pressure Bearing Material	Port Connections and Sizes		mbient erature	0.0000000000000000000000000000000000000	eximum erature	Design Code of Construction
	Mai	Material		Inlet	Outlet	Inlet	Outlet	
RS6	Body	Stainless Steel (UNS S31603 / ASTM A479)	Female NPT 3/4" Female ISO/BSP 3/4" ASME B16.5 Flange 3/4"	1015 psi @ 100 °F	406 psi @ 100 °F	1015 psi @ 302 °F	406 psi @ 302 °F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted
RS10	Body	Stainless Steel (UNS S31603 / ASTM A479)	Female NPT 1" Female ISO/BSP 1" ASME B16.5 Flange 1"	1015 psi @ 100 °F REGISTRAT	290 psi @ 100 °F	Lucian	TTINGS 5 290 psi 0 302 F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
RS15	Body	Stainless Steel (UNS S31603 / ASTM A479)	Female NPT 1-1/12" Female ISO/BSP 1-1/2" ASME B16.5 Flange 1-1/2"	T1015 psi F @ 100 °F UN 2	290 psi @ 100 °F	1015 psi @ 302 °F	290/psi 0 302/FF 0 DEDOVIC N SURVEYOR	ASME B31.1 Compodents) and ASME B31.3 (Unlisted Components)
RS20	Body	Stainless Steel (UNS S31603 / ASTM A479)	Female NPT 2" Female ISO/BSP 2" ASME B16.5 Flange 2"	1015 psi @ 100 °F	290 psi @ 100 °F	1015 psi @ 302 °F	290 psi @ 302 ^º F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
RSH2	Body	Stainless Steel (UNS S31603 / ASTM A479)	Female NPT 1/4"	6800 psi @ 100 ⁰ F	4500 psi @ 100 ⁰ F	6800 psi @ 302 ⁰ F	4500 psi @ 302 ⁰ F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)

+	sure	Main			Maximum Rated Pressure					
Product Series	Main Pressure Bearing Component	Main Pressure Bearing Bearing Material Main Pressure Bearing Sizes			At ambient temperature		aximum perature	Design Code of Construction		
	Mai	Material		Inlet	Outlet	Inlet	Outlet	Construction		
RSH4	Body	Stainless Steel (UNS S31603 / ASTM A479)	Female ISO/BSP 1/2"	5800 psi @ 100 ⁰ F	4900 psi @ 100 °F	5800 psi @ 302 °F	4900 psi @ 302 °F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)		
RSH6	Body	Stainless Steel (UNS S31603 / ASTM A479)	Female NPT 3/4" Female ISO/BSP 3/4" ASME B16.5 Flange 3/4"	5800 psi @ 100 °F	5800 psi @ 100 °F	5800 psi @ 302 ⁰ F	5800 psi @ 302 ⁰ F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)		
RSH8	Body	Stainless Steel (UNS S31603 / ASTM A479)	Female NPT 1" Female ISO/BSP 1" ASME B16.5 Flange 1"	5800 psi @ 100 °F	5700 psi @ 100 °F	5800 psi @ 302 °F	5700 psi @ 302 °F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)		
RSH10	Body	Stainless Steel (UNS S31603 / ASTM A479)	Female NPT 1" Female ISO/BSP 1" ASME B16.5 Flange 1"	5800 psi @ 100 °F	3625 psi @ 100 °F	5800 psi @ 302 °F	3625 psi @ 302 °F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)		
RSH15	Body	Stainless Steel (UNS S31603 / ASTM A479)	Female NPT 1-1/12" Female ISO/BSP 1-1/2"	5800 psi @ 100 °F	3625 psi @ 100 °F	5800 psi @ 302 °F	3625 psi @ 302 ⁰ F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)		
RSH15	Body	Stainless Steel (UNS S31603 / ASTM A479)	ASME B16.5 Flange 1-1/2"	5700 psi @ 100 °F	1 5 7 3625 psi @ 100 °F	5700 psi @ 100 °F	3625 psi @ 302 °F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)		
RSH20	Body	Stainless Steel (UNS S31603 / ASTM A479)	Female NPT 2" Female ISO/BSP 2"	5800 psi @ 100 °F	290 psi @ 100 °F	4400 psi @ 302 °F	290 psi @ 302 °F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)		
RSH20	Body	Stainless Steel (UNS S31603 / ASTM A479)	ASME B16.5 Flange 2"	5500 psi @ 100 °F	290 psi @ 100 °F	5500 psi @ 100 °F	290 psi @ 302 °F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)		

	ure				Maximum R	ated Pressu	re	
Product Series	Main Pressure Bearing Component	Main Pressure Bearing	Port Connections and Sizes	12,000,000	At ambient temperature		eximum erature	Design Code of Construction
	Mair	Material		Inlet	Outlet	Inlet	Outlet	- Construction
RD2	Body	Stainless Steel (UNS S31603 / ASTM A479)	Female NPT 1/4"	5800 psi @ 100 °F	4500 psi @ 100 °F	5800 psi @ 302 °F	4500 psi @ 302 °F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
RD6DP	Body	Stainless Steel (UNS S31603 / ASTM A479)	Female NPT 3/4" Female ISO/BSP 3/4" ASME B16.5 Flange 3/4"	1015 psi @ 100 °F	1015 psi @ 100 °F	1015 psi @ 302 °F	1015 psi @ 302 °F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
RD10	Body	Stainless Steel (UNS S31603 / ASTM A479)	Female NPT 1" Female ISO/BSP 1" ASME B16.5 Flange 1"	1015 psi @ 100 °F	1015 psi @ 100 °F	1015 psi @ 302 °F	1015 psi @ 302 °F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
RD15	Body	Stainless Steel (UNS S31603 / ASTM A479)	Female NPT 1-1/12" Female ISO/BSP 1-1/2" ASME B16.5 Flange 1- 1/2"	1015 psi @ 100 °F	1015 psi @ 100 °F	1015 psi @ 302 °F	1015 psi @ 302 °F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
RD20	Body	Stainless Steel (UNS S31603 / ASTM A479)	Female NPT 2" Female ISO/BSP 2" ASME B16.5 Flange 2"	1015 psi @ 100 °F	1015 psi @ 100 °F	1015 psi @ 302 °F	1015 psi @ 302 °F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
RD25	Body	Stainless Steel (UNS S31603 / ASTM A479)	Female NPT 2-1/2" Female ISO/BSP 2-1/2" ASME B16.5 Flange 2- 1/2"	0 C 1015 psi @ 100 °F	1 5 7 1015 psi @ 100 °F	4 1 1015 psi @ 302 °F	2 1015 psi @ 302 °F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
RD30	Body	Stainless Steel (UNS S31603 / ASTM A479)	ASME B16.5 Flange 3"	1015 psi @ 100 °F	1015 psi @ 100 ⁰ F	1015 psi @ 302 ⁰ F	1015 psi @ 302 ⁰ F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
RD40	Body	Stainless Steel (UNS S31603 / ASTM A479)	ASME B16.5 Flange 4*	1015 psi @ 100 ⁰ F	1015 psi @ 100 ⁰ F	1015 psi @ 302 °F	1015 psi @ 302 ⁰ F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)

	ure				Maximum R	re		
Product Series	Main Pressure Bearing Component	Main Pressure Bearing	Port Connections and Sizes	0.000	At ambient temperature		ximum erature	Design Code of Construction
	Mair	Material		Inlet	Outlet	Inlet	Outlet	Construction
RDH6	Body	Stainless Steel (UNS S31603 / ASTM A479)	Female NPT 3/4" Female ISO/BSP 3/4" ASME B16.5 Flange 3/4"	5800 psi @ 100 °F	5800 psi @ 100 °F	5800 psi @ 302 °F	5800 psi @ 302 °F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
RDH6DP	Body	Stainless Steel (UNS S31603 / ASTM A479)	Female NPT 3/4" Female ISO/BSP 3/4" ASME B16.5 Flange 3/4"	5800 psi @ 100 °F	3335 psi @ 100 °F	5800 psi @ 302 °F	3335 psi @ 302 °F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
RDH8	Body	Stainless Steel (UNS S31603 / ASTM A479)	Female NPT 1" Female ISO/BSP 1" ASME B16.5 Flange 1"	5800 psi @ 100 °F	5700 psi @ 100 °F	5800 psi @ 302 °F	5700 psi @ 302 °F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
RDH10	Body	Stainless Steel (UNS S31603 / ASTM A479)	Female NPT 1" Female ISO/BSP 1" ASME B16.5 Flange 1"	5800 psi @ 100 °F	3625 psi @ 100 °F	5800 psi @ 302 °F	3625 psi @ 302 °F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
RDH15	Body	Stainless Steel (UNS S31603 / ASTM A479)	Female NPT 1-1/12" Female ISO/BSP 1-1/2"	5800 psi @ 100 °F	3400 psi @ 100 °F	5800 psi @ 302 ⁰ F	3400 psi @ 302 ⁰ F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
RDH15	Body	Stainless Steel (UNS S31603 / ASTM A479)	ASME B16.5 Flange 1- 1/2"	5700 psi @ 100 °F	3625 psi @ 100 °F	5700 psi @ 100 °F	3625 psi @ 302 °F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
RDH20	Body	Stainless Steel (UNS S31603 / ASTM A479)	Female NPT 2" Female ISO/BSP 2"	5800 psi @ 100 ⁰ F	2900 psi @ 100 ⁰ F	5800 psi @ 100 ⁰ F	2900 psi @ 302 ⁰ F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
RDH20	Body	Stainless Steel (UNS S31603 / ASTM A479)	ASME B16.5 Flange 2"	5500 psi @ 100 °F	2900 psi @ 100 °F	5500 psi @ 100 ⁰ F	2900 psi @ 302 °F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)

The products shown in the table below are a part of the above product families and were previously registered under CRN registration number 0C15099.5C

	ure at							
Product Series	Main Pressure Bearing Component	Main Pressure Bearing	Port Connections and Sizes	2 Control of the 20th Section 15	At ambient temperature		ximum erature	Design Code of Construction
Main	Mat Go	Material		Inlet	Outlet	Inlet	Outlet	Constitution
RDH25	Body	Stainless Steel (UNS S31603 / ASTM A479)	ASME B16.5 Flange 2-1/2"	4060 psi @ 100 °F	2900 psi @ 100 ⁰ F	4060 psi @ 100 °F	2900 psi @ 302 °F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
RDH30	Body	Stainless Steel (UNS S31603 / ASTM A479)	ASME B16.5 Flange 3"	4060 psi @ 100 °F	1900 psi @ 100 °F	4060 psi @ 100 °F	1900 psi @ 302 °F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
RDH40	Body	Stainless Steel (UNS S31603 / ASTM A479)	ASME B16.5 Flange 4"	4040 psi @ 100 °F	1900 psi @ 100 °F	4040 psi @ 100 °F	1900 psi @ 302 °F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
BS10	Body	Stainless Steel (UNS S31603 / ASTM A479)	Female NPT 1" Female ISO/BSP 1" ASME B16.5 Flange 1"	1015 psi @ 100 °F	290 psi @ 100 °F	1015 psi @ 302 °F	290 psi @ 302 ⁰ F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
RS2	Body	Stainless Steel (UNS S31603 / ASTM A479)	Female NPT 1/4"	5800 psi @ 100 °F	4500 psi @ 100 °F	5800 psi @ 302 °F	4500 psi @ 302 °F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
RS4	Body	Stainless Steel (UNS S31603 / ASTM A479)	Female NPT 1/2" Female ISO/BSP 1/2" ASME B16.5 Flange 1/2"	1015 psi @ 100 °F	406 psi @ 100 ^p F	1015 psi @ 302 [©] F	406 psi @ 302 ⁰ F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
RS8	Body	Stainless Steel (UNS S31603 / ASTM A479)	Female NPT 1" Female tSO/BSP 1" ASME B16.5 Flange 1"	1015 psi @ 100 ⁰ F	406 psi @ 100 ⁰ F	1015 psi @ 302 °F	406 psi @ 302 ⁰ F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
RD6	Body	Stainless Steel (UNS S31603 / ASTM A479)	Female NPT 3/4" Female ISO/BSP 3/4" ASME B16.5 Flange 3/4"	1015 psi @ 100 [®] F	1015 psi @ 100 ^⁰ F	1015 psl @ 302 °F	1015 psi @ 302 ⁰ F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)

	ure			Maximum Rated Pressure				
Product Series	Main Bearing Bearing Material		Port Connections and Sizes		At ambient temperature		ximum erature	Design Code of Construction
	Main	Material		Inlet	Outlet	Inlet	Outlet	
RD8	Body	Stainless Steel (UNS S31603 / ASTM A479)	Female NPT 1" Female ISO/BSP 1" ASME B16.5 Flange 1"	1015 psi @ 100 °F	1015 psi @ 100 °F	1015 psi @ 302 °F	1015 psi @ 302 °F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
BS4	Body	Stainless Steel (UNS S31603 / ASTM A479)	Female NPT 1/2" Female ISO/BSP 1/2" ASME B16.5 Flange 1/2"	1015 psi @ 100 °F	406 psi @ 100 °F	1015 psi @ 302 °F	406 psi @ 302 ⁰ F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)
BS8	Body	Stainless Steel (UNS S31603 / ASTM A479)	Female NPT 1" Female ISO/BSP 1" ASME B16.5 Flange 1"	1015 psi @ 100 °F	203psi @ 100 °F	1015 psi @ 302 °F	203 psi @ 302 ⁰ F	ASME B31.1 (Unlisted Components) and ASME B31.3 (Unlisted Components)

Product Illustration



RS(H)2



RS(H)4, 6, 8



RS(H)10, 15, 20

0015741.2



RD2



RD(H)6, 8



RD(H)6DP



Typical Product Characteristics:

Some of the product options listed below affect the pressure-temperature ratings shown in the Summary Table, but in all cases the ratings are less than those shown in the Summary Table. All of the following options are within the scope of this registration:

- Body Seal Materials: FKM, Nitrile, EPDM, FFKM, HNBR
- Diaphragm Materials: FKM, Nitrile, EPDM, FFKM, HNBR, PTFE, 316SS
- Piston Seal Materials: FKM, Nitrile, EPDM, FFKM, HNBR
- Seat Materials: FKM, Nitrile, EPDM, FFKM, HNBR, PCTFE, PEEK, Polyurethane

Some of the product options listed below do not affect the pressure-temperature ratings shown in the Summary Table. All of the following options are within the scope of this registration:

Handle Type
Cleaning options
Panel Mounting
Feedback Loops
Handle color
Anti-tamper
Laser Etching
ASTM G93 cleaning
NACE Components
External Feedback
External Feedback to the Pilot

OC15741.2

Quality System

The Swagelok Company quality system complies with the requirements of BS EN ISO 9001:2008. The Swagelok Company maintains British Standards Institution Certificate of Registration Number FM 01729, which applies to all locations listed on the Certificate. The Swagelok RHPS Series Pressure Regulators (RS, RSH, RD, RDH and BS) are manufactured and assembled at Swagelok Company locations in Solon, Ohio and Tromode, Isle of Man, British Isles.

References

The product catalog does not represent the full scope of registration, but rather details some of the most common options.

RHPS Series Pressure Regulator Catalog MS-02-430, R1