UNIFORM ST	TATUTORY DECLARAT	ION FORM FOR THE REGISTRA	TION OF FITTING DESIGNS
NEW BRUNSWICK NUNAVUT	NOVA SCOTIA YUKON	PRINCE EDWARD ISLAND NORTHWEST TERRITORIES	NEWFOUNDLAND AND LABRADOR
MANUFACTURERS NAME	Swagelok Company		
MANUFACTURERS ADDRE		, Solon, Ohio 44139 USA	
PLANT LOCATIONS: Hea	dquarters: 29500 Solon	Road, Solon, Ohio 44139 USA (Se	e Attachment A)
CATEGORY OF F	ITTINGS TO BE REGISTERE	D. CIRCLE ONE CATEGORY ONLY	TITLE OF THE STANDARD OF CONSTRUCTION
Pipe fittings, including cot B Flanges: all flanges C Valves: all line valves D Expansion joints, flaxible E Stratners, filters, separato F Messuring devices, includ pressuris transmitters G Certified capacity-rated pr bollers, pressure vessels, H Pressure retaining compor	ASME B16.5 and ASME B31.3 Chapter IX, for unlisted components where applicable		
N Nuclear components: Cla	ss 1 🗆 Class 2 🗖 Class 3 🗆	, (Meeting AECB or ASME requirements)	
	ame trademark, or lo	GO AS IT WILL APPEAR ON THE PROD	FORGED & WELDED D WROUGHT D CAST D OTHER D DESCRIBE OTHER
iny knowledge represents the emperature ratings, and ide in anufacture of these fittings or in part and has been verifical eclaration conscientiously beginned before me at	e product for which registre in thirdication markings are in this regulated by a Quality Cled by BSI selleving the betrue, and keep the company of the betrue, and keep the company of the	ation is sought. The dimensions, material secondance with the herein named state control Program which extends to each as being suitable for mowing that it is of the same force and same to the same same to the same same to the same same same same same same same sam	andards. I further declare that the the plant where fabrication occurs in whole or that purpose and I make the purpose and I make the purpose.
r Notary Public: (sign)	(Affix Official seal to the right	<u>C</u>	57
This	This sp	pace for Regulatory Authority use dated after ten (10) years from the da	ate of acceptance.
CRN: 0A17712.2 FIDM: 1214 Notes: All fittings shall be registered. Each category shall be supp	i in the name of the Manufacts	Nunavut	NUNAVUT Boilers and Pressure Vessels Act REGISTERED
orms and one copy of supporting. The declaration shall be madesponsibility for the quality of the Quality control programs, shall be control programs.	fe by the person having full au ne end product.	thority and CRN OA	17712.5 N

Chief inspector

Territorial Registration Fee



Canadian Registration Number Submittal Swagelok Submission #SS-FLANGE-2017

Attachment B: Scope of Registration for 316 SS ASME (ANSI) Flange Adapters (Category A)

Product Scope

The table below presents the scope of Swagelok ANSI Flange Adapters with tube connections covered by this submission for CRN approval. The referenced product catalogues do not represent the full scope of the submission but rather detail some of the most common options...


Summary Table

Product Description or Series	Material	Port Connections and Sizes	Maximum Allowable Working Pressure		Design Code
			Up to 100°F	At maximum temperature	of Construction
Swagelok Flange Adapters	F316 SS ASTM A182	Swagelok End Connection 1/16 - 2 inch (Fractional) 3mm - 50 mm (Metric)	As documented in ASME B16.5 Class and pressure ratings. See "Swagelok SS Tube Fitting Pressure Rating Table" on p.2 as the fitting end may be a limiting factor.		ASME B16.5 ASME B31.1 for unlisted components ASME B31.3 for unlisted components

Product Description And Ratings

The Swagelok Flange Fitting body is a combination of a flange end designed and machined to ASME B16.5 dimensions and requirements, and Swagelok's proprietary design tube fitting end which is identical to the design approved in Swagelok SS Tube Fitting CRN 0A12577.5 (0A10622.2 for Alberta). Flange pressure ratings are based on Class and pressure-temperature ratings as documented in ASME B16.5-2013. Actual flange product ratings may be reduced due to the tube fitting end acting as the limiting factor (see table below for Tube fitting pressure ratings)

An example flange adapter section view is shown below. All Swagelok Flange Fitting wall thicknesses are the same or thicker than those noted in the above Swagelok SS Tube Fitting CRNs.





Canadian Registration Number Submittal Swagelok Submission #SS-FLANGE-2017

Swagelok SS Tube Fitting Pressure Rating Table

Connection Size 60°E to 100°E At maximum tempera	1)	
1/8" 10 900 psig 8284 psig 3/16" 10 200 psig 7752 psig 1/4" 10 200 psig 7752 psig 5/16" 8 000 psig 6080 psig 3/8" 7500 psig 5700 psig 1/2" 6700 psig 5092 psig 5/8" 6000 psig 4560 psig 3/4" 5800 psig 4408 psig 7/8" 4800 psig 3648 psig 1" 4700 psig 3572 psig	Working Pressure (1) At maximum temperature 1000°F (537°C) (2)	
3/16" 10 200 psig 7752 psig 1/4" 10 200 psig 7752 psig 5/16" 8 000 psig 6080 psig 3/8" 7500 psig 5700 psig 1/2" 6700 psig 5092 psig 5/8" 6000 psig 4560 psig 3/4" 5800 psig 4408 psig 7/8" 4800 psig 3648 psig 1" 4700 psig 3572 psig		
1/4" 10 200 psig 7752 psig 5/16" 8 000 psig 6080 psig 3/8" 7500 psig 5700 psig 1/2" 6700 psig 5092 psig 5/8" 6000 psig 4560 psig 3/4" 5800 psig 4408 psig 7/8" 4800 psig 3648 psig 1" 4700 psig 3572 psig		
5/16" 8 000 psig 6080 psig 3/8" 7500 psig 5700 psig 1/2" 6700 psig 5092 psig 5/8" 6000 psig 4560 psig 3/4" 5800 psig 4408 psig 7/8" 4800 psig 3648 psig 1" 4700 psig 3572 psig		
3/8" 7500 psig 5700 psig 1/2" 6700 psig 5092 psig 5/8" 6000 psig 4560 psig 3/4" 5800 psig 4408 psig 7/8" 4800 psig 3648 psig 1" 4700 psig 3572 psig		
1/2" 6700 psig 5092 psig 5/8" 6000 psig 4560 psig 3/4" 5800 psig 4408 psig 7/8" 4800 psig 3648 psig 1" 4700 psig 3572 psig		
5/8" 6000 psig 4560 psig 3/4" 5800 psig 4408 psig 7/8" 4800 psig 3648 psig 1" 4700 psig 3572 psig		
3/4" 5800 psig 4408 psig 7/8" 4800 psig 3648 psig 1" 4700 psig 3572 psig		
7/8" 4800 psig 3648 psig 1" 4700 psig 3572 psig		
1" 4700 psig 3572 psig		
1 1/4" 4900 noin 3724 noin		
1/4 4500 psig 5/24 psig		
1 1/2" 4900 psig 3724 psig		
2" 3600 psig 2736 psig		
3 mm 670 bar 509 bar		
6 mm 710 bar 540 bar		
8 mm 520 bar 395 bar		
10 mm 580 bar 441 bar		
12 mm 470 bar 357 bar		
14 mm 430 bar 327 bar		
15 mm 400 bar 304 bar		
16 mm 400 bar 304 bar		
18 mm 370 bar 281 bar		
20 mm 380 bar 289 bar		
22 mm 340 bar 258 bar		
25 mm 320 bar 243 bar		
28 mm 330 bar 251 bar		
30 mm 310 bar 236 bar		
32 mm 330 bar 251 bar		
38 mm 310 bar 236 bar		
50 mm 270 bar 205 bar		

Note (1): Values based on thickest wall tubing. Thinner tubing may be used but in all cases the ratings are less than, or equal to, those shown in the table.

Note (2): The working pressure ratings for stainless steel Swagelok end connections are based on the allowable working pressure for stainless steel tubing (TP316 A269 listed in ASME B31.3), and are de-rated for use at 1000°F by a derating factor of 0.76 per the Swagelok Tubing Data publication MS-01-107.





Canadian Registration Number Submittal Swagelok Submission #SS-FLANGE-2017

Quality System
The Swagelok Company quality system complies with the requirements of BS EN ISO 9001:2015. Swagelok Company maintains BSI Certificate of Registration Number FM 01729, which applies to all locations listed on the Certificate.

References

The product catalogs noted below do not represent the full scope of registration, but rather details some of the most common options.

- Flange Adapters MS-02-200
- Tubing Data Sheet MS-01-107