NEW BRUNSWICK NUNAVUT	NOVA SCOTIA YUKON	PRINCE EDWARD ISLAND NORTHWEST TERRITORIES	NEWFOUNDLAND AND LABRADOR
MANUFACTURERS NAME:	Swagelok Company		
MANUFACTURERS ADDRES	58: 20500 Solon Pand	, Solon. Ohio 44139 USA	
PLANT LOCATIONS: Head	quarters: 29500 Solon	Road, Solon, Ohio 44139 USA (See	•
CATEGORY OF FI	TINGS TO BE REGISTERE	D. CIRCLE ONE CATEGORY ONLY	Attachment A)
A Pipe fittings, including coup B Flanges: all flanges C Valves: all file relives D Expansion joints, flaxible of E Strainers, filters, separation F Measuring devices, including pressure transmitters C certified capacity-rated pre- boilers, pressure vessels, in H Pressure retaining componi	plings, toes, elbows, Ys, plug connections, and hose assemi s, and steam traps ng pressure gauges, level gas assure relief devices acceptat piping and fusible plugs ents that do not fall into one o	blies: all types  uges, sight glasses, levels, or  ble as primary over pressure protection on	Rubber Products Manufacturers (ARPM) Hose Handbook
M Nuclear components: Clas	s 1 🗆 Class 2 🗆 Class 3 🗆	I, (Meeting AECB or ASME requirements)	
Swa	gelok	GO AS IT WILL APPEAR ON THE PRODU	CAST OTHER X DESCRIBE OTHER: PTFE Core
LIST OF BUPPORTING DOC	IMENTATION AND IDENTIF	FICATION OF THE ACTUAL ITEMS TO BE	REGISTERED.
emperature ratings, and ider nanufacture of these fittings or in part and has been verifi- lectaration conscientiously b Signature of Declarer:	of the end product do sole a product for which registratification markings are in its regulated by a Quality (ed by RSI elleving it to be true, and it hable to get a label due to CADA	mnly declare that the Information conte ation is sought. The dimensions, mate accordance with the herein named sta Control Program which extends to each as being suitable fo knowing that it is of the same force and inotary signature of	ndards. I further declare that the plant where fabrication occurs in whole r that purpose and I make this solemn deflect as if made under oath.  SSPACE FOR THE
CRN: 0D22735,5 FID#: 1214 Crimped Swagelok F	registration must be reval	ose Nunavut	Boilers and Pressure Vessels Act
All fittings shall be registered.     Each category shall be supp forms and one copy of supporting.     The declaration shall be made responsibility for the quality of till.     Quality control programs shall appropriate and appropriate shall be supported by the statement of the statement	in the name of the Manufact orted with two Statutory Deci ng documentation. Se by the person having full a ne and oroduct.	laretion CRN OD	22735.5N mbes 6,2020

Territorial Registration Fee



Canadian Registration Number Submittal Category D Crimped Swagelok FC series PTFE Hose

# THIS IS PART OF CRN 0D22735.5

Technical Standards and Safety Authority

Boilers and Pressure Vessels Safety

Program

September 1, 2020 Page 1 of 2

# Attachment B: Scope of Registration for Crimped Swagelok FC series PTFE Hose Assemblies (Category D)

This document represents the scope of the Swagelok Coreflex FC series hose and crimped assemblies covered by this submission for CRN approval. These products have been evaluated in accordance with the Association for Rubber Products Manufacturers (ARPM) Hose Handbook.

### **Summary Table**

FC Maximum Pressure (psig)			(psig)			
series Hose Size	At Minimum Temp. (-65°F)	Room temperature (0°-100°F)	At Maximum Temp. (450°F)	Pressure Retaining Material	End Connections and Sizes	Design Code of Construction
1/4"	455	800	160		Swagelok Tube Fitting <b>[SL, SM]</b> 1/8" – 2" (3-50mm)	
3/8"	480	650	170	Core Carbon Black filled virgin PTFE	Male & Female NPT Tapered Pipe Fitting [PM, PF] 1/8" – 2"  Male & Female ISO/BSP Tapered (ISO 7) Pipe Threads [MT, FT] 1/4" – 1"	
1/2"	450	450	225	Braid Fiberglass Braid Reinforcement  End Connections 316 SS	Male 37° JIC & Female 37° JIC with female swivel nut [AN, AS] 1/4" – 2"  Tube Butt Welds [TB] 1/2" – 1"  Male & Female VCO O-ring Face seal Fitting [VF, VM] 1/8" - 2"	Association for Rubber Products Manufacturers (ARPM) Hose Handbook
3/4"	325	325	160	Crimp on Collar 304 SS	Male & Female VCR Metal Gasket Face seal Fitting [RF, RM] 1/8" – 2" Female ISO/BSP Parallel Threads (ISO 228) [FS] 1/4" – 1"	



Canadian Registration Number Submittal
Category D Crimped Swagelok FC series PTFE Hose

OD22735.5
Technical Standards and Safety Authority

THIS IS PART OF CRN
0D22735.5
Technical Standards and Safety Authority
Boilers and Pressure Vessels Safety
Program


September 1, 2020 Page 2 of 2

#### **Product Description**

Swagelok's FC series hose is a carbon black filled virgin PTFE liner with fiberglass braid reinforcement. All FC series hoses undergo production testing in accordance with ASTM D380 "Test Methods for Rubber Hose" (version current to hose production date).

#### **Configurations**

All end connection inserts are crimped onto the hose using crimp collars.



#### **Product Options:**

Additional options that do not affect pressure and/or temperature ratings may be made available and are within the scope of this approval. Examples of these would include, but not limited to, the following:

#### **Cover Options**

- Armor guard Interlocking, flexible 302 stainless steel.
- Fire jacket Woven fiberglass coated with specially compounded aerospace-grade silicone rubber
- Spiral guard Helical HDPE plastic

#### **Tag and Marking Options**

- Mat tag Polyester tag with customer-specified text
- Lanyard tag Stainless steel tag with customer-specified text

#### **End Connection Seals or Sealants Options**

- VCO O-rings
- Pipe Thread ends thread sealant

#### **Quality System**

The Swagelok Company quality system complies with the requirements of ISO 9001:2015. The Swagelok Company maintains BSI Certificate of Registration Number FM 01729, which applies to all locations listed on the Certificate.

#### References

The product catalog does not represent the full scope of the registration but rather details some of the most common options. Hose Assemblies, Bulk Hose, and End Connections Product Catalog MS-01-180.

## THIS IS PART OF CRN 0D22735.5

Technical Standards and Safety Authority

Boilers and Pressure Vessels Safety

Program

### Attachment A. Swagelok Manufacturing Locations

This document lists the Swagelok locations where end item or component level manufacturing activities take place.

Swagelok Company	Swagelok Company (Falon 1)	
29500 Solon Road	348 Bishop Road	
Solon, Ohio 44139	Highland Heights, Ohio 44143	
USA	USA	
Swagelok Company (Highland)	Swagelok Company (Falon 2)	
318 Bishop Road	358 Bishop Road	
Highland Heights, Ohio 44143	Highland Heights, Ohio 44143	
USA	USA	
Swagelok Company (OFC)	Swagelok Company (HPF)	
29495 F.A. Lennon Drive	6050 Cochran Road	
Solon, Ohio 44139	Solon, Ohio 44139	
USA	USA	
Swagelok Company (Atlantic)	Swagelok Company (Snow Metal)	
26651 Curtiss Wright Parkway	6060 Cochran Road	
Willoughby Hills, Ohio 44092	Solon, Ohio 44139	
USA	USA	
Swagelok Company (Micro) 26653 Curtiss Wright Parkway Willoughby Hills, Ohio 44092 USA	Swagelok Company (Alfred) 29500 Ambina Drive Solon, Ohio 44139	
Swagelok Hose Services Company (SHSC)	Swagelok Company (Strongsville)	
29900 Solon Industrial Parkway	15400 Foltz Road	
Solon, Ohio 44139	Strongsville, Ohio 44119	
Swagelok (China) Fluid System Technologies Ltd. Changshu Export Process Zone Changshu Economic Development Zone Changshu, Jiangshu 215513 China	Swagelok Limited Ballafletcher Road Tromode IM4 4RA Isle of Man	