

Technical Standards and Safety Authority 345 Carlingview Drive Toronto, Ontario M9W 6N9 www.tssa.org Show facsimile of manufacturer's logo or trademark, as it will appear on the fitting, in the space below



I, Joel Feldman, Vice President of Engineering (Name and Position, e.g. President,	Plant Manager, Chief Engineer)	
of Swagelok Company		
(Name of Man	ufacturer)	
Located at 29500 Solon Road, Solon, Ohio 44139 USA	(440) 248-4600	(440) 349-5970
(Plant Address)	(Telephone No.)	(Fax No.)
do solemnly declare that the fittings listed hereunder, which a and Pressure Vessels Regulation, comply with all of the required.	uirements of	ds and Safety Act, Boile
ASME B31.1 for unlisted components, and ASME B31.3 fo		
(Title of recognized North A which specifies the dimensions, materials of construction, pressure		no the fittings and service
pressure/temperature ratings and the basis for such ratings, the I further declare that the manufacture of these fittings is controlled by	ached data which identifies the dimension e marking of the fitting for identification a quality system meeting the requirem	ons, material of construction and service.
which has been verified by the following authority, B		t (10) t
The items covered by this declaration, for which I seek registration, are cate		
		type fittings. In support o
this application, the following information and/or test data are attached as for	ollows:	
this application, the following information and/or test data are attached as for ISO 9001:2015 Certificate, Attachment A, Attachment B, Catalog	illows: Information and other Support Docu	
this application, the following information and/or test data are attached as for ISO 9001:2015 Certificate, Attachment A, Attachment B, Catalog (drawings, calculations)	illows: Information and other Support Docui , test reports, etc.)	
this application, the following information and/or test data are attached as for ISO 9001:2015 Certificate, Attachment A, Attachment B, Catalog (drawings, calculations	illows: Information and other Support Docu	
this application, the following information and/or test data are attached as for ISO 9001:2015 Certificate, Attachment A, Attachment B, Catalog (drawings, calculations) Declared before me at day of March AD 20 20	in the	ments
this application, the following information and/or test data are attached as for ISO 9001:2015 Certificate, Attachment A, Attachment B, Catalog (drawings, calculations) Declared before me at	in the	ments
this application, the following information and/or test data are attached as for ISO 9001:2015 Certificate, Attachment A, Attachment B, Catalog (drawings, calculations) Declared before me at day of AD 20 20 Commissioner for Oaths:	in the	ments
this application, the following information and/or test data are attached as for ISO 9001:2015 Certificate, Attachment A, Attachment B, Catalog (drawings, calculations) Declared before me at	Information and other Support Documents, test reports, etc.) in the	of Onvo
this application, the following information and/or test data are attached as for ISO 9001:2015 Certificate, Attachment A, Attachment B, Catalog (drawings, calculations) Declared before me at	Information and other Support Documents, test reports, etc.) in the State	of Chio
this application, the following information and/or test data are attached as for ISO 9001:2015 Certificate, Attachment A, Attachment B, Catalog (drawings, calculations) Declared before me at	Information and other Support Documents, test reports, etc.) in the	of Chio
this application, the following information and/or test data are attached as for ISO 9001:2015 Certificate, Attachment A, Attachment B, Catalog (drawings, calculations) Declared before me at	Information and other Support Documents, test reports, etc.) in the State (Signature of	of Chio
this application, the following information and/or test data are attached as for ISO 9001:2015 Certificate, Attachment A, Attachment B, Catalog (drawings, calculations) Declared before me at day of March AD 20 do Commissioner for Oaths: Breada Name (Printed name) Breada (Signature) FOR OFFICE	Information and other Support Documents (set reports, etc.) in the State (Signature of USE ONLY rements of the	of Ohio
this application, the following information and/or test data are attached as for ISO 9001:2015 Certificate, Attachment A, Attachment B, Catalog (drawings, calculations) Declared before me at day of March AD 20 do Commissioner for Oaths: Breado Mannel (Printed name) Breado Mannel (Signature) FOR OFFICE	Information and other Support Documents, test reports, etc.) in the State (Signature of USE ONLY rements of the	of Chio
this application, the following information and/or test data are attached as for ISO 9001:2015 Certificate, Attachment A, Attachment B, Catalog (drawings, calculations) Declared before me at day of AD 20 D Commissioner for Oaths: Breada (Printed name) (Signature) FOR OFFICE To the best of my knowledge and belief, the application meets the requirements of the property of the	Information and other Support Documents, test reports, etc.) in the State (Signature of USE ONLY rements of the Regulation, and Standards and Safety	of Chio
this application, the following information and/or test data are attached as for ISO 9001:2015 Certificate, Attachment A, Attachment B, Catalog (drawings, calculations) Declared before me at	Information and other Support Documents, test reports, etc.) in the State (Signature of USE ONLY rements of the Regulation, and Standards	Declarer) Boilers and Pressure Vessels Safety Program
this application, the following information and/or test data are attached as for ISO 9001:2015 Certificate, Attachment A, Attachment B, Catalog (drawings, calculations) Declared before me at	Information and other Support Document, test reports, etc.) in the State (Signature of USE ONLY rements of the Regulation, and Standards and Safety Authority This Document has been digitally signed The stamp size has CRN: DA22505.5	Declarer) Boilers and Pressure Vessels Safety Program
this application, the following information and/or test data are attached as for ISO 9001:2015 Certificate, Attachment A, Attachment B, Catalog (drawings. calculations) Declared before me at	Information and other Support Document is test reports, etc.) in the State (Signature of USE ONLY rements of the Regulation, and Standards and Safety Authority This Document has been digitally signed been digitally sig	Declarer) Boilers and Pressure Vessels Safety Program TERED



Canadian Registration Number Submittal Category A: Swagelok Brass Pipe Fittings

THIS IS PART OF CRN

0A22505.5

Technical Standards and Safety Authority

Boilers and Pressure Vessels Safety

Program

Date: March 13, 2020

Page 1 of 2

Attachment B. Scope of Registration for Swagelok Brass Pipe Fittings (Category A)

This document represents the scope of Swagelok Brass Pipe Fittings covered by this submission for CRN approval. These Swagelok Pipe Fittings have been evaluated in accordance with ASME B31.1-2018 for unlisted components and ASME B31.3-2018 for unlisted components.

Summary Table

Product Description or	Material	Port Connections and Sizes	Maximum Allowable Working Pressure		Design Code
Description or Series			Up to 100°F	At maximum temperature	of Construction
		Male NPT & Male ISO-7 (tapered) (RT) 1/16 – 2 inch	5500 - 1900 psig	718 - 248 psig @400°F	ASME B31.3
Pipe Straight Fittings Brass C36000	Female NPT & Female ISO-7 (tapered) (RT) 1/16 – 2 inch	3300 - 1900 psig	431 - 248 psig @400°F	(Unlisted Components)	
(includes pipe plugs and pipe caps)	I Bar	Male NPT & Male ISO-7 (tapered) (RT) 1/16 – 2 inch	5500 - 1900 psig	4950 - 1710 psig @200°F	ASME B31.1
		Female NPT & Female ISO-7 (tapered) (RT) 1/16 – 2 inch	3300 - 1900 psig	2970 - 1710 psig @200°F	(Unlisted Components)
/Saa tha	Brass C37700 (ASTM B283) Forging	Male NPT & Male ISO-7 (tapered) (RT) 1/8 – 1 inch	2700 - 2100 psig	352 - 274 psig @400°F	ASME B31.3 (Unlisted Components)
		Female NPT & Female ISO-7 (tapered) (RT) 1/8 – 1 inch	2700 - 2100 psig	352 - 274 psig @400°F	
		Male NPT & Male ISO-7 (tapered) (RT) Male 1/8 – 1 inch	2700 - 2100 psig	2430 - 1890 psig @200°F	ASME B31.1 (Unlisted
5,00000.)		Female NPT & Female ISO-7 (tapered) (RT) 1/8 – 1 inch	2700 - 2100 psig	2430 - 1890 psig @200°F	Components)



Canadian Registration Number Submittal Category A: Swagelok Brass Pipe Fittings

THIS IS PART OF CRN

0A22505.5

Technical Standards and Safety Authority
Boilers and Pressure Vessels Safety
Program

Date: March 13, 2020 Page 2 of 2

Product Description

Swagelok Pipe Fittings are furnished in a variety of configurations and shapes (straight, elbow, tee or cross).



Configurations

1. Nipples, Adapters, Couplings, Reducers

Male & Female NPT, Male & Female RT (ISO Taper), adapters and reducing to other sizes



2. Elbows / Street Elbows / Tees / Street Tees / Crosses

Male and Female NPT, Male & Female RT (ISO Taper), adapters and reducing to other sizes. Elbows and Tees are limited to a maximum size of one-inch in brass. Crosses are limited to a maximum size of three-quarter-inch in brass.



Caps and Plugs Male NPT, RT (ISO Taper)





Product Options:

The sealant options for tapered pipe threads (NPT and ISO-7), such as curable resin with PTFE and PTFE tape, affect pressure and/or temperature ratings shown in the above Summary Table, but the ratings with these options are less than or equal to those shown in the table.

Additional options that do not affect pressure and/or temperature ratings may be made available within the scope of this approval. Examples of these would include the following:

- 1. Special marking
- 2. Special cleaning
- 3. Wire drills
- 4. Snubbers and orifice plates

All of the options noted above are within the scope of this approval.

Quality System

The Swagelok Company quality system complies with the requirements of ISO 9001:2015. The Swagelok Company maintains BSI Certificate of Registration Number FM 01729, which applies to all locations listed on the Certificate.

References

The product catalog does not represent the full scope of the registration but rather details some of the most common options.

Pipe Fittings Catalog MS-01-147, Rev. P

THIS IS PART OF CRN 0A22505.5

Technical Standards and Safety Authority
Boilers and Pressure Vessels Safety
Program

Attachment A. Swagelok Manufacturing Locations

This document lists the Swagelok locations where end item or component level manufacturing activities take place.

Swagelok Company	Swagelok Company (Falon 1)
29500 Solon Road	348 Bishop Road
Solon, Ohio 44139	Highland Heights, Ohio 44143
USA	USA
Swagelok Company (Highland)	Swagelok Company (Falon 2)
318 Bishop Road	358 Bishop Road
Highland Heights, Ohio 44143	Highland Heights, Ohio 44143
USA	USA
Swagelok Company (OFC)	Swagelok Company (HPF)
29495 F.A. Lennon Drive	6050 Cochran Road
Solon, Ohio 44139	Solon, Ohio 44139
USA	USA
Swagelok Company (Atlantic)	Swagelok Company (Snow Metal)
26651 Curtiss Wright Parkway	6060 Cochran Road
Willoughby Hills, Ohio 44092	Solon, Ohio 44139
USA	USA
Swagelok Company (Micro) 26653 Curtiss Wright Parkway Willoughby Hills, Ohio 44092 USA	Swagelok Company (Alfred) 29500 Ambina Drive Solon, Ohio 44139
Swagelok Hose Services Company (SHSC)	Swagelok Company (Strongsville)
29900 Solon Industrial Parkway	15400 Foltz Road
Solon, Ohio 44139	Strongsville, Ohio 44119
Swagelok (China) Fluid System Technologies Ltd. Changshu Export Process Zone Changshu Economic Development Zone Changshu, Jiangshu 215513 China	Swagelok Limited Ballafletcher Road Tromode IM4 4RA Isle of Man