UNIFORM STATUTORY DECLARATION FORM FOR THE REGISTRATION OF FITTING DESIGNS NEW BRUNSWICK NOVA SCOTIA PRINCE EDWARD ISLAND NEWFOUNDLAND AND LABRADOR NUNAVUIT YUKON NORTHWEST TERRITORIES MANUFACTURERS NAME: Swagelok Company MANUFACTURERS ADDRESS: 29500 Solon Road, Solon, Ohio 44139 USA PLANT LOCATIONS: Headquarters: 29500 Selon Road, Solon, Ohio 44139 USA (See Attachment A) CATEGORY OF FITTINGS TO BE REGISTERED. CIRCLE ONE CATEGORY DALY. TITLE OF THE STANDARD OF CORE TRUSTICAL A Pipe fittings, including couplings, tees, elbows, Ys, plugs, unions, pipe caps, or reducers ASME B31.1 for B Flanges: eli flanges C Velves: all line volves unlisted components. D Expansion joints, flexible connections, and hose assemblies: an types ASME B31.3 for E Strainers, litters, separators, and steam traps F Massuring devices, including pressure gauges, level gauges, sight glasses, levels, or unlisted components pressure transmitters G Cartified capacity-rated pressure rollof devices acceptable as primary over pressure protection on bollers, pressure vessels, piping and Tusible plugs H Pressure retaining components that do not full into one of the above categories N Nuclear components: Class 1 □ Class 2 □ Class 3 □, (Meeting AECB or ASME requirements) SHOW MANUFACTURERS NAME, TRADEMARK, OR LOGO AS IT WILL APPEAR ON THE PRODUCT TYPE OF CONSTRUCTION PORGEO O WELDED D WROUGHT ME CAST I OTHER LIST OF SUPPORTING DOCUMENTATION AND IDENTIFICATION OF THE ACTUAL ITEMS TO BE REGISTERED: ISO 9001:2015 Certificate, Attachment A, Attachment B, Catalog Information and other Support Recuments DECLARATION: | Joel Feldman, Vice President, Engineering (see note 3) Omployed by Swagelok Company and being the person having full authority and responsibility for the quality of the and product do solamnly declare that the information contained in this form is true and to the best of my knowledge represents the product for which registration is sought. The dimensions, materials of construction, pressure temperature ratings, and identification markings are in accordance with the herein named standards. I further declare that the manufacture of these fittings is regulated by a Quality Control Program which extends to each plant where fabrication occurs in whole or in part and has been verified by FSI as being suitable for that purpose and I make this sciemn declaration conscientiously believing it to be true, and knowing that it is of the same force and effect as if made under oath. 611.211-E

0.0	sfore me at	C.K. TWO	v	SI	E	ТН	118	5	SF	Α (C E	F	OR	т	H
This	day of	AD				0	FF	1	GI	AL	s	£ .	AL		
	ner of Oaths ublic: (sign)														
	(Affix C	Official seal to the right)													
	This regist	This space for Ri retion must be revalidated affe				tha	date	ol	BOO NE	epter	Sir und	Nar	nd	ð	

CRN: 0C22395.5

1214

H & HK series bellows valves

Notes:

- 1. All filtings shall be registered in the name of the Manufacturer. 2. Each category shall be supported with two Statutory Declaration
- forms and one copy of supporting documentation. 3. The declaration shall be made by the person having full authority and responsibility for the quality of the end product.
- 4. Quality control programs shall be resubmitted for validation

of a recommendation of five (5) years. CRN expires May 6, 2030 - DG

Labrador

Service NL

Registered OC 223

Engineering and Inspect on Services

Registered by

UNDER THE AUTHORITY OF THE PUBLIC SAFETY ACT YND THE BOILER, PRESSURE VESSEL AND COMPRESSED GAS REGULATIONS



Canadian Registration Number Submittal #H-BELLOWS-2020

Date: February 5, 2020 Category C: Swagelok H, HK Series Bellows Valves Page 1 of 3

Attachment B: Scope of Registration for Swagelok H and HK Series **Bellows Valves (Category C)**

This document represents the scope of the Swagelok H and HK Series Bellows Valves covered by this submission for CRN approval. These H and HK Series Bellows Valves have been ITHIS IS PART OF CRN evaluated in accordance with ASME B31.1 and B31.3 for unlisted components.

Summary Table

0C22395.5 Boilers and Pressure Vessels Safety

						Program	
Main		Main		Maximum Ra	Design Code		
Product Series	Pressure Bearing Component	Pressure Bearing Material	Port Connections and Sizes	At ambient temperature	At maximum temperature	of Construction	
2H (1/8")	Body, Bonnet		Swagelok tube fitting 1/8" Female NPT 1/8" Male NPT 1/8" Female VCR fitting 1/8" Tube socket weld 1/8", 1/4" Tube butt weld 1/8", 1/4"				
4H (1/4")	Body, Bonnet	316 SS (ASTM A479)	Swagelok tube fitting 1/4" Female NPT 1/4" Male NPT 1/4" Integral male VCR fitting 1/4" Female VCR fitting 1/4" VCO gland 1/4" Tube socket weld 1/4", 3/8" Tube butt weld 1/4", 3/8"	1000 psig @ -80 to 100° F	1000 psig @ 600°F	ASME B31.1 & ASME B31.3 (Unlisted Components)	
6H-MM (6mm)	Body, Bonnet		Swagelok tube fitting 6mm				
2HK*, 2HG* (1/8")	Body, Stem Adapter	Body: Brass C36000	Swagelok tube fitting 1/8" Female NPT 1/8" Male NPT1/8"		500 psig @		
4HK*, 4HG* (1/4")	Body, Stem Adapter	(ASTM B16) Stem Adapter: H04 Phosphor	Swagelok tube fitting 1/4" Female NPT 1/4" Male NPT 1/4"	1000 psig @ -20 to 100° F	200°F 150 psi @	ASME B31.1 & ASME B31.3 (Unlisted Components)	
6HK-MM*, 6HG-MM* (6mm)	Body, Stem Adapter	Bronze C51000 (ASTM B139)	6mm Swagelok tube fitting		400°F for HG	, ,	

^{*} Includes Valves with 1 Series Air Actuators


Note: HG series valves are the HK series valve but with a copper stem tip and a copper gasket for body-to-bonnet seal.



Canadian Registration Number Submittal #H-BELLOWS-2020 Category C: Swagelok H, HK Series Bellows Valves

Product Illustration


All H and HK Series Bellows Valves have the same features as shown below.



Configurations







Hand Operated HK, HG Series


THIS IS PART OF CRN 0C22395.5

Date: February 5, 2020

Page 2 of 3

Technical Standards and Safety Authority
Boilers and Pressure Vessels Safety
Program

1 Series Air Actuator (Offered on HK Series Bellows Valve Only)



HK with Normally Closed Air Op

HK with Normally Open Air Op



Canadian Registration Number Submittal #H-BELLOWS-2020 Category C: Swagelok H, HK Series Bellows Valves

Product Options:

Additional options that do not affect pressure and/or temperature ratings may be made available within the scope of this approval. Examples of these would include the following:

- H Series Cobalt-Based Stem Tip.
- Swagelok Special Cleaning and Packaging (SC-11).
- 1 Series air actuator on HK Series Bellows Valve.

Quality System

The Swagelok Company quality system complies with the requirements of ISO 9001:2015. Swagelok Company maintains BSI Certificate of Registration Number FM 01729, which applies to all locations listed on the Certificate.

References

The product catalog does not represent the full scope of the registration but rather details some of the most common options.

H and HK Series Bellows Valve Product Catalog MS-01-36, R13

THIS IS PART OF CRN

Date: February 5, 2020

Page 3 of 3

0C22395.5

Technical Standards and Safety Authority
Boilers and Pressure Vessels Safety
Program

Attachment A. Swagelok Manufacturing Locations

This document lists the Swagelok locations where end item or component level manufacturing activities take place.

THIS IS PART OF CRN

0C22395.5

Technical Standards and Safety Authority
Boilers and Pressure Vessels Safety

		Program			
Swagelok Company 29500 Solon Road Solon, Ohio 44139 USA	Swagelok Company (Falon 1) 348 Bishop Road Highland Heights, Ohio 44143 USA				
Swagelok Company (Highland)	Swagelok Company (Falon 2)				
318 Bishop Road	358 Bishop Road				
Highland Heights, Ohio 44143	Highland Heights, Ohio 44143				
USA	USA				
Swagelok Company (OFC)	Swagelok Company (HPF)				
29495 F.A. Lennon Drive	6050 Cochran Road				
Solon, Ohio 44139	Solon, Ohio 44139				
USA	USA				
Swagelok Company (Atlantic)	Swagelok Company (Snow Metal)				
26651 Curtiss Wright Parkway	6060 Cochran Road				
Willoughby Hills, Ohio 44092	Solon, Ohio 44139				
USA	USA				
Swagelok Company (Micro) 26653 Curtiss Wright Parkway Willoughby Hills, Ohio 44092 USA	Swagelok Company (Alfred) 29500 Ambina Drive Solon, Ohio 44139				
Swagelok Hose Services Company (SHSC)	Swagelok Company (Strongsville)				
29900 Solon Industrial Parkway	15400 Foltz Road				
Solon, Ohio 44139	Strongsville, Ohio 44119				
Swagelok (China) Fluid System Technologies Ltd. Changshu Export Process Zone Changshu Economic Development Zone Changshu, Jiangshu 215513 China	Swagelok Limited Ballafletcher Road Tromode IM4 4RA Isle of Man				