

UNIFORM STATUTORY DECLARATION FORM FOR THE REGISTRATION OF FITTING DESIGNS

NEW BRUNSWICK
NUNAVUT

NOVA SCOTIA
YUKON

PRINCE EDWARD ISLAND
NORTHWEST TERRITORIES

NEWFOUNDLAND AND LABRADOR

MANUFACTURERS NAME: Swagelok Company

MANUFACTURERS ADDRESS: 29500 Solon Road, Solon, Ohio 44139 USA

PLANT LOCATIONS: Headquarters: 29500 Solon Road, Solon, Ohio 44139 USA (See Attachment A)

<p align="center">CATEGORY OF FITTINGS TO BE REGISTERED. CIRCLE ONE CATEGORY ONLY</p> <p>A Pipe fittings, including couplings, tees, elbows, Ys, plugs, unions, pipe caps, or reducers B Flanges: all flanges C Valves: all line valves <input checked="" type="radio"/> D Expansion joints, flexible connections, and hose assemblies: all types E Strainers, filters, separators, and steam traps F Measuring devices, including pressure gauges, level gauges, sight glasses, levels, or pressure transmitters G Certified capacity-rated pressure relief devices acceptable as primary over pressure protection on boilers, pressure vessels, piping and fusible plugs H Pressure retaining components that do not fall into one of the above categories N Nuclear components: Class 1 <input type="checkbox"/> Class 2 <input type="checkbox"/> Class 3 <input type="checkbox"/> (Meeting AECB or ASME requirements)</p>	<p align="center">TITLE OF THE STANDARD OF CONSTRUCTION</p> <p>Association for Rubber Products Manufacturers (ARPM) Hose Handbook</p>
--	--


<p>SHOW MANUFACTURERS NAME, TRADEMARK, OR LOGO AS IT WILL APPEAR ON THE PRODUCT</p> <p align="center">Swagelok</p>	<p align="center">TYPE OF CONSTRUCTION</p> <p>FORGED <input type="checkbox"/> WELDED <input type="checkbox"/> WROUGHT <input type="checkbox"/> CAST <input type="checkbox"/> OTHER <input checked="" type="checkbox"/> DESCRIBE OTHER: <u>PTFE Core</u></p>
---	--

LIST OF SUPPORTING DOCUMENTATION AND IDENTIFICATION OF THE ACTUAL ITEMS TO BE REGISTERED:

ISO 9001:2015 Certificate, Attachment A, Attachment B, Catalog Information and other Support Documents

DECLARATION:
 I, Joel Feldman, Vice President, Engineering (see note 3) employed by Swagelok Company and being the person having full authority and responsibility for the quality of the end product do solemnly declare that the information contained in this form is true and to the best of my knowledge represents the product for which registration is sought. The dimensions, materials of construction, pressure temperature ratings, and identification markings are in accordance with the herein named standards. I further declare that the manufacture of these fittings is regulated by a Quality Control Program which extends to each plant where fabrication occurs in whole or in part and has been verified by BSI as being suitable for that purpose and I make this solemn declaration conscientiously believing it to be true, and knowing that it is of the same force and effect as if made under oath.

Signature of Declarer: Joel C. Feldman
 Declared before me at Unable to get a notary signature THIS SPACE FOR THE
 This _____ day of August or seal due to COVID-19 situation OFFICIAL SEAL
 Commissioner of Oaths August 10, 2020
 or Notary Public (sign) _____
 (Affix Official seal to the right)

<p align="center">This space for Regulatory Authority use</p> <p align="center">This registration must be revalidated after ten (10) years from the date of issuance.</p> <p>CRN: <u>0D22655.5</u></p> <p>FID#: <u>1214</u></p> <p>BT series hose assemblies.3000psi @ -65F to 100F.2900psi @ 450F</p> <p>Notes: 1. All fittings shall be registered in the name of the Manufacturer. 2. Each category shall be supported with two Statutory Declaration forms and one copy of supporting documentation. 3. The declaration shall be made by the person having full authority and responsibility for the quality of the end product. 4. Quality control programs shall be resubmitted for validation at a maximum interval of five (5) years.</p> <p>CRN expires <u>Aug.31, 2030 - DG</u></p>	 <p align="center">Northwest Territories</p> <p align="center">REGISTERED UNDER THE AUTHORITY OF THE BOILER AND PRESSURE VESSEL ACT.</p> <p>C.R.N. <u>0D22655.5T</u></p> <p>SIGNED <u>[Signature]</u></p> <p>DATE <u>Oct 6 2020</u></p> <p align="right">8200</p>
---	--



Attachment B: Scope of Registration for Swagelok BT Series Hose Assemblies (Category D)


This document represents the scope of Swagelok BT series PTFE hose and assemblies covered by this submission for CRN approval. These products have been evaluated in accordance with the Association for Rubber Products Manufacturers (ARPM) Hose Handbook.

Summary Table

Product Series	Pressure Retaining Material	Nom. Hose Size (in)	End Connections & Sizes	Maximum Working Pressure (psig)		Design Code of Construction
				At -65 to 100°F	@ Max. Temp.	
BT Series Hose	<p>Core Smooth Bore (PTFE)</p> <p>Braid 304 SS Braid Reinforcement</p> <p>End Connections 316 SS Crimp on Collar 304 SS</p>	1/8	Tube Fitting [SL, SM] 1/8" – 2" (3mm – 50mm)	3000	2900 @450°F	Association for Rubber Products Manufacturers (ARPM) Hose Handbook
			Male & Female Pipe Threads, NPT [PM, PF] 1/8" – 1"			
			Male & Female VCR Metal Gasket Face Seal Fittings [RM, RF] 1/8" – 3/4"			
			Male & Female VCO O-Ring Face Seal Fittings [VF, VM] 1/4" - 1/2"			
			Tube Butt Welds [TB] 1/8"-1"			
			ISO/BSP Parallel Female Threads (ISO 228) [FS] 1/8" – 3/4"			
			Male & Female ISO Tapered (ISO 7) [FT] 1/4" – 1/2"			
			SAE 37° Male [AN] 1/4" – 3/8"			
			SAE 37° (JIC) Female Swivel [AS] 1/8" – 5/8"			
			Male Pipe Weld [MPW] 1/8" – 1/2"			
UN / UNF (SAE) [ST] 3/16" – 5/8"						

Configurations

All end connection inserts are crimped onto the hose using crimp collars.



Product Options:

Additional options that do not affect pressure and/or temperature ratings may be made available within the scope of this approval. Examples of these would include the following:

- Fire jacket - Woven fiberglass coated with specially compounded aerospace-grade silicone rubber
- Mat tag - Polyester tag with customer-specified text
- Lanyard tag - Stainless steel tag with customer-specified text
- Thread sealant for tapered pipe thread ends

All the above options are within the scope of this approval.

Quality System

The Swagelok Company quality system complies with the requirements of ISO 9001:2015. The Swagelok Company maintains BSI Certificate of Registration Number FM 01729, which applies to all locations listed on the Certificate.

References

The product catalog does not represent the full scope of the registration but rather details some of the most common options.

- Hose Assemblies, Bulk Hose, and End Connections Product Catalog MS-01-180

Attachment A. Swagelok Manufacturing Locations

This document lists the Swagelok locations where end item or component level manufacturing activities take place.

THIS IS PART OF CRN
0D22655.5
Technical Standards and Safety Authority
Boilers and Pressure Vessels Safety
Program

Swagelok Company 29500 Solon Road Solon, Ohio 44139 USA	Swagelok Company (Falon 1) 348 Bishop Road Highland Heights, Ohio 44143 USA
Swagelok Company (Highland) 318 Bishop Road Highland Heights, Ohio 44143 USA	Swagelok Company (Falon 2) 358 Bishop Road Highland Heights, Ohio 44143 USA
Swagelok Company (OFC) 29495 F.A. Lennon Drive Solon, Ohio 44139 USA	Swagelok Company (HPF) 6050 Cochran Road Solon, Ohio 44139 USA
Swagelok Company (Atlantic) 26651 Curtiss Wright Parkway Willoughby Hills, Ohio 44092 USA	Swagelok Company (Snow Metal) 6060 Cochran Road Solon, Ohio 44139 USA
Swagelok Company (Micro) 26653 Curtiss Wright Parkway Willoughby Hills, Ohio 44092 USA	Swagelok Company (Alfred) 29500 Ambina Drive Solon, Ohio 44139
Swagelok Hose Services Company (SHSC) 29900 Solon Industrial Parkway Solon, Ohio 44139	Swagelok Company (Strongsville) 15400 Foltz Road Strongsville, Ohio 44119
Swagelok (China) Fluid System Technologies Ltd. Changshu Export Process Zone Changshu Economic Development Zone Changshu, Jiangshu 215513 China	Swagelok Limited Ballafletcher Road Tromode IM4 4RA Isle of Man