UNIFORM STATUTORY DECLARATION FORM FOR THE REGISTRATION OF FITTING DESIGNS.

	NOVA SCOTIA YUKON	PRINCE EDWARD ISLAND NORTHWEST TERRITORIES	NEWFOUNDLAND AND LABRADOR
MANUFACTURERS NAME	Swagelok Company		
MANUFACTURERS ADDE	THE PERSON NAMED IN COLUMN TWO IS NOT THE PERSON NAMED IN COLUMN TWO IS NAMED IN C	Solon, Ohio 44139 USA	
PLANT LOCATIONS: He	adquarters: 29500 Solon !	Road, Solon, Ohio 44139 USA (See Atta	achment A)
CATEGORY OF	FITTINGS TO BE REGISTERE	D. CIRCLE ONE CATEGORY ONLY	TITLE OF THE STANDARD OF CONSTRUCTION
B Flanges: all flanges C Valves: all fine valves D Expansion Joints, flexible E Strainers, filters, separal F Measuring devices, inch pressure transmitters C Certified capacity-rated boilers, pressure vessel H Pressure retaining comp M Nuclear components: C	iding pressure gauges, level gau pressure refet devices acceptab s, piping and fuelble plugs onents that do not fall into one o less 1 Class 2 Class 3	ges, alight glasses, levels, or le as primary over pressure protection on if the above categories (Meeting AECB or ASME requirements)	Rubber Products Manufacturers (ARPM) Hose Handbook
SHOW MANUFACTURERS	NAME, TRADEMARK, OR LO	GO AS IT WILL APPEAR ON THE PRODUCT	Type OF CONSTRUCTION
0	V V		FORGED D WELDED C WROUGHT CI CAST D CTHER M DESCRIBE OTHER:
Sun	adelok		PTFE Core
0 44	adolok		
responsibility for the quality in whowledge represents temperature ratings, and it manufacture of these fitting or in part and has been we declaration conscientious. Signature of Declarer: Declared before me at	the product for which registred dentification markings are in ups is regulated by a Quality writed by BSI believing it to be true, and	mnly declare that the information contained ation is sought. The dimensions, materials accordance with the herein named standar Control Program which extends to each pla as being suitable for the knowing that it is of the same force and eff	of construction, pressure ds. if surther declare that the and where fabrication occurs in whole
This day of		notary signature on is	
		notary signature on is	
Commissioner of Coffus		notary signature or is 'TD-19 situation OFFI	
or Notary Public: (sign)	September 17, (Affix Official soul to the right	notary signature or is 'TD-19 situation OFFI	CIAL SEAL



Canadian Registration Number Submittal Category D Crimped Swagelok CT Series PTFE Hose

THIS IS PART OF CRN 0D22736.5

Technical Standards and Safety Authority

Boilers and Pressure Vessels Safety

September 1, 2020 Page 1 of 2

Attachment B: Scope of Registration for Crimped Swagelok CT Series PTFE Hose Assemblies (Category D)

This document represents the scope of the Swagelok Coreflex (CT series) hose and crimped assemblies covered by this submission for CRN approval. These products have been evaluated in accordance with the Association for Rubber Products Manufacturers (ARPM) Hose Handbook.

Summary Table

CT Maximum Pressure		ure	Pressure			
Series Hose Size	At Minimum Temp.	Room temperature (0°-100°F)	At Maximum Temp.	Retaining Material	End Connections and Sizes	Design Code of Construction
1/2"	1500 psig @ -65°F	1500 psig	1500 psig @ 450°F		Swagelok Tube Fitting [SL SM] 1/8" – 2" (3-50mm)	
3/4"	1100 psig @ -65°F	1110 psig	900 psig @ 450°F	Core Helical Convoluted PTFE	Male & Female NPT Tapered Pipe Fitting [PM PF] 1/8" – 2" Female & Male VCO O-ring Face seal Fitting [VF, VM] 1/8" - 2"	
1"	750 psig @ -65°F	750 psig	490 psig @ 450°F	Braid 304 SS Braid Reinforcement End Connections	Male & Female ISO/BSP Tapered (ISO 7) Pipe Threads [MT FT] 1/4" – 1" Male 37° JIC & Female 37° JIC with female swivel nut [AN AS] 1/4" – 2"	Association for Rubber Products Manufacturers (ARPM) Hose Handbook
1 1/2"	675 psig @ -20°F	700 psig	330 psig @340°F	316 SS Crimp on Collar 300 series SS	Tube Butt Welds [TB] 1/2" – 1" Female & Male VCR Metal Gasket Face Seal [RF, RM] 1/8" – 2" Female ISO/BSP Parallel	
2"	525 psig @ -20°F	525 psig	485 psig @340°F		Threads (ISO 228) [FS] 1/4" – 1"	



Canadian Registration Number Submittal
Category D Crimped Swagelok CT Series PTFE Hose

THIS IS PART OF CRN
0D22736.5
Technical Standards and Safety Authority
Boilers and Pressure Vessels Safety
Program


September 1, 2020 Page 2 of 2

Product Description

Swagelok's CT series hose is helical convoluted PTFE, 300 series stainless steel braided hose. All CT series hoses undergo production testing in accordance with ASTM D380 "Test Methods for Rubber Hose" (version current to hose production date).

Configurations

All end connection inserts are crimped onto the hose using crimp collars.



Product Options:

Additional options that do not affect pressure and/or temperature ratings may be made available and are within the scope of this approval. Examples of these would include, but not limited to, the following:

Cover Options

- Armor guard Interlocking, flexible 302 stainless steel.
- Fire jacket Woven fiberglass coated with specially compounded aerospace-grade silicone rubber
- Spiral guard Helical HDPE plastic

Tag and Marking Options

- Mat tag Polyester tag with customer-specified text
- Perma tag (JT only)- Polyester tag encapsulated in platinum-cured silicone with customerspecified text
- Lanyard tag Stainless steel tag with customer-specified text

End Connection Seals or Sealants Options

- VCO O-rings
- Pipe Thread ends thread sealant

Quality System

The Swagelok Company quality system complies with the requirements of ISO 9001:2015. The Swagelok Company maintains BSI Certificate of Registration Number FM 01729, which applies to all locations listed on the Certificate.

References

The product catalog does not represent the full scope of the registration but rather details some of the most common options. Hose Assemblies, Bulk Hose, and End Connections Product Catalog MS-01-180.

THIS IS PART OF CRN

0D22736.5

Technical Standards and Safety Authority
Boilers and Pressure Vessels Safety
Program

Attachment A. Swagelok Manufacturing Locations

This document lists the Swagelok locations where end item or component level manufacturing activities take place.

Swagelok Company	Swagelok Company (Falon 1)
29500 Solon Road	348 Bishop Road
Solon, Ohio 44139	Highland Heights, Ohio 44143
USA	USA
Swagelok Company (Highland)	Swagelok Company (Falon 2)
318 Bishop Road	358 Bishop Road
Highland Heights, Ohio 44143	Highland Heights, Ohio 44143
USA	USA
Swagelok Company (OFC)	Swagelok Company (HPF)
29495 F.A. Lennon Drive	6050 Cochran Road
Solon, Ohio 44139	Solon, Ohio 44139
USA	USA
Swagelok Company (Atlantic)	Swagelok Company (Snow Metal)
26651 Curtiss Wright Parkway	6060 Cochran Road
Willoughby Hills, Ohio 44092	Solon, Ohio 44139
USA	USA
Swagelok Company (Micro) 26653 Curtiss Wright Parkway Willoughby Hills, Ohio 44092 USA	Swagelok Company (Alfred) 29500 Ambina Drive Solon, Ohio 44139
Swagelok Hose Services Company (SHSC)	Swagelok Company (Strongsville)
29900 Solon Industrial Parkway	15400 Foltz Road
Solon, Ohio 44139	Strongsville, Ohio 44119
Swagelok (China) Fluid System Technologies Ltd. Changshu Export Process Zone Changshu Economic Development Zone Changshu, Jiangshu 215513 China	Swagelok Limited Ballafletcher Road Tromode IM4 4RA Isle of Man