

# Filters




## FW, F, and TF Series

- Remove system particulate contaminants
- Gas and liquid service
- 1/8 to 1/2 in. and 3 to 12 mm end connections
- Stainless steel and brass materials

## Features


### All-Welded Inline Filters (FW Series)

- All-welded construction provides reliable fluid containment.
- Inline filters are for use where space is limited.
- Filter is easily cleaned by backflushing.
- Sintered element is available in 0.5 µm nominal pore size; pleated mesh elements are available in 2, 7, and 15 µm nominal pore sizes.
- End connections include Swagelok® tube fittings, NPT, and male VCR® face seal fittings.




### Inline Filters (F Series)

- Inline filters are for use where space is limited.
- Replaceable sintered elements are available in 0.5, 2, 7, 15, 60, and 90 µm nominal pore sizes; replaceable strainer elements are available in 40, 140, 230, and 440 µm nominal pore sizes.
- End connections include Swagelok tube fittings, NPT, tube adapter, and male VCR face seal fittings.



### Tee-Type Filters (TF Series)

- Filter element can be replaced without removing body from system.
- Replaceable sintered elements are available in 0.5, 2, 7, 15, 60, and 90 µm nominal pore sizes; replaceable strainer elements are available in 40, 140, 230, and 440 µm nominal pore sizes.
- End connections include Swagelok tube fittings, NPT, and tube socket or tube butt weld ends.
- Select TF series filters are available with ECE R110-type approval for use in alternative fuel service. See **Options and Accessories**, page 8.



## Filter Elements


### FW Series

#### Sintered



- Traps particles as small as 0.5 µm in diameter
- 316L SS construction


#### Pleated Mesh



- Retainer screen
- Pleated mesh element
- Retainer screen
- Offers larger filtration area
- Stainless steel construction


### F and TF Series

#### Sintered



- Traps fine particles in a dense matrix
- 316 SS construction

#### Strainer



- Removes larger particles
- 316 SS construction

## Pressure-Temperature Ratings

Ratings are based on standard materials of construction. Ratings for TF series filters with PCTFE gaskets are limited to 200°F and 3000 psig (93°C and 206 bar). See page 8.

Filter Series	FW, TF <sup>①</sup>	2F, 4F	6F, 8F	F	TF
Material	316 SS			Brass	
Temperature, °F (°C)	Working Pressure, psig (bar)				
-20 (-28) to 100 (37)	6000 (413)	3000 (206)	2500 (172)	1000 (68.9)	2000 (137)
200 (93)	5160 (355)	2580 (177)	2150 (148)	780 (53.7)	1730 (119)
300 (148)	4660 (321)	2330 (160)	1940 (133)	680 (46.8)	1470 (101)
400 (204)	4280 (294)	2140 (147)	1780 (122)	—	—
500 (260)	3980 (274)	1990 (137)	1660 (114)	—	—
600 (315)	3760 (259)	1880 (129)	1560 (107)	—	—
650 (343)	3700 (254)	1845 (127)	1540 (106)	—	—
700 (371)	3600 (248)	1800 (124)	1500 (103)	—	—
750 (398)	3520 (242)	1760 (121)	1460 (100)	—	—
800 (426)	3460 (238)	1725 (118)	1440 (99.2)	—	—
850 (454)	3380 (232)	1690 (116)	1410 (97.1)	—	—
900 (482)	3280 (225)	1640 (112)	1360 (93.7)	—	—

① 316 SS TF series filters low temperature rating is -40 to 100°F (-40 to 37°C) with a working pressure of 6000 psig (413 bar).

## Differential Pressure Ratings

Filter Series	Maximum Differential Pressure psig (bar)		
	Sintered Element	Strainer Element	Pleated Element
FW	600 (41.3)	—	100 (6.8)
F, TF	1000 (68.9)		—

## Materials of Construction

Component	Filter Series	Filter Body Materials	
		Brass <sup>①</sup>	316 SS
Material Grade/ASTM Specification			
Bonnet nut	TF	Brass/B16	316 SS/A479
<i>Bonnet</i>	<i>TF</i>	<i>Brass/B16</i>	<i>316 SS/A479</i>
Retainer screens (2)	FW	—	316 SS
Element	FW	—	0.5 µm size— 316L SS 2, 7, and 15 µm size— 316 SS
	F, TF	Sintered—316 SS Strainer—316 SS with silver solder	
Spring	F, TF	302 SS	
Gasket	F, TF	Aluminum/B209	Silver-plated 316 SS/A240
Body	All	Brass/B16	316 SS/A479
Retaining ring	TF	PH 15-7 Mo <sup>®</sup> SS	
Lubricant	F	Silicone-based	

Wetted components listed in *italics*.

① FW series filters not available in brass.

## Filtration Area

Filter Series	Sintered Element in. <sup>2</sup> (mm <sup>2</sup> )	Strainer Element in. <sup>2</sup> (mm <sup>2</sup> )	Pleated Element in. <sup>2</sup> (mm <sup>2</sup> )
FW	0.44 (283)	—	2.25 (1450)
2F	0.55 (350)	—	—
4F, 2TF, 4TF	1.3 (830)	1.0 (640)	—
6F, 8F, 6TF, 8TF	2.0 (1280)	1.7 (1090)	—

## Flow Data at 70°F (20°C)

## FW Series

End Connections		Element Nominal Pore Size µm	Inlet Pressure, <sup>①</sup> psig (bar)			Pressure Drop, psi (bar)		
			5 (0.34)	10 (0.68)	15 (1.0)	10 (0.68)	50 (3.4)	100 (6.8)
Inlet/Outlet	Size		Air Flow, std ft <sup>3</sup> /min (std L/min)			Water Flow, U.S. gal/min (L/min)		
Swagelok tube fittings, male VCR fittings	1/4 in., 6 mm	0.5	0.04 (1.1)	0.06 (1.7)	0.12 (3.4)	0.01 (0.03)	0.04 (0.15)	0.12 (0.45)
		2, 7, 15				1.7 (6.4)	5.5 (20)	8.3 (31)
Female NPT	1/4 in.	2, 7, 15	5.6 (150)	10 (280)	14 (390)	4.5 (17)	14 (52)	18 (68)
Male NPT, male/female NPT	1/4 in.	2, 7, 15				3.5 (13)	11 (41)	14 (52)

<sup>①</sup> Outlet is discharged to atmosphere.

## F Series

Element Nominal Pore Size µm	Inlet Pressure, <sup>①</sup> psig (bar)			Pressure Drop, psi (bar)		
	5 (0.34)	10 (0.68)	15 (1.0)	10 (0.68)	50 (3.4)	100 (6.8)
	Air Flow, std ft <sup>3</sup> /min (std L/min)			Water Flow, U.S. gal/min (L/min)		
<b>2F Series</b>						
0.5	0.04 (1.1)	0.06 (1.7)	0.12 (3.4)	0.01 (0.03)	0.04 (0.15)	0.12 (0.45)
2	0.20 (5.6)	0.40 (11)	0.60 (17)	0.08 (0.30)	0.24 (0.91)	0.40 (1.5)
7	0.50 (14)	0.90 (25)	1.2 (34)	0.10 (0.37)	0.30 (1.1)	0.48 (1.8)
15	0.80 (22)	1.3 (36)	1.5 (42)	0.12 (0.45)	0.36 (1.3)	0.58 (2.1)
60	1.7 (48)	2.2 (62)	2.4 (68)	0.15 (0.56)	0.50 (1.8)	0.70 (2.6)
90	1.8 (51)	2.2 (62)	2.6 (73)	0.20 (0.75)	0.50 (1.8)	0.60 (2.2)
<b>4F Series</b>						
0.5	0.12 (3.4)	0.26 (7.3)	0.48 (13)	0.04 (0.15)	0.17 (0.64)	0.29 (1.0)
2	0.60 (17)	1.4 (39)	2.3 (65)	0.24 (0.90)	0.86 (3.2)	1.3 (4.9)
7	1.4 (39)	2.9 (82)	4.7 (130)	0.40 (1.5)	1.3 (4.9)	2.0 (7.5)
15	1.2 (34)	2.9 (82)	4.7 (130)	0.50 (1.8)	1.3 (4.9)	2.1 (7.9)
60	3.1 (87)	5.9 (160)	8.5 (240)	0.90 (3.4)	3.3 (12)	4.6 (17)
90	4.1 (110)	7.5 (210)	10 (280)	1.2 (4.5)	4.2 (15)	6.1 (23)
40, 140, 230, 440	4.7 (130)	8.8 (250)	12 (340)	1.7 (6.4)	5.6 (21)	7.8 (29)
<b>6F and 8F Series</b>						
0.5	0.36 (10)	0.86 (24)	1.6 (45)	0.09 (0.34)	0.40 (1.5)	0.76 (2.8)
2	1.4 (39)	2.8 (79)	4.0 (110)	0.26 (0.98)	1.1 (4.1)	1.6 (6.0)
7	1.8 (51)	4.2 (119)	6.8 (190)	0.64 (2.4)	2.2 (8.3)	3.5 (13)
15	1.8 (51)	4.9 (130)	7.9 (220)	0.84 (3.1)	2.6 (9.8)	4.1 (15)
60	5.1 (140)	10 (280)	15 (420)	2.0 (7.5)	6.7 (25)	10 (37)
90	6.1 (170)	11 (310)	16 (450)	2.3 (8.7)	7.6 (28)	11 (41)
40, 140, 230, 440	7.2 (200)	14 (390)	20 (560)	4.8 (18)	15 (56)	19 (71)

<sup>①</sup> Outlet is discharged to atmosphere.

## Flow Data at 70°F (20°C)

### TF Series

Element Nominal Pore Size µm	Inlet Pressure, <sup>①</sup> psig (bar)			Pressure Drop, psi (bar)		
	5 (0.34)	10 (0.68)	15 (1.0)	10 (0.68)	50 (3.4)	100 (6.8)
	Air Flow, std ft <sup>3</sup> /min (std L/min)			Water Flow, U.S. gal/min (L/min)		
<b>2TF Series</b>						
0.5	0.04 (1.1)	0.06 (1.7)	0.12 (3.4)	0.04 (0.15)	0.17 (0.64)	0.29 (1.0)
2	0.20 (5.6)	0.40 (11)	0.60 (17)	0.08 (0.30)	0.24 (0.91)	0.40 (1.5)
7	0.50 (14)	0.90 (25)	1.2 (34)	0.10 (0.37)	0.30 (1.1)	0.48 (1.8)
15	0.80 (22)	1.3 (36)	1.5 (42)	0.12 (0.45)	0.36 (1.3)	0.58 (2.1)
60	1.7 (48)	2.2 (62)	2.4 (68)	0.15 (0.56)	0.50 (1.8)	0.70 (2.6)
90	1.8 (51)	2.2 (62)	2.6 (73)	0.20 (0.75)	0.50 (1.8)	0.60 (2.2)
40, 140, 230, 440	1.8 (51)	2.3 (65)	2.6 (73)	0.20 (0.75)	0.50 (1.8)	0.60 (2.2)
<b>4TF Series</b>						
0.5	0.12 (3.4)	0.26 (7.3)	0.48 (13)	0.04 (0.15)	0.17 (0.64)	0.29 (1.0)
2	0.60 (17)	1.4 (39)	2.3 (65)	0.24 (0.90)	0.86 (3.2)	1.3 (4.9)
7	1.4 (39)	2.9 (82)	4.7 (130)	0.40 (1.5)	1.3 (4.9)	2.0 (7.5)
15	1.2 (34)	2.9 (82)	4.7 (130)	0.50 (1.8)	1.3 (4.9)	2.1 (7.9)
60	3.1 (87)	5.9 (160)	8.5 (240)	0.80 (3.0)	2.7 (10)	3.9 (14)
90	4.1 (110)	7.5 (210)	10 (280)	1.1 (4.1)	3.4 (12)	4.9 (18)
40, 140, 230, 440	4.7 (130)	8.8 (250)	12 (340)	1.2 (4.5)	4.2 (15)	5.6 (21)
<b>6TF and 8TF Series</b>						
0.5	0.36 (10)	0.86 (24)	1.6 (45)	0.09 (0.34)	0.40 (1.5)	0.76 (2.8)
2	1.4 (39)	2.8 (79)	4.0 (110)	0.26 (0.98)	1.1 (4.1)	1.6 (6.0)
7	1.8 (51)	4.2 (119)	6.8 (190)	0.64 (2.4)	2.2 (8.3)	3.5 (13)
15	1.8 (51)	4.9 (130)	7.9 (220)	0.84 (3.1)	2.6 (9.8)	4.1 (15)
60	5.1 (140)	10 (280)	15 (420)	1.5 (5.6)	4.8 (18)	6.7 (25)
90	6.1 (170)	11 (310)	16 (450)	1.7 (6.4)	5.5 (20)	7.6 (28)
40, 140, 230, 440	7.2 (200)	14 (390)	20 (560)	2.4 (9.0)	7.2 (27)	10 (37)

① Outlet is discharged to atmosphere.

### Testing

Every Swagelok filter is factory tested with nitrogen at 1000 psig (69 bar) to a requirement of no detectable leakage with a liquid leak detector.

### Cleaning and Packaging

Swagelok filters with VCR end connections are processed in accordance with Swagelok *Special Cleaning and Packaging (SC-11)* catalog, [MS-06-63](#), to ensure compliance with product cleanliness requirements stated in ASTM G93 Level C.

Swagelok filters with other end connections are processed in accordance with Swagelok *Standard Cleaning and Packaging (SC-10)* catalog, [MS-06-62](#), special cleaning and packaging are available as an option.


## Ordering Information and Dimensions

Dimensions are for reference only and are subject to change.

### FW Series

Add an element designator to the basic ordering number.

Example: SS-4FWS-05



### FW Series

End Connections		Element Nominal Pore Size μm	Basic Ordering Number	Dimensions, in. (mm)	
Inlet/Outlet	Size			Orifice	A
Swagelok tube fittings	1/4 in.	0.5	SS-4FWS-	0.187 (4.75)	2.09 (53.1)
	1/4 in.	2, 7, 15	SS-4FW-		2.15 (54.6)
	6 mm	0.5	SS-6FWS-MM-		2.13 (54.1)
	6 mm	2, 7, 15	SS-6FW-MM-		2.15 (54.6)
Female NPT	1/4 in.	2, 7, 15	SS-4FW4-	0.453 (11.5)	1.57 (39.9)
Male NPT	1/4 in.		SS-4FW2-	0.281 (7.14)	1.89 (48.0)
Male/female NPT	1/4 in.		SS-4FW5-	0.281 (7.14)	1.72 (43.7)
Male VCR fittings	1/4 in.	0.5	SS-4FWS-VCR-	0.187 (4.75)	2.00 (50.8)
	1/4 in.	2, 7, 15	SS-4FW-VCR-		2.04 (51.8)

Dimensions shown with Swagelok tube fitting nuts finger-tight.

### FW Series Elements

Elements remove 95 % of particles larger than the nominal pore size.

Nominal Pore Size μm	Pore Size Range μm	Element Type	Element Designator
0.5	0.5 to 2	Sintered	05
2	—	Pleated	2
7	—		7
15	—		15

### F Series and TF Series

#### Stainless Steel Filters

Add an element designator to the basic ordering number.

Example: SS-2F-2

#### Brass Filters

Replace **SS** with **B** in the ordering number.

Example: B-2F-2

Filters with VCR fitting end connections are not available in brass.

### F and TF Series Elements

Elements remove 95 % of particles larger than the nominal pore size.

Nominal Pore Size μm	Pore Size Range μm	Element Type	Element Designator
0.5	0.5 to 2	Sintered	05
2	1 to 4		2
7	5 to 10		7
15	11 to 25		15
40 <sup>①</sup>	—	Strainer	40
60	50 to 75	Sintered	60
90	75 to 100		90
140 <sup>①</sup>	—	Strainer	140
230 <sup>①</sup>	—		230
440 <sup>①</sup>	—		440


<sup>①</sup> Not available for 2F series.

## Ordering Information and Dimensions




### F Series

End Connections		Basic Ordering Number	Filter Series	Dimensions, in. (mm)		
Inlet/Outlet	Size			Orifice	A	B
Swagelok tube fittings	1/8 in.	SS-2F-	2F	0.094 (2.39)	2.35 (59.7)	9/16 (14.3)
	1/4 in.	SS-4F-	4F	0.187 (4.75)	2.95 (74.9)	3/4 (19.0)
	3/8 in.	SS-6F-	6F	0.281 (7.14)	3.21 (81.5)	1 (25.4)
	1/2 in.	SS-8F-	8F	0.406 (10.3)	3.49 (88.6)	
	3 mm	SS-3F-MM-	2F	0.094 (2.39)	2.38 (60.5)	9/16 (14.3)
	6 mm	SS-6F-MM-	4F	0.187 (4.75)	2.96 (75.2)	3/4 (19.0)
Female NPT	1/8 in.	SS-2F4-	2F	0.094 (2.39)	2.16 (54.9)	9/16 (14.3)
	1/4 in.	SS-4F4-	4F	0.187 (4.75)	2.87 (72.9)	3/4 (19.0)
Male NPT	1/4 in.	SS-4F2-	4F		2.69 (68.3)	
Male VCR fittings	1/4 in.	SS-4F-VCR-	4F		2.82 (71.6)	
Swagelok tube fitting/ tube adapter	1/8 in.	SS-2F-T7-	2F	0.094 (2.39)	2.29 (58.2)	9/16 (14.3)
	1/4 in.	SS-4F-T7-	4F	0.187 (4.75)	2.91 (73.9)	3/4 (19.0)

Dimensions shown with Swagelok tube fitting nuts finger-tight.



### TF Series



Bolt circle:  
1.00 (25.4) for  
2TF, 4TF;  
1.13 (28.7) for  
6TF, 8TF

End Connections		Basic Ordering Number	Filter Series	Dimensions, in. (mm)						
Type	Size			Orifice	A	B	C	D	E	F
Swagelok tube fitting	1/8 in.	SS-2TF-	2TF	0.094 (2.39)	2.27 (57.7)	1.07 (27.2)	1.00 (25.4)	0.38 (9.7)	1.87 (47.5)	1 (25.4)
	1/4 in.	SS-4TF-	4TF	0.174 (4.41)	2.47 (62.7)	1.06 (26.9)				
	3/8 in.	SS-6TF-	6TF	0.213 (5.41)	2.84 (72.1)	1.32 (33.5)	1.13 (28.7)	0.46 (11.7)	2.20 (55.9)	1 1/8 (28.6)
	1/2 in.	SS-8TF-	8TF	0.250 (6.35)	3.04 (77.2)	1.31 (33.3)				
	6 mm	SS-6TF-MM-	4TF	0.172 (4.36)	2.46 (62.5)	1.06 (26.9)	1.00 (25.4)	0.38 (9.7)	1.87 (47.5)	1 (25.4)
	8 mm	SS-8TF-MM-	6TF	0.213 (5.41)	2.84 (72.1)	1.38 (35.1)				
	10 mm	SS-10TF-MM-	8TF	0.250 (6.35)	2.86 (72.6)	1.32 (33.5)	1.13 (28.7)	0.46 (11.7)	2.20 (55.9)	1 1/8 (28.6)
12 mm	SS-12TF-MM-	8TF	3.04 (77.2)		1.31 (33.3)					
Female NPT	1/8 in.	SS-2TF4-	2TF	0.174 (4.41)	2.00 (50.8)	1.00 (25.4)	1.00 (25.4)	0.38 (9.7)	1.87 (47.5)	1 (25.4)
	1/4 in.	SS-4TF4-	4TF		2.13 (54.1)					
Male NPT	1/4 in.	SS-4TF2-	4TF	0.174 (4.41)	2.13 (54.1)	1.00 (25.4)	1.00 (25.4)	0.38 (9.7)	1.87 (47.5)	1 (25.4)
	3/8 in.	SS-6TF2-	6TF	0.250 (6.35)	2.38 (60.5)	1.25 (31.8)	1.13 (28.7)	0.46 (11.7)	2.20 (55.9)	1 1/8 (28.6)
	1/2 in.	SS-8TF2-	8TF		2.75 (69.9)					
Tube socket weld and tube butt weld	1/4 and 3/8 in.	SS-4TF-TW-	4TF	0.174 (4.41)	1.68 (42.7)	1.00 (25.4)	1.00 (25.4)	0.38 (9.7)	1.87 (47.5)	1 (25.4)

Dimensions shown with Swagelok nuts finger-tight.

① Mounting holes not available with 1/4 in. female NPT end connections.

## Options and Accessories

### All Filters

#### Special Cleaning and Packaging (SC-11)

Swagelok filters with VCR end connections are processed in accordance with Swagelok *Special Cleaning and Packaging (SC-11)* catalog, [MS-06-63](#), to ensure compliance with product cleanliness requirements stated in ASTM G93 Level C.

To order special cleaning and packaging for filters with other end connections, add **-SC11** to the valve ordering number.

Example: SS-4FWS-40-**SC11**

### F and TF Series

#### Element Kits

Kits include element and instructions.

Select a basic kit ordering number and add an element designator.

Example:  
**SS-2F-K4-05**

Filter Series <sup>①</sup>	Basic Kit Ordering Number
2F	SS-2F-K4-
4F, 2TF, 4TF	SS-4F-K4-
6F, 8F, 6TF, 8TF	SS-8F-K4-

<sup>①</sup> See **Dimensions** tables, page 7, for filter series information.

Nominal Pore Size µm	Pore Size Range µm	Element Type	Element Designator
0.5	0.5 to 2	Sintered	05
2	1 to 4		2
7	5 to 10		7
15	11 to 25	Strainer	15
40 <sup>①</sup>	—		40
60	50 to 75	Sintered	60
90	75 to 100		90
140 <sup>①</sup>	—	Strainer	140
230 <sup>①</sup>	—		230
440 <sup>①</sup>	—		440

<sup>①</sup> Not available for 2F series.

#### Gasket Kits

Kits include gasket and instructions. To order a stainless steel gasket kit, select a kit ordering number. For other gasket materials, replace **SS** with **A** for aluminum or **KF** for PCTFE (TF series only).

Example: **A-2F-K3**

Filter Series <sup>①</sup>	Kit Ordering Number
2F	SS-2F-K3
4F	SS-4F-K3
6F, 8F	SS-8F-K3
2TF, 4TF	SS-4TF-K2
6TF, 8TF	SS-8TF-K2

<sup>①</sup> See **Dimensions** tables, page 7, for filter series information.

### F Series

#### Special Alloys

Filters of alloy C-276 are available in some sizes. Contact your authorized Swagelok sales and service representative for more information.

### TF Series

#### Bypass Port

The bypass port at the filter bottom enables sampling or purging. To order, insert a designator into the filter ordering number.

Example:  
SS-2TF-**F1**-05

Filter Series	Bypass Port End Connection	Designator	Overall Height in. (mm)
2TF, 4TF	1/8 in. Swagelok tube fitting	-F1	2.36 (59.9)
	1/8 in. female NPT	-F2	2.09 (53.1)
	1/4 in. Swagelok tube fitting	-F3	2.82 (71.6)
	1/4 in. tube socket weld	-F8	2.21 (56.1)
6TF, 8TF	1/8 in. female NPT	-F4	2.46 (62.5)
	1/4 in. Swagelok tube fitting	-F5	3.14 (79.8)
	3/8 in. Swagelok tube fitting	-F6	3.20 (81.3)
	1/2 in. Swagelok tube fitting	-F7	3.42 (86.9)

#### Filters Without Elements

TF series filters can be ordered without elements. Add **LE** to the basic ordering number.

Example: SS-2TF-**LE**

#### Filters With ECE R110-Type Approval

Stainless steel TF series filters with stainless steel sintered or strainer elements are available tested with ECE R110-type approval for use in alternative fuel service.

■ Temperature rating: -40 to 248°F (-40 to 120°C)

■ Pressure rating within the range: 3770 psig (260 bar)

To order, add **-12463** to a standard TF series filter ordering number.

Example: SS-2TF-05-**12463**

### Oxygen Service Hazards

For more information about hazards and risks of oxygen-enriched systems, refer to Swagelok *Oxygen System Safety* technical report, [MS-06-13](#).

**⚠ Warning: Do not mix/interchange Swagelok products or components not governed by industrial design standards, including Swagelok tube fitting end connections, with those of other manufacturers.**



## Introduction

Since 1947, Swagelok has designed, developed, and manufactured high-quality, general-purpose and specialty fluid system products to meet the evolving needs of global industries. Our focus is on understanding our customers' needs, finding timely solutions, and adding value with our products and services.

We are pleased to provide this global edition of the book-bound *Swagelok Product Catalog*, which compiles more than 100 separate product catalogs, technical bulletins, and reference documents into one convenient, easy-to-use volume. Each product catalog is up to date at the time of printing, with its revision number shown on the last page of the individual catalog. Subsequent revisions will supersede the printed version and will be posted on the Swagelok website and in the Swagelok electronic Desktop Technical Reference (eDTR) tool.

For more information, visit your Swagelok website or contact your authorized Swagelok sales and service representative.

## Warranty Information

Swagelok products are backed by The Swagelok Limited Lifetime Warranty. For a copy, visit [swagelok.com](http://swagelok.com) or contact your authorized Swagelok representative.

### Safe Product Selection

**When selecting a product, the total system design must be considered to ensure safe, trouble-free performance. Function, material compatibility, adequate ratings, proper installation, operation, and maintenance are the responsibilities of the system designer and user.**

### WARNING

**Do not mix/interchange Swagelok products or components not governed by industrial design standards, including Swagelok tube fitting end connections, with those of other manufacturers.**

Not all trademarks listed below apply to this catalog.  
Swagelok, Cajon, Ferrule-Pak, Goop, Hinging-Colleting, IGC, Kenmac, Micro-Fit, Nupro, Snoop, Sno-Trik, SWAK, VCO, VCR, Ultra-Torr, Whitey—TM Swagelok Company  
15-7 PH—TM AK Steel Corp.  
AccuTrak, Beacon, Westlock—TM Tyco International Services  
Atlas—TM Asahi Glass Co., Ltd.  
ASCO, El-O-Matic—TM Emerson  
AutoCAD—TM Autodesk, Inc.  
CSA—TM Canadian Standards Association  
Crastin, DuPont, Kalrez, Krytox, Teflon, Viton—TM E.I. duPont Nemours and Company  
DeviceNet—TM ODVA  
Dyneon, Elgiloy, TFM—TM Dyneon  
Elgiloy—TM Elgiloy Specialty Metals  
FM—TM FM Global  
Grafoil—TM GrafTech International Holdings, Inc.  
Honeywell, MICRO SWITCH—TM Honeywell  
MAC—TM MAC Valves  
Microsoft, Windows—TM Microsoft Corp.  
NACE—TM NACE International  
PH 15-7 Mo, 17-7 PH—TM AK Steel Corp  
picofast—Hans Turck KG  
Pillar—TM Nippon Pillar Packing Company, Ltd.  
Raychem—TM Tyco Electronics Corp.  
Sandvik, SAF 2507—TM Sandvik AB  
Simriz—TM Freudenberg-NOK  
SolidWorks—TM SolidWorks Corporation  
UL—Underwriters Laboratories Inc.  
Xylan—TM Whitford Corporation  
© 2022 Swagelok Company