## UNIFORM STATUTORY DECLARATION FORM FOR THE REGISTRATION OF FITTING DESIGNS

NEW BRUNSWICK NUMANUT	NOVA SCOTIA YUKON	PRINCE EDWARD ISLAND NORTHWEST TERRITORIES	NEWFOUNDLAND AND LABRADOR
	Swagelok Company		
MANUFACTURERS ADDRESS:	COOCO SURVIT ROBU,		
PLANT LOCATIONS: Headqu	arters: 29500 Solon	Road, Solon, Ohio 44139 USA (See Att	tachment A)
SAJEGORY DE EITH	NGS TO BE REGISTERE	D. CIRCLE ONE CAYEGORY ONLY	TITLE OF THE STANDARD OF CONSTRUCTION
bollers, pressure vessets, ploi	nections, and hose essemb and steam traps pressure gauges, level gau are rollef devices acceptable no and fusible alues	elles: all types ges, sight glasses, lovels, or lo as primary over pressure protection on	ASME B31.3 for unlisted components
H Pressure retaining component			]
SHOW MANUFACTUREDS WAM	E TRADEMARY OF LO	(Meeting AECB or ASME requirements) 20 AS IT WILL, APPEAR ON THE PRODUCT	
Swa	2 2	ED AS II VIBLE AFFEAR ON THE PRODUCT	TYPE OF CONSTRUCTION FORGED D WELDER D WROUGHT M CAST D OTHER DESCRIBE OTHER
ISO 9001:2015 Certificate, An		ICATION OF THE ACTUAL ITEMS TO BE RE It B, Catalog Information and other Suppor	GISSERED: rt Documents
emperature ratings, and identifi nanufacture of these fittings is a or in part and has been verified.	ne end product do selen roduct for which registre callon markings are in a regulated by a Quality C by RSI	only declare that the Information contained ation is sought. The dimensions, materials accordance with the herein named standar control Program which extends to each old	of construction, pressure ds. I further declare that the nt where fabrication occurs in whole
Signature of Declarer:	all. table		O ATTHER OF
heclared before me et 50 hts 1844 day et 50	on, Ohio	USETHIS OFFI	SPACE NO HED
commissioner of Oatha r Notary Public: (eign) <u>Sto</u> (Al	The Official seal to the right	nel	* O
Th. 1.	This of	pace for Regulatory Authority use	A Management
i nis ref	hatration must be reven	deted after ten (10) years from the date of	gobisptange
CRN: <u>OD21780.5</u>		148	
FID#:1214		137	(F)
FL SECIES 1466E ASS Notes: 1. All fittings shall be registered in 2. Each category shall be supporte forms and one capy of supporting of 3. The doctaration shall be made to responsibility for the quality of the a 4. Quality control programs shall be at a maximum interval of five (5) ye RNERICES SEPT 15, 2	the name of the Manufach of with two Statutory Decia locumentation. by the person having full out and product. a resubmitted for validation ans.	therity and DATE 1	0/21/2019
		ON FO	CERANCH



Canadian Registration Number Submittal Category D Submission # FL-HOSE-2019

# Attachment B: Scope of Registration for Swagelok FL Series Hose Assemblies (Category D)

The table below represents the scope of Swagelok FL series hose assemblies covered by this submission for CRN approval. These hose assemblies have been evaluated in accordance with ASME B31.3:2016 Process Piping as unlisted components. The referenced port connections and product catalog(s) do not represent the full scope of the submission but rather detail some of the most common options.


#### **Summary Table**

Product Re	Pressure	Nom. Hose Size (in)	End Connections & Sizes	Maximum Working Pressure (psig)		Design Code
	Retaining Material		Life Connections & Sizes	Up to 100°F	@ Max. Temp.	Construction
Core 316L SS (EN 10088-2)  Braid 321 SS (EN 10088-3)  End Connections Strain- Hardened 316 SS, 316L SS, or 316LV SS (ASTM A479)	Standards & Safe	Authority Vescals	Tube Fitting [TA, TM, SL, SM] 1/4" – 1/2" (6mm – 10mm)  Male & Female VCR Metal Gasket Face Seal Fittings [RM, RF] 1/4" – 1/2"  SAE 37° (JIC) Female Swivel [AS] 1/4" – 3/8"	1500	840 @850°F	
	1/4	Tube Butt Welds [TB]				
		316L SS IN 10088-2)  Braid 321 SS IN 10088-3)  End connections Strain- Hardened 316 SS, 16L SS, or 316LV SS	Female VCO O-Ring Face Seal Fittings [VF] 1/4"	1500	975 @500°F	ASME B31.3
	(EN 10088-2) <b>Braid</b> 321 SS		Male & Female Pipe Threads, NPT [PM, PF] 1/4" – 1/2"  ISO/BSP Tapered (ISO 7) [MT][FT] 1/4" – 1/2"	1500	1050 @400°F	
	Connections Strain- Hardened 316 SS, 316L SS, or 316LV SS		Tube Fitting [TA, TM, SL, SM] 1/4" – 3/4" (6mm – 18mm)  Male & Female VCR Metal Gasket Face Seal Fittings [RM, RF] 1/4" – 3/4"  SAE 37° (JIC) Female Swivel [AS] 1/2" – 5/8"  Tube Butt Welds [TB] 1/2"	1200	672 @850°F	(Unlisted Components)
			Female VCO O-Ring Face Seal Fittings [VF] 1/2"	1200	780 @500°F	
			Male Pipe Threads, NPT [PM]  1/4" – 3/4"  Female Pipe Threads, NPT [PF]  3/8" – 1/2"  ISO/BSP Tapered (ISO 7) [MT][FT]  3/8" – 1/2"	1200	840 @400°F	



Canadian Registration Number Submittal Category D Submission # FL-HOSE-2019


#### **Product Illustration**




#### Configuration Example:


FL hoses are available in two sizes with many end types, end sizes, and possible overall lengths.


The corrugated tubing and braid are attached to the end connection with a Gas Tungsten Arc Weld (GTAW) cap weld process.





#### Weld Detail:







Canadian Registration Number Submittal Category D Submission # FL-HOSE-2019

#### Product Options:

Additional options and non-pressure boundary alterations that do not affect pressure ratings may be made available within the scope of this approval. Examples of these would include the following:

- Cover Options (ex. fire jacket, thermosleeve, etc.)
- Tag and Marking Options (ex. tags, lanyards, retaining clamps, etc.)
- Special Testing Options (ex. hydrostatic pressure test, inboard helium leak test, nitrogen leak test, etc.)
- Other Options (ex. traceable certificates for product).

Additional options that may affect pressure and/or temperature ratings may be made available within the scope of this approval. Examples of these would include the following:

• End Connection Seals or Sealant Options (ex. VCO O-rings, VCR gaskets, pipe thread sealant, etc.)

#### **Quality System**

The Swagelok Company quality system complies with the requirements of ISO 9001:2015. The Swagelok Company maintains BSI Certificate of Registration Number FM 01729, which applies to all locations listed on the Certificate.

#### References

The below product catalog does not represent the full scope of the registration but rather details some of the most common options.

Hose Assemblies, Bulk Hose, and End Connections Product Catalog MS-01-180, Rev. S



### Attachment A. Swagelok Manufacturing Locations

This document lists the Swagelok locations where end item or component level manufacturing activities take place.

Swagelok Company	Swagelok Company (Falon 1)		
29500 Solon Road	348 Bishop Road		
Solon, Ohio 44139	Highland Heights, Ohio 44143		
USA	USA		
Swagelok Company (Highland)	Swagelok Company (Falon 2)		
318 Bishop Road	358 Bishop Road		
Highland Heights, Ohio 44143	Highland Heights, Ohio 44143		
USA	USA		
Swagelok Company (OFC)	Swagelok Company (HPF)		
29495 F.A. Lennon Drive	6050 Cochran Road		
Solon, Ohio 44139	Solon, Ohio 44139		
USA	USA		
Swagelok Company (Atlantic)	Swagelok Company (Snow Metal)		
26651 Curtiss Wright Parkway	6060 Cochran Road		
Willoughby Hills, Ohio 44092	Solon, Ohio 44139		
USA	USA		
Swagelok Company (Micro) 26653 Curtiss Wright Parkway Willoughby Hills, Ohio 44092 USA	Swagelok Company (Alfred) 29500 Ambina Drive Solon, Ohio 44139		
Swagelok Hose Services Company (SHSC)	Swagelok Company (Strongsville)		
29900 Solon Industrial Parkway	15400 Foltz Road		
Solon, Ohio 44139	Strongsville, Ohio 44119		
Swagelok (China) Fluid System Technologies Ltd. Changshu Export Process Zone Changshu Economic Development Zone Changshu, Jiangshu 215513 China	Swagelok Limited Ballafletcher Road Tromode IM4 4RA Isle of Man		

