UNIFORM STATUTORY DECLARATION FORM FOR THE REGISTRATION OF FITTING DESIGNS

Manufacturers Name	: Swagelok Company SS: 29500 Solon Road, Solo				
Manufacturers Name	Swagelok Company SS: 29500 Solon Road, Solo				
	SS: 29500 Solon Road, Solor				
Plant Locations: Heads	underet 20500 Salen Boad S	n, Ohio 44139 USA			
Category o	of Fittings to be regis	tered. Circle one Category only	Title of the Standard of		
A Pipe fittings, including of	couplings, tees, elbows, Y	s, plugs, unions, pipe caps, or reducers	Construction		
B Flanges: all flanges			ASME P21 1 for unlisted		
D Expansion joints, flexib	le connections, and hose	assemblies; all types	ASIVE BS1.1 IOI uniisted		
E Strainers, filters, separa	ators, and steam traps	aval gaugaa aight glassaa lougla, ar waasuwa	Components		
transmitters	uding pressure gauges, i	evel gauges, signt glasses, levels, of pressure	ASIME B31.3 for unlisted		
G Certified capacity-rated boilers, pressure vesse H Pressure retaining com	pressure relief devices a s, piping and fusible plug ponents that do not fall in	cceptable as primary over pressure protection on s to one of the above categories	components		
N Nuclear components:	Class 1 Class 2 C	class 3 . (Meeting CNSC or ASME requirements)			
Show Manufacturers	Name, Trademark, or	Logo as it will appear on the product	Type of Construction		
0			Forged D Welded D Wrought		
Samme	alale		Describe other:		
Owade	sione				
List of supporting do	umontation and idea	diffection of the actual items to be register			
	comentation and iden	timcation of the actual tiens to be register			
ISO 9001:2015 C	ertificate, Attachr	nent A, Attachment B, Catalog Info	ormation and other Support		
Documents.					
Declaration: James Northolt and responsibility for the my knowledge represent ratings, and identification fittings is regulated by a verified by <u>BSL</u> believing it to be true, an Signature of Declarer: Declared before me at This day o Commissioner of Oaths Or Notary Public: (sign)	(see note 3) equality of the end product to the product for which markings are in acco Quality Ontrol Dogra d knowing that it is of SGLONI, OH f FEBRUARY Affix Official seal to t	employed by Swagelok Company a duct do solemnly declare that the information of n registration is sought. The dimensions, mate rdance with the herein named standards. I fur m which extends to each plant where fabricat is being suitable for that purpose and I make the same force and effect as if made under or application of the same force and the sa	nd being the person having full authority contained in this form is true to the best of erials of construction, pressure temperature ther declare that the manufacture of these ion occurs in whole or in part and has been his solemn declaration conscientiously th. JEFFREY C. TRUMBULL Notary Public Des for the Mole Seel Recorded In Lake County Certificate # 2020-RE-813693 My Commission Expires April 15, 2025		
	This registration m	ust be revalidated after ten (10) years from the date	of acceptance.		
CRN: 0C25329.	5		anner		
FID# 1214			SI PAL		
			D/BY / TOI		
Notes:					
2. Each Category shall be	supported with two Statutory	Declaration forms	CRN 0C25329.5Y		
and one copy of suppor	ting documentation.				
3. The Declaration shall be responsibility for the out	e made by the person having ality of the end product.	full authority and	DATE 08/23/2024		
4. Quality Control program	ns shall be resubmitted for va	lidation.			
Scope: Pressure Regulat SGBD, SHBS, SGRA, an 11/2016 (DGallant)	ors (SGRS, SGRD, SHF d SGBA Series). 15 plan	In locations,	Sect 1.0 - Hillings, Rev. 2		



1.0 <u>SCOPE</u>

The Swagelok Process Pressure Regulators (SGRS, SGRD, SHRS, SHRD, SGBS, SGBD, SHBS, SGRA, and SGBA Series) comply with the requirements of ASME B31.1-2020 "Power Piping" as an unlisted component per Section 104.7.2 and ASME B31.3-2022 "Process Piping" as an unlisted component per Section 304.7.2.

Compliance is supported by:

- Material properties and allowable stress values from ASME B31.3 Table 1A, ASME B31.3 Table 1B and industry standards.
- Design calculations consistent with the design criteria of ASME B31.3 Section 304.7.2 for minimum wall thickness and ANSI B1.1 Appendix B for thread strength.
- Burst testing to meet the Minimum Required Burst Pressure including Adjustment Factors per ASME B31.1 and ASME B31.3 under laboratory test conditions.

2.0 PRODUCT DESCRIPTION AND RATINGS

The process regulator line of products is highly configurable, as such this design file will review sections of the regulator by feature. Descriptions used in the document relate to the catalogue series and size, where the first 4 characters describe the "Series" of the regulator, and the next 2 digits describe the nominal connection "size" in 16th of an inch. The terms "series" and "size" will be used subsequently in the document.

uct s & e	rial	Maximum Rated Pressure					
od erie Siz	ate	At ambient temperatur		re	At m	maximum temperature	
Pr	Ÿ	Inlet	Outlet	Dome	Inlet	Outlet	Dome
SGRS08	316	6000psi @100°F	6000psi @100°F	N/A	1450psi @356°F	1450psi @356°F	N/A
SGRS12	316	6000psi @100°F	6000psi @100°F	N/A	1450psi @356°F	1450psi @356°F	N/A
SGRS16	316	6000psi @100°F	6000psi @100°F	N/A	1450psi @356°F	1450psi @356°F	N/A
SGRS24	316	6000psi @100°F	6000psi @100°F	N/A	1450psi @356°F	1450psi @356°F	N/A
SGBS08	316	6000psi @100°F	6000psi @100°F	N/A	1450psi @356°F	1450psi @356°F	N/A
SGBS12	316	6000psi @100°F	6000psi @100°F	N/A	1450psi @356°F	1450psi @356°F	N/A
SGBS16	316	6000psi @100°F	6000psi @100°F	N/A	1450psi @356°F	1450psi @356°F	N/A
SGBS24	316	6000psi @100°F	6000psi @100°F	N/A	1450psi @356°F	1450psi @356°F	N/A
SGRD08	316	6000psi @100°F	6000psi @100°F	6000psi @100°F	1450psi @356°F	1450psi @356°F	1450psi @356°F
SGRD12	316	6000psi @100°F	6000psi @100°F	6000psi @100°F	1450psi @356°F	1450psi @356°F	1450psi @356°F
SGRD16	316	6000psi @100°F	6000psi @100°F	6000psi @100°F	1450psi @356°F	1450psi @356°F	1450psi @356°F
SGRD24	316	6000psi @100°F	6000psi @100°F	6000psi @100°F	1450psi @356°F	1450psi @356°F	1450psi @356°F
SGRA08	316	6000psi @100°F	6000psi @100°F	250psi @100°F	1450psi @356°F	1450psi @356°F	188psi @356°F
SGRA12	316	6000psi @100°F	6000psi @100°F	250psi @100°F	1450psi @356°F	1450psi @356°F	188psi @356°F
SHRS08	316	250psi @100°F	250psi @100°F	N/A	188psi @356°F	188psi @356°F	N/A
SHRS12	316	250psi @100°F	250psi @100°F	N/A	188psi @356°F	188psi @356°F	N/A
SHRS16	316	250psi @100°F	250psi @100°F	N/A	188psi @356°F	188psi @356°F	N/A
SHRS24	316	250psi @100°F	250psi @100°F	N/A	188psi @356°F	188psi @356°F	N/A
SHRD08	316	250psi @100°F	250psi @100°F	250psi @100°F	188psi @356°F	188psi @356°F	188psi @356°F
SHRD12	316	250psi @100°F	250psi @100°F	250psi @100°F	188psi @356°F	188psi @356°F	188psi @356°F
SHRD16	316	250psi @100°F	250psi @100°F	250psi @100°F	188psi @356°F	188psi @356°F	188psi @356°F
SHRD24	316	250psi @100°F	250psi @100°F	250psi @100°F	188psi @356°F	188psi @356°F	188psi @356°F
SGBD08	316	6000psi @100°F	6000psi @100°F	6000psi @100°F	1450psi @356°F	1450psi @356°F	1450psi @356°F
SGBD12	316	6000psi @100°F	6000psi @100°F	6000psi @100°F	1450psi @356°F	1450psi @356°F	1450psi @356°F
SGBD16	316	6000psi @100°F	6000psi @100°F	6000psi @100°F	1450psi @356°F	1450psi @356°F	1450psi @356°F
SGBD24	316	6000psi @100°F	6000psi @100°F	6000psi @100°F	1450psi @356°F	1450psi @356°F	1450psi @356°F
SGBA08	316	6000psi @100°F	6000psi @100°F	250psi @100°F	1450psi @356°F	1450psi @356°F	188psi @356°F
SGBA12	316	6000psi @100°F	6000psi @100°F	250psi @100°F	1450psi @356°F	1450psi @356°F	188psi @356°F
SHBS08	316	250psi @100°F	250psi @100°F	N/A	188psi @356°F	188psi @356°F	N/A
SHBS12	316	250psi @100°F	250psi @100°F	N/A	188psi @356°F	188psi @356°F	N/A
SHBS16	316	250psi @100°F	250psi @100°F	N/A	188psi @356°F	188psi @356°F	N/A
SHBS24	316	250psi @100°F	250psi @100°F	N/A	188psi @356°F	188psi @356°F	N/A

This document and information on it are the confidential property of Swagelok Company and are loaned to you for a limited purpose. Neither may be copied, exhibited, or furnished to others in any form without the written consent of Swagelok Company.



Series "SGRS"

General service, pressure reducing, spring loaded. These units can be offered with a diaphragm or piston sensing mechanism dependent on the downstream pressure.

Series "SGRD" (sizes up to and including 24)

General service, pressure reducing, dome loaded. These units are loaded externally with pressure via the dome port.



Figure 1 SGRS & SGRD General, Pressure Reducing,

Series "SHRS"

High sensitivity, pressure reducing, spring loaded. These units are offered with a diaphragm sensing mechanism.

Series "SHRD"

High sensitivity, pressure reducing, dome loaded. These units are loaded externally with pressure via the dome port.



This document and information on it are the confidential property of Swagelok Company and are loaned to you for a limited purpose. Neither may be copied, exhibited, or furnished to others in any form without the written consent of Swagelok Company.



Series "SGBS"

General service, back pressure, spring loaded. These units can be offered with a diaphragm or piston sensing mechanism dependant on the upstream pressure.

Series "SGBD"

General service, back pressure, dome loaded. These units are loaded externally with pressure via the dome port.



Figure 3 SGBS & SGBD, General, Back pressure

Series "SHBS"

High sensitivity, back pressure, spring loaded. These units are offered with a diaphragm sensing mechanism.





Series "SGRA"

General service, pressure reducing, ratio loaded. These units are loaded externally with pressure via the dome port.

Series "SGBA"

General service, pressure reducing, ratio loaded. These units are loaded externally with pressure via the dome port.



3.0 MATERIALS

The materials of construction for pressure-containing components of the Swagelok Process Pressure Regulators (SGRS, SGRD, SGBS, SGBD, SHRS, SHBS, SHRD, SGRA, and SGBA Series) are listed in the table below. These are the only materials used for the pressure-retaining components. The table below gives the maximum allowable stress values. The source of these values is provided in the table.

			ASME		Tensile	Strength
Component	Material Type & Form	Material Standard & grade	B31.1 or ASME B31.3 code listing	Allowable Stress Source	Max Allowable Stress at 0 to 100°F	Max Allowable Stress at rated temperature
Body	Stainless Steel	ASTM		ASME B31.1		
Spring Housing	316L Annealed Bar	A479 316	listed	Table A-3 (1)	20000 psi	14872 psi
Bolt	Stainless Steel 304 carbide solution treated, and strain	ASTM A193- B8-C2	listed	ASME B31.1 Table A-10 & ASME SEC II PART D	25000 psi	25000 psi
	hardened			Table 3 (2)		

Table 1 Materials

(1) MDMT -425°F as listed in ASME B31.3 Table A1

(2) MDMT -325°F as listed in ASME B31.3 Table A2

This document and information on it are the confidential property of Swagelok Company and are loaned to you for a limited purpose. Neither may be copied, exhibited, or furnished to others in any form without the written consent of Swagelok Company.



4.0 BURST TESTING

The modularity of the Process Regulator design lends itself to a test matrix approach, ensuring that that each critical component has been tested without the need for many expensive tests. The table below shows the 6 main components of the product (as labelled in section 2), and how each planned test covers the various sizes of product.

The tests in this table account for the pressure containing components used in the smallest and largest sizes of each regulator series (SGRS, SGRD, SHRS, SHRD, SGBS, SGBD, SHBS, SGRA, and SGBA Series).

For example, burst test ordering number SGRS16 demonstrates that all size 16 bodies can withstand 413bar, and that both the size 16 & 24 spring housings & bolting can withstand 413bar as they share the same spring housings and bolts.

Burst test		Product covered						
Ordering Number	Working Pressure (WP) Rating psig (bar)	Body & Body plug	Piston & Piston plate	Spring housing	Dome	High sensitivity plates	Bolting	
SGRD08	6000 (413)	All size 08 & 12			General service size 08 & 12		General service size 08 & 12	
SGRD24	6000 (413)	All size 24			General service size 16 & 24		General service size 16 & 24	
SGRS08	6000 (413)	All size 08 & 12	General service size 08 & 12	General service size 08 & 12			General service size 08 & 12	
SGRS16	6000 (413)	All size 16	General service size 16 & 24	General service size 16 & 24			General service size 16 & 24	
SHRS08	250 (17.2)			High Sensitivity size 08, 12, 16 & 24		High Sensitivity size 08 & 12	High Sensitivity size 08 & 12	
SHRD16	250 (17.2)				High Sensitivity size 08, 12, 16 & 24	High Sensitivity size 16 & 24	High Sensitivity size 16 & 24	



4.1. TEST RESULTS

A number of burst tests were conducted to validate the above's calculations compliance to ASME B31.1 & B31.3 and documented in CTR-10821

	Working Pressure			Target Pressure Including Adjustment	
Ordering Number	(WP) Rating psig (bar)	4 x WP psig (bar)	Material Factor	Factors psig (bar)	Pass/ Fail
SGRD08	6000 (413)	24000 (1655)	1.108	26592 (1833)	Pass
SGRD24	6000 (413)	24000 (1655)	1.108	26592 (1833)	Pass
SGRS08	6000 (413)	24000 (1655)	1.118	26832 (1850)	Pass
SGRS16	6000 (413)	24000 (1655)	1.147	27528 (1898)	Pass
SHRS08	250 (17.2)	1000 (68.9)	1.118	1118 (77)	Pass
SHRD16	250 (17.2)	1000 (68.9)	1.147	1147 (79)	Pass

4.2. UNLISTED COMPONENT QUALIFICATION

The Swagelok Process Pressure Regulators (SGRS, SGRD, SHRS, SHRD, SGBS, SGBD, SHBS, SGRA, and SGBA Series) are qualified in accordance with ASME B31.1 2022 "Prover Piping" as an unlisted component per Section 104.7.2 and ASME B31.3 2022 "Process Piping" as an unlisted component per Section 304.7.2. Burst testing was conducted per ASME BPVC Code Section I, A-22 (Ref. 2.10) and ASME Code Section VIII, Division 1, UG-101. For results, see Product Test Report CTR-10821.

4.3. PRESSURE RATINGS AT RATED TEMPERATURE

Using the allowable stress values from section 3 above, a pressure rating for the valves was calculated at the temperature. In the table below, these calculated values are compared to the valve's actual pressure ratings at the temperature rating published in the product catalogue. In all cases, the valves are de-rated at temperature more than what the allowable stress values from the code require.

				At Maximum Rat	ed Temperature
Product Series	Material	Maximum working Pressure rating @ -49 to 100°F	Maximum Rated Temperature	Calculated Maximum Pressure based on Allowable Stress	Actual Maximum Working Pressure at Temperature Rating
SG	316 SS	6000psi	356°F	4680psi	1450psi
SH	316 SS	250psi	356°F	194psi	188psi



5.0 END CONNECTIONS

The NPT pipe fittings are covered by registration number OA12577.5C. The BSP end connections conform to ISO/EN 10226. The ASME flanges are covered by registration number 0A0395.3C.

Swagelok Process Regulators are supplied with a variety of end connections, including female NPT and ASME Flange connections. The geometries of these end connections are identical to the geometry qualified under separate Swagelok Fitting (Category A) CRN's.

The ratings of the end connections are accounted for in the product rating so if the end connection pressure rating is less than the regulator pressure rating, the product would be rated to the lesser value.

The following table indicates the Swagelok Fitting CRN numbers that correspond to end connections that may be used with Swagelok Process Regulators:

End Connection	CRN
316 SS Swagelok Tube Fitting	0A21025.5C
316 SS Flange Adapters	0A17712.2C

6.0 MARKING

The Swagelok Process Series Pressure Regulators (SGRS, SGRD, SHRS, SHRD, SGBS, SGBD, SHBS, SGRA, and SGBA) are marked on the exterior of the body with the following information: manufacturer's name (Swagelok), order number, and part number including material designator as noted in MSS SP-25.

7.0 CONCLUSIONS

The summary provided above supports compliance of the Swagelok Process Pressure Regulators (SGRS, SGRD, SHRS, SHRD, SGBS, SGBD, SHBS, SGRA, and SGBA Series) with the requirements of ASME B31.1-2020 "Power Piping" as an unlisted component per Section 104.7.2 and ASME B31.3-2022 "Process Piping" as an unlisted component per Section 304.7.2.

Product Engineer: G.H. Stephenson **Date:** September 16, 2024