



Technical Standards and Safety Authority  
345 Carlingview Drive  
Toronto, Ontario M9W 6N9  
www.tssa.org

Show facsimile of manufacturer's logo or trademark, as it will appear on the fitting, in the space below

Swagelok

## STATUTORY DECLARATION

### Registration of Fittings

I, Joel Feldman, Vice President of Engineering  
(Name and Position, e.g. President, Plant Manager, Chief Engineer)

of Swagelok Company  
(Name of Manufacturer)

Located at 29500 Solon Road, Solon, Ohio 44139 USA (440) 248-4600 (440) 349-5970  
(Plant Address) (Telephone No.) (Fax No.)

☒ do solemnly declare that the fittings listed hereunder, which are subject to the **Technical Standards and Safety Act**, Boilers and Pressure Vessels Regulation, comply with all of the requirements of  
ASME B31.3 for unlisted components

(Title of recognized North American Standard)

which specifies the dimensions, materials of construction, pressure/temperature ratings, identification marking the fittings and service;

☐ or are not covered by the provisions of a recognized North American standard and are therefore manufactured to comply with  
as supported by the attached data which identifies the dimensions, material of construction, pressure/temperature ratings and the basis for such ratings, the marking of the fitting for identification and service.

I further declare that the manufacture of these fittings is controlled by a quality system meeting the requirements of ISO 9001:2015  
which has been verified by the following authority, BSI

The items covered by this declaration, for which I seek registration, are category D. Hoses type fittings. In support of this application, the following information and/or test data are attached as follows:

ISO 9001:2015 Certificate, Attachment A, Attachment B, Catalog Information and other Support Documents

(drawings, calculations, test reports, etc.)

Declared before me at SOLON in the STATE of OHIO

the 31 day of JANUARY AD 2023

Commissioner for Oaths:

JEFFREY C TRUMBULL

(Printed name)

[Signature]

(Signature)



JEFFREY C. TRUMBULL  
Notary Public  
State of Ohio  
Recorded in Lake County  
Certificate # 2020-RE-813693  
My Commission Expires  
April 15, 2025

[Signature]  
(Signature of Declarer)

### FOR OFFICE USE ONLY

To the best of my knowledge and belief, the application meets the requirements of the **Technical Standards and Safety Act**, Boilers and Pressure Vessels Regulation, and CSA Standard B51 and is accepted for registration in Category "D"

CRN: \_\_\_\_\_

Registered by: \_\_\_\_\_

Dated: 2023-07-06

NOTE: This registration expires on: 2029-09-15

2023-03794

**ABSA**

SAFETY CODES ACT - PROVINCE OF ALBERTA

ACCEPTED: **0D21780.52**

See acceptance letter for conditions of registration.

Date: **7/6/2023**

By:

[Signature]

ASHLING POON, P. Eng.  
DOP: D00007936

This stamp and signature have been affixed electronically to this registered design as required by Section 20(1) of the Pressure Equipment Safety Regulation, in accordance with the Electronic Transactions Act.

\*Information provided in this application is releasable under the Freedom of Information and Privacy Protection Act and may be disclosed upon request.

PV 09553 (04/17) \*\* Scope of registration: see attachment A and B. This is a revision to 0D21780.5 for fixing a typographical error with the hose core EN standard and to also add an extra source for the bulk hose material in which ASTM standards are specified for the hose core and braid instead of the EN standard.

### 1. SCOPE

The Swagelok FL series hose assembly product complies with the requirements of ASME B31.3-2016 as an unlisted component. Compliance is supported by burst testing witnessed by an ASME Authorized Inspection Agency.

### 2. DESCRIPTION OF ADDENDUM

This addendum to CRN 0D21780.5 is to fix a typographical error with the hose core EN standard and to also add an extra source for the bulk hose material in which ASTM standards are specified for the hose core and braid instead of the EN standards.

**THIS IS PART OF CRN**

**0D21780.5ADD1**

Technical Standards and Safety Authority  
Boilers and Pressure Vessels Safety  
Program

Regarding the typographical error, the hose core material specification is currently noted as 316L per EN 10088-2, number 1.4404. The material standard that should have been referenced is 316L per EN 10028-7, number 1.4404. The analysis section remains unchanged from this correction since the chemical and mechanical properties are the same between the two EN standards for number 1.4404.

Regarding the extra source for the bulk hose material, the materials of construction for pressure-containing components of the Swagelok FL series hose assemblies are listed in the updated Table 2 below. The updated table includes the EN standards and the newly added ASTM standards, which are comparable to the EN standards. Notation numbers are designated by parentheses ().

Since the allowable stresses between the EN standards and the ASTM standards are the same (reference notations 5 with 7 and notations 6 with 8), the analysis and the allowable pressures at maximum temperature remain unchanged from the original submission.

**UPDATED Table 2 – Materials**

| Component<br>(see Figure 1)                        | Material Type, Form                 | UNS /<br>Material<br>Standard | ASME<br>B31.3<br>Code<br>listing | Tensile Strength                                  |                                          |
|----------------------------------------------------|-------------------------------------|-------------------------------|----------------------------------|---------------------------------------------------|------------------------------------------|
|                                                    |                                     |                               |                                  | Max Allowable<br>Stress (psi) @ -<br>325 to 100°F | Max Allowable<br>Stress (psi) @<br>850°F |
| End<br>Connections<br>with Integral<br>Weld Collar | 316 SS Strain-<br>Hardened Bar      | S31600<br>ASTM A479           | Not Listed<br>(1)                | 31,667<br>(1)(2)                                  | 28,567<br>(1)(2)                         |
|                                                    | 316L SS Strain-<br>Hardened Bar     | S31603<br>ASTM A479           | Not Listed<br>(1)                | 31,667<br>(1)(3)                                  | 28,567<br>(1)(3)                         |
|                                                    | 316L VAR SS Strain-<br>Hardened Bar | S31603                        | Not Listed<br>(1)                | 31,667<br>(1)(4)                                  | 28,567<br>(1)(4)                         |
| Core                                               | 316L SS, Strip                      | 1.4404 /<br>EN 10028-7        | Not Listed<br>(1)                | 16,667<br>(1)(5)                                  | 9,400<br>(1)(5)                          |
| Core                                               | 316L SS, Strip                      | S31603<br>ASTM A240           | Listed                           | 16,667<br>(7)                                     | 9,400<br>(7)                             |
| Braid                                              | 321 SS, Wire                        | 1.4541 /<br>EN 10088-3        | Not Listed<br>(1)                | 20,000<br>(1)(6)                                  | 12,400<br>(1)(6)                         |
| Braid                                              | 321 SS, Wire                        | S32100<br>ASTM A580           | Not Listed<br>(1)                | 20,000<br>(1)(8)                                  | 12,400<br>(1)(8)                         |



This stamp and signature have been affixed electronically to this registered design as required by Section 20(1) of the Pressure Equipment Safety Regulation, in accordance with the Electronic Transactions Act.

This document and information on it are the confidential property of Swagelok Company and are loaned to you for a limited purpose. Neither exhibited, or furnished to others in any form without the written consent of Swagelok Company.



## CRN Code Compliance Summary Swagelok FL Series Hoses

**THIS IS PART OF CRN**  
**0D21780.5ADD1** June 15, 2022  
Page 2 of 3  
Technical Standards and Safety Authority  
Submitter #0D21780.5ADD1  
Boilers and Pressure Vessels Safety  
Program

### Notes:

- (1) The material is an unlisted material in ASME B31.3. The allowable stresses shown in the above table are the most conservative values based on Code requirements in ASME B31.3-2016 paragraph 323.1.2 "Unlisted Materials," which allows unlisted materials be used provided they "conform to a published specification covering chemistry, physical and mechanical properties, method and process of manufacture, heat treatment, and quality control..." Paragraph 302.3.2(d) "Basis for design stresses – other materials": the lesser of one-third of the minimum tensile strength or two-thirds of the specified minimum yield strength.
- (2) 316 SS strain-hardened bar (ASTM A479) is an unlisted material in ASME B31.3. A 316 SS Grade B8M2 bolt material was selected from the ASME B&PVC, Section II, Part D, Table U as being the most similar: the minimum tensile strength of 95 ksi in this Code matches the Swagelok's proprietary material specification. The maximum allowable tensile stresses at (-20 to 100°F) and at maximum rated temperature (850°F, 85.7 ksi) were calculated based on the stress vs. temperature values listed in Table U for this selected material, using the calculation cited in above Note (1) a.  
  
S31600/ASTM A479 material that Swagelok uses has a carbon content < 0.1% and is in the cold-drawn condition after solution annealing. As such, according to ASME B31.3 Table 323.2.2, no additional impact testing is necessary at temperatures above the value in Table A-1. This low temperature rating (MDMT) of this product is -325°F. This value is the Minimum Temperature listed in Table A-1 for this material (-325°F).
- (3) The 316L SS strain-hardened bar material is an unlisted material in ASME B31.3. The material is controlled per Swagelok's proprietary material specification and possesses minimum room temperature tensile and yield strengths equivalent to the 316 SS, strain-hardened bar in the above Note (2). The values used for the 316 SS, strain-hardened bar were used for the 316L SS strain-hardened bar.
- (4) The 316L SS VAR strain-hardened bar material is an unlisted material in ASME B31.3. The material is controlled per Swagelok's proprietary material specification and possesses minimum room temperature tensile and yield strengths equivalent to the 316 SS, strain-hardened bar in the above Note (2). The values used for the 316 SS, strain-hardened bar were used for the 316L SS VAR strain-hardened bar.
- (5) The 316L SS strip material per EN 10028-7 grade 1.4404 is an unlisted material in ASME B31.3. The EN 10028-7 grade 1.4404 material has a similar chemistry composition to ASTM A240's S31603 316L material, but there are some chemistry differences which push it out of specification regarding Silicon and Chromium. The 316L physical properties fall within ASTM A240 and A479 limits. Even though these differences exist, these are the best matches for this material within the ASME B31.3 and ASME BPVC. Furthermore, compared to the strength at elevated temperatures listed within EN 10028-7, the ASME codes are more conservative. Based on this, an ASME SA-240 specification, plate product form, 316L SS, S31603 material was selected for the stresses within the ASME B&PVC, Section II, Part D (min. tensile of 70ksi from Table U and min. yield of 25ksi from Table Y-1, both at room temperature)..
- (6) The 321 SS wire material per EN 10088-3 grade 1.4541 is an unlisted material in ASME B31.3. The chemistry for the material is similar to ASTM A320 321 SS, S32100. The condition of the wire is annealed, and the ASTM A320 321 SS, S32100 material condition is solution treated. The room temperature mechanical properties of ASTM A320 321 SS, S32100 based from ASME BPVC are more conservative than the mechanical properties specified through Swagelok's proprietary material specification for this material. Based on this, an ASME SA-320 specification, B8T/B8TA grades, 321 SS, S32100 material was selected with class 1/1A as the more conservative class for the stresses within the ASME B&PVC, Section II, Part D (min. tensile of 75ksi from Table U and min. yield of 30ksi from Table Y-1, both at room temperature).

- 
- (7) The core is made from strip stock using ASTM A240 316L SS, S31603 material, which is listed in ASME B31.3. The allowable stresses are based on ASME B31.3, Table A-1, for 316L ASTM A240 S31603 material for plates and sheets. No assembly-level witness testing occurred for this core material since, per note (5), the ASTM A240 316L SS, S31603 material is comparable to the EN 10028-7 grade, which was tested.
- (8) The wire is annealed and meets ASTM A580 321 SS, S32100 material, which is an unlisted material in ASME B31.3. The ASTM A320 321 SS, S32100 material has similar chemistry and mechanical properties to the ASTM A580, B8T/B8TA grades, 321 SS, S32100 material, which is solution treated. Based on this, an ASME SA-320 specification, B8T/B8TA grades, 321 SS, S32100 material was selected with class 1/1A as the more conservative class for the stresses within the ASME B&PVC, Section II, Part D (min. tensile of 75ksi from Table U and min. yield of 30ksi from Table Y-1, both at room temperature). No assembly-level witness testing occurred with this wire material since, per this note and note (6), ASTM A580 321 SS, S32100 is similar to ASTM A320 321 SS, S32100, which is comparable to EN 10088-3 grade 1.4541, which was tested.

Product Engineer: Ben Chan  
Date: April 18, 2023

**THIS IS PART OF CRN**  
**0D21780.5ADD1**  
Technical Standards and Safety Authority  
Boilers and Pressure Vessels Safety  
Program