

Compact, High-Flow Gas Regulators



HF Series

- Precise pressure control
- Tamper-free design
- High-purity design
- Preset and adjustable dome-loaded models

Features

- Compact, high-flow design
 - Less than half the size of conventional diaphragm pressure regulators
 - Flows up to 300 std L/min
- Innovative gas-actuated pressure-sensing assembly
 - Low supply-pressure effect ensures precise pressure control
 - Low droop eliminates the need for adjustment in many systems
 - Outlet tolerates maximum rated inlet pressure without damage
- Self-centering poppet
 - Minimizes outlet pressure creep
- Tamper-free design
 - Reduces potential of improper adjustment
 - Simplifies installation

Models

Preset Pressure Regulators

Preset pressure models are factory-charged with an inert gas mix to deliver 10, 20, 30, 50, or 80 psig (0.68, 1.3, 2.0, 3.4, or 5.5 bar) outlet pressures.



**Cylinder Model
(HFS4A Model)**

**Inline
Point-of-Use Model
(HFS4B Model)**



**Compact Inline
Point-of-Use Model
(HFS3B Model)**



- High-purity design
 - Tied poppet for clean operation and positive shutoff
 - All-welded design—no seals to atmosphere
 - 5 $\mu\text{in.}$ R_a electropolished finish
 - 316L VIM-VAR stainless steel body
- Choice of end connection/mounting styles
 - 1/4 in. VCR® split-nut connections
 - 1/4 and 3/8 in. butt weld connections
 - IGC™ II surface-mount

Swagelok® HF series gas pressure regulators use a gas-actuated pressure-sensing assembly to precisely control outlet pressure. A slight decrease or increase in the outlet pressure causes the pressure-sensing assembly to expand or contract, respectively. The expansion or contraction of the pressure-sensing assembly moves the poppet to provide precise pressure control.

Dome-Loaded Pressure Regulators

Dome-loaded regulators may be adjusted during operation using a pilot regulator or can be factory-charged to deliver 10, 20, 30, or 50 psig (0.68, 1.3, 2.0, or 3.4 bar) outlet pressures.

Point-of-Use Models (HFD3B and MSM-HFD3B Models)

**HFD3B Model
VCR split-nut option**



**MSM-HFD3B Model
IGC II modular surface-mount**



Regulator Calibration

Preset pressure regulators are calibrated with filtered nitrogen at 1 std L/min flow rate.

- For outlet pressures up to 85 psig (5.8 bar), the inlet pressure is calibrated at 100 psig (6.8 bar).
- For outlet pressures greater than 85 psig (5.8 bar), the inlet pressure is calibrated at 160 psig (11 bar).

Technical Data

Model Number	Pressure Rating psig (bar)		Temperature Rating °F (°C)		Supply-Pressure Effect (SPE)	Flow Coefficient (C _v)	Flow Capacity std L/min	Orifice Size in. (mm)	Internal Volume with 1/4 in. Butt Weld Ends in. ³ (cm ³)	Preset Outlet Pressure psig (bar)
	Max Inlet (P ₁)	Outlet (P ₂) Range	Operating	Bakeout ^①						
HFS4A	3000 (206) ^②	5 to 150 (0.35 to 10.3)	-10 to 150 (-23 to 65)	302 (150)	0.4	0.1	200	0.090 (2.3)	0.97 (15.9)	80 (5.5)
HFS4B					0.9		300			
HFS3B	1000 (68.9)				1.3	200	0.120 (3.0)	0.40 (6.6)	10 (0.68) 20 (1.3) 30 (2.0) 50 (3.4)	
Adjustable Dome-Loaded										
HFD3B	1000 (68.9)	5 to 150 (0.35 to 10.3)	-10 to 150 (-23 to 65)	302 (150)	1.6	0.2	200	0.120 (3.0)	0.28 (4.7)	10 (0.68) 20 (1.3) 30 (2.0) 50 (3.4)
MSM-HFD3B									0.24 (3.9)	

① Contact your authorized Swagelok sales and service representative for more information.

② Operating ranges for 10 and 20 psig (0.68 and 1.3 bar) preset HFS4B models are limited to 1000 and 2000 psig (70 and 137 bar) inlet pressure, respectively, due to the calibration method specified on page 2. To increase the operating range, a special calibration is available.

Process Specifications


Refer to Swagelok *Ultrahigh-Purity Process Specification (SC-01)* catalog, [MS-06-61](#), for details on processes, process controls, and process verification.

Cleaning	Assembly and Packaging	Wetted Surface Roughness (R _a)	Testing
Ultrahigh-purity cleaning with a continuously monitored, deionized water, ultrasonic cleaning system	Performed in Class 100 work areas; regulators are individually bagged and vacuum sealed in cleanroom bags	5 μin. (0.13 μm) average, machine finished and electropolished	Inboard helium leak tested to a rate of 1 × 10 ⁻⁹ std cm ³ /s

Materials of Construction


Wetted Component	Material / Specification
1 Body (inlet, outlet)	316L SS VIM-VAR / SEMI F20 Ultrahigh-Purity ^①
2 Support housing	
3 Face plate	
4 Diaphragm	Alloy 625 / AMS 5879
5 Fill screw	316L SS / ASTM A479
6 Fill screw gasket	Nickel 200 / ASTM B160
7 Stem	316L SS / ASTM A479
8 Poppet-retaining wafer	Alloy X-750 / ASTM B637
9 Poppet	PCTFE
10 Poppet port seal (not shown)	Nickel 200 / ASTM B160

① 20 % minimum elongation allowed.




Flow Data


HFS4A Model



HFS4B Model



HFS3B, HFD3B, MSM-HFD3B Models



Calculating Outlet Pressures for Other Inlet Pressures

A change in inlet pressure will have an inverse effect on the outlet pressure. The adjusted outlet pressure is a function of the supply-pressure effect (SPE) and can be calculated by the equation:

$$p_4 = p_3 + [(p_1 - p_2)/100] \times \text{SPE}$$

where:


- p_4 = adjusted outlet pressure
- p_3 = initial outlet pressure
- p_1 = initial inlet pressure
- p_2 = new inlet pressure

Dimensions


Dimensions, in inches (millimeters), are for reference only and are subject to change.

Preset Pressure Regulators

HFS4A and HFS4B Models




HFS3B Model




Dome-Loaded Pressure Regulators

HFD3B Model




MSM-HFD3B Surface-Mount Model



Ordering Information

Create a regulator ordering number by adding the designators as shown below.



Swagelok VCR Split-Nut Assemblies

Swagelok VCR split-nut technology offers:

- Flexibility of inventory
- Shorter end-to-end dimensions
- Rotatable, nonwelded S17400 end connections.

When ordering a regulator with VCR end connections, VCR split-nut assemblies must be ordered separately.

VCR split-nut assemblies are field assembled. To order, select the ordering number for the male or female assemblies.

Male split-nut assembly
 ordering number:
SS-4-VCR-4-SN

Female split-nut assembly
 ordering number:
SS-4-VCR-1-SN



⚠ WARNING
 Do not mix/interchange Swagelok products or components not governed by industrial design standards, including Swagelok tube fitting end connections, with those of other manufacturers.

Introduction

Since 1947, Swagelok has designed, developed, and manufactured high-quality, general-purpose and specialty fluid system products to meet the evolving needs of global industries. Our focus is on understanding our customers' needs, finding timely solutions, and adding value with our products and services.

We are pleased to provide this global edition of the book-bound *Swagelok Product Catalog*, which compiles more than 100 separate product catalogs, technical bulletins, and reference documents into one convenient, easy-to-use volume. Each product catalog is up to date at the time of printing, with its revision number shown on the last page of the individual catalog. Subsequent revisions will supersede the printed version and will be posted on the Swagelok website and in the Swagelok electronic Desktop Technical Reference (eDTR) tool.

For more information, visit your Swagelok website or contact your authorized Swagelok sales and service representative.

Warranty Information

Swagelok products are backed by The Swagelok Limited Life-time Warranty. For a copy, visit swagelok.com or contact your authorized Swagelok representative.

Safe Product Selection

When selecting a product, the total system design must be considered to ensure safe, trouble-free performance. Function, material compatibility, adequate ratings, proper installation, operation, and maintenance are the responsibilities of the system designer and user.

WARNING

Do not mix/interchange Swagelok products or components not governed by industrial design standards, including Swagelok tube fitting end connections, with those of other manufacturers.

Not all trademarks listed below apply to this catalog.
Swagelok, Cajon, Ferrule-Pak, Goop, Hinging-Colleting, IGC, Kenmac, Micro-Fit, Nupro, Snoop, Sno-Trik, SWAK, VCO, VCR, Ultra-Torr, Whitey—TM Swagelok Company
15-7 PH—TM AK Steel Corp.
AccuTrak, Beacon, Westlock—TM Tyco International Services
Atlas—TM Asahi Glass Co., Ltd.
Alleima—TM Alleima
ASCO, El-O-Matic—TM Emerson
AutoCAD—TM Autodesk, Inc.
CSA—TM Canadian Standards Association
Crastin, DuPont, Kalrez, Krytox, Teflon, Viton—TM E.I. duPont
Nemours and Company
DeviceNet—TM ODVA
Dyneon, Elgiloy, TFM—TM Dyneon
Elgiloy—TM Elgiloy Specialty Metals
Festo—TM Festo SE & Co. KG
FM—TM FM Global
Grafoil—TM GrafTech International Holdings, Inc.
Honeywell, MICRO SWITCH—TM Honeywell
MAC—TM MAC Valves
Microsoft, Windows—TM Microsoft Corp.
NACE—TM NACE International
PH 15-7 Mo, 17-7 PH—TM AK Steel Corp
picofast—Hans Turck KG
Pillar—TM Nippon Pillar Packing Company, Ltd.
Raychem—TM Tyco Electronics Corp.
Sandvik, SAF 2507—TM Sandvik AB
Simriz—TM Freudenberg-NOK
SolidWorks—TM SolidWorks Corporation
UL—Underwriters Laboratories Inc.
Xylan—TM Whitford Corporation
© 2022 Swagelok Company