



OPERATING CHARACTERISTICS

Valve Stem Position vs. Applied Control Signal

2-Way Ball Valves




4-Way Ball Valves



Swagelok®

141 Series Type ACN Electric Ball
Valve Actuators

USER'S MANUAL



THIS MANUAL COVERS THE FOLLOWING MODEL:


MS-141ACNO

FOR USE ON 2-WAY AND 4-WAY BALL VALVES

NOTE: Please read this user's manual completely and carefully before installing or operating related Swagelok electric ball valve actuators.

CONSTRUCTION INFORMATION

Exploded View of the 141 Series Type ACN Actuator



141AC Series

CONSTRUCTION INFORMATION

Parts List and Materials of Construction

Item	Qty	Description	Material
1	1	Base	Die Cast Aluminum
2	1	Bushing	Nylon
3	1	Shaft Seal	Buna-N
4	1	Washer	Stainless Steel
5	1	Retaining Ring	Steel
6	1	Specification Label	Polyester
7	1	Assembled PC Board	
8	4	Motor Standoffs	Nickel Plated Brass
9	1	AC Garmotor	Stainless Steel Shaft
10	1	Connector Body	Nylon
11	2	Terminals	Tin Plated Copper
12	1	Dual Cam	Nylon
13	1	Spring Pin	Stainless Steel
14	1	Roll Pin	Stainless Steel
15	4	Mounting Screws	Cadmium Plated Steel
16	1	Cover	Die Cast Aluminum
17	1	Cover Seal	Buna-N
18	1	Wiring Label	Polyester
19	1	Schematic Label	Polyester
20	4	Cover Screws	Stainless Steel
	1	User's Manual	

User Wiring and Internal Circuit

