ASSEMBLY INSTRUCTIONS PEEK

1. This kit is used to assemble a transmitter to a manifold.

2. Install flange seals in grooves of manifold flange. Maximum rating is $600^{\circ}F$ (315°C).

3. Position mounting flange end of transmitter against flange end of manifold, aligning bolt holes. Install cap screws. Torque to 300 in-lbs. (25 ft.-lbs.).

ASSEMBLY INSTRUCTIONS Reinforced and Virgin TFE

1. This kit is used to assemble a transmitter to a manifold.

2. Install flange seals in grooves of manifold flange. Maximum rating is 250°F (121°C).

3. Position mounting flange end of transmitter against flange end of manifold, aligning bolt holes. Install cap screws. Torque to 300 in-lbs. (25 ft.-lbs.).

ASSEMBLY INSTRUCTIONS Viton A

 This kit is used to assemble a transmitter to a manifold.
Apply a thin film of lube to each O-Ring.

 Apply a finite information of tobe to each O-Ring.
Install O-Rings in grooves of manifold flange. Maximum rating is 450°F (232°C).
Position mounting flange end of transmitter against flange end of manifold, aligning bolt holes. Install cap screws. Torque to 300 in-lbs. (25 ft.-lbs.).

nuuo

www.swagelok.com These instructions are also available in French, Italian, German and Spanish.

> MS-INS-M3K-1 CP Revision C Printed in U.S.A. ©1991-1992 Swagelok Co., all rights reserved