

Product Test Report

Swagelok Company 29500 Solon Road Solon, Ohio 44139 U.S.A. PTR-3560 Ver 03 November 2022 Page 1 of 3

TITLE

Hydrostatic Pressure Test of Tungum® Tubing with Stainless Steel Swagelok® Tube Fittings

PRODUCT TESTED

Samples Tested	Tungum Tubing Size OD × Wall in.	Tubing Hardness 15-T	Part Description Ordering Number	Form
			Male Connector SS-400-1-4	Bar stock
24	1/4 × 0.065	81	Union Elbow SS-400-9	Forging
			Plug SS-400-P	Bar stock
			Male Connector SS-600-1-4	Bar stock
24	3/8 × 0.065	82	Union Elbow SS-600-9	Forging
			Plug SS-600-P	Bar stock
24	1/2 × 0.083	83	Male Connector SS-810-1-4	Bar stock
			Union Elbow SS-810-9	Forging
			Plug SS-810-P	Bar stock
	3/4 × 0.109		Male Connector SS-1210-1-8	Bar stock
24		84	Union Elbow SS-1210-9	Forging
			Plug SS-1210-P	Bar stock
24		84	Male Connector SS-1610-1-8	Bar stock
	1 × 0.120		Union Elbow SS-1610-9	Forging
			Plug SS-1610-P	Bar stock



Product Test Report

Swagelok Company 29500 Solon Road Solon, Ohio 44139 U.S.A. PTR-3560 Ver 03 November 2022 Page 2 of 3

PURPOSE

These assemblies were tested under laboratory conditions to observe the tube grip performance of stainless steel Swagelok tube fittings when installed on heavy-wall, Tungum tubing with hydrostatic pressure.

TEST CONDITIONS

Original test date: January 2014

- Each sample tested consisted of one tube length and two test fittings. The fittings were assembled according to Swagelok tube fitting installation instructions.
- Testing was conducted at room temperature in a laboratory environment.

TEST METHOD

Hardness Measurements of Tubing:

- 1. Performed five hardness measurements equally spaced apart on each tube OD using the 15-T scale with the 1/16-inch diameter ball penetrator.
- 2. Reported the average of the five measurements.
- 3. Added the tubing cylindrical values taken from the Wilson Chart #53 Cylindrical Conversion Table.

Hydrostatic Pressure Test:

- 1. Each sample was attached to a hydraulic test stand.
- 2. The tubing was restricted from burst by clamping blocks, thereby forcing a failure at the fittingto-tubing engagement.
- Pressure was gradually increased and the pressure was recorded when loss of tube grip, material rupture or leakage that prevented applying higher pressure occurred, whichever came first.
- 4. Results were compared to the tubing working pressure.

TES	ST	RE	SU	LT	S	

Samples Tested	Tungum Tubing Size OD × Wall in.	Working Pressure (WP) psig (bar)	4 × Working Pressure psig (bar)	Samples Attaining 4 × WP
24	1/4 × 0.065	10 200 (702)	40 800 (2811)	24 / 24
24	3/8 × 0.065	6500 (447)	26 000 (1791)	24 / 24
24	1/2 × 0.083	6700 (461)	26 800 (1846)	24 / 24
24	3/4 × 0.109	5800 (399)	23 200 (1598)	24 / 24
24	1 × 0.120	4700 (323)	18 800 (1295)	24 / 24



Product Test Report

	PTR-3560
Swagelok Company	Ver 03
29500 Solon Road	November 2022
Solon, Ohio 44139 U.S.A.	Page 3 of 3

The tests were conducted beyond the product's recommended operating parameters and do not modify the published product ratings.

These tests were performed to consider a specific set of conditions and should not be considered valid outside those conditions. Swagelok Company makes no representation or warranties regarding these selected conditions or the results attained. Laboratory tests cannot duplicate the variety of actual operating conditions. See the product catalog for technical data.

SAFE PRODUCT SELECTION

When selecting a product, the total system design must be considered to ensure safe, trouble-free performance. Function, material compatibility, adequate ratings, proper installation, operation, and maintenance are the responsibilities of the system designer and user.

REFERENCES

Wilson Cylindrical Correction Chart # 53, Wilson Instrument Division, 929 Connecticut Avenue, Bridgeport, CT 06602

Swagelok—TM Swagelok Company Tungum—TM Tungum LTD