

Statutory Declaration Registration of Fittings

(a) Design Qualification

I¹ Joel Feldman
Vice President, Engineering
(Position eg, president, plant manager, chief eng.)

Of Swagelok Company
(name of company)

Located at Headquarters: 29500 Solon Road, Solon, Ohio 44139 USA (See Attachment A)
(plant address)

do solemnly declare that the fittings listed hereunder, which are subject to the Boilers & Pressure Vessels Act:

- comply with all the requirements of the ANSI/ASME codes as to their dimensions, material, identification & service for which are required:
 Or
 are not covered by the provisions of the ANSI/ASME codes, and are therefore constructed to comply with ARPM Hose Handbook code and standard, and are designed to the best current engineering practice, as shown by the supporting test data.

(b) Quality control of Manufacture

I further declare the manufacture of these fittings is controlled by a quality control program which complies with the requirements of ISO 9001:2015, and has been verified by the following authority or authorized agency BSI

The fittings² covered by this declaration, for which I seek registration, are Category D. Hose

In support of the application, the following information, calculations and/or test data are attached:
ISO 9001:2015 Certificate, Attachment A, Attachment B, Catalog Information and other Support Documents

Declared before me at _____

In the of _____ of _____

The Unable to get a notary signature or seal due to COVID-19 situation Day of _____ AD 2020

- September 17, 2020
A (commissioner for notary)



Signature of Declarer³

For Official Use Only	
The application is accepted for registration in Category _____ in accordance with the Boilers and Pressure Vessels Act and CSA Standard B51.	
This registration must be revalidated after ten (10) years from the date of acceptance.	
Registered Number CRN _____	For the Chief Inspector Date _____



- 1 Three completed copied of Statutory Declaration form together with three copies of Catalogs, drawings and test data relating above fittings shall be submitted.
- 2 All fittings are required to be registered in the name of the Manufacturer.
- 3 This form shall be completed and signed by the president of highest official in the manufacturing plan where the fitting is produced.




Attachment B: Scope of Registration for Crimped Swagelok ST series PTFE Hose Assemblies (Category D)

This document represents the scope of the Swagelok Coreflex ST series hose and crimped assemblies covered by this submission for CRN approval. These products have been evaluated in accordance with the Association for Rubber Products Manufacturers (ARPM) Hose Handbook.

Summary Table

ST series Hose Size	Maximum Pressure (psig)			Pressure Retaining Material	End Connections and Sizes	Design Code of Construction
	At Minimum Temp. (-65°F)	Room temperature (0°-100°F)	At Maximum Temp. (400°F)			
1/8"	3000	3000	2550	Core Smooth Bore PTFE Braid Synthetic Fiber Braid & 304 SS Braid Reinforcement Cover Silicone cover End Connections 316 SS Crimp on Collar 300 series SS	Swagelok Tube Fitting [SL SM] 1/8" – 2" (3 – 50mm)	Association for Rubber Products Manufacturers (ARPM) Hose Handbook
1/4"	3500	3500	3250		Male & Female NPT Tapered Pipe Fitting [PM, PF] 1/8" – 2"	
3/8"	3000	3000	2350		Male & Female ISO/BSP Tapered (ISO 7) Pipe Threads [MT, FT] 1/4" – 1" Male 37° JIC & Female 37° JIC with female swivel nut [AN, AS] 1/4" – 2"	
1/2"	1800	1800	1800		Tube Butt Welds [TB] 1/2" – 1" Male & Female VCO O-ring Face seal Fitting [VF, VM] 1/8" - 2"	
3/4"	1250	1250	1250		Male & Female VCR Metal Gasket Face seal Fitting [RF, RM] 1/8"- 2" Female ISO/BSP Parallel Threads (ISO 228) [FS] 1/4" – 1"	
1"	1000	1000	1000			




Product Description

The Swagelok ST series hose is a virgin PTFE-lined hose with a fiber braid reinforcement and 304 stainless steel reinforcement with silicone cover. The exceptions are the 1/8-inch nominal size hose does not have the fiber braid and the 1 inch nominal size is constructed with two stainless steel braids and no fiber braid. All ST series hoses undergo production testing in accordance with ASTM D380 "Test Methods for Rubber Hose" (version current to hose production date).

Configurations

All end connection inserts are crimped onto the hose using crimp collars.



Product Options:

Additional options that do not affect pressure and/or temperature ratings may be made available and are within the scope of this approval. Examples of these would include, but not limited to, the following:

Cover Options

- Armor guard - Interlocking, flexible 302 stainless steel.
- Fire jacket - Woven fiberglass coated with specially compounded aerospace-grade silicone rubber
- Spiral guard - Helical HDPE plastic

Tag and Marking Options

- Mat tag - Polyester tag with customer-specified text
- Lanyard tag - Stainless steel tag with customer-specified text

End Connection Seals or Sealants Options

- VCO – O-rings
- Pipe Thread ends – thread sealant

Quality System

The Swagelok Company quality system complies with the requirements of ISO 9001:2015. The Swagelok Company maintains BSI Certificate of Registration Number FM 01729, which applies to all locations listed on the Certificate.

References

The product catalog does not represent the full scope of the registration but rather details some of the most common options. Hose Assemblies, Bulk Hose, and End Connections Product Catalog MS-01-180.

Attachment A. Swagelok Manufacturing Locations

This document lists the Swagelok locations where end item or component level manufacturing activities take place.

Swagelok Company 29500 Solon Road Solon, Ohio 44139 USA	Swagelok Company (Falon 1) 348 Bishop Road Highland Heights, Ohio 44143 USA
Swagelok Company (Highland) 318 Bishop Road Highland Heights, Ohio 44143 USA	Swagelok Company (Falon 2) 358 Bishop Road Highland Heights, Ohio 44143 USA
Swagelok Company (OFC) 29495 F.A. Lennon Drive Solon, Ohio 44139 USA	Swagelok Company (HPF) 6050 Cochran Road Solon, Ohio 44139 USA
Swagelok Company (Atlantic) 26651 Curtiss Wright Parkway Willoughby Hills, Ohio 44092 USA	Swagelok Company (Snow Metal) 6060 Cochran Road Solon, Ohio 44139 USA
Swagelok Company (Micro) 26653 Curtiss Wright Parkway Willoughby Hills, Ohio 44092 USA	Swagelok Company (Alfred) 29500 Ambina Drive Solon, Ohio 44139
Swagelok Hose Services Company (SHSC) 29900 Solon Industrial Parkway Solon, Ohio 44139	Swagelok Company (Strongsville) 15400 Foltz Road Strongsville, Ohio 44119
Swagelok (China) Fluid System Technologies Ltd. Changshu Export Process Zone Changshu Economic Development Zone Changshu, Jiangshu 215513 China	Swagelok Limited Ballafletcher Road Tromode IM4 4RA Isle of Man

