

An Installer's  
Pocket Guide  
for Swagelok®

# Tube Fittings



Swagelok®



# Table of Contents

Intermix/Interchange.....10

Metric Swagelok Tube Fittings .....10

## Installation Instructions

- Safety Precautions.....11
- Up to 1 in./25 mm Swagelok Tube Fittings .....12
- Over 1 in./25 mm Swagelok Tube Fittings .....13
- Gaugeability.....13
- Reassembly .....14
- O-Seal Male Connectors.....15
- Caps and Plugs .....15
- Pipe Thread Fittings.....15
- Port Connectors .....16
- Positionable Elbows and Tees .....18
- Tube Adapters .....19
- Weld Fittings .....20
- Depth Marking Tool.....20
- Non-Gaugable Preswaging Tool.....21
- Tools Required for Gaugeable Preswaging  
Tool Instructions .....22
- Gaugeable Preswaging Tool Instructions.....23
- Gaugeable Preswaging Tool, Tube  
Fitting Installation .....24
- Gaugeability.....25

## Hydraulic Swaging Units

- Multihead (MHSU) .....26
- Air-Actuated (AHSU) .....27

## **Tubing**

■ Installation .....	28
■ Selection .....	29
■ Gas Service.....	29
■ Fractional Carbon Steel Tubing .....	30
■ Metric Carbon Steel Tubing .....	32
■ Fractional Stainless Steel Seamless Tubing ..	34
■ Metric Stainless Steel Seamless Tubing .....	36
■ Fractional Copper Tubing.....	38

## **Ordering Information . . . . . 39**

## **Straight Fittings**

### **Unions**



■ Union.....	40
■ Reducing Union .....	42
■ Bulkhead Union .....	44
■ Bulkhead Reducing Union.....	44

### **Male Connectors**



■ NPT.....	45
■ ISO/BSP Tapered Thread (RT).....	47
■ ISO/BSP Parallel Thread (RS) .....	49
■ ISO/BSP Parallel Thread (RP) .....	51
■ Bulkhead NPT .....	53
■ SAE/MS Straight Thread (ST) .....	54
■ O-Seal (SAE/MS Straight Thread) ..	55
■ O-Seal (NPT) .....	55
■ AN Fitting .....	56
■ AN Bulkhead Fitting.....	56
■ 10-32 Thread .....	57
■ M5 × 0.8 Thread .....	57
■ Metric Thread (RS).....	57

### **Weld Connectors**



■ Tube Socket Weld .....	58
■ Male Pipe Weld .....	58

## **Straight Fittings**

### **Female Connectors**



- NPT ..... 60
- ISO/BSP Tapered Thread (RT) ..... 62
- ISO/BSP Parallel Thread (RJ) ..... 63
- ISO/BSP Parallel Thread (RP) ..... 63
- ISO/BSP Parallel Thread (RG, Gauge) ..... 64
- Bulkhead NPT ..... 65

### **Reducers**



- Reducer ..... 66
- Long Reducer ..... 69
- Bulkhead Reducer ..... 69

### **Port Connectors**



- Port Connector ..... 70
- Reducing Port Connector ..... 71

### **Caps and Plugs**



- Cap ..... 72
- Plug ..... 73
- Vent Protectors ..... 74

## **90° Elbows**

### **Unions**



- Union ..... 75

### **Male**



- NPT ..... 76
- ISO/BSP Tapered Thread (RT) ..... 78
- Reducing ..... 80
- Positionable, SAE/MS Straight Thread (ST) ..... 80
- Positionable, ISO/BSP Parallel Thread (PR) ..... 81

### **Weld**



- Tube Socket Weld ..... 82
- Male Pipe Weld ..... 82

### **Female**



- NPT ..... 83

## **45° Elbows**

### **Male**



- NPT ..... 84
- Positionable, SAE/MS  
Straight Thread (ST) ..... 84

## **Tees**



- Union ..... 85
- Reducing Union ..... 86

### **Male**



- Branch, NPT (TTM) ..... 88
- Run, NPT (TMT) ..... 89
- Positionable Branch, SAE/MS  
Straight Thread (TTS) ..... 90
- Positionable Run, SAE/MS  
Straight Thread (TST) ..... 90
- Positionable Branch, ISO/BSP  
Parallel Thread (TTR) ..... 91
- Positionable Run, ISO/BSP  
Parallel Thread (TRT) ..... 92

### **Female**



- Run, NPT (TFT) ..... 93
- Branch, NPT (TTF) ..... 94



- Cross, Union ..... 95



- Sanitary Flange Fittings ..... 96

## Tube Adapters

### **Male**



- NPT ..... 97
- ISO/BSP Tapered Thread (RT) ..... 98
- ISO/BSP Parallel Thread (RS) ..... 99
- ISO/BSP Parallel Thread (RP) ..... 100
- SAE/MS Straight Thread (ST) ..... 100
- O-Seal (SAE/MS Straight Thread) ..... 101
- AN Thread ..... 101
- Pipe Weld ..... 101

### **Female**



- NPT ..... 102
- ISO/BSP Tapered Thread (RT) ..... 103
- ISO/BSP Parallel Thread (RP) ..... 103
- ISO/BSP Parallel Thread (RG, Gauge) ..... 104
- ISO/BSP Parallel Thread (RJ) ..... 105
- AN Thread ..... 105

### **Part Numbering**

- Tube Fitting Part Numbers ..... 106
- Tube Adapter Part Numbers ..... 109

## **Replacement Parts**

### **Nuts**



- Female ..... 111
- Knurled Female ..... 112
- Male ..... 112

### **Ferrules**



- Front ..... 113
- Back ..... 114
- Nut-Ferrule Sets, Packages ..... 115
- Ferrule Sets, Ferrule-Paks™ ..... 116

### **ISO/BSP Parallel Gaskets**



- Steel and Stainless Steel (RS Fitting) ..... 117
- Copper (RP and RS Fitting) ..... 118
- Copper and Nickel (RG, Gauge Fitting) ..... 118
- PTFE (RJ Fitting) ..... 118

### **O-Rings**



- Buna N (O-Seal Straight Threads) ..... 119
- Buna N (O-Seal Pipe Threads) ..... 119
- Fluorocarbon FKM (Positionable Fittings, ISO/BSP Parallel Threads) ..... 120
- Fluorocarbon FKM (SAE/MS Straight Threads) ..... 120

## **Tools and Accessories**



- Bulkhead Retainers ..... 121



- Gap Inspection Gauges ..... 122



- Depth Marking Tools ..... 124



- Preswaging Tools ..... 125



- Inserts for Soft Plastic Tubing ..... 126

## About Swagelok

Swagelok is a leading developer and provider of fluid system products, assemblies, and services for the oil and gas, chemical and petrochemical, semiconductor, transportation, and power industries. With millions of our products in use around the world and a growing offering of services, Swagelok has long been synonymous with exceptional quality and reliability.

Our expertise in materials science and product design, combined with an extensive global sales and service network, enables us to be a highly valued resource for our customers, even in the most demanding applications, for experience, insight, and support. We are committed to fostering a culture that promotes our core values of innovation, continuous improvement, respect, quality, customer focus, and integrity.

We are pleased to provide this global edition of the *An Installer's Pocket Guide for Swagelok Tube Fittings*. This is up to date at the time of printing, with its revision number shown on the back page. Subsequent revisions will supersede the printed version and will be posted on the Swagelok website and in the Swagelok electronic Desktop Technical Reference (eDTR) tool.

Visit [swagelok.com](http://swagelok.com) to locate your Swagelok representative and obtain information on features, technical information and product references, and the variety of services available only through authorized Swagelok sales and service centers.

## Markets Served

Oil and gas; chemical/petrochemical; semiconductor; transportation; power; food, beverage, and dairy; biopharmaceutical; pulp and paper; analytical instrumentation; process instrumentation


## Intermix/Interchange with Other Manufacturers' Components

This practice can be dangerous. Leak-tight seals that will withstand high pressure, vibration, vacuum, and temperature changes depend on close tolerances and consistent, exacting quality control in conjunction with good design principles. The critical interaction of precision parts is essential for reliability and safety.

Components of other manufacturers may look like Swagelok tube fitting components—but they cannot be manufactured in accordance with Swagelok engineering standards, nor do they benefit from innovations in design and manufacture defined by more than 36 active Swagelok tube fitting patents issued since 1989.

### Metric Swagelok Tube Fittings

Metric tube fittings have a stepped shoulder on the body hex.



Shaped fittings, such as elbows, crosses, and tees, are stamped MM for metric tubing and have no step on the forging.

# Installation Instructions

Swagelok tube fittings 1 in./25 mm and smaller can be installed quickly, easily, and reliably with simple hand tools.

Over 1 in./25 mm sizes require use of a hydraulic swaging unit to swage the ferrules onto the tubing.

## Safety Precautions

- Do not bleed system by loosening fitting nut or fitting plug.
- Do not assemble and tighten fittings when system is pressurized.
- Make sure that the tubing rests firmly on the shoulder of the tube fitting body before tightening the nut.
- Use the correct Swagelok gap inspection gauge to ensure sufficient pull-up upon initial installation.
- Always use proper thread sealants on tapered pipe threads.
- Do not mix materials or fitting components from various manufacturers—tubing, ferrules, nuts, and fitting bodies.
- Never turn fitting body. Instead, hold fitting body and turn nut.
- Avoid unnecessary disassembly of unused fittings.
- Use only long reducers in female Swagelok end connections.

See the instructions starting on the next page for installation of Swagelok tube fittings, O-seal male connectors, caps and plugs, port connectors, tube adapters, positionable elbows and tees, weld fittings, depth marking tool, and preswaging tool.

# Swagelok Tube Fittings

## Up to 1 in./25 mm


Safe practices and proper installation are imperative to the performance of the Swagelok tube fitting, especially in critical applications.

For 5/8, 3/4, 7/8 and 1 in.; 16, 18, 20, 22 and 25 mm tube fittings, in all materials except for aluminum and brass, it is a best practice to preswage the ferrules onto the tube adapter using a Swagelok multihead hydraulic swaging unit (MHSU) to lower installation time and increase ease of installation (see Multihead Hydraulic Swaging Unit (MHSU), Setup and Operating Instructions, [MS-12-37](#)).


Fully insert the tube into the fitting and against the shoulder; rotate the nut finger-tight.

**High-pressure applications and high safety-factor systems:**

Further tighten the nut until the tube will not turn by hand or move axially in the fitting.




Mark the nut at the 6 o'clock position.



While holding the fitting body steady, tighten the nut one and one-quarter turns to the 9 o'clock position.

For 1/16, 1/8, and 3/16 in.; 2, 3, and 4 mm tube fittings, tighten the nut three-quarters turn to the 3 o'clock position.



# Swagelok Tube Fittings

## Over 1 in./25 mm


1. Preswage the ferrules onto the tube using a Swagelok multihead hydraulic swaging unit (MHSU).
2. Apply the lubricant packaged with the fitting lightly to the body threads and the rear surface of the back ferrule. For gas service also apply lightly to the front angled surface of the front ferrule.
3. Insert the tube with preswaged ferrules into the fitting until the front ferrule seats against the fitting body; rotate the nut finger-tight.
4. Mark the nut at the 6 o'clock position.
5. While holding the fitting body steady, tighten the nut one-half turn to the 12 o'clock position.

*Use the Swagelok MHSU gap inspection gauge to ensure that the fitting has been tightened sufficiently.*

### Gaugeability

On initial installation, the Swagelok gap inspection gauge assures the installer or inspector that a fitting has been sufficiently tightened.

Position the Swagelok gap inspection gauge next to the gap between the nut and body.



If the gauge **will not** enter the gap, **the fitting is sufficiently tightened.**

If the gauge **will** enter the gap, **additional tightening is required.**

#### **⚠ Warning**

**Always depressurize a system before adjusting the tightness of a tube fitting connection.**

# Swagelok Tube Fittings


## Reassembly—All Sizes

You may disassemble and reassemble Swagelok tube fittings many times.

**⚠ Always depressurize the system before disassembling a Swagelok tube fitting.**


Prior to disassembly, mark the tube at the back of the nut; mark a line along the nut and fitting body flats.

*Use these marks to ensure that you return the nut to the previously pulled-up position.*




Insert the tube with preswaged ferrules into the fitting until the front ferrule seats against the fitting body.

**Over 1 in./25 mm sizes:** If needed, reapply lubricant lightly to the body threads and the rear surface of the back ferrule.



While holding the fitting body steady, rotate the nut with a wrench to the previously pulled-up position, as indicated by the marks on the tube and flats. At this point, you will feel a significant increase in resistance. Tighten the nut slightly.



**⚠ Caution**

**Do not use the Swagelok gap inspection gauge with reassembled fittings.**

## O-Seal Male Connectors

1. Turn the O-seal connector into the female end until it is finger-tight.
2. Tighten the O-seal connector until it makes metal-to-metal contact with the face of the female end.
3. Tighten slightly with a wrench.

*O-rings are coated with a thin film of silicone-based lubricant. Removal of factory-applied lubricants may alter performance.*

## Caps and Plugs



### Caps

See Swagelok tube fitting installation and reassembly, page 15 and 14



### Plugs

While holding fitting body steady, tighten the plug one-quarter turn from the finger-tight position.

*For 1/16, 1/8, and 3/16 in.; 2, 3, and 4 mm tube fittings, tighten the plug one-eighth turn.*

*For over 1 in. and over 25 mm tube fittings, tighten the plug one-quarter turn.*

**⚠ Do not use the Swagelok gap inspection gauge with plug assemblies.**

### Reassembly

You may disassemble and reassemble Swagelok plugs many times. Make subsequent connections by slightly tightening with a wrench after snugging the nut by hand.

## Pipe Thread Fittings

A thread sealant should always be used when assembling tapered threads. SWAK™ anaerobic pipe thread sealant, PTFE-Free pipe thread sealant, and Swagelok PTFE Tape are available. For more information, see the Swagelok *Leak Detectors, Lubricants, and Sealants* catalog, [MS-01-91](#).

# Port Connectors

Connect the machined ferrule end **before** connecting the tube adapter end.

## Machined Ferrule End


1. Remove the nut and ferrules from the Swagelok end connection. Discard the ferrules.




2. Slip the nut over the machined ferrule end of the port connector.

### Over 1 in./25 mm sizes:

*The nut is preassembled on the port connector.*




3. Insert the port connector into the end connection and finger-tighten the nut.



4. While holding fitting body steady, tighten the nut one-quarter turn.

*For 1/16, 1/8, and 3/16 in.; 2, 3, and 4 mm tube fittings, tighten the nut one-eighth turn.*



**⚠ Do not use the Swagelok gap inspection gauge with machined ferrule ends.**


# Port Connectors

## Reassembly

You may disassemble and reassemble Swagelok port connectors many times. Make subsequent connections by slightly tightening with a wrench after snugging the nut by hand.


### Tube Adapter End

5. Insert the tube adapter until it rests firmly on the shoulder of the Swagelok tube fitting body. Finger-tighten the nut.



**Over 1 in./25 mm sizes:** Remove and discard the nut and ferrules from the end connection, then insert the tube adapter.

6. Mark the nut at the 6 o'clock position. While holding fitting body steady, tighten the nut one and one-quarter turns to the 9 o'clock position.



For 1/16, 1/8, and 3/16 in.; 2, 3, and 4 mm tube fittings, tighten the nut three-quarters turn to the 3 o'clock position.

For preswaged over 1 in./25 mm and over tube fittings, tighten the nut one-half turn to the 12 o'clock position.

**⚠ Do not use the Swagelok gap inspection gauge with preswaged tube adapter connections over 1 in./25 mm.**

## Reassembly

See Swagelok tube fitting reassembly, page 14.

## Positionable Elbows and Tees

1. Turn the positionable end into the female fitting until the metal backup washer contacts the face of the fitting.
2. Turn the positionable end out of the female fitting (not more than one turn) until the Swagelok tube fitting end is positioned properly.
3. While holding fitting body steady, tighten the lock nut until the metal backup washer contacts the face of the fitting.




# Tube Adapters

## Up to 1 in./25 mm

Safe practices and proper installation are imperative to the performance of the Swagelok tube fitting, especially in critical applications.

For 5/8, 3/4, 7/8 and 1 in.; 16, 18, 20, 22 and 25 mm tube fittings, in all materials except for aluminum and brass, it is a best practice to preswage the ferrules onto the tube adapter using a Swagelok multihead hydraulic swaging unit (MHSU) to lower installation time and increase ease of installation (see Multihead Hydraulic Swaging Unit (MHSU), Setup and Operating Instructions, [MS-12-37](#)).

1. Install the end opposite the tube adapter end.



2. Insert the tube adapter into the Swagelok tube fitting. Make sure that the tube adapter rests firmly on the shoulder of the tube fitting body and that the nut is finger-tight.
3. Mark the nut at the 6 o'clock position.
4. While holding fitting body steady, tighten the nut one and one-quarter turns to the 9 o'clock position.



*For 1/16, 1/8, and 3/16 in.; 2, 3, and 4 mm tube fittings, tighten the nut three-quarters turn to the 3 o'clock position.*

## Over 1 in./25 mm

Swagelok tube adapters over 1 in./25 mm are furnished with nuts and preswaged ferrules.

To assemble, follow steps 2 through 5 of the Swagelok tube fittings over 1 in./25 mm assembly instructions, page 13.

**⚠ Do not use the Swagelok gap inspection gauge with preswaged tube adapter connections over 1 in./25 mm.**

# Tube Adapters

## Reassembly

See Swagelok tube fitting reassembly, page 14.

## Weld Fittings

### ***Welding Precautions for Swagelok Tube Fittings with Weld End Connections***

1. Remove the nut and ferrules.
2. Turn a Swagelok tube fitting plug or another nut onto the fitting so that it is finger-tight. This protects the threads and sealing components.
3. Provide a suitable heat sink to dissipate the heat.
4. Tack weld at four positions 90° apart to hold the fitting in place and to ensure alignment and concentricity of the components.
5. Complete the weld.
6. Remove the plug or nut and replace the nut and ferrules.



#### **Caution**

**When welding carbon steel fittings, the heat often removes the protective oil from the threads. It is important to apply another lubricant, such as Goop™ thread lubricant.**

## Depth Marking Tool


1. Insert cleanly cut, fully deburred tube into the depth marking tool (DMT) until the tube is against the shoulder of the tool. Using a pen or pencil, mark the tube at the top of the DMT.
2. Remove the tube from the DMT and insert it into the Swagelok fitting until it is against the shoulder of the fitting body. Rotate the nut finger-tight. If any portion of the mark on the tube can be seen above the fitting nut, the tube is not fully inserted into the fitting.
3. While holding the fitting body steady, follow Swagelok tube fitting installation instructions, page 12.

## Non-Gaugable Preswaging Tool

Note: These instructions apply only to non-gaugeable preswaging tools. Tool will not have a colored band and the ordering number does not contain GA.

1. Install the Swagelok nut and ferrules onto the preswaging tool.
2. Insert the tube into the preswaging tool.
3. Make sure that the tube rests firmly on the shoulder of the preswaging tool body and that the nut is finger-tight.
4. Mark the nut at the 6 o'clock position.
5. While holding the preswaging tool steady, tighten the nut one and one-quarter turns to the 9 o'clock position.

*For 1/16, 1/8, and 3/16 in.; 2, 3, and 4 mm tube fittings, tighten the nut only three-quarters turn to the 3 o'clock position.*



6. Loosen the nut.
7. Remove the tube with preswaged ferrules from the preswaging tool. If the tube sticks in the preswaging tool, remove the tube by gently rocking it back and forth. Do not turn the tube.
8. Insert the tube with preswaged ferrules into the fitting body until the front ferrule seats against the fitting body.
9. While holding the fitting body steady, rotate the nut with a wrench to the previously pulled-up position; at this point, you will feel a significant increase in resistance.
10. Tighten the nut slightly.



**⚠ Do not use the Swagelok gap inspection gauge with fittings that were assembled with a non-gaugeable preswaging tool.**

## Tools Required for Gaugeable Preswaging Tool Instructions

1. Gaugeable preswage tool will have a colored band. Gaugeable tools are available in sizes 1/4, 3/8, 1/2, 5/8 in., and 6, 8, 10, 12, 16 mm.



2. Body wrench and nut wrench.



3. Standard gap gauge for standard assembly.




4. Severe-service gap gauge for severe service assembly.




# Gaugeable Preswaging Tool Instructions


1. Install the Swagelok nut and ferrules onto the preswaging tool.




2. Insert the tube into the preswaging tool until it rests firmly on the shoulder of the tool; rotate the nut finger-tight.



3. While holding the preswaging tool steady, tighten the nut with a wrench until it stops against the collar.




4. Loosen the nut and remove the tube with preswaged ferrules from the preswaging tool. If the tube sticks, gently rock it back and forth. Do not turn the tube.



## Gaugeable Preswaging Tool, Tube Fitting Installation

1. Insert the tube with preswaged ferrules into the fitting until the front ferrule seats against the fitting body; rotate the nut finger-tight.



2. Mark the nut at the 6 o'clock position.



3. While holding the fitting body steady, tighten the nut one-half turn to the 12 o'clock position.

Note: If assembling fittings for high-pressure applications or high safety-factor systems, tighten one hex flat further than one-half turn.



## Gaugeability

On initial installation, the Swagelok gap inspection gauge assures the installer or inspector that a fitting has been sufficiently tightened.

If the nut was tightened additionally during installation (step 3 on previous page), use Fig. 1 for gauging, otherwise use Fig. 2.

Position the Swagelok gap inspection gauge next to the gap between the nut and body.

- If the gauge will not enter the gap, the fitting is sufficiently tightened.
- If the gauge will enter the gap, additional tightening is required.

**Fig. 1**



**Fig. 2**



## Hydraulic Swaging Units

Swagelok hydraulic swaging units preswage Swagelok ferrules onto tubing prior to assembly and provide Swagelok tube fitting connections that are 100 % gaugeable upon initial installation. Multihead hydraulic and air-actuated hydraulic swaging units:

- Place no initial strain on fitting body threads or on body seal surfaces
- Are available with interchangeable fractional and metric tooling
- Fit neatly in a rugged plastic carrying case
- Reduce assembly and installation time and operator error

### **Multihead (MHSU)**



- Is available in two unit sizes, with tooling for:
  - 1/2 to 1 in. and 12 to 25 mm tubing and tube adapters
  - 1 to 2 in. and 25 to 50 mm tubing
- **Must** be used to install 1 1/4, 1 1/2, and 2 in. and 28, 30, 32, 38, and 50 mm Swagelok tube fittings
- Is standard with a tube marking feature to indicate when tube is properly bottomed in the unit
- Is available with a support base (as shown)
- Is available with hydraulic hose; support base is required

**The MHSU cannot be used for alloy 2507 tubing 1/2 in. and under.**

**For 5/8 and 3/4 in. alloy 2507 tubing, order the 1 in./25 mm and over unit and alloy 2507 tooling kit and gap inspection gauges.**

# Hydraulic Swaging Units

## Air-Actuated (AHSU)



- Requires only one unit with interchangeable tooling to swage 1/4 to 1/2 in. and 6 to 12 mm Swagelok tube fitting ferrule sizes
- Requires no threading of nut on or off the tooling

**The AHSU cannot be used for alloy 2507 tubing or for medium-pressure tubing.**


### ***Additional Information, MHSU and AHSU***

See the *Swagelok Gaugeable Tube Fittings and Adapters catalog*, [MS-01-140](#). For instructions, see *Multihead Hydraulic Swaging Unit (MHSU) Setup and Operation Instructions*, [MS-12-37](#), and *Air-Actuated Hydraulic Swaging Unit (AHSU) Setup and Operation Instructions*, [MS-12-38](#).

## Tubing Installation

Tubing properly selected and handled, when combined with the quality of Swagelok fittings, will give you leak-tight systems. Properly installed on such tubing, Swagelok fittings provide reliable service under a wide variety of fluid applications.

When installing fittings near tube bends, there must be a sufficient straight length of tubing to allow the tube to be bottomed in the Swagelok fitting (see tables below).



Fractional, in.		
T Tube OD	L <sup>①</sup>	
1/16	1/2	
1/8	23/32	
3/16	3/4	
1/4	13/16	
5/16	7/8	
3/8	15/16	
1/2	1 3/16	
5/8	1 1/4	
3/4		
7/8	1 5/16	
1	1 1/2	
1 1/4	2	
1 1/2	2 13/32	
2	3 1/4	

① Required straight tube length.

Metric, mm		
T Tube OD	L <sup>①</sup>	
3	19	
6	21	
8	23	
10	25	
12	31	
14	32	
15		
16		
18		
20	34	
22		
25		
28	46	
30	50	
32	54	
38	63	
50	80	

# Tubing Selection

- Metal tubing material should be softer than fitting material. For example, stainless steel tubing should not be used with brass fittings.
- When tubing and fittings are made of the same material, tubing must be fully annealed.
- Always use an insert with extremely soft or pliable plastic tubing.
- Extremes of wall thickness should always be checked against the suggested minimum and maximum wall thickness limitations.
- Surface finish is very important to proper sealing. Tubing with any kind of depression, scratch, raised portion, or other surface defect will be difficult to seal, particularly in gas service.
- Tubing that is oval and will not easily fit through fitting nuts, ferrules, and bodies should never be forced into the fitting.

## Gas Service

Gases (air, hydrogen, helium, nitrogen, etc.) have very small molecules that can escape through even the most minute leak path. Some surface defects on the tubing can provide such a leak path. As tube outside diameter (OD) increases, so does the likelihood of a scratch or other surface defect interfering with proper sealing.

The most successful connection for gas service will occur if all installation instructions are carefully followed and the heavier wall thicknesses of tubing on the following tables are selected.

A heavy-wall tube resists ferrule action more than a thin-wall tube, allowing the ferrules to coin out minor surface imperfections. A thin-wall tube offers less resistance to ferrule action during installation, reducing the chance of coining out surface defects, such as scratches. Within the applicable suggested allowable working pressure table, select a tube wall thickness whose working pressure is *outside* of the shaded areas.

## Fractional Carbon Steel Tubing

Allowable working pressures are calculated from an S value of 15 700 psi (108.2 MPa) for ASTM A179 tubing at -20 to 100°F (-28 to 37°C), as listed in ASME B31.3. For working pressure in accordance with ASME B31.1, multiply by 0.85.

### ***Suggested Ordering Information***

High-quality, soft annealed seamless carbon steel hydraulic tubing, ASTM A179 or equivalent. Hardness not to exceed 72 HRB or 130 HV. Tubing to be free of scratches, suitable for bending and flaring.

Tube OD in.	Carbon Steel Tube Wall Thickness, in.										Swagelok Fitting Series	
	0.028	0.035	0.049	0.065	0.083	0.095	0.109	0.120	0.134	0.148	0.165	0.180
<b>Note:</b> For gas service, select a tube wall thickness outside of the shaded area. (See Gas Service, page 29.)												
1/8	8000	10 200										200
3/16	5100	6 600	9600									300
1/4	3700	4 800	7000	9600								400
5/16		3 800	5500	7600								500
3/8		3 100	4500	6200								600
1/2	2 300	3300	4500	5900								810
5/8		1 800	2600	3500	4600	5300						1010
3/4		2100	2900	3700	4300	5100						1210
7/8		1800	2400	3200	3700	4300						1410
1		1500	2100	2700	3200	3700	4100					1610
1 1/4		1600	2100	2500	2900	3200	3600	4000	4600	5000		2000
1 1/2				1800	2000	2400	2600	3000	3300	3700	4100	5100
2					1500	1700	1900	2200	2400	2700	3000	3700
												3200

## Metric Carbon Steel Tubing

Allowable working pressures are based on equations from ASME B31.3 for EN 10305-1 tubing, using a stress value of 113 MPa (16 300 psi) and tensile strength of 340 MPa (49 300 psi).

### ***Suggested Ordering Information***

High-quality, soft annealed carbon steel tubing, EN 10305-1 or equivalent. Hardness not to exceed 72 HRB or 130 HV. Tubing to be free of scratches, suitable for bending or flaring.

Tube OD mm	Carbon Steel Tube Wall Thickness, mm										Swagelok Fitting Series						
	0.8	1.0	1.2	1.5	1.8	2.0	2.2	2.5	2.8	3.0	3.5	4.0	4.5				
<b>Working Pressure, bar</b> Note: For gas service, select a tube wall thickness outside of the shaded area. (See Gas Service, page 29.)																	
3	620	790											3M0				
6	290	370	460	590									6M0				
8		270	330	430									8M0				
10	210	260	330										10M0				
12	170	210	270	330	380	420							12M0				
14	150	180	230	280	320	350							14M0				
15	140	170	210	260	290	330							15M0				
16	130	160	200	240	270	300	350						16M0				
18		140	170	210	240	270	310						18M0				
20	120	160	190	210	240	270	310						20M0				
22		110	140	170	190	210	250	280					22M0				
25		100	120	150	170	180	210	240	260				25M0				
28										210	230	270	28M0				
30										170	200	250	30M0				
32										160	180	200	240	270	32M0		
38										120	140	150	160	200	230	260	38M0

# Fractional Stainless Steel Seamless Tubing

Allowable working pressures are calculated from an S value of 20 000 psi (138 MPa) for ASTM A269 tubing at -20 to 100°F (-28 to 37°C), as listed in ASME B31.3, except as noted.

## For Welded Tubing

For welded and drawn tubing, a derating factor must be applied for weld integrity:

- for double-welded tubing, multiply pressure rating by 0.85
- for single-welded tubing, multiply pressure rating by 0.80.

## Suggested Ordering Information

High-quality, fully annealed (Type 304, 304/304L, 316, 316/316L, 317, 317/317L, 321, 347) (seamless or welded and drawn) stainless steel hydraulic tubing, ASTM A269 or A213, or equivalent.

Hardness not to exceed 90 HRB or 200 HV. Tubing to be free of scratches, suitable for bending and flaring. OD tolerances not to exceed  $\pm 0.003$  in. for 1/16 in. OD tubing.

*Certain austenitic stainless tubing has an allowable ovality tolerance double the OD tolerance and may not fit into Swagelok precision tube fittings. Dual-certified grades such as 304/304L, 316/316L, and 317/317L meet the minimum chemistry and the mechanical properties of both alloy grades.*

Tube OD in.	Stainless Steel Tube Wall Thickness, in.										Swagelok Fitting Series				
	0.010	0.012	0.014	0.016	0.020	0.028	0.035	0.049	0.065	0.083	0.095	0.109	0.120	0.134	0.156
<b>Working Pressure, psig</b> Note: For gas service, select a tube wall thickness outside of the shaded area. (See Gas Service, page 29.)															
1/16	5600	6800	8100	9400	12 000										100
1/8						8500	10 900								200
3/16						5400	7000	10 200							300
1/4						4000	5100	7500	10 200 <sup>(1)</sup>						400
5/16						4000	5800	8000							500
3/8						3300	4800	6500	7500 <sup>(1)(2)</sup>						600
1/2						2600	3700	5100	6700						810
5/8						2900	4000	5200	6000						1010
3/4						2400	3300	4200	4900	5800					1210
7/8						2000	2800	3600	4200	4800					1410
1						2400	3100	3600	4200	4700					1610
1 1/4								2400	2800	3300	3600	4100	4900		2000
1 1/2									2300	2700	3000	3400	4000	4900	2400
2									2000	2200	2500	2900	3600	3200	

① For higher pressures, see the *Swagelok Medium- and High-Pressure Fittings, Tubing, Valves and Accessories* catalog, [MS-02-472](#).

② Rating based on repeated pressure testing of the Swagelok tube fitting with a 4:1 design factor based upon hydraulic fluid leakage.

## Metric Stainless Steel Seamless Tubing

Allowable working pressures are calculated from an S value of 138 MPa (20 000 psi) for EN ISO 1127 tubing (D4, T4 tolerance for 3 to 12 mm; D4, T3 tolerance 14 to 50 mm), at -28 to 37°C (-20 to 100°F), as listed in ASME B31.3, except as noted.

### **For Welded Tubing**

For welded and drawn tubing, a derating factor must be applied for weld integrity:

- for double-welded tubing, multiply pressure rating by 0.85
- for single-welded tubing, multiply pressure rating by 0.80.

### **Suggested Ordering Information**

High-quality, fully annealed (Type 304, 304/304L, 316, 316/316L, 317, 317/317L, 321, 347) stainless steel tubing, EN ISO 1127 or equivalent. Hardness not to exceed 90 HRB or 200 HV. Tubing to be free of scratches, suitable for bending or flaring. OD tolerances not to exceed  $\pm 0.076$  mm for 3 mm OD tubing.

*Dual-certified grades such as 304/304L, 316/316L, and 317/317L meet the minimum chemistry and the mechanical properties of both alloy grades.*

Tube OD mm	Stainless Steel Tube Wall Thickness, mm										Swagelok Fitting Series			
	0.8	1.0	1.2	1.5	1.8	2.0	2.2	2.5	2.8	3.0	3.5	4.0	4.5	5.0
2	660 <sup>(1)</sup>													2M0
3	680													3M0
4	500	670												4M0
6	320	430	550	720										6M0
8	310	390	530											8M0
10	240	310	410	510	580									10M0
12	200	250	330	420	480									12M0
14	160	200	270	340	390	430								14M0
15	150	190	250	310	360	400								15M0
16		180	230	290	330	370	400 <sup>(1)</sup>							16M0
18		150	210	260	290	330	380							18M0
20		140	180	230	260	290	330	380						20M0
22		120	170	210	240	260	300	340						22M0
25			180	200	230	260	300	320						25M0
28				180	200	230	260	280	330					28M0
30					170	190	210	240	260	310				30M0
32						160	170	200	230	240	290	330		32M0
38							140	170	190	200	240	270	310	38M0
50									150	180	200	230	260	50M0

**Note:** For gas service, select a tube wall thickness outside of the shaded area. (See **Gas Service**, page 29.)

<sup>(1)</sup> Rating based on repeated pressure testing of the Swagelok tube fitting with a 4:1 design factor based upon hydraulic fluid leakage.

## Fractional Copper Tubing

Allowable working pressures are calculated from an S value of 6000 psi (41.3 MPa) for ASTM B75 and ASTM B88 tubing at -20 to 100°F (-28 to 37°C), as listed in ASME B31.3 and ASME B31.1.

### Suggested Ordering Information

High-quality, soft annealed seamless copper tubing, ASTM B75 or equivalent. Also soft annealed (Temper O) copper water tube, type K or type L to ASTM B88.

Tube OD in.	Copper Tube Wall Thickness, in.							Swagelok Fitting Series
	0.020	0.028	0.030	0.035	0.049	0.065	0.083	
1/16	3600 <sup>(1)</sup>							100
1/8		2800	3000	3600				200
3/16		1800	1900	2300	3400			300
1/4		1300	1400	1600	2500	3400		400
5/16				1300	1900	2700		500
3/8				1000	1600	2200		600
1/2				800	1100	1600	2100	810
5/8					900	1200	1600	1900
3/4					700	1000	1300	1500
7/8					600	800	1100	1300
1					500	700	900	1100
1 1/8						600	800	1000
							1100	1300
							1400	1600
							1800	2000
							2100	2300
							2400	2600
							2700	3000
							3100	3400
							3500	3800
							3900	4200
							4300	4600
							4700	5000
							5100	5400
							5500	5800
							5900	6200
							6300	6600
							6700	7000
							7100	7400
							7500	7800
							7900	8200
							8300	8600
							8700	9000
							9100	9400
							9500	9800
							9900	10200
							10300	10600
							10700	11000
							11100	11400
							11500	11800
							11900	12200
							12300	12600
							12700	13000
							13100	13400
							13500	13800
							14100	14400
							14500	14800
							15100	15400
							15700	16000
							16300	16600
							17100	17400
							18100	18400

<sup>(1)</sup> Rating based on repeated pressure testing of the Swagelok tube fitting with a 4:1 design factor based upon hydraulic fluid leakage.

## Ordering Numbers

Select a basic ordering number.

Example: **-100-6**

Add a material designator.

Example: **SS-100-6**

Minimum order quantities may apply to certain materials and configurations.

Material	Designator
316 SS	SS
6-moly	6Mo
Aluminum	A
Alloy 400	M
Alloy 600	INC
Alloy 625	625
Alloy 825	825
Alloy 2507	2507
Alloy C-276	HC
Brass	B
Carbon steel	S
PTFE	T
Titanium	TI

## Additional Products

- For alloy 2507 super duplex tube fittings, see the Swagelok *Gaugeable Alloy 2507 Super Duplex Tube Fittings* catalog, [MS-01-174](#).
- For alloy 400 tube fittings, see the Swagelok *Gaugeable Alloy 400 Mechanically Attached Pipe and Tube Fittings* catalog, [MS-02-332](#).
- For PFA tube fittings, see the Swagelok *PFA Tube Fittings* catalog, [MS-01-05](#).
- For heavy-wall tube fittings and medium-pressure tube fittings, see the Swagelok *Medium- and High-Pressure Fittings, Tubing, Valves and Accessories* catalog, [MS-02-472](#).

Contact your authorized Swagelok sales and service center about additional sizes and special alloys.

# Unions



## Union

Tube OD in.	Basic Ordering Number
1/16	-100-6
1/8	-200-6
3/16	-300-6
1/4	-400-6
5/16	-500-6
3/8	-600-6
1/2	-810-6
1/2	-810-6-0030 <sup>①</sup>
5/8	-1010-6
3/4	-1210-6
7/8	-1410-6
1	-1610-6
1 1/8	-1810-6
1 1/4	-2000-6
1 1/2	-2400-6
2	-3200-6

① Bored through.

Tube OD mm	Basic Ordering Number
2	-2M0-6
3	-3M0-6
4	-4M0-6
6	-6M0-6
8	-8M0-6
10	-10M0-6
12	-12M0-6
14	-14M0-6
15	-15M0-6
16	-16M0-6
18	-18M0-6
20	-20M0-6
22	-22M0-6
25	-25M0-6
28	-28M0-6
30	-30M0-6
32	-32M0-6
38	-38M0-6
50	-50M0-6

# Unions

## *Union (Metric to Fractional)*



Tube OD		Basic Ordering Number
T, mm	Tx, in.	
2	1/8	-2M0-6-2
	1/4	-2M0-6-4
3	1/8	-3M0-6-2
4	1/8	-4M0-6-2
	1/4	-4M0-6-4
6	1/16	-6M0-6-1
	1/8	-6M0-6-2
	1/4	-6M0-6-4
	5/16	-6M0-6-5
	3/8	-6M0-6-6
8	1/4	-8M0-6-4
	3/8	-8M0-6-6
10	1/8	-10M0-6-2
	1/4	-10M0-6-4
	5/16	-10M0-6-5
	3/8	-10M0-6-6
12	1/4	-12M0-6-4
	5/16	-12M0-6-5
	3/8	-12M0-6-6
	1/2	-12M0-6-8
15	1/2	-15M0-6-8
16	5/8	-16M0-6-10
18	3/4	-18M0-6-12
20	1/2	-20M0-6-8
	1	-20M0-6-16
25	1	-25M0-6-16

# Unions

## Reducing Union



Tube OD, in.		Basic Ordering Number
T	Tx	
1/8	1/16	-200-6-1
3/16	1/16	-300-6-1
	1/8	-300-6-2
1/4	1/16	-400-6-1
	1/8	-400-6-2
	3/16	-400-6-3
5/16	1/8	-500-6-2
	1/4	-500-6-4
3/8	1/16	-600-6-1
	1/8	-600-6-2
	1/4	-600-6-4
	5/16	-600-6-5
1/2	1/8	-810-6-2
	1/4	-810-6-4
	3/8	-810-6-6
5/8	3/8	-1010-6-6
	1/2	-1010-6-8
3/4	1/4	-1210-6-4
	3/8	-1210-6-6
	1/2	-1210-6-8
	5/8	-1210-6-10
1	1/2	-1610-6-8
	3/4	-1610-6-12

# Unions

## Reducing Union



Tube OD, mm		Basic Ordering Number
T	Tx	
3	2	-3M0-6-2M
6	2	-6M0-6-2M
	3	-6M0-6-3M
	4	-6M0-6-4M
8	6	-8M0-6-6M
10	6	-10M0-6-6M
	8	-10M0-6-8M
12	6	-12M0-6-6M
	8	-12M0-6-8M
	10	-12M0-6-10M
16	10	-16M0-6-10M
	12	-16M0-6-12M
18	12	-18M0-6-12M
25	18	-25M0-6-18M
	20	-25M0-6-20M
30	18	-30M0-6-18M
	20	-30M0-6-20M
	25	-30M0-6-25M
32	18	-32M0-6-18M
	20	-32M0-6-20M
	25	-32M0-6-25M
38	20	-38M0-6-20M
	25	-38M0-6-25M
	30	-38M0-6-30M

# Unions

## Bulkhead Union



Tube OD in.	Basic Ordering Number
1/16	-100-61
1/8	-200-61
3/16	-300-61
1/4	-400-61
5/16	-500-61
3/8	-600-61
1/2	-810-61
5/8	-1010-61
3/4	-1210-61
1	-1610-61
1 1/4	-2000-61
1 1/2	-2400-61
2	-3200-61

Tube OD mm	Basic Ordering Number
3	-3M0-61
4	-4M0-61
6	-6M0-61
8	-8M0-61
10	-10M0-61
12	-12M0-61
14	-14M0-61
15	-15M0-61
16	-16M0-61
18	-18M0-61
20	-20M0-61
25	-25M0-61
30	-30M0-61
32	-32M0-61
38	-38M0-61

## Bulkhead Reducing Union



Tube OD, in.	Basic Ordering Number	
	T	Tx
1/8	1/16	-200-61-1
1/4	1/8	-400-61-2
3/8	1/4	-600-61-4
1/2	1/4	-810-61-4

## Bulkhead Reducing Union (Metric to Fractional)

Tube OD		Basic Ordering Number
T, mm	Tx, in.	
6	1/8	-6M0-61-2

# Male Connectors

## NPT



Tube OD in.	NPT Size in.	Basic Ordering Number
1/16	1/16	-100-1-1
	1/8	-100-1-2
	1/4	-100-1-4
1/8	1/16	-200-1-1
	1/8	-200-1-2
	1/4	-200-1-4
	3/8	-200-1-6
	1/2	-200-1-8
3/16	1/8	-300-1-2
	1/4	-300-1-4
1/4	1/16	-400-1-1
	1/8	-400-1-2
	1/4	-400-1-4
	3/8	-400-1-6
	1/2	-400-1-8
	3/4	-400-1-12
5/16	1/8	-500-1-2
	1/4	-500-1-4
	3/8	-500-1-6
3/8	1/8	-600-1-2
	1/4	-600-1-4
	3/8	-600-1-6
	1/2	-600-1-8
	3/4	-600-1-12
	1	-600-1-16
1/2	1/8	-810-1-2
	1/4	-810-1-4
	3/8	-810-1-6
	1/2	-810-1-8
	3/4	-810-1-12
	1	-810-1-16

Tube OD in.	NPT Size in.	Basic Ordering Number
5/8	1/4	-1010-1-4
	3/8	-1010-1-6
	1/2	-1010-1-8
	3/4	-1010-1-12
3/4	3/8	-1210-1-6
	1/2	-1210-1-8
	3/4	-1210-1-12
	1	-1210-1-16
7/8	1/2	-1410-1-8
	3/4	-1410-1-12
	1	-1410-1-16
1	1/2	-1610-1-8
	3/4	-1610-1-12
	1	-1610-1-16
1 1/8	1	-1810-1-16
1 1/4	1	-2000-1-16
	1 1/4	-2000-1-20
1 1/2	1 1/2	-2400-1-24
2	2	-3200-1-32

# Male Connectors

Installation

Straight Fittings

Elbows and Tees

Adapters

Parts

Accessories

## NPT



Tube OD mm	NPT Size in.	Basic Ordering Number
2	1/8	-2M0-1-2
3	1/8	-3M0-1-2
	1/4	-3M0-1-4
4	1/8	-4M0-1-2
	1/4	-4M0-1-4
6	1/8	-6M0-1-2
	1/4	-6M0-1-4
	3/8	-6M0-1-6
	1/2	-6M0-1-8
8	1/8	-8M0-1-2
	1/4	-8M0-1-4
	3/8	-8M0-1-6
	1/2	-8M0-1-8
10	1/8	-10M0-1-2
	1/4	-10M0-1-4
	3/8	-10M0-1-6
	1/2	-10M0-1-8
	3/4	-10M0-1-12
12	1/8	-12M0-1-2
	1/4	-12M0-1-4
	3/8	-12M0-1-6
	1/2	-12M0-1-8
	3/4	-12M0-1-12
14	1/4	-14M0-1-4
	3/8	-14M0-1-6
	1/2	-14M0-1-8
15	1/2	-15M0-1-8
16	3/8	-16M0-1-6
	1/2	-16M0-1-8
	3/4	-16M0-1-12
18	1/2	-18M0-1-8
	3/4	-18M0-1-12
20	1/2	-20M0-1-8
	3/4	-20M0-1-12
22	3/4	-22M0-1-12
	1	-22M0-1-16
25	1/2	-25M0-1-8
	3/4	-25M0-1-12
	1	-25M0-1-16
28	1	-28M0-1-16
	1 1/4	-28M0-1-20
30	1 1/4	-30M0-1-20
32	1 1/4	-32M0-1-20
38	1 1/2	-38M0-1-24

# Male Connectors

## *ISO/BSP Tapered Thread (RT)*



Tube OD in.	ISO Thread Size in.	Basic Ordering Number
1/8	1/8	-200-1-2RT
	1/4	-200-1-4RT
1/4	1/8	-400-1-2RT
	1/4	-400-1-4RT
	3/8	-400-1-6RT
	1/2	-400-1-8RT
5/16	1/8	-500-1-2RT
	1/4	-500-1-4RT
3/8	1/8	-600-1-2RT
	1/4	-600-1-4RT
	3/8	-600-1-6RT
	1/2	-600-1-8RT
	3/4	-600-1-12RT
1/2	1/4	-810-1-4RT
	3/8	-810-1-6RT
	1/2	-810-1-8RT
	3/4	-810-1-12RT
5/8	1/2	-1010-1-8RT
3/4	3/4	-1210-1-12RT
	1	-1210-1-16RT
1	3/4	-1610-1-12RT
	1	-1610-1-16RT
1 1/4	1 1/4	-2000-1-20RT

# Male Connectors

## ISO/BSP Tapered Thread (RT)



Tube OD mm	ISO Thread Size in.	Basic Ordering Number
2	1/8	-2M0-1-2RT
3	1/8	-3M0-1-2RT
	1/4	-3M0-1-4RT
4	1/8	-4M0-1-2RT
	1/4	-4M0-1-4RT
6	1/8	-6M0-1-2RT
	1/4	-6M0-1-4RT
	3/8	-6M0-1-6RT
	1/2	-6M0-1-8RT
8	1/8	-8M0-1-2RT
	1/4	-8M0-1-4RT
	3/8	-8M0-1-6RT
	1/2	-8M0-1-8RT
10	1/8	-10M0-1-2RT
	1/4	-10M0-1-4RT
	3/8	-10M0-1-6RT
	1/2	-10M0-1-8RT
	3/4	-10M0-1-12RT
12	1/4	-12M0-1-4RT
	3/8	-12M0-1-6RT
	1/2	-12M0-1-8RT
	3/4	-12M0-1-12RT
14	1/4	-14M0-1-4RT
	3/8	-14M0-1-6RT
15	1/2	-15M0-1-8RT
16	1/4	-16M0-1-4RT
	3/8	-16M0-1-6RT
	1/2	-16M0-1-8RT
	3/4	-16M0-1-12RT
18	1/2	-18M0-1-8RT
	3/4	-18M0-1-12RT
20	1/2	-20M0-1-8RT
	3/4	-20M0-1-12RT
22	3/4	-22M0-1-12RT
	1	-22M0-1-16RT
25	1/2	-25M0-1-8RT
	3/4	-25M0-1-12RT
	1	-25M0-1-16RT
28	1	-28M0-1-16RT
	1 1/4	-28M0-1-20RT
30	1 1/4	-30M0-1-20RT
32	1 1/4	-32M0-1-20RT
38	1 1/2	-38M0-1-24RT

Installation

Straight Fittings

Elbows and Tees


Adapters

Parts

Accessories

## Male Connectors

### *ISO/BSP Parallel Thread (RS)*



Tube OD in.	ISO Thread Size in.	Basic Ordering Number
1/8	1/8	-200-1-2RS
	1/4	-200-1-4RS
	3/8	-200-1-6RS
1/4	1/8	-400-1-2RS
	1/4	-400-1-4RS
	3/8	-400-1-6RS
	1/2	-400-1-8RS
3/8	1/8	-600-1-2RS
	1/4	-600-1-4RS
	3/8	-600-1-6RS
	1/2	-600-1-8RS
1/2	1/4	-810-1-4RS
	3/8	-810-1-6RS
	1/2	-810-1-8RS
3/4	1/2	-1210-1-8RS
	3/4	-1210-1-12RS
1	1/2	-1610-1-8RS
	3/4	-1610-1-12RS
	1	-1610-1-16RS

# Male Connectors

Installation

Straight Fittings


Elbows and Tees

Adapters

Parts

Accessories

## ISO/BSP Parallel Thread (RS)



Tube OD mm	ISO Thread Size in.	Basic Ordering Number
2	1/8	-2M0-1-2RS
3	1/8 1/4	-3M0-1-2RS -3M0-1-4RS
4	1/8	-4M0-1-2RS
6	1/8 1/4 3/8 1/2	-6M0-1-2RS -6M0-1-4RS -6M0-1-6RS -6M0-1-8RS
8	1/8 1/4 3/8 1/2	-8M0-1-2RS -8M0-1-4RS -8M0-1-6RS -8M0-1-8RS
10	1/4 3/8 1/2	-10M0-1-4RS -10M0-1-6RS -10M0-1-8RS
12	1/4 3/8 1/2 3/4	-12M0-1-4RS -12M0-1-6RS -12M0-1-8RS -12M0-1-12RS
14	3/8 1/2	-14M0-1-6RS -14M0-1-8RS
15	3/8 1/2 3/4	-15M0-1-6RS -15M0-1-8RS -15M0-1-12RS
16	3/8 1/2 3/4	-16M0-1-6RS -16M0-1-8RS -16M0-1-12RS
18	1/2 3/4	-18M0-1-8RS -18M0-1-12RS
20	1/2 3/4	-20M0-1-8RS -20M0-1-12RS
22	3/4 1	-22M0-1-12RS -22M0-1-16RS
25	3/4 1	-25M0-1-12RS -25M0-1-16RS
28	1 1 1/4	-28M0-1-16RS -28M0-1-20RS
30	1 1/4	-30M0-1-20RS
32	1 1/4	-32M0-1-20RS
38	1 1/2	-38M0-1-24RS

## Male Connectors

### *ISO/BSP Parallel Thread (RP)*



Tube OD in.	ISO Thread Size in.	Basic Ordering Number
1/8	1/8	-200-1-2RP
	1/4	-200-1-4RP
1/4	1/8	-400-1-2RP
	1/4	-400-1-4RP
1/2	3/8	-810-1-6RP
	1/2	-810-1-8RP
3/4	1/2	-1210-1-8RP
	3/4	-1210-1-12RP
1	1	-1610-1-16RP

# Male Connectors

Installation

Straight Fittings

Elbows and Tees

Adapters

Parts

Accessories

## ISO/BSP Parallel Thread (RP)



Tube OD mm	ISO Thread Size in.	Basic Ordering Number
3	1/8	-3M0-1-2RP
	1/4	-3M0-1-4RP
4	1/8	-4M0-1-2RP
	1/4	-6M0-1-2RP
	3/8	-6M0-1-4RP
	1/2	-6M0-1-6RP
6	1/8	-6M0-1-8RP
	1/4	-8M0-1-2RP
	3/8	-8M0-1-4RP
	1/2	-8M0-1-6RP
8	1/8	-8M0-1-8RP
	1/4	-10M0-1-2RP
	3/8	-10M0-1-4RP
	1/2	-10M0-1-6RP
10	1/4	-10M0-1-8RP
	3/8	-12M0-1-2RP
	1/2	-12M0-1-4RP
	3/4	-12M0-1-6RP
12	1/4	-12M0-1-8RP
	3/8	-12M0-1-10RP
	1/2	-15M0-1-2RP
	3/4	-15M0-1-4RP
15	1/2	-16M0-1-6RP
	3/4	-16M0-1-8RP
16	1/2	-18M0-1-8RP
	3/4	-18M0-1-12RP
18	1/2	-20M0-1-8RP
	3/4	-20M0-1-12RP
20	1/2	-22M0-1-12RP
	3/4	-22M0-1-16RP
22	1	-25M0-1-12RP
	3/4	-25M0-1-16RP
25	1	-28M0-1-16RP
	3/4	-28M0-1-20RP
28	1	-30M0-1-20RP
	1 1/4	-32M0-1-20RP
30	1 1/4	-38M0-1-24RP
32	1 1/4	
38	1 1/2	

# Male Connectors

## Bulkhead NPT




Tube OD in.	NPT Size in.	Basic Ordering Number
1/8	1/8	-200-11-2
1/4	1/8 1/4	-400-11-2 -400-11-4
3/8	1/4	-600-11-4
	3/8	-600-11-6
	1/2	-600-11-8
1/2	3/8 1/2	-810-11-6 -810-11-8
3/4	3/4	-1210-11-12
1	1	-1610-11-16

Tube OD mm	NPT Size in.	Basic Ordering Number
6	1/8 1/4	-6M0-11-2 -6M0-11-4
12	1/2	-12M0-11-8

# Male Connectors

## SAE/MS Straight Thread (ST)



Tube OD in.	SAE/MS Thread Size	Basic Ordering Number
1/8	5/16-24 7/16-20 9/16-18	-200-1-2ST -200-1-4ST -200-1-6ST
1/4	5/16-24 7/16-20 9/16-18 3/4-16 7/8-14	-400-1-2ST -400-1-4ST -400-1-6ST -400-1-8ST -400-1-10ST
5/16	1/2-20	-500-1-5ST
3/8	7/16-20 9/16-18 3/4-16 7/8-14	-600-1-4ST -600-1-6ST -600-1-8ST -600-1-10ST
1/2	9/16-18 3/4-16 7/8-14 1 1/16-12	-810-1-6ST -810-1-8ST -810-1-10ST -810-1-12ST
5/8	3/4-16 7/8-14	-1010-1-8ST -1010-1-10ST
3/4	3/4-16 1 1/16-12 1 5/16-12	-1210-1-8ST -1210-1-12ST -1210-1-16ST
7/8	1 3/16-12	-1410-1-14ST
1	1 1/16-12 1 5/16-12	-1610-1-12ST -1610-1-16ST
1 1/4	1 5/8-12	-2000-1-20ST
1 1/2	1 7/8-12	-2400-1-24ST
2	2 1/2-12	-3200-1-32ST

Tube OD mm	SAE/MS Thread Size	Basic Ordering Number
6	9/16-18	-6M0-1-6ST
10	9/16-18 3/4-16	-10M0-1-6ST -10M0-1-8ST
12	7/16-20 9/16-18 3/4-16	-12M0-1-4ST -12M0-1-6ST -12M0-1-8ST

Tube OD in.	SAE/MS Thread Size	Basic Ordering Number
1/4	7/16-20	-400-1L-4ST
1/2	3/4-16	-810-1L-8ST

**Long  
SAE/MS  
Straight  
Thread (ST)**

## Male Connectors

### O-Seal (SAE/MS Straight Thread)



Tube OD in.	SAE/MS Thread Size	Basic Ordering Number
1/16	5/16-24	-100-1-OR
1/8	5/16-24	-200-1-OR
3/16	3/8-24	-300-1-OR
1/4	7/16-20	-400-1-OR
5/16	1/2-20	-500-1-OR
3/8	9/16-18	-600-1-OR
1/2	3/4-16	-810-1-OR
3/4	1 1/16-12	-1210-1-OR
1	1 5/16-12	-1610-1-OR

### O-Seal (NPT)



Tube OD in.	NPT Size in.	Basic Ordering Number
1/8	1/8	-200-1-2-OR
1/4	1/8 1/4	-400-1-2-OR -400-1-4-OR
3/8	1/4 3/8 1/2	-600-1-4-OR -600-1-6-OR -600-1-8-OR
1/2	1/2	-810-1-8-OR

# Male Connectors

Installation

Straight Fittings

Elbows and Tees

Adapters

Parts

Accessories

## AN Fitting



Tube OD in.	AN Tube Flare Size in.	Basic Ordering Number
1/16	1/8	-100-6-2AN
1/8	1/8	-200-6-2AN
	1/4	-200-6-4AN
1/4	1/4	-400-6-4AN
5/16	5/16	-500-6-5AN
3/8	1/4	-600-6-4AN
	3/8	-600-6-6AN
1/2	1/2	-810-6-8AN
3/4	3/4	-1210-6-12AN
1	1	-1610-6-16AN

## AN Bulkhead Fitting



Tube OD in.	AN Tube Flare Size in.	Basic Ordering Number
1/4	1/4	-400-61-4AN
3/8	3/8	-600-61-6AN
1/2	1/2	-810-61-8AN
3/4	3/4	-1210-61-12AN
1	1	-1610-61-16AN

## Male Connectors

### 10-32 Thread




Tube OD in.	Basic Ordering Number
1/8	-200-1-0157
1/4	-400-1-0256

### M5 × 0.8 Thread



Tube OD mm	Basic Ordering Number
6	-6M0-1-0046

### Metric Thread (RS)



Tube OD mm	Basic Ordering Number
6	-6M0-1-M10X1.0RS -6M0-1-M12X1.0RS
12	-12M0-1-M16X1.5RS

# Weld Connectors

Installation

## Tube Socket Weld



Straight Fittings

## Male Pipe Weld (Fractional)



Elbows and Tees

Adapters

Parts

Accessories

Tube OD in.	Socket Weld Size in.	Basic Ordering Number
1/8	1/8	-200-6-2W
1/4	1/4	-400-6-4W
3/8	3/8	-600-6-6W
1/2	1/2	-810-6-8W
3/4	3/4	-1210-6-12W
1	1	-1610-6-16W

Tube OD in.	Pipe Weld Size in.	Basic Ordering Number
1/8	1/8	-200-1-2W
3/16	1/8	-300-1-2W
1/4	1/8 1/4	-400-1-2W -400-1-4W
5/16	1/8 1/4	-500-1-2W -500-1-4W
3/8	1/4 3/8 1/2 3/4	-600-1-4W -600-1-6W -600-1-8W -600-1-12W
1/2	3/8 1/2 3/4 1	-810-1-6W -810-1-8W -810-1-12W -810-1-16W
5/8	1/2	-1010-1-8W
3/4	1/2 3/4	-1210-1-8W -1210-1-12W
1	1	-1610-1-16W
1 1/4	1 1/4	-2000-1-20W
1 1/2	1 1/2	-2400-1-24W
2	2	-3200-1-32W

# Weld Connectors

## Male Pipe Weld (Metric to Fractional)



Tube OD mm	Pipe Weld Size in.	Basic Ordering Number
3	1/8	-3M0-1-2W
4	1/8	-4M0-1-2W
6	1/8 1/4	-6M0-1-2W -6M0-1-4W
8	1/8 1/4 1/2	-8M0-1-2W -8M0-1-4W -8M0-1-8W
10	1/4 3/8 1/2	-10M0-1-4W -10M0-1-6W -10M0-1-8W
12	1/4 3/8 1/2 3/4	-12M0-1-4W -12M0-1-6W -12M0-1-8W -12M0-1-12W
14	3/8	-14M0-1-6W
15	1/2	-15M0-1-8W
16	1/2	-16M0-1-8W
18	1/2	-18M0-1-8W
30	1 1/4	-30M0-1-20W
32	1 1/4	-32M0-1-20W
38	1 1/2	-38M0-1-24W

Installation

Straight Fittings

Elbows and Tees

Adapters

Parts

Accessories

# Female Connectors

Installation

Straight Fittings

Elbows and Tees

Adapters

Parts

Accessories

## NPT



Tube OD in.	NPT Size in.	Basic Ordering Number
1/16	1/16 1/8	-100-7-1 -100-7-2
1/8	1/8 1/4	-200-7-2 -200-7-4
3/16	1/8	-300-7-2
1/4	1/8 1/4 3/8 1/2	-400-7-2 -400-7-4 -400-7-6 -400-7-8
5/16	1/8 1/4	-500-7-2 -500-7-4
3/8	1/8 1/4 3/8 1/2 3/4	-600-7-2 -600-7-4 -600-7-6 -600-7-8 -600-7-12
1/2	1/4 3/8 1/2 3/4	-810-7-4 -810-7-6 -810-7-8 -810-7-12
5/8	3/8 1/2 3/4	-1010-7-6 -1010-7-8 -1010-7-12
3/4	1/2 3/4	-1210-7-8 -1210-7-12
7/8	3/4	-1410-7-12
1	3/4 1	-1610-7-12 -1610-7-16
1 1/4	1 1/4	-2000-7-20
1 1/2	1 1/2	-2400-7-24
2	2	-3200-7-32

# Female Connectors

## NPT



Tube OD mm	NPT Size in.	Basic Ordering Number
3	1/8	-3M0-7-2
	1/4	-3M0-7-4
4	1/8	-4M0-7-2
6	1/8	-6M0-7-2
	1/4	-6M0-7-4
	3/8	-6M0-7-6
	1/2	-6M0-7-8
8	1/8	-8M0-7-2
	1/4	-8M0-7-4
	3/8	-8M0-7-6
	1/2	-8M0-7-8
10	1/4	-10M0-7-4
	3/8	-10M0-7-6
	1/2	-10M0-7-8
12	1/4	-12M0-7-4
	3/8	-12M0-7-6
	1/2	-12M0-7-8
15	1/2	-15M0-7-8
16	1/2	-16M0-7-8
20	1/2	-20M0-7-8
	3/4	-20M0-7-12
22	3/4	-22M0-7-12
	1	-22M0-7-16
25	3/4	-25M0-7-12
	1	-25M0-7-16

# Female Connectors

Installation

Straight Fittings

Elbows and Tees

Adapters

Parts

Accessories

## ISO/BSP Tapered Thread (RT)



Tube OD in.	ISO Thread Size in.	Basic Ordering Number
1/8	1/8	-200-7-2RT
1/4	1/8	-400-7-2RT
	1/4	-400-7-4RT
	3/8	-400-7-6RT
	1/2	-400-7-8RT
3/8	1/4	-600-7-4RT
	3/8	-600-7-6RT
	1/2	-600-7-8RT
1/2	1/4	-810-7-4RT
	3/8	-810-7-6RT
	1/2	-810-7-8RT

Tube OD mm	ISO Thread Size in.	Basic Ordering Number
3	1/8	-3M0-7-2RT
6	1/8	-6M0-7-2RT
	1/4	-6M0-7-4RT
	3/8	-6M0-7-6RT
	1/2	-6M0-7-8RT
8	1/8	-8M0-7-2RT
	1/4	-8M0-7-4RT
	3/8	-8M0-7-6RT
	1/2	-8M0-7-8RT
10	1/8	-10M0-7-2RT
	1/4	-10M0-7-4RT
	3/8	-10M0-7-6RT
	1/2	-10M0-7-8RT
12	1/8	-12M0-7-2RT
	1/4	-12M0-7-4RT
	3/8	-12M0-7-6RT
	1/2	-12M0-7-8RT
	3/4	-12M0-7-12RT
15	3/8	-15M0-7-6RT
	1/2	-15M0-7-8RT
20	1/2	-20M0-7-8RT
	3/4	-20M0-7-12RT
22	3/4	-22M0-7-12RT
	1	-22M0-7-16RT
25	3/4	-25M0-7-12RT
	1	-25M0-7-16RT

## Female Connectors

**ISO/BSP  
Parallel  
Thread (RJ)**



Tube OD in.	ISO Thread Size in.	Ordering Number
1/4	1/4	SS-400-7-4RJ
	3/8	SS-400-7-6RJ
	1/2	SS-400-7-8RJ
5/16	1/4	SS-500-7-4RJ
	1/2	SS-500-7-8RJ
3/8	1/4	SS-600-7-4RJ
	3/8	SS-600-7-6RJ
	1/2	SS-600-7-8RJ
1/2	1/4	SS-810-7-4RJ
	3/8	SS-810-7-6RJ
	1/2	SS-810-7-8RJ

Tube OD mm.	ISO Thread Size in.	Ordering Number
6	1/4	SS-6M0-7-4RJ
	3/8	SS-6M0-7-6RJ
	1/2	SS-6M0-7-8RJ
8	1/4	SS-8M0-7-4RJ
	3/8	SS-8M0-7-6RJ
	1/2	SS-8M0-7-8RJ
10	1/4	SS-10M0-7-4RJ
	3/8	SS-10M0-7-6RJ
	1/2	SS-10M0-7-8RJ
12	1/4	SS-12M0-7-4RJ
	3/8	SS-12M0-7-6RJ
	1/2	SS-12M0-7-8RJ

**ISO/BSP  
Parallel  
Thread (RP)**

Tube OD mm	ISO Thread Size in.	Basic Ordering Number
6	1/8	-6M0-7-2RP
	1/4	-6M0-7-4RP
22	3/4	-22M0-7-12RP
25	1	-25M0-7-16RP

# Female Connectors

Installation

Straight Fittings

Elbows and Tees

Adapters

Parts

Accessories

## ISO/BSP Parallel Thread (RG, Gauge)



Tube OD in.	ISO Thread Size in.	Basic Ordering Number
1/8	1/4	-200-7-4RG
1/4	1/8	-400-7-2RG
	1/4	-400-7-4RG
	3/8	-400-7-6RG
	1/2	-400-7-8RG
5/16	1/4	-500-7-4RG
	1/2	-500-7-8RG
3/8	1/4	-600-7-4RG
	3/8	-600-7-6RG
	1/2	-600-7-8RG
1/2	3/8	-810-7-6RG
	1/2	-810-7-8RG

Tube OD mm	ISO Thread Size in.	Basic Ordering Number
3	1/4	-3M0-7-4RG
6	1/8	-6M0-7-2RG
	1/4	-6M0-7-4RG
	3/8	-6M0-7-6RG
	1/2	-6M0-7-8RG
8	1/4	-8M0-7-4RG
	3/8	-8M0-7-6RG
	1/2	-8M0-7-8RG
10	1/4	-10M0-7-4RG
	3/8	-10M0-7-6RG
	1/2	-10M0-7-8RG
12	1/4	-12M0-7-4RG
	3/8	-12M0-7-6RG
	1/2	-12M0-7-8RG
20	1/2	-20M0-7-8RG
22	1/2	-22M0-7-8RG

# Female Connectors

## Bulkhead NPT



Tube OD in.	NPT Size in.	Basic Ordering Number
1/8	1/8	-200-71-2
1/4	1/8	-400-71-2
	1/4	-400-71-4
3/8	1/4	-600-71-4
1/2	3/8	-810-71-6
	1/2	-810-71-8

Tube OD mm	NPT Size in.	Basic Ordering Number
6	1/4	-6M0-71-4
12	1/2	-12M0-71-8

# Reducers

Installation

## Reducer (Fractional)



1 in. and Under



Over 1 in.

Tube OD, in.		Basic Ordering Number
T	Tx	
1/16	1/8	-100-R-2
	1/4	-100-R-4
1/8	1/16	-200-R-1
	1/8	-200-R-2
	3/16	-200-R-3
	1/4	-200-R-4
	3/8	-200-R-6
	1/2	-200-R-8
3/16	1/8	-300-R-2
	1/4	-300-R-4
1/4	1/8	-400-R-2
	3/16	-400-R-3
	1/4	-400-R-4
	5/16	-400-R-5
	3/8	-400-R-6
	1/2	-400-R-8
	5/8	-400-R-10
	3/4	-400-R-12
	5/16	-500-R-6
	1/2	-500-R-8
3/8	1/4	-600-R-4
	3/8	-600-R-6
	1/2	-600-R-8
	5/8	-600-R-10
	3/4	-600-R-12
1/2	1/4	-810-R-4
	3/8	-810-R-6
	1/2	-810-R-8
	5/8	-810-R-10
	3/4	-810-R-12
	1	-810-R-16
5/8	3/4	-1010-R-12
	7/8	-1010-R-14
	1	-1010-R-16
3/4	1/2	-1210-R-8
	1	-1210-R-16
1	1 1/4	-1610-R-20 <sup>①</sup>
	1 1/2	-1610-R-24 <sup>①</sup>
	2	-1610-R-32 <sup>①</sup>
1 1/4	1 1/2	-2000-R-24 <sup>①</sup>
	2	-2000-R-32 <sup>①</sup>
1 1/2	2	-2400-R-32 <sup>①</sup>

① Furnished with nut and preswaged ferrules.

Straight Fittings

Elbows and Tees

Adapters

Parts

Accessories

# Reducers

## Reducer (Metric)



Tube OD, mm		Basic Ordering Number
T	$T_x$	
2	3	-2M0-R-3M
3	4	-3M0-R-4M
	6	-3M0-R-6M
	10	-3M0-R-10M
4	6	-4M0-R-6M
6	3	-6M0-R-3M
	8	-6M0-R-8M
	10	-6M0-R-10M
	12	-6M0-R-12M
	18	-6M0-R-18M
8	6	-8M0-R-6M
	10	-8M0-R-10M
	12	-8M0-R-12M
10	6	-10M0-R-6M
	8	-10M0-R-8M
	12	-10M0-R-12M
	15	-10M0-R-15M
	18	-10M0-R-18M
12	6	-12M0-R-6M
	8	-12M0-R-8M
	10	-12M0-R-10M
	16	-12M0-R-16M
	18	-12M0-R-18M
	20	-12M0-R-20M
	22	-12M0-R-22M
	25	-12M0-R-25M
16	12	-16M0-R-12M
18	12	-18M0-R-12M
	16	-18M0-R-16M
	20	-18M0-R-20M
	22	-18M0-R-22M
	25	-18M0-R-25M
20	16	-20M0-R-16M
	18	-20M0-R-18M
	22	-20M0-R-22M
	25	-20M0-R-25M
22	18	-22M0-R-18M
	20	-22M0-R-20M
	25	-22M0-R-25M
25	18	-25M0-R-18M
	20	-25M0-R-20M

# Reducers

## *Reducer (Metric to Fractional)*



Tube OD		Basic Ordering Number
T, mm	Tx, in.	
2	1/8	-2M0-R-2
3	1/8	-3M0-R-2
	1/4	-3M0-R-4
4	1/4	-4M0-R-4
6	1/8	-6M0-R-2
	1/4	-6M0-R-4
	5/16	-6M0-R-5
	3/8	-6M0-R-6
	1/2	-6M0-R-8
8	1/4	-8M0-R-4
	3/8	-8M0-R-6
	1/2	-8M0-R-8
10	3/8	-10M0-R-6
	1/2	-10M0-R-8
12	1/2	-12M0-R-8
	3/4	-12M0-R-12
18	3/4	-18M0-R-12
	1	-18M0-R-16
25	1	-25M0-R-16

## *Reducer (Fractional to Metric)*

Tube OD		Basic Ordering Number
T, in.	Tx, mm	
1/8	6	-200-R-6M

# Reducers

## Long Reducer



Tube OD, in.		Basic Ordering Number
T	Tx	-600-RF-8
3/8	1/2	

Use only long reducers in female Swagelok end connections.

## Bulkhead Reducer



Tube OD in,	Basic Ordering Number
1/8	-200-R1-2
1/4	-400-R1-4
3/8	-600-R1-6
1/2	-810-R1-8
5/8	-1010-R1-10
3/4	-1210-R1-12
1	-1610-R1-16

# Port Connectors

Installation

## Port Connector



1 in./25 mm and Under



Over 1 in./25 mm

Straight Fittings

Elbows and Tees

Adapters

Parts

Accessories

Tube OD in.	Basic Ordering Number
1/16	-101-PC
1/8	-201-PC
1/4	-401-PC
5/16	-501-PC
3/8	-601-PC
1/2	-811-PC
5/8	-1011-PC
3/4	-1211-PC
1	-1611-PC
1 1/4	-2000-PC <sup>①</sup>
1 1/2	-2400-PC <sup>①</sup>
2	-3200-PC <sup>①</sup>

① Furnished with nut and preswaged ferrules.

Tube OD mm	Basic Ordering Number
3	-3M1-PC
6	-6M1-PC
8	-8M1-PC
10	-10M1-PC
12	-12M1-PC
15	-15M1-PC
16	-16M1-PC
18	-18M1-PC
20	-20M1-PC
25	-25M1-PC
28	-28M0-PC <sup>①</sup>
30	-30M0-PC <sup>①</sup>
32	-32M0-PC <sup>①</sup>
38	-38M0-PC <sup>①</sup>

① Furnished with nut and preswaged ferrules.

# Port Connectors

## Reducing Port Connector



Tube OD, in.		Basic Ordering Number
T	Tx	
1/8	1/16	-201-PC-1
1/4	1/16	-401-PC-1
	1/8	-401-PC-2
3/8	1/8	-601-PC-2
	1/4	-601-PC-4
1/2	1/4	-811-PC-4
	3/8	-811-PC-6
3/4	1/2	-1211-PC-8
1	1/2	-1611-PC-8
	3/4	-1611-PC-12

Tube OD, mm		Basic Ordering Number
T	Tx	
6	3	-6M1-PC-3M
8	6	-8M1-PC-6M
10	6	-10M1-PC-6M
	8	-10M1-PC-8M
12	6	-12M1-PC-6M
	8	-12M1-PC-8M
	10	-12M1-PC-10M
16	12	-16M1-PC-12M
28	25	-28M1-PC-25M
32	25	-32M1-PC-25M
38	25	-38M1-PC-25M

# Caps and Plugs

## Cap



Installation

Straight Fittings

Elbows and Tees

Adapters

Parts

Accessories

Tube OD in.	Basic Ordering Number
1/16	-100-C
1/8	-200-C
3/16	-300-C
1/4	-400-C
5/16	-500-C
3/8	-600-C
1/2	-810-C
5/8	-1010-C
3/4	-1210-C
7/8	-1410-C
1	-1610-C
1 1/8	-1810-C
1 1/4	-2000-C
1 1/2	-2400-C
2	-3200-C

Tube OD mm	Basic Ordering Number
2	-2M0-C
3	-3M0-C
4	-4M0-C
6	-6M0-C
8	-8M0-C
10	-10M0-C
12	-12M0-C
14	-14M0-C
15	-15M0-C
16	-16M0-C
18	-18M0-C
20	-20M0-C
22	-22M0-C
25	-25M0-C
28	-28M0-C
30	-30M0-C
32	-32M0-C
38	-38M0-C

# Caps and Plugs

## Plug



Tube OD in.	Basic Ordering Number
1/16	-100-P
1/8	-200-P
3/16	-300-P
1/4	-400-P
5/16	-500-P
3/8	-600-P
1/2	-810-P
5/8	-1010-P
3/4	-1210-P
7/8	-1410-P
1	-1610-P
1 1/4	-2000-P
1 1/2	-2400-P
2	-3200-P

Tube OD mm	Basic Ordering Number
2	-2M0-P
3	-3M0-P
4	-4M0-P
6	-6M0-P
8	-8M0-P
10	-10M0-P
12	-12M0-P
15	-15M0-P
16	-16M0-P
18	-18M0-P
20	-20M0-P
22	-22M0-P
25	-25M0-P
28	-28M0-P
30	-30M0-P
32	-32M0-P
38	-38M0-P

# Vent Protectors

## Mud Dauber

Swagelok vent protectors, more commonly known as **mud dauber fittings**, protect open ends of instruments, tubing, outlet vents, and bleed-off lines.

The mesh wire screen prevents foreign objects, such as mud dauber insects, from entering and clogging various systems and causing damage.

Vent protectors are available in stainless steel and brass. To order brass, replace **SS** in the ordering number with **B**.

Example: **B-MD-2**



NPT Size in.	Ordering Number
1/8	SS-MD-2
1/4	SS-MD-4
3/8	SS-MD-6
1/2	SS-MD-8
3/4	SS-MD-12

# Elbows Unions



Tube OD in.	Basic Ordering Number
1/16	-100-9
1/8	-200-9
3/16	-300-9
1/4	-400-9
5/16	-500-9
3/8	-600-9
1/2	-810-9
5/8	-1010-9
3/4	-1210-9
7/8	-1410-9
1	-1610-9
1 1/8	-1810-9
1 1/4	-2000-9
1 1/2	-2400-9
2	-3200-9

Tube OD mm	Basic Ordering Number
3	-3M0-9
4	-4M0-9
6	-6M0-9
8	-8M0-9
10	-10M0-9
12	-12M0-9
14	-14M0-9
15	-15M0-9
16	-16M0-9
18	-18M0-9
20	-20M0-9
22	-22M0-9
25	-25M0-9
28	-28M0-9
30	-30M0-9
32	-32M0-9
38	-38M0-9
50	-50M0-9

Installation

Straight Fittings

Elbows and Tees

Adapters

Parts

Accessories

**Male****NPT**

Tube OD in.	NPT Size in.	Basic Ordering Number
1/16	1/16	-100-2-1
	1/8	-100-2-2
1/8	1/16	-200-2-1
	1/8	-200-2-2
	1/4	-200-2-4
3/16	1/8	-300-2-2
	1/4	-300-2-4
1/4	1/16	-400-2-1
	1/8	-400-2-2
	1/4	-400-2-4
	3/8	-400-2-6
	1/2	-400-2-8
5/16	1/8	-500-2-2
	1/4	-500-2-4
	3/8	-500-2-6
3/8	1/8	-600-2-2
	1/4	-600-2-4
	3/8	-600-2-6
	1/2	-600-2-8
	3/4	-600-2-12
1/2	1/4	-810-2-4
	3/8	-810-2-6
	1/2	-810-2-8
	3/4	-810-2-12
5/8	3/8	-1010-2-6
	1/2	-1010-2-8
	3/4	-1010-2-12
3/4	1/2	-1210-2-8
	3/4	-1210-2-12
7/8	3/4	-1410-2-12
1	3/4	-1610-2-12
	1	-1610-2-16
1 1/4	1 1/4	-2000-2-20
1 1/2	1 1/2	-2400-2-24
2	2	-3200-2-32

**Male****NPT**

Tube OD mm	NPT Size in.	Basic Ordering Number
3	1/8	-3M0-2-2
	1/4	-3M0-2-4
4	1/8	-4M0-2-2
	1/4	-4M0-2-4
6	1/8	-6M0-2-2
	1/4	-6M0-2-4
	3/8	-6M0-2-6
	1/2	-6M0-2-8
8	1/8	-8M0-2-2
	1/4	-8M0-2-4
	3/8	-8M0-2-6
	1/2	-8M0-2-8
10	1/8	-10M0-2-2
	1/4	-10M0-2-4
	3/8	-10M0-2-6
	1/2	-10M0-2-8
12	1/4	-12M0-2-4
	3/8	-12M0-2-6
	1/2	-12M0-2-8
	3/4	-12M0-2-12
15	1/2	-15M0-2-8
16	3/8	-16M0-2-6
	1/2	-16M0-2-8
	3/4	-16M0-2-12
18	1/2	-18M0-2-8
	3/4	-18M0-2-12
20	1/2	-20M0-2-8
	3/4	-20M0-2-12
22	3/4	-22M0-2-12
	1	-22M0-2-16
25	3/4	-25M0-2-12
	1	-25M0-2-16
30	1 1/4	-30M0-2-20
32	1 1/4	-32M0-2-20
38	1 1/2	-38M0-2-24

# Male


## *ISO/BSP Tapered Thread (RT)*



Tube OD in.	ISO Thread Size in.	Basic Ordering Number
1/8	1/8	-200-2-2RT
	1/4	-200-2-4RT
1/4	1/8	-400-2-2RT
	1/4	-400-2-4RT
	3/8	-400-2-6RT
	1/2	-400-2-8RT
5/16	1/4	-500-2-4RT
3/8	1/8	-600-2-2RT
	1/4	-600-2-4RT
	3/8	-600-2-6RT
1/2	1/4	-810-2-4RT
	3/8	-810-2-6RT
	1/2	-810-2-8RT
3/4	1/2	-1210-2-8RT
1	1	-1610-2-16RT

**Male*****ISO/BSP  
Tapered  
Thread (RT)***

Tube OD mm	ISO Thread Size in.	Basic Ordering Number
3	1/8	-3M0-2-2RT
	1/4	-3M0-2-4RT
4	1/8	-4M0-2-2RT
	1/4	-4M0-2-4RT
6	1/8	-6M0-2-2RT
	1/4	-6M0-2-4RT
	3/8	-6M0-2-6RT
	1/2	-6M0-2-8RT
8	1/8	-8M0-2-2RT
	1/4	-8M0-2-4RT
	3/8	-8M0-2-6RT
	1/2	-8M0-2-8RT
10	1/4	-10M0-2-4RT
	3/8	-10M0-2-6RT
	1/2	-10M0-2-8RT
12	1/8	-12M0-2-2RT
	1/4	-12M0-2-4RT
	3/8	-12M0-2-6RT
	1/2	-12M0-2-8RT
	3/4	-12M0-2-12RT
14	1/2	-14M0-2-8RT
15	1/2	-15M0-2-8RT
16	3/8	-16M0-2-6RT
	1/2	-16M0-2-8RT
18	1/2	-18M0-2-8RT
	3/4	-18M0-2-12RT
20	1/2	-20M0-2-8RT
	3/4	-20M0-2-12RT
22	3/4	-22M0-2-12RT
	1	-22M0-2-16RT
25	3/4	-25M0-2-12RT
	1	-25M0-2-16RT
28	1	-28M0-2-16RT

**Male****Reducing**

Tube OD, mm		Basic Ordering Number
T	Tx	
6	6	-6M0-2R-6M
12	12	-12M0-2R-12M

**Positionable,  
SAE/MS  
Straight  
Thread (ST)**

Tube OD in.	SAE/MS Thread Size	Basic Ordering Number
1/4	7/16-20 9/16-18	-400-2-4ST -400-2-6ST
5/16	1/2-20	-500-2-5ST
3/8	7/16-20 9/16-18 3/4-16	-600-2-4ST -600-2-6ST -600-2-8ST
1/2	9/16-18 3/4-16	-810-2-6ST -810-2-8ST
5/8	7/8-14	-1010-2-10ST
3/4	1 1/16-12	-1210-2-12ST
7/8	1 3/16-12	-1410-2-14ST
1	1 5/16-12	-1610-2-16ST
1 1/4	1 5/8-12	-2000-2-20ST
1 1/2	1 7/8-12	-2400-2-24ST
2	2 1/2-12	-3200-2-32ST

# Male

**Positionable,  
ISO/BSP  
Parallel  
Thread (PR)**



Tube OD in.	ISO Thread Size in.	Basic Ordering Number
1/4	1/8	-400-2-2PR
	1/4	-400-2-4PR
3/8	1/4	-600-2-4PR
	3/8	-600-2-6PR
1/2	1/4	-810-2-4PR
	3/8	-810-2-6PR
	1/2	-810-2-8PR
5/8	1/2	-1010-2-8PR
3/4	1/2	-1210-2-8PR
	3/4	-1210-2-12PR
1	3/4	-1610-2-12PR
	1	-1610-2-16PR

Tube OD mm	ISO Thread Size in.	Basic Ordering Number
6	1/8	-6M0-2-2PR
	1/4	-6M0-2-4PR
8	1/8	-8M0-2-2PR
	1/4	-8M0-2-4PR
10	1/4	-10M0-2-4PR
	3/8	-10M0-2-6PR
12	1/4	-12M0-2-4PR
	3/8	-12M0-2-6PR
	1/2	-12M0-2-8PR
	3/4	-12M0-2-12PR

# Weld

## Tube Socket Weld



Tube OD in.	Socket Weld Size in,	Basic Ordering Number
1/4	1/4	-400-9-4W
3/8	3/8	-600-9-6W
1/2	1/2	-810-9-8W
3/4	3/4	-1210-9-12W
1	1	-1610-9-16W

## Male Pipe Weld



Tube OD in.	Pipe Weld Size in.	Basic Ordering Number
1/4	1/8 1/4	-400-2-2W -400-2-4W
3/8	1/4	-600-2-4W
1/2	1/2	-810-2-8W
3/4	3/4	-1210-2-12W

## Female

### NPT



Tube OD in.	NPT Size in.	Basic Ordering Number
1/8	1/8	-200-8-2
	1/4	-200-8-4
3/16	1/8	-300-8-2
1/4	1/8	-400-8-2
	1/4	-400-8-4
	3/8	-400-8-6
	1/2	-400-8-8
5/16	1/8	-500-8-2
	1/4	-500-8-4
3/8	1/8	-600-8-2
	1/4	-600-8-4
	3/8	-600-8-6
	1/2	-600-8-8
1/2	1/4	-810-8-4
	3/8	-810-8-6
	1/2	-810-8-8
5/8	3/8	-1010-8-6
	1/2	-1010-8-8
3/4	1/2	-1210-8-8
	3/4	-1210-8-12
7/8	3/4	-1410-8-12
1	3/4	-1610-8-12
	1	-1610-8-16

Tube OD mm	NPT Size in.	Basic Ordering Number
6	1/8	-6M0-8-2
	1/4	-6M0-8-4
	1/2	-6M0-8-8
8	1/4	-8M0-8-4
10	1/8	-10M0-8-2
	1/4	-10M0-8-4
12	1/4	-12M0-8-4
	1/2	-12M0-8-8
16	1/2	-16M0-8-8

# Male

## NPT



Tube OD in,	NPT Size in,	Basic Ordering Number
1/4	1/8	-400-5-2
	1/4	-400-5-4
3/8	1/8	-600-5-2
	1/4	-600-5-4
	3/8	-600-5-6
1/2	3/8	-810-5-6
	1/2	-810-5-8
3/4	3/4	-1210-5-12
1	1	-1610-5-16

## Positionable, SAE/MS Straight Thread (ST)



Tube OD in,	SAE/MS Thread Size	Basic Ordering Number
1/4	7/16-20	-400-5-4ST
3/8	9/16-18	-600-5-6ST
1/2	3/4-16	-810-5-8ST
3/4	1 1/16-12	-1210-5-12ST
1	1 5/16-12	-1610-5-16ST

# Tees Unions

## *Union*



Tube OD in.	Basic Ordering Number
1/16	-100-3
1/8	-200-3
3/16	-300-3
1/4	-400-3
5/16	-500-3
3/8	-600-3
1/2	-810-3
5/8	-1010-3
3/4	-1210-3
7/8	-1410-3
1	-1610-3
1 1/8	-1810-3
1 1/4	-2000-3
1 1/2	-2400-3
2	-3200-3

Tube OD mm	Basic Ordering Number
2	-2M0-3
3	-3M0-3
4	-4M0-3
6	-6M0-3
8	-8M0-3
10	-10M0-3
12	-12M0-3
14	-14M0-3
15	-15M0-3
16	-16M0-3
18	-18M0-3
20	-20M0-3
22	-22M0-3
25	-25M0-3
28	-28M0-3
30	-30M0-3
32	-32M0-3
38	-38M0-3
50	-50M0-3

# Unions

## Reducing Union




Tube OD, in.		Basic Ordering Number
T	Tx	
3/8	1/4	-600-3-6-4
1/2	1/4	-810-3-8-4
	3/8	-810-3-8-6
5/8	3/8	-1010-3-10-6
3/4	3/8	-1210-3-12-6
	1/2	-1210-3-12-8
1	3/8	-1610-3-16-6
	1/2	-1610-3-16-8
	3/4	-1610-3-16-12
1 1/4	1	-2000-3-20-16
1 1/2	1	-2400-3-24-16
2	1	-3200-3-32-16


Tube OD, mm		Basic Ordering Number
T	Tx	
3	6	-3M0-3-3M-6M
8		-8M0-3-8M-6M
10		-10M0-3-10M-6M
12		-12M0-3-12M-6M
15	12	-15M0-3-15M-12M
16		-16M0-3-16M-12M
18		-18M0-3-18M-12M
22		-22M0-3-22M-12M
25		-25M0-3-25M-12M

# Unions


## Reducing Union



Tube OD, in.		Basic Ordering Number	
T	Tx		
3/8	1/4	-600-3-4-6	



Tube OD, in.		Basic Ordering Number	
T	Tx		
1/2		-810-3-6-6	
5/8	3/8	-1010-3-6-6	
3/4		-1210-3-6-6	



Tube OD, in.			Basic Ordering Number	
T	Tx	Tx <sub>1</sub>		
5/8	1/2		-1010-3-8-6	
3/4	1/2	3/8	-1210-3-8-6	
1	3/4		-1610-3-12-6	

# Male

## **Branch, NPT (TTM)**



Tube OD in.	NPT Size in.	Basic Ordering Number
1/8	1/8	-200-3TTM
	1/4	-200-3-4TTM
3/16	1/8	-300-3TTM
1/4	1/8	-400-3TTM
	1/4	-400-3-4TTM
5/16	1/8	-500-3TTM
3/8	1/4	-600-3TTM
	3/8	-600-3-6TTM
1/2	3/8	-810-3TTM
	1/2	-810-3-8TTM
5/8	1/2	-1010-3TTM
3/4	3/4	-1210-3TTM

Tube OD mm	NPT Size in.	Basic Ordering Number
6	1/8	-6M0-3TTM
	1/4	-6M0-3-4TTM
8	1/8	-8M0-3TTM
8	1/4	-8M0-3-4TTM
10	1/4	-10M0-3TTM
12	3/8	-12M0-3TTM
	1/4	-12M0-3-4TTM
	1/2	-12M0-3-8TTM
16	1/2	-16M0-3TTM

**Male****Run, NPT (TMT)**

Tube OD in.	NPT Size in.	Basic Ordering Number
1/8	1/8	-200-3TMT
	1/4	-200-3-4TMT
3/16	1/8	-300-3TMT
1/4	1/8	-400-3TMT
	1/4	-400-3-4TMT
5/16	1/8	-500-3TMT
3/8	1/4	-600-3TMT
	3/8	-600-3-6TMT
1/2	3/8	-810-3TMT
	1/2	-810-3-8TMT
5/8	1/2	-1010-3TMT
3/4	3/4	-1210-3TMT

Tube OD mm	NPT Size in.	Basic Ordering Number
6	1/8	-6M0-3TMT
	1/4	-6M0-3-4TMT
8	1/4	-8M0-3-4TMT
	1/2	-12M0-3-4TMT
12	1/4	-12M0-3-8TMT
	1/2	-16M0-3TMT

# Male

## **Positionable Branch, SAE/MS Straight Thread (TTS)**



Tube OD in,	SAE/MS Thread Size	Basic Ordering Number
1/4	7/16-20	-400-3TTS
3/8	9/16-18	-600-3TTS
1/2	3/4-16	-810-3TTS
3/4	1 1/16-12	-1210-3TTS
1	1 5/16-12	-1610-3TTS
1 1/4	1 5/8-12	-2000-3TTS
1 1/2	1 7/8-12	-2400-3TTS
2	2 1/2-12	-3200-3TTS

## **Positionable Run, SAE/MS Straight Thread (TST)**



Tube OD in,	SAE/MS Thread Size	Basic Ordering Number
1/4	7/16-20	-400-3TST
3/8	9/16-18	-600-3TST
1/2	3/4-16	-810-3TST
3/4	1 1/16-12	-1210-3TST
1	1 5/16-12	-1610-3TST
1 1/4	1 5/8-12	-2000-3TST
1 1/2	1 7/8-12	-2400-3TST
2	2 1/2-12	-3200-3TST

## Male

**Positionable  
Branch,  
ISO/BSP Parallel  
Thread (TTR)**



Tube OD in.	ISO Thread Size in.	Basic Ordering Number
1/4	1/8 1/4	-400-3TTR -400-3-4TTR
3/8	1/4	-600-3TTR
1/2	3/8 1/2	-810-3TTR -810-3-8TTR
5/8	1/2	-1010-3TTR
3/4	3/4 1/2	-1210-3TTR -1210-3-8TTR
1	1	-1610-3TTR

Tube OD mm	ISO Thread Size in.	Basic Ordering Number
6	1/8 1/4	-6M0-3TTR -6M0-3-4TTR
8	1/8 1/4	-8M0-3TTR -8M0-3-4TTR
10	1/4	-10M0-3TTR
12	3/8 1/2	-12M0-3TTR -12M0-3-8TTR

# Male

## **Positionable Run, ISO/BSP Parallel Thread (TRT)**



Tube OD in.	ISO Thread Size in.	Basic Ordering Number
1/4	1/8 1/4	-400-3TRT -400-3-4TRT
3/8	1/4	-600-3TRT
1/2	3/8 1/2	-810-3TRT -810-3-8TRT
5/8	1/2	-1010-3TRT
3/4	3/4 1/2	-1210-3TRT -1210-3-8TRT
1	1	-1610-3TRT

Tube OD mm	ISO Thread Size in.	Basic Ordering Number
6	1/8 1/4	-6M0-3TRT -6M0-3-4TRT
8	1/8 1/4	-8M0-3TRT -8M0-3-4TRT
10	1/4	-10M0-3TRT
12	3/8 1/2	-12M0-3TRT -12M0-3-8TRT

## Female

### *Run, NPT (TFT)*



Tube OD in.	NPT Size in.	Basic Ordering Number
1/8	1/8	-200-3TFT
1/4	1/8	-400-3TFT
	1/4	-400-3-4TFT
3/8	1/4	-600-3TFT
1/2	3/8	-810-3TFT
	1/2	-810-3-8TFT
3/4	3/4	-1210-3TFT
1	3/4	-1610-3-12TFT
	1	-1610-3TFT

Tube OD mm	NPT Size in.	Basic Ordering Number
6	1/8	-6M0-3TFT
	1/4	-6M0-3-4TFT
8	1/8	-8M0-3TFT
	1/4	-8M0-3-4TFT
10	1/4	-10M0-3TFT
12	1/4	-12M0-3-4TFT
	3/8	-12M0-3TFT
	1/2	-12M0-3-8TFT
16	1/2	-16M0-3TFT

# Female

## Branch, NPT (TTF)



Tube OD in.	NPT Size in.	Basic Ordering Number
1/8	1/8	-200-3TTF
1/4	1/8 1/4	-400-3TTF -400-3-4TTF
3/8	1/4	-600-3TTF
	3/8	-600-3-6TTF
	1/2	-600-3-8TTF
1/2	1/4	-810-3-4TTF
	3/8	-810-3TTF
	1/2	-810-3-8TTF
5/8	1/2	-1010-3TTF
3/4	3/4	-1210-3TTF
1	3/4	-1610-3-12TTF
	1	-1610-3TTF

Tube OD mm	NPT Size in.	Basic Ordering Number
6	1/8	-6M0-3TTF
	1/4	-6M0-3-4TTF
8	1/8	-8M0-3TTF
	1/4	-8M0-3-4TTF
10	1/4	-10M0-3TTF
12	1/4	-12M0-3-4TTF
	3/8	-12M0-3TTF
	1/2	-12M0-3-8TTF
16	1/2	-16M0-3TTF

# Union



Tube OD in.	Basic Ordering Number
1/8	-200-4
1/4	-400-4
5/16	-500-4
3/8	-600-4
1/2	-810-4
3/4	-1210-4
1	-1610-4

Tube OD mm	Basic Ordering Number
3	-3M0-4
6	-6M0-4
8	-8M0-4
10	-10M0-4
12	-12M0-4
16	-16M0-4
18	-18M0-4
20	-20M0-4
22	-22M0-4
25	-25M0-4

Installation

Straight Fittings

Elbows and Tees

Adapters

Parts

Accessories

# Kwik-Clamp Flange To Swagelok Tube Fitting

Installation


Straight Fittings

Elbows and Tees

Adapters

Parts

Accessories



Tube OD in.	Flange Size in.	Ordering Number
1/4	1/2	SS-400-SC-8
	3/4	SS-400-SC-12
	1	SS-400-SC-16
	1 1/2	SS-400-SC-24
3/8	1/2	SS-600-SC-8
	3/4	SS-600-SC-12
	1	SS-600-SC-16
	1 1/2	SS-600-SC-24
1/2	1/2	SS-810-SC-8
	3/4	SS-810-SC-12
	1	SS-810-SC-16
	1 1/2	SS-810-SC-24
1	1	SS-1610-SC-16
	2	SS-1610-SC-32

# Tube Adapters

## Male

**NPT**



1 in./25 mm and Under



Over 1 in./25 mm

Tube OD in.	NPT Size in.	Basic Ordering Number
1/8	1/8	-2-TA-1-2
	1/4	-2-TA-1-4
3/16	1/8	-3-TA-1-2
	1/4	-3-TA-1-4
	1/8	-4-TA-1-2
	1/4	-4-TA-1-4
1/4	3/8	-4-TA-1-6
	1/2	-4-TA-1-8
	1/8	-5-TA-1-2
	1/4	-5-TA-1-4
5/16	1/8	-6-TA-1-2
	1/4	-6-TA-1-4
	3/8	-6-TA-1-6
	1/2	-6-TA-1-8
1/2	1/4	-8-TA-1-4
	3/8	-8-TA-1-6
	1/2	-8-TA-1-8
5/8	1/2	-10-TA-1-8
3/4	1/2	-12-TA-1-8
	3/4	-12-TA-1-12
1	3/4	-16-TA-1-12
	1	-16-TA-1-16
1 1/4	1 1/4	-20-TA-1-20 <sup>①</sup>
1 1/2	1 1/2	-24-TA-1-24 <sup>①</sup>
2	2	-32-TA-1-32 <sup>①</sup>

**⚠ Swagelok tube adapters are to be used ONLY in Swagelok tube fittings. Use in fittings made by other manufacturers may result in leakage or slippage.**

<sup>①</sup> Furnished with nut and preswaged ferrules.

Tube OD mm	NPT Size in.	Basic Ordering Number
6	1/8	-6-MTA-1-2
	1/4	-6-MTA-1-4
8	1/4	-8-MTA-1-4
	3/8	-8-MTA-1-6
	1/2	-10-MTA-1-4
10	3/8	-10-MTA-1-6
	1/2	-10-MTA-1-8
	1/4	-12-MTA-1-4
12	1/2	-12-MTA-1-8
	1/4	-12-MTA-1-4
28	1	-28-MTA-1-16 <sup>①</sup>
	1 1/4	-28-MTA-1-20 <sup>①</sup>
30	1	-30-MTA-1-16 <sup>①</sup>
	1 1/4	-30-MTA-1-20 <sup>①</sup>
32	1 1/4	-32-MTA-1-20 <sup>①</sup>
38	1 1/2	-38-MTA-1-24 <sup>①</sup>

# Male

## ***ISO/BSP Tapered Thread (RT)***

**1 in./25 mm and Under****Over 1 in./25 mm**

Tube OD in.	ISO Thread Size in.	Basic Ordering Number
1/8	1/8	-2-TA-1-2RT
	1/4	-2-TA-1-4RT
1/4	1/8	-4-TA-1-2RT
	1/4	-4-TA-1-4RT
3/8	1/4	-6-TA-1-4RT
	3/8	-6-TA-1-6RT
	1/2	-6-TA-1-8RT
1/2	1/4	-8-TA-1-4RT
	3/8	-8-TA-1-6RT
	1/2	-8-TA-1-8RT
3/4	3/4	-12-TA-1-12RT
1	1	-16-TA-1-16RT

Tube OD mm	ISO Thread Size in.	Basic Ordering Number
6	1/8	-6-MTA-1-2RT
	1/4	-6-MTA-1-4RT
8	1/4	-8-MTA-1-4RT
10	1/4	-10-MTA-1-4RT
	3/8	-10-MTA-1-6RT
12	1/4	-12-MTA-1-4RT
	3/8	-12-MTA-1-6RT
	1/2	-12-MTA-1-8RT
28	1	-28-MTA-1-16RT <sup>①</sup>
	1 1/4	-28-MTA-1-20RT <sup>①</sup>
30	1 1/4	-30-MTA-1-20RT <sup>①</sup>
32	1 1/4	-32-MTA-1-20RT <sup>①</sup>
38	1 1/2	-38-MTA-1-24RT <sup>①</sup>

① Furnished with nut and preswaged ferrules.

# Male

## ISO/BSP Parallel Thread (RS)



1 in./25 mm and Under



Over 1 in./25 mm

Tube OD in.	ISO Thread Size in.	Basic Ordering Number
1/8	1/8	-2-TA-1-2RS
	1/4	-2-TA-1-4RS
1/4	1/8	-4-TA-1-2RS
	1/4	-4-TA-1-4RS
3/8	1/4	-6-TA-1-4RS
	3/8	-6-TA-1-6RS
1/2	1/4	-8-TA-1-4RS
	3/8	-8-TA-1-6RS
	1/2	-8-TA-1-8RS
3/4	3/4	-12-TA-1-12RS
1	1	-16-TA-1-16RS

Tube OD mm	ISO Thread Size in.	Basic Ordering Number
6	1/8	-6-MTA-1-2RS
	1/4	-6-MTA-1-4RS
8	1/4	-8-MTA-1-4RS
10	1/4	-10-MTA-1-4RS
	3/8	-10-MTA-1-6RS
	1/2	-10-MTA-1-8RS
12	1/4	-12-MTA-1-4RS
	3/8	-12-MTA-1-6RS
	1/2	-12-MTA-1-8RS
18	1/2	-18-MTA-1-8RS
	3/4	-18-MTA-1-12RS
28	1	-28-MTA-1-16RS <sup>①</sup>
	1 1/4	-28-MTA-1-20RS <sup>①</sup>
30	1 1/4	-30-MTA-1-20RS <sup>①</sup>
32	1 1/4	-32-MTA-1-20RS <sup>①</sup>
38	1 1/2	-38-MTA-1-24RS <sup>①</sup>

① Furnished with nut and preswaged ferrules.

# Male

## *ISO/BSP Parallel Thread (RP)*



Tube OD mm	ISO Thread Size in.	Basic Ordering Number
28	1 1 1/4	-28-MTA-1-16RP <sup>①</sup> -28-MTA-1-20RP <sup>①</sup>
30	1 1/4	-30-MTA-1-20RP <sup>①</sup>
32	1 1/4	-32-MTA-1-20RP <sup>①</sup>
38	1 1/2	-38-MTA-1-24RP <sup>①</sup>

① Furnished with nut and preswaged ferrules.

## *SAE/MS Straight Thread (ST)*



1 in./25 mm and Under



Over 1 in./25 mm

Tube OD in.	SAE/MS Thread Size	Basic Ordering Number
1/8	5/16-24	-2-TA-1-2ST
1/4	7/16-20	-4-TA-1-4ST
3/8	7/16-20 9/16-18 3/4-16	-6-TA-1-4ST -6-TA-1-6ST -6-TA-1-8ST
1/2	9/16-18 3/4-16	-8-TA-1-6ST -8-TA-1-8ST
5/8	7/8-14	-10-TA-1-10ST
3/4	1 1/16-12	-12-TA-1-12ST
1	1 5/16-12	-16-TA-1-16ST
1 1/4	1 5/8-12	-20-TA-1-20ST <sup>①</sup>
1 1/2	1 7/8-12	-24-TA-1-24ST <sup>①</sup>
2	2 1/2-12	-32-TA-1-32ST <sup>①</sup>

① Furnished with nut and preswaged ferrules.

## Male

### O-Seal (SAE/MS Straight Thread)



Tube OD in.	SAE/MS Thread Size	Basic Ordering Number
1/8	5/16-24	-2-TA-1-OR
3/16	3/8-24	-3-TA-1-OR
1/4	7/16-20	-4-TA-1-OR
5/16	1/2-20	-5-TA-1-OR
3/8	9/16-18	-6-TA-1-OR
1/2	3/4-16	-8-TA-1-OR

### AN Thread



Tube OD in.	AN Tube Flare Size in.	Thread Size	Basic Ordering Number
1/4	1/4	7/16-20UNJF-3	-4-TA-1-4AN
3/8	1/4	7/16-20UNJF-3	-6-TA-1-4AN
	3/8	9/16-18UNJF-3	-6-TA-1-6AN
1/2	1/2	3/4-16UNJF-3	-8-TA-1-8AN
3/4	3/4	1 1/16-12UNJ-3	-12-TA-1-12AN
1	1	1 5/16-12UNJ-3	-16-TA-1-16AN

### Pipe Weld



Tube OD in.	Pipe Weld Size in.	Basic Ordering Number
1/4	1/4	-4-TA-1-4W
3/8	1/2	-6-TA-1-8W
1/2	1/2	-8-TA-1-8W
	3/4	-8-TA-1-12W
3/4	3/4	-12-TA-1-12W

# Female

## NPT

**1 in./25 mm and Under****Over 1 in./25 mm**

Tube OD in.	NPT Size in.	Basic Ordering Number
1/8	1/8	-2-TA-7-2
	1/4	-2-TA-7-4
3/16	1/4	-3-TA-7-4
	1/8	-4-TA-7-2
	1/4	-4-TA-7-4
	3/8	-4-TA-7-6
1/4	1/2	-4-TA-7-8
	1/4	-5-TA-7-4
	1/8	-6-TA-7-2
	1/4	-6-TA-7-4
5/16	3/8	-6-TA-7-6
	1/2	-6-TA-7-8
	1/4	-8-TA-7-4
	3/8	-8-TA-7-6
1/2	1/2	-8-TA-7-8
	1/4	-10-TA-7-8
	3/8	-12-TA-7-8
3/4	1	-12-TA-7-12
	1/2	-12-TA-7-16
	3/4	-16-TA-7-12
1	1	-16-TA-7-16
	1 1/4	-20-TA-7-20 <sup>①</sup>
1 1/2	1 1/2	-24-TA-7-24 <sup>①</sup>
2	2	-32-TA-7-32 <sup>①</sup>

① Furnished with nut and preswaged ferrules.

Tube OD mm	NPT Size in.	Basic Ordering Number
6	1/8	-6-MTA-7-2
	1/4	-6-MTA-7-4
8	1/4	-8-MTA-7-4
	1/4	-10-MTA-7-4
	3/8	-10-MTA-7-6
10	1/2	-10-MTA-7-8
	1/4	-12-MTA-7-4
	1/2	-12-MTA-7-8
12	1/4	-12-MTA-7-4
	1/2	-12-MTA-7-8

## Female

### *ISO/BSP Tapered Thread (RT)*



Tube OD in.	ISO Thread Size in.	Basic Ordering Number
1/4	1/8	-4-TA-7-2RT
	1/4	-4-TA-7-4RT
3/8	1/4	-6-TA-7-4RT
	3/8	-6-TA-7-6RT
1/2	1/4	-8-TA-7-4RT
	3/8	-8-TA-7-6RT
	1/2	-8-TA-7-8RT

Tube OD mm	ISO Thread Size in.	Basic Ordering Number
6	1/8	-6-MTA-7-2RT
8	1/4	-8-MTA-7-4RT
10	1/4	-10-MTA-7-4RT

### *ISO/BSP Parallel Thread (RP)*

Tube OD in.	ISO Thread Size in.	Basic Ordering Number
1/8	1/8	-2-TA-7-2RP
1/4	1/8	-4-TA-7-2RP
	1/4	-4-TA-7-4RP
3/8	1/4	-6-TA-7-4RP
	3/8	-6-TA-7-6RP
1/2	3/8	-8-TA-7-6RP
	1/2	-8-TA-7-8RP

Tube OD mm	ISO Thread Size in.	Basic Ordering Number
6	1/8 1/4	-6-MTA-7-2RP -6-MTA-7-4RP
12	1/2	-12-MTA-7-8RP

## Female

### *ISO/BSP Parallel Thread (RG, Gauge)*



Tube OD in.	ISO Thread Size in.	Basic Ordering Number
1/4	1/4	-4-TA-7-4RG
3/8	3/8	-6-TA-7-6RG
1/2	1/2	-8-TA-7-8RG

Tube OD mm	ISO Thread Size in.	Basic Ordering Number
6	1/4	-6-MTA-7-4RG
	3/8	-6-MTA-7-6RG
	1/2	-6-MTA-7-8RG
8	1/4	-8-MTA-7-4RG
	3/8	-8-MTA-7-6RG
	1/2	-8-MTA-7-8RG
10	1/4	-10-MTA-7-4RG
	3/8	-10-MTA-7-6RG
	1/2	-10-MTA-7-8RG
12	1/4	-12-MTA-7-4RG
	3/8	-12-MTA-7-6RG
	1/2	-12-MTA-7-8RG
16	1/2	-16-MTA-7-8RG
18	1/2	-18-MTA-7-8RG

## Female

### ISO/BSP Parallel Thread (RJ)



ISO/BSP parallel thread (RJ) fittings are available in stainless steel only.

Tube OD in.	ISO Thread Size in.	Ordering Number
1/4	1/4	SS-4-TA-7-4RJ
3/8	3/8	SS-6-TA-7-6RJ
1/2	1/2	SS-8-TA-7-8RJ

Tube OD mm	ISO Thread Size in.	Ordering Number
6	1/4	SS-6-MTA-7-4RJ
	3/8	SS-6-MTA-7-6RJ
	1/2	SS-6-MTA-7-8RJ
8	1/4	SS-8-MTA-7-4RJ
	3/8	SS-8-MTA-7-6RJ
	1/2	SS-8-MTA-7-8RJ
10	1/4	SS-10-MTA-7-4RJ
	3/8	SS-10-MTA-7-6RJ
	1/2	SS-10-MTA-7-8RJ
12	1/4	SS-12-MTA-7-4RJ
	3/8	SS-12-MTA-7-6RJ
	1/2	SS-12-MTA-7-8RJ

### AN Thread



Tube OD in.	AN Tube Flare Size in.	Basic Ordering Number
1/8	1/8	-200-A-2ANF
	1/4	-200-A-4ANF
1/4	1/4	-400-A-4ANF
3/8	3/8	-600-A-6ANF
1/2	1/2	-810-A-8ANF
3/4	3/4	-1210-A-12ANF

# Tube Fitting Part Numbers

Swagelok tube fitting part numbers follow the sequence shown below.

**A   -   B   C   D   -   E   -   F   G**  
**SS   -   2   0   0   -   1   -   2   RT**

## **A Material**

**A** = Aluminum

**B** = Brass

**HC** = Alloy C-276

**INC** = Alloy 600

**M** = Alloy 400

**S** = Carbon steel

**SS** = 316 stainless steel

**6ELT** = High-temperature  
316 stainless steel

**T** = PTFE

**TI** = Titanium

**6MO** = 6-Moly

**625** = Alloy 625

**825** = Alloy 825

**2507** = Alloy 2507

## **B Size (Tube OD)**

Fractional, in.	Metric, mm
1 = 1/16	2 = 2
2 = 1/8	3 = 3
3 = 3/16	4 = 4
4 = 1/4	6 = 6
5 = 5/16	8 = 8
6 = 3/8	10 = 10
8 = 1/2	12 = 12
10 = 5/8	14 = 14
12 = 3/4	15 = 15
14 = 7/8	16 = 16
16 = 1	18 = 18
18 = 1 1/8	20 = 20
20 = 1 1/4	22 = 22
24 = 1 1/2	25 = 25
32 = 2	28 = 28
	32 = 32
	38 = 38
	50 = 50

**A** - **B** **C** **D** - **E** - **F** **G**  
**SS** - **2** **0** **0** - **1** - **2** **RT**

### **C Series**

**0** = Fractional 1/16 to 3/8 in.  
and 1 1/4 to 2 in.

**1** = Fractional 1/2 to 1 1/8 in.

**3** = HC 3/4 in. and 1 in. with  
advanced geometry ferrules

**M** = Millimeter tube size

To order a female Swagelok tube fitting, add **F**.

Example: SS-100F-1-1.

### **D Component**

**0** = Fitting

**1** = Body

### **E Fitting Type**

**1** = Male connector

**2** = 90° male elbow

**3** = Tee, union

**4** = Cross, union

**5** = 45° male elbow

**6** = Union

**7** = Female connector

**8** = Female elbow

**9** = Elbow, union

**11** = Bulkhead male connector

**61** = Bulkhead union

**71** = Bulkhead female connector

**A** = Adapter

**C** = Cap

**P** = Plug

**PC** = Port connector

**R** = Reducer

**R1** = Bulkhead reducer

**2R** = Reducing elbow

**TFT** = Tee, female run

**TMT** = Tee, male run

**TRT** = Tee, ISO/BSP parallel  
male positionable run

**TST** = Tee, straight thread with O-ring  
male positionable run

**TTF** = Tee, female branch

**TTM** = Tee, male branch

**TTR** = Tee, ISO/BSP parallel  
male positionable branch

**TTS** = Tee, straight thread with O-ring  
male positionable branch

**A - B C D - E - F G**  
**SS - 2 0 0 - 1 - 2 RT**

### **F Second End Connection Size**

Add a size designator from the list on page 106 for the second end connection or if the fitting is a reducing union.

### **G Second End Connection Type**

Add a second end connection type designator as needed.

**AN** = 37° male AN flare

**ANF** = 37° female AN flare

**BT** = Bored-through fitting

**F** = Female thread

**KN** = Knurled nut, nylon ferrules

**KT** = Knurled nut, PTFE ferrules

**M** = Metric tube end

**OR** = O-seal connection

**PR** = ISO/BSP positionable parallel pipe thread

**RG** = ISO/BSP parallel pipe thread (gauge)

**RJ** = ISO/BSP parallel pipe thread  
(Japanese gauge)

**RP** = ISO/BSP parallel pipe thread

**RS** = ISO/BSP parallel pipe thread

**RT** = ISO/BSP tapered pipe thread


**ST** = Straight thread with O-ring (for SAE/MS)

**W** = Male pipe weld/tube socket weld

## **Tees and Crosses**

Ordering numbers for tees and crosses indicate first the size of the run (**1** to **2**) and then the size of the branch (**3** for tees and **3** to **4** for crosses).

Example: SS-6M0-3-4TTF for a 316 SS female tee for 6 mm tube with 1/4 in. female NPT branch



# Tube Adapter Part Numbers

Swagelok tube adapter part numbers follow the sequence shown below.

**A - B - C - D - E F**  
**SS - 2 - TA - 1 - 4 RT**

## A Material

**A** = Aluminum

**B** = Brass

**HC** = Alloy C-276

**INC** = Alloy 600

**M** = Alloy 400

**S** = Steel

**SS** = Stainless steel

**6ELT** = High-temperature  
316 stainless steel

**T** = PTFE

**TI** = Titanium

**6MO** = 6-Moly

**625** = Alloy 625

**825** = Alloy 825

**2507** = Alloy 2507

## B Size (Tube OD)

Fractional, in.	Metric, mm
<b>1</b> = 1/16	<b>2</b> = 2
<b>2</b> = 1/8	<b>3</b> = 3
<b>3</b> = 3/16	<b>4</b> = 4
<b>4</b> = 1/4	<b>6</b> = 6
<b>5</b> = 5/16	<b>8</b> = 8
<b>6</b> = 3/8	<b>10</b> = 10
<b>8</b> = 1/2	<b>12</b> = 12
<b>10</b> = 5/8	<b>14</b> = 14
<b>12</b> = 3/4	<b>15</b> = 15
<b>14</b> = 7/8	<b>16</b> = 16
<b>16</b> = 1	<b>18</b> = 18
<b>18</b> = 1 1/8	<b>20</b> = 20
<b>20</b> = 1 1/4	<b>22</b> = 22
<b>24</b> = 1 1/2	<b>25</b> = 25
<b>32</b> = 2	<b>28</b> = 28
	<b>32</b> = 32
	<b>38</b> = 38
	<b>50</b> = 50

A - B - C - D - E F  
SS - 2 - TA - 1 - 4 RT

**C Component**

TA = Fractional tube adapter

MTA = Metric tube adapter

**D Adapter Type**

1 = Male adapter

7 = Female adapter

**E Second End Connection Size**

Add a size designator from the list on page 109 for the second end connection.

**F Second End Connection Type**

Add a second end connection type designator as needed.

**AN** = 37° male AN flare

**ANF** = 37° female AN flare

**RG** = ISO/BSP parallel pipe thread (gauge)

**RJ** = ISO/BSP parallel pipe thread  
(Japanese gauge)

**RP** = ISO/BSP parallel pipe thread

**RS** = ISO/BSP parallel pipe thread

**RT** = ISO/BSP tapered pipe thread

**ST** = Straight thread with O-ring (for SAE/MS)

**W** = Male pipe weld/tube socket weld

# Nuts



## Female

Tube OD in.	Basic Ordering Number
1/16	-102-1
1/8	-202-1
3/16	-302-1
1/4	-402-1
5/16	-502-1
3/8	-602-1
1/2	-812-1
5/8	-1012-1
3/4	-1212-1
7/8	-1412-1
1	-1612-1
1 1/4	-2002-1
1 1/2	-2402-1
2	-3202-1

Tube OD mm	Basic Ordering Number
2	-2M2-1
3	-3M2-1
4	-4M2-1
6	-6M2-1
8	-8M2-1
10	-10M2-1
12	-12M2-1
14	-14M2-1
15	-15M2-1
16	-16M2-1
18	-18M2-1
20	-20M2-1
22	-22M2-1
25	-25M2-1
28	-28M2-1
30	-30M2-1
32	-32M2-1
38	-38M2-1
50	-50M2-1

# Nuts



## ***Knurled Female***

The Swagelok knurled nut tube fitting provides a leak-tight seal without the use of inserts on most wall thicknesses of polyethylene tubing. Inserts may be required for larger sizes.

To set the ferrules on the tubing, initial connections must be made with a wrench, tightening the nut one and one-quarter turns from finger-tight (three-quarters turn for 1/16, 1/8 and 3/16 in.; 2, 3, and 4 mm fittings). Leak-tight connections may be reassembled with finger-tight assembly.

To order a knurled nut, add **K** to the female nut basic ordering number.

Example: B-402-1**K**

To order a knurled nut on an assembled fitting with nylon ferrules, add **KN** to the fitting ordering number.

Example: SS-400-1-2**KN**

To order a knurled nut on an assembled fitting with PTFE ferrules, add **KT** to the fitting ordering number.

Example: SS-400-1-2**KT**

## ***Male***



For use in female Swagelok end connections.

Tube OD in,	Basic Ordering Number
1/16	-1F2-1GC
1/8	-2F2-1GC
1/4	-4F2-1
1/2	-8F2-1

Tube OD mm	Basic Ordering Number
10	-10MF2-1
12	-12MF2-1

# Ferrules



## Front

Tube OD in.	Basic Ordering Number
1/16	-103-1
1/8	-203-1
3/16	-303-1
1/4	-403-1
5/16	-503-1
3/8	-603-1
1/2	-813-1
5/8	-1013-1
3/4	-1213-1
7/8	-1413-1
1	-1613-1
1 1/4	-2003-1 <sup>①</sup>
1 1/2	-2403-1 <sup>①</sup>
2	-3203-1 <sup>①</sup>

<sup>①</sup> Over 1 in. and over 25 mm stainless steel front ferrules are PFA coated. To order silver-plated front ferrules, add **-BL** to the basic ordering number.

Example:  
SS-2003-1-**BL**

Tube OD mm	Basic Ordering Number
2	-2M3-1
3	-3M3-1
4	-4M3-1
6	-6M3-1
8	-8M3-1
10	-10M3-1
12	-12M3-1
14	-14M3-1
15	-15M3-1
16	-16M3-1
18	-18M3-1
20	-20M3-1
22	-22M3-1
25	-25M3-1
28	-28M3-1 <sup>①</sup>
30	-30M3-1 <sup>①</sup>
32	-32M3-1 <sup>①</sup>
38	-38M3-1 <sup>①</sup>
50	-50M3-1 <sup>①</sup>

# Ferrules



Installation

Straight Fittings

Elbows and Tees

Adapters

Parts

Accessories

## Back

Tube OD in.	Basic Ordering Number
1/16	-104-1
1/8	-204-1
3/16	-304-1
1/4	-404-1
5/16	-504-1
3/8	-604-1
1/2	-814-1
5/8	-1014-1
3/4	-1214-1
7/8	-1414-1
1	-1614-1
1 1/4	-2004-1 <sup>①</sup>
1 1/2	-2404-1 <sup>①</sup>
2	-3204-1 <sup>①</sup>

- <sup>①</sup> Over 1 in. and over 25 mm stainless steel back ferrules are PFA coated. To order back ferrules without PFA coating, add **-WC** to the basic ordering number.

Example:  
SS-2004-1-**WC**

Tube OD mm	Basic Ordering Number
2	-2M4-1
3	-3M4-1
4	-4M4-1
6	-6M4-1
8	-8M4-1
10	-10M4-1
12	-12M4-1
14	-14M4-1
15	-15M4-1
16	-16M4-1
18	-18M4-1
20	-20M4-1
22	-22M4-1
25	-25M4-1
28	-28M4-1 <sup>①</sup>
30	-30M4-1 <sup>①</sup>
32	-32M4-1 <sup>①</sup>
38	-38M4-1 <sup>①</sup>
50	-50M4-1 <sup>①</sup>

# Nut-Ferrule Sets and Nut-Ferrule Packages

## Nut-Ferrule Set

The nut-ferrule set contains one nut, one back ferrule, and one front ferrule.

To order, add a material designator to the basic ordering number. Please order nut-ferrule sets in multiples of five.

Example: **SS-400-NFSET**

Material	Designator
Brass	B
Carbon steel	S
316 stainless steel	SS

Tube OD in.	Basic Ordering Number
1/4	-400-NFSET
3/8	-600-NFSET
1/2	-810-NFSET

Tube OD mm	Basic Ordering Number
6	-6M0-NFSET
8	-8M0-NFSET
10	-10M0-NFSET
12	-12M0-NFSET

## Nut-Ferrule Package

To order the nut-ferrule package (50 nut-ferrule sets), contact your authorized Swagelok sales and service center.



# Ferrule Sets and Ferrule-Paks

## Ferrule Set

The ferrule set contains one front ferrule and one back ferrule.

To order, add a material designator to the basic ordering number. Please order ferrule sets in multiples of ten.

Example: **SS-100-SET**


Material	Designator
Alloy 400	M
Aluminum	A
Brass	B
Carbon steel	S
Nylon	NY
PTFE	T
316 stainless steel	SS

Tube OD in.	Basic Ordering Number
1/16	-100-SET
1/8	-200-SET
3/16	-300-SET
1/4	-400-SET
5/16	-500-SET
3/8	-600-SET
1/2	-810-SET

Tube OD mm	Basic Ordering Number
6	-6M0-SET
8	-8M0-SET
10	-10M0-SET
12	-12M0-SET

## Ferrule-Pak

To order the ferrule-pak package (100 front and back sets), contact your authorized Swagelok sales and service center.



# ISO/BSP Parallel Gaskets

## **Steel and Stainless Steel (RS Fitting)**



**RS/RSD  
Gasket**

RS fitting steel gaskets provide a seal with male ISO/BSP parallel threads.

The RS gasket is of a fluorocarbon FKM inner ring bonded to a carbon steel outer ring.



**RSNB  
Gasket**

The RSD (DIN-style) gasket is a fluorocarbon FKM inner ring bonded to a stainless steel or carbon steel outer ring as recommended in ISO 1179-1973. It can be used with end connections designed in accordance with DIN 3852 Part 2.

The RSNB gasket is an all-metal 304L stainless steel gasket similar to DIN 7603 form D.

ISO Thread Size, in.	Ordering Number		
	RS Gasket <sup>①</sup>	RSD Gasket <sup>②</sup>	RSNB Gasket
1/8	S-2-RS-2V	SS-2-RSD-2V	304L-2-RSNB-2
1/4	S-4-RS-2V <sup>③</sup>	SS-4-RSD-2V	304L-4-RSNB-2
3/8	S-6-RS-2V <sup>③</sup>	SS-6-RSD-2V	304L-6-RSNB-2
1/2	S-8-RS-2V <sup>③</sup>	SS-8-RSD-2V	304L-8-RSNB-2
3/4	S-12-RS-2V	SS-12-RSD-2V	304L-12-RSNB-2
1	S-16-RS-2V	SS-16-RSD-2V	304L-16-RSNB-2
1 1/4	S-20-RS-2V	SS-20-RSD-2V	304L-20-RSNB-2
1 1/2	S-24-RS-2V	SS-24-RSD-2V	304L-24-RSNB-2

<sup>①</sup> Also available with a Buna inner ring. To order, replace **V** with **B** in the ordering number.

Example: S-2-RS-2**B**

<sup>②</sup> Also available with a carbon steel outer ring. To order, replace **SS** with **S** in the ordering number.

Example: **S**-8-RSD-2V

<sup>③</sup> Also available with a stainless steel outer ring. To order, replace **S** with **SS** in the ordering number.

Example: **SS**-8-RS-2V

# ISO/BSP Parallel Gaskets



## Copper (RP and RS Fitting)

The RP and RS fitting copper gasket provides a seal with male ISO/BSP parallel threads.

ISO Thread Size, in.	Ordering Number
1/8	CU-2-RP-2
1/4	CU-4-RP-2
3/8	CU-6-RP-2
1/2	CU-8-RP-2
3/4	CU-12-RP-2
1	CU-16-RP-2
1 1/4	CU-20-RP-2
1 1/2	CU-24-RP-2



## Copper and Nickel (RG, Gauge Fitting)

The RG fitting gasket provides a seal on pressure gauges equipped with ISO/BSP parallel male threads.

ISO Thread Size, in.	Ordering Number
<b>Copper Gaskets</b>	
1/4	CU-4-RG-2
3/8	CU-6-RG-2
1/2	CU-8-RG-2
<b>Nickel Gaskets</b>	
1/4	NI-4-RG-2
3/8	NI-6-RG-2
1/2	NI-8-RG-2



## PTFE (RJ Fitting)

The RJ fitting PTFE gasket provides a seal with ISO/BSP parallel male threads.

ISO Thread Size, in.	Ordering Number
<b>Regular Gaskets</b>	
1/4	T-4-RJ-2
3/8	T-6-RJ-2
1/2	T-8-RJ-2
<b>Thick Gaskets</b>	
1/4	T-4-RJ-2-T
3/8	T-6-RJ-2-T
1/2	T-8-RJ-2-T

## O-Rings

### **Buna N (O-Seal Straight Threads)**

O-ring  
hardness is 70  
durometer.

Thread Size in.	Uniform Size Number	Ordering Number
5/16-24	011	BN-70-OR-011
3/8-24	012	BN-70-OR-012
7/16-20	013	BN-70-OR-013
1/2-20	112	BN-70-OR-112
9/16-18	113	BN-70-OR-113
3/4-16	116	BN-70-OR-116
1 1/16-12	121	BN-70-OR-121
1 5/16-12	125	BN-70-OR-125

### **Buna N (O-Seal Pipe Threads)**

O-ring  
hardness is 70  
durometer.

NPT/ISO Pipe Size in.	Uniform Size Number	Ordering Number
1/8	013	BN-70-OR-013
1/4	113	BN-70-OR-113
3/8	116	BN-70-OR-116
1/2	118	BN-70-OR-118

# O-Rings

**Fluorocarbon  
FKM  
(Positionable  
Fittings,  
ISO/BSP  
Parallel  
Threads)**

O-ring hardness is 90 durometer.

ISO Thread Size in.	Uniform Size Number	Ordering Number
1/8	502 <sup>①</sup>	FSP-90-OR-502
1/4	111	FCBR-90-OR-111
3/8	113	FCBR-90-OR-113
1/2	508 <sup>①</sup>	FCBR-90-OR-508
3/4	119	FCBR-90-OR-119
1	217	FCBR-90-OR-217

<sup>①</sup> Not a uniform O-ring size.

**Fluorocarbon  
FKM  
(SAE/MS  
Straight  
Threads)**

O-ring hardness is 90 durometer.

SAE/MS Thread Size	Uniform Size Number	Ordering Number
5/16-24	902	FCBR-90-OR-902
3/8-24	903	FCBR-90-OR-903
7/16-20	904	FCBR-90-OR-904
1/2-20	905	FCBR-90-OR-905
9/16-18	906	FCBR-90-OR-906
3/4-16	908	FCBR-90-OR-908
7/8-14	910	FCBR-90-OR-910
1 1/16-12	912	FCBR-90-OR-912
1 3/16-12	914	FCBR-90-OR-914
1 5/16-12	916	FCBR-90-OR-916
1 5/8-12	920	FCBR-90-OR-920
1 7/8-12	924	FCBR-90-OR-924
2 1/2-12	932	FCBR-90-OR-932

## Bulkhead Retainers

The bulkhead retainer acts as a backup wrench, enabling one person with one wrench to install a bulkhead fitting.



Fitting Size		Ordering Number
in.	mm	
1/16	—	SS-102-61F
1/8	—	SS-202-61F
3/16	3, 4	SS-302-61F
1/4	6	SS-402-61F
5/16	—	SS-502-61F
—	8	SS-8M2-61F
3/8	—	SS-602-61F
—	10	SS-10M2-61F
1/2	12	SS-812-61F
5/8	15, 16	SS-1012-61F
3/4	18	SS-1212-61F
7/8	—	SS-1412-61F
1	—	SS-1612-61F

# Gap Inspection Gauges



Swagelok gap inspection gauges assure the installer or inspector that the fitting has been sufficiently pulled up on initial installation, whether using a multihead hydraulic swaging unit (MHSU) or air-actuated hydraulic swaging unit (AHSU), or wrench tightening. All metal Swagelok tube fittings are gaugeable, with the exception of a few forged bodies in aluminum.

## *For Installation Using a Wrench*

Fitting Size		Ordering Number
in.	mm	
<b>Female Nut</b>		
1/16	—	MS-IG-100
1/8	2, 3	MS-IG-200
3/16	4	MS-IG-300
1/4	6	MS-IG-400
1/4, 3/8, 1/2	6, 12	MS-IG-468
1/4, 1/2	6, 8, 10, 12	MS-IG-612M
5/16	8	MS-IG-500
3/8	—	MS-IG-600
—	10	MS-IG-10M0
1/2	12	MS-IG-810
5/8	14, 15, 16	MS-IG-1010
5/8 (alloy 2507)	—	MS-IG-2507-1010
3/4	18	MS-IG-1210
3/4 (alloy 2507)	—	MS-IG-2507-1210
7/8	20, 22	MS-IG-1410
1	25	MS-IG-1610
<b>Male Nut</b>		
1/16	—	MS-IG-1F0
1/8	2, 3	MS-IG-2F0

# Gap Inspection Gauges

## For Installation Using the AHSU

Fitting Size		Ordering Number
in.	mm	
<b>Female Nut</b>		
1/4, 3/8, 1/2	—	MS-AHSU-IG-468
—	6, 8, 10, 12	MS-AHSU-IG-612M

## For Installation Using the MHSU

Fitting Size		Ordering Number
in.	mm	
<b>Female Nut</b>		
1/2 <sup>①</sup>	12	MS-MHSU-IG-810
5/8 <sup>②</sup>	14, 15, 16	MS-MHSU-IG-1010
5/8 (alloy 2507)	—	MS-MHSU-IG-2507-1010
3/4 <sup>②</sup>	18	MS-MHSU-IG-1210
3/4 (alloy 2507)	—	MS-MHSU-IG-2507-1210
7/8	20, 22	MS-MHSU-IG-1410
1	25	MS-MHSU-IG-1610-1
—	28	MS-MHSU-IG-28M0-1
—	30	MS-MHSU-IG-30M0-1
1 1/4	—	MS-MHSU-IG-2000-2
—	32	MS-MHSU-IG-32M0-1
—	38	MS-MHSU-IG-38M0-1
1 1/2	—	MS-MHSU-IG-2400-1
—	50	MS-MHSU-IG-50M0-1
2	—	MS-MHSU-IG-3200-1

<sup>①</sup> The MHSU cannot be used for alloy 2507 tubing 1/2 in. and under.

<sup>②</sup> For 5/8 and 3/4 in. alloy 2507 tubing, order the 1 in. (25 mm) and over unit and alloy 2507 tooling and gauge.

## Depth Marking Tools



Swagelok depth marking tools help ensure that tubing is bottomed on the shoulder inside the Swagelok tube fitting body.

Tube OD in.	Ordering Number
1/4	MS-DMT-400
3/8	MS-DMT-600
1/2	MS-DMT-810
5/8	MS-DMT-1010
3/4	MS-DMT-1210
7/8	MS-DMT-1410
1	MS-DMT-1610

Tube OD mm	Ordering Number
6	MS-DMT-6M0
8	MS-DMT-8M0
10	MS-DMT-10M0
12	MS-DMT-12M0
16	MS-DMT-16M0
18	MS-DMT-18M0

## Preswaging Tools

For Swagelok tube fitting installations in close quarters, the Swagelok preswaging tool is a convenient accessory.

A gaugeable preswaging tool is available in the following sizes: 1/4, 3/8, 1/2, and 5/8 inch and 6, 8, 10, 12, and 16 mm. All other sizes are not gaugeable. The gaugeable feature allows the installer to quickly measure the gap between the nut and the fitting body with a standard Swagelok gap gauge during initial installation. The gaugeable preswage tool is distinguished from the standard tool by the addition of a colored band located between the wrench pad and the Swagelok tube fitting end.

Tube OD in.	Ordering Number
1/16	MS-ST-100
1/8	MS-ST-200
3/16	MS-ST-300
1/4 <sup>②</sup>	MS-ST-400GA
5/16	MS-ST-500
3/8 <sup>②</sup>	MS-ST-600GA
1/2 <sup>②</sup>	MS-ST-810GA
5/8 <sup>①②</sup>	MS-ST-1010GA
5/8 (alloy 2507)	MS-ST-2507-1010
3/4 <sup>①</sup>	MS-ST-1210
3/4 (alloy 2507)	MS-ST-2507-1210
7/8	MS-ST-1410
1	MS-ST-1610
Male Nut	
1/16	MS-ST-1F0
1/2	MS-ST-8F0



Tube OD mm	Ordering Number
3	MS-ST-3M0
4	MS-ST-4M0
6 <sup>①</sup>	MS-ST-6M0GA
8 <sup>①</sup>	MS-ST-8M0GA
10 <sup>①</sup>	MS-ST-10M0GA
12 <sup>①</sup>	MS-ST-12M0GA
14	MS-ST-14M0
15	MS-ST-15M0
16 <sup>①</sup>	MS-ST-16M0GA
18	MS-ST-18M0
20	MS-ST-20M0
22	MS-ST-22M0
25	MS-ST-25M0

<sup>①</sup> Ordering numbers containing **GA** at the end are gaugeable preswage tools, all others are non-gaugeable preswage tools.

<sup>②</sup> For alloy 2507 tubing, use the preswaging tool for the appropriate tube OD and with 2507 in the ordering number.

<sup>②</sup> Ordering numbers containing **GA** at the end are gaugeable preswage tools, all others are non-gaugeable preswage tools.

## Inserts for Soft Plastic Tubing

Swagelok inserts help secure soft plastic tubing being used with standard Swagelok tube fittings.



To determine the correct size of the Swagelok insert to be used, check both outside diameter and inside diameter of the plastic tubing.

Add the insert material designator to the basic ordering number.

Example:  
**B-305-2**

For a complete line of hose connectors for soft plastic tubing, refer to *Swagelok Hose and Flexible Tubing catalog, MS-01-180*.

Material	Designator
Alloy 400	M
Aluminum	A
Brass	B
Carbon steel	S
Stainless steel	SS

Tube OD in.	Tube ID in.	Bore ID in.	Basic Ordering Number
3/16	1/8	0.09	-305-2
1/4	1/8	0.09	-405-2
	0.17	0.11	-405-170
	3/16	0.14	-405-3
5/16	1/8	0.09	-505-2
	3/16	0.12	-505-3
	1/4	0.19	-505-4
3/8	3/16	0.12	-605-3
	1/4	0.19	-605-4
1/2	1/4	0.19	-815-4
	3/8	0.31	-815-6
5/8	3/8	0.31	-1015-6
	1/2	0.44	-1015-8
3/4	1/2	0.44	-1215-8
	5/8	0.56	-1215-10
1	3/4	0.69	-1615-12

Tube OD mm	Tube ID mm	Bore ID mm	Basic Ordering Number
6	4	2.8	-6M5-4M
8	6	4.4	-8M5-6M
10	8	6.4	-10M5-8M
12	8	6.4	-12M5-8M
	10	8.3	-12M5-10M

For product technical data, see the Swagelok *Gaugeable Tube Fittings and Adapters* catalog, [MS-01-140](#).

### **Safe Product Selection**

**When selecting a product, the total system design must be considered to ensure safe, trouble-free performance. Function, material compatibility, adequate ratings, proper installation, operation, and maintenance are the responsibilities of the system designer and user. The complete catalog contents must be reviewed to ensure that the system designer and user make a safe product selection.**



### **WARNING**

**Do not mix/interchange Swagelok products or components not governed by industrial design standards, including Swagelok tube fitting end connections, with those of other manufacturers.**

## **Warranty Information**

Swagelok products are backed by The Swagelok Limited Lifetime Warranty, [MS-13-123](#). For a copy, visit [swagelok.com](#) or contact your authorized Swagelok sales and service center.



Swagelok, Ferrule-Pak, Goop, Swak—  
TM Swagelok Company  
© 2006–2025 Swagelok Company  
Printed in U.S.A., AGS  
MS-13-151, RevP, June 2025