# Trunnion Ball Valves



# 83 Series and H83 Series


- Working pressures up to 10 000 psig (689 bar)
- 1/8 to 1/2 in. and 6 to 12 mm Swagelok® tube fitting or NPT end connections
- 316 stainless steel materials

# **Contents**

Features	Materials of Construction 4
Important Information About Ball Valves 2	Ordering Information and Dimensions 6
Technical Data	Options and Accessories 8
Pressure-Temperature Ratings	Service Options
Flow Data at 70°F (20°C)	Pneumatic Actuators
Testing	ISO 5211-Compliant Actuators
Low Fugitive Emissions	Electric Actuators
Cleaning and Packaging	

#### **Features**

- Compact, maximum-flow design
- Low operating torque
- 2- or 3-way flow patterns
- Panel mounting
- Pneumatic and electric actuators available
- Low Emissions certification per API 641 available



Spring-loaded seats:

- provide leak-tight integrity in both low- and high-pressure systems
- contribute to low operating torque
- reduce seat wear from pressure surges.

# **Technical Data**

#### Pressure Rating at 100°F (37°C) Temperature psig (bar) Rating Seat Stainless Steel Material °F (°C) Alloy 400 open or fully closed position. 83 Series PCTFE, 2-way valves-0 to 250 6000 (413) 5000 (344) reinforced (-17 to 121) depending on nylon end connection; PEEK 6000 (413) 5000 (344) 0 to 450 3-way valves-(-17 to 232) PTFE 1500 (103)

				i
		H83 Series		
PEEK	0 to 450 (-17 to 232)	6000 to 10 000 (413 to 689) depending on end connection	_	2-way valves— 1.0 to 1.6 depending on end connection; 3-way valves— 0.75

torque.

Flow

Coefficient

 $(C_{\nu})$ 

1.0 to 1.6

0.75

# **Important Information About Ball Valves**

- **⚠** Swagelok ball valves are designed to be used in a fully
- for a period of time may have a higher initial actuation torque.



# **Pressure-Temperature Ratings**

#### 83 Series

Pressure-temperature ratings for 83 series valves are based on listed seat materials, fluorocarbon FKM O-rings, and reinforced PTFE backup rings.

Low-temperature L83 series ball valves are available, see page 9.

Material	316 SS				Alloy 400	
Seat Material	PCTFE, Nylon	PTFE	PEEK	PCTFE, Nylon	PTFE	PEEK
Temperature, °F (°C)		Working Pressure, psig (bar)				
0 (-17) to 100 (37)	6000 (413)	1500 (103)	6000 (413)	5000 (344)	1500 (103)	5000 (344)
150 (65)	3000 (206)	1125 (77.5)	5800 (399)	3000 (206)	1125 (77.5)	4690 (323)
200 (93)	2000 (137)	750 (51.6)	5000 (344)	2000 (137)	750 (51.6)	4390 (302)
250 (121)	1000 (68.9)	625 (43.0)	4100 (282)	1000 (68.9)	625 (43.0)	4100 (282)
300 (148)	_	500 (34.4)	3200 (220)	_	500 (34.4)	3200 (220)
350 (176)	_	375 (25.8)	2300 (158)	_	375 (25.8)	2300 (158)
400 (204)	_	250 (17.2)	1400 (96.4)	_	250 (17.2)	1400 (96.4)
450 (232)	_	125 (8.6)	500 (34.4)	_	125 (8.6)	500 (34.4)

#### **H83 Series**

Pressure-temperature ratings for H83 series valves are based on PEEK seats, fluorocarbon FKM O-rings, and reinforced PTFE backup rings.

Low-temperature LH83 series ball valves are available, see page 9.

Material	316 SS				
End Connections	F2, F4, S4, S6MM	S10MM	S6, S8MM	S8	S12MM
Temperature, °F (°C)	Working Pressure, psig (ba			sig (bar)	
0 (-17) to 100 (37) 150 (65) 200 (93) 250 (121)	10 000 (689) 7 500 (516) 5 000 (344) 4 100 (282)	8400 (578) 7500 (516) 5000 (344) 4100 (282)	7500 (516) 7500 (516) 5000 (344) 4100 (282)	6700 (461) 6700 (461) 5000 (344) 4100 (282)	6600 (454) 6600 (454) 5000 (344) 4100 (282)
300 (148) 350 (176) 400 (204) 450 (232)	3 200 (220) 2 300 (158) 1 400 (96.4) 500 (34.4)	3200 (220) 2300 (158) 1400 (96.4) 500 (34.4)	3200 (220) 2300 (158) 1400 (96.4) 500 (34.4)	3200 (220) 2300 (158) 1400 (96.4) 500 (34.4)	3200 (220) 2300 (158) 1400 (96.4) 500 (34.4)

# Flow Data at 70°F (20°C)

#### 83 Series 2-Way

0.187 in. (4.75 mm) orifice, 1.2  $C_{\nu}$ 

Pressure Drop to Atmosphere (Δ <i>p</i> ) psi (bar)	Air Flow std ft³/min (std L/min)	Water Flow U.S. gal/min (L/min)
10 (0.68)	14 (390)	3.8 (14)
50 (3.4)	36 (1000)	8.5 (32)
100 (6.8)	64 (1800)	12 (45)

#### 83 Series 3-Way

0.187 in. (4.75 mm) orifice, 0.75  $C_{\nu}$ 

Pressure Drop to Atmosphere (Δ <i>p</i> ) psi (bar)	Air Flow std ft³/min (std L/min)	Water Flow U.S. gal/min (L/min)
10 (0.68)	8.0 (220)	2.4 (9.0)
50 (3.4)	23 (650)	5.3 (20)
100 (6.8)	40 (1100)	7.5 (28)

# H83 Series 2-Way

0.187 in. (4.75 mm) orifice, 1.2  $C_{\nu}$ 

Pressure Drop to Atmosphere (Δp) psi (bar)	Air Flow std ft³/min (std L/min)	Water Flow U.S. gal/min (L/min)
150 (10.3)	92 (2600)	15 (56)
600 (41.3)	340 (9600)	29 (100)
1000 (68.9)	570 (16 100)	38 (140)

#### H83 Series 3-Way

0.187 in. (4.75 mm) orifice, 0.75  $C_{\nu}$ 

Pressure Drop to Atmosphere (Δ <i>p</i> ) psi (bar)	Air Flow std ft³/min (std L/min)	Water Flow U.S. gal/min (L/min)
150 (10.3)	57 (1600)	9.2 (34)
600 (41.3)	210 (5900)	18 (68)
1000 (68.9)	350 (9900)	24 (90)

# **Testing**

Every Swagelok trunnion ball valve is factory tested with nitrogen at 1000 psig (69 bar). Seats have a maximum allowable leak rate of 0.1 std cm<sup>3</sup>/min. Shell testing is performed to a requirement of no detectable leakage with a liquid leak detector.

# **Low Fugitive Emissions**

The American Petroleum Institute's API 641 tests for fugitive emissions to atmosphere for quarter turn ball valves. The tests are conducted at a third party lab and certify that at no point in the test did the valve leak in excess of 100 ppm of methane. Certificates stating that the valve is certified for Low Emissions service are available for the 83 series with Fluorocarbon FKM stem O-rings. For more information, contact your authorized Swagelok sales and service representative.


# **Cleaning and Packaging**


All Swagelok trunnion ball valves are cleaned and packaged in accordance with Swagelok Standard Cleaning and Packaging (SC-10) catalog, MS-06-62. Cleaning and packaging in accordance with Swagelok Special Cleaning and Packaging (SC-11) catalog, MS-06-63, to ensure compliance with product cleanliness requirements stated in ASTM G93 Level C are available as an option for 83 series valves, see page 10.



# **Materials of Construction**

# 83 Series






		Valve Body Material				
		Stainles	ss Steel	Alloy	400	
		2-Way	3-Way	2-Way	3-Way	
	Component	Mat	terial Grade/A	STM Specifica	tion	
1	Handle	Phenolic v	vith powdered r	metal 300 series	s SS insert	
2	Set screw		S174	00 SS		
3	Panel nut		316 SS	S/B783		
4	Stop pins (2-way-2; 3-way-1)		Stainles	ss steel		
5	Body	316 SS	S/A479	Alloy 40	00/B164	
6	Stem	316 SS	S/A276	Alloy 40	00/B164	
7	Stem O-rings (2-way—2; 3-way—1)		Fluorocar	bon FKM		
8	Primary stem backup ring	_	PEEK	_	PEEK	
9	Secondary stem backup ring	_	PTFE/D1710	_	PTFE/D1710	
10	Stem bearing	Reinforced PTFE	PEEK	Reinforced PTFE	PEEK	
11	Ball <sup>1</sup>	316 SS/A276	S21800/A276	Alloy 40	00/B164	
12	Trunnion backup rings (2)	Reinforced PTFE	_	Reinforced PTFE	_	
13	Trunnion O-rings (2)	Fluorocarbon FKM	_	Fluorocarbon FKM	_	
14	Trunnion bearings	_	PEEK	_	PEEK	
15	Seats (2)	PCTFE, I	PTFE/D1710, re	inforced nylon,	or PEEK	
16	Seat carriers (2)	316 SS	S/A276	Alloy 40	00/B164	
17	Seat springs (6 with PTFE; 12 with all others)		Alloy X-750	/AMS 5542		
18	Seat carrier guides (2)	316 SS	S/A276	Alloy 40	00/B164	
19	Seat carrier backup rings (4)	Reinforced PTFE				
20	Seat carrier O-rings (2)	Fluorocarbon FKM				
21	End screw seals (2)		PTFE/	D1710		
22	End screws (2)	316 SS	S/A479	Alloy 40	00/B164	
	Wetted lubricants	tungsten d	Fluorinated-ba		EEK seats)	
	Nonwetted lubricant	Molybdenum	n disulfide with	hydrocarbon bi	nder coating	

Wetted components listed in italics.

① Ball trunnions are PTFE coated in 83 series 2-way valve.

# **Materials of Construction**

# **H83 Series**









		2-Way	3-Way	
		_	3-way   Grade/	
	Component	ASTM Specification		
1	Handle	Phenolic with powdered metal 300 series SS insert		
2	Set screw	S1740	00 SS	
3	Panel nut	316 SS	S/B783	
4	Stop pin (2-way-2; 3-way-1)	Stainles	ss steel	
5	Body	316 SS	S/A479	
6	Stem	316 SS	S/A276	
7	Stem O-ring	Fluorocarbon FKM		
8	Primary stem backup ring	PEEK		
9	Secondary stem backup ring	PTFE/D1710		
10	Stem bearing	PEEK		
11	Ball <sup>①</sup>	S2180	0/A276	
12	Plug (2-way only)	316 SS/A276	_	
13	Seats (2)	PE	EK	
14	Seat carriers (2)	316 SS	S/A276	
15	Seat springs (12)	Alloy X-750	/AMS 5542	
16	Seat carrier guides (2)	316 SS	S/A276	
17	Seat carrier backup rings (4)	Reinforc	ed PTFE	
18	Seat carrier O-rings (2)	Fluorocar	bon FKM	
19	End screw seals (2)	PTFE/	D1710	
20	End screws (2)	316 SS	S/A479	
	Wetted lubricants	Tungsten disulfide and fluorinated-based		
	Nonwetted lubricant	,	disulfide with binder coating	

Wetted components listed in italics.


 $^{\scriptsize \textcircled{\scriptsize 1}}$  Ball trunnions are Xylan  $^{\scriptsize \textcircled{\scriptsize 8}}$  coated.




# **Ordering Information and Dimensions**

Dimensions, in inches (millimeters), are for reference only and are subject to change. Dimensions shown with Swagelok tube fitting nuts finger-tight.

83 Series 2-Way 1.50 (38.1) 0.38 (9.7) max panel thickness 29/32 (23.0) panel hole drill 1.84 (46.7)0.51 (13.0) Swagelok 0.58 (14.7)В





# **Ordering Information and Dimensions**

# 83 Series

Select a valve ordering number from the table below.

Valve ordering numbers specify stainless steel material. To order valves of alloy 400 material, replace SS in the ordering number with M.

Example: M-83KF2

Valve ordering numbers specify a PCTFE seat. To order valves with other seat materials, replace  ${\bf K}$  in the ordering number with a seat material designator.

Seat Material	Designator
PTFE	Т
Reinforced nylon	N
PEEK	Р

Example: SS-83TF2

# **H83 Series**

Select a valve ordering number from the table below.

End Con	End Connections Flow 83 Series H83 Series Dimensions, in. (mm)							
Type Size		Coefficient (C <sub>v</sub> )	Valve Ordering Number	Valve Ordering Number	A	B		
Турс	2-Way Valve, 0.187 in. (4.75 mm) Orifice							
	1/8 in.	SS-H83PF2	2.94 (74.7)	1.47 (37.3)				
Female			SS-83KF4	_	2.94 (74.7)	1.47 (37.3)		
NPT	1/4 in.	1.0	_	SS-H83PF4	3.93 (99.8)	1.97 (50.0)		
	1/2 in. <sup>①</sup>	1.2	SS-83KF8	_	4.25 (108)	2.13 (54.1)		
Fractional	1/4 in.	1.6	SS-83KS4	SS-H83PS4	4.14 (105)	2.07 (52.6)		
Swagelok	3/8 in.	1.4	SS-83KS6	SS-H83PS6	4.39 (112)	2.19 (55.6)		
tube fitting	1/2 in. <sup>①</sup>	1.0	SS-83KS8	SS-H83PS8	4.60 (117)	2.30 (58.4)		
	6 mm	1.6	SS-83KS6MM	SS-H83PS6MM	4.14 (105)	2.07 (52.6)		
Metric	8 mm	1.5	SS-83KS8MM	SS-H83PS8MM	4.15 (105)	2.07 (52.6)		
Swagelok tube fitting	10 mm	1.3	SS-83KS10MM	SS-H83PS10MM	4.41 (112)	2.20 (55.9)		
	12 mm <sup>①</sup>	1.0	SS-83KS12MM	SS-H83PS12MM	4.60 (117)	2.30 (58.4)		
		3-Wa	y Valve, 0.187 in. (4.	75 mm) Orifice				
	1/8 in.		SS-83XKF2	SS-H83XPF2	2.94 (74.7)	1.47 (37.3)		
Female NPT <sup>©</sup>	4/4:		SS-83XKF4	_	2.94 (74.7)	1.47 (37.3)		
IVI 1	1/4 in.		_	SS-H83XPF4	3.93 (99.8)	1.97 (50.0)		
Fractional	1/4 in.		SS-83XKS4	SS-H83XPS4	4.14 (105)	2.07 (52.6)		
Swagelok	3/8 in.	0.75	SS-83XKS6	SS-H83XPS6	4.39 (112)	2.19 (55.6)		
tube fitting <sup>②</sup>	1/2 in. <sup>①</sup>	0.75	SS-83XKS8	SS-H83XPS8	4.60 (117)	2.30 (58.4)		
	6 mm		SS-83XKS6MM	SS-H83XPS6MM	4.14 (105)	2.07 (52.6)		
Metric Swagelok	8 mm		SS-83XKS8MM	SS-H83XPS8MM	4.15 (105)	2.07 (52.6)		
tube fitting <sup>®</sup>	10 mm		SS-83XKS10MM	SS-H83XPS10MM	4.41 (112)	2.20 (55.9)		
	12 mm <sup>①</sup>		SS-83XKS12MM	SS-H83XPS12MM	4.60 (117)	2.30 (58.4)		

For more information about pressure ratings of valves with tube fitting end connections, refer to Tubing Data catalog, MS-01-107.



① Not recommended for panel mounting.

② Bottom port of all 3-way valves is 1/4 in. female NPT.

# **Options and Accessories**

#### 83 and H83 Series Handles

Black phenolic handles are standard. Colored phenolic, oval, and 316 stainless steel bar handles are available. To order, add a handle designator to the valve ordering number.

Example: SS-83KF2-RD

Handle	Designator
Black phenolic	-BK
Blue phenolic	-BL
Green phenolic	-GR
Orange phenolic	-OG
Red phenolic	-RD
Yellow phenolic	-YW
Stainless steel bar	-SH

#### Handle Kits

Handle kits contain a handle and set screw.

Standard black phenolic handle kit ordering number:

#### PH-5K-83-BK

To order handles in other colors, replace **-BK** in the kit ordering number with a handle designator.

Example: PH-5K-83-RD

Oval handles are available factory assembled only.

Stainless steel bar handle kit ordering number: SS-5K-83

#### Locking Handle

The stainless steel locking handle accommodates shackle diameters from 1/4 to 5/16 in. (6.4 to 7.9 mm) and a 3/4 in. (19.0 mm) minimum shackle length. It can lock 83 series and H83 series 2-way and 3-way valves in the open or closed position.



To order a valve with a factory-assembled locking handle, add **-LH** to a valve ordering number.

Examples: SS-83KS8-LH SS-83KKS8-LH

#### **Locking Handle Kits**

The stainless steel locking handle kit is available for replacing an existing phenolic or stainless steel bar handle; it cannot be used to replace an existing oval handle. The kit includes a locking handle, lock plate, set screw, and instructions.

Kit ordering number: SS-5K-83LH

#### 83 Series Seal Kits

Seal kits contain components of the same materials as new components. See **Materials of Construction**, page 4, or

Low-Temperature Service,

page 9.

For a complete ordering number, add a seat material designator to a basic seal kit ordering number.

Example: SS-9K-83K

Seat Material	Designator
PEEK	Р
PCTFE	K
PTFE	Т
Reinforced nylon	N

Valve Series	Basic Seal Kit Ordering Number	Kit Contents
83 2-way	SS-9K-83	O-rings, stem bearing, ball, seat subassemblies (seats and seat
Low- temperature 83 2-way	SS-9K-L83	carriers), seat springs, end screw seals, lubricant, lubricant Material Safety Data Sheet (MSDS), instructions
83 3-way	SS-9K-83X	Stem, handle set screw, O-rings, backup rings, bearings, ball, seat
Low- temperature 83 3-way	SS-9K-L83X	subassemblies (seats and seat carriers), seat springs, end screw seals, lubricant, lubricant MSDS, instructions

Seal kit ordering numbers specify stainless steel material. For alloy 400 material, replace **SS** with **M** for in the basic ordering number.

Example: M-9K-83K

#### **H83 Series Seal Kits**

Seal kits contain components of the same materials as new components. See **Materials of Construction**, page 5, or **Low-Temperature Service**, page 9.

Valve Series	Seal Kit Ordering Number	Kit Contents
H83 2-way	SS-9K-H83P	Stem, handle set screw,
Low-temperature H83 2-way	SS-9K-LH83P	O-rings, backup rings, stem bearing, ball, seat subassemblies (seats and
H83 3-way	SS-9K-H83XP	seat carriers), seat springs,
Low-temperature H83 3-way	SS-9K-LH83XP	end screw seals, lubricant, lubricant MSDS, instructions

### 83 Series Vent Options

A downstream or upstream ball vent is available in 83 series 2-way valves. The vent port in the ball does not intersect the main flow passage, ensuring no leakage of system media from the vent port. When the valve is open, flow is straight through. The pressure rating with a ball vent is reduced to 500 psig (34.4 bar).

## Downstream (DV) Vent

When a downstream-vented valve is closed, full shutoff occurs at the upstream seat. Downstream system media passes through the vent hole in the ball trunnion and vents to atmosphere through the bottom of the trunnion.

To order, insert **DV** into the valve ordering number.

Example: SS-83K**DV**F2

## Upstream (UV) Vent

When an upstream-vented valve is closed, full shutoff occurs at the downstream seat. Upstream system media passes through the vent hole in the ball trunnion and vents to atmosphere through the bottom of the trunnion.

To order, insert **UV** into the valve ordering number.

Example: SS-83K**UV**F2



# **Service Options**

### 83 and H83 Series Low-Temperature Service

Trunnion ball valves for low-temperature service, with a temperature rating of –40 to 200°F (–40 to 93°C), are available. Low-temperature valves have low-temperature Buna C O-rings. All other materials and ratings are the same as those of standard valves.

To order a valve for low-temperature service, insert **L** into the valve ordering number.

Example: SS-L83KF2

#### L83 Series Pressure-Temperature Ratings

Material	316 SS				Alloy 400	
Seat Material	PCTFE, Nylon	PTFE	PEEK	PCTFE, Nylon	PTFE	PEEK
Temperature, °F (°C)	Working Pressure, psig (bar)					
-40 (-40) to 100 (37) 150 (65) 200 (93)	6000 (413) 3000 (206) 2000 (137)	1500 (103) 1125 (77.5) 750 (51.6)	6000 (413) 5800 (399) 5000 (344)	5000 (344) 3000 (206) 2000 (137)	1500 (103) 1125 (77.5) 750 (51.6)	5000 (344) 4690 (323) 4390 (302)

### LH83 Series Pressure-Temperature Ratings

Material	316 SS						
End Connections	F2, F4, S4, S6MM	S10MM	S8	S12MM			
Temperature, °F (°C)	Working Pressure, psig (bar)						
-40 (-40) to 100 (37) 150 (65) 200 (93)	10 000 (689) 7 500 (516) 5 000 (344)	8400 (578) 7500 (516) 5000 (344)	7500 (516) 7500 (516) 5000 (344)	6700 (461) 6700 (461) 5000 (344)	6600 (454) 6600 (454) 5000 (344)		

# 83 Series Valves With ECE R110-Type Approval

## -40 to 185°F (-40 to 85°C) Temperature Range

Stainless steel 83 series 2-way and 3-way valves with PEEK seats and Buna C O-rings are available with ECE R110-type approval for use in alternative fuel service.

- Temperature rating: -40 to 185°F (-40 to 85°C)
- Pressure rating within the range: 3770 psig (260 bar)

To order, add **-11354** to a PEEK-seated, low-temperature valve ordering number.

Examples: SS-L83PS8-11354 SS-L83XPS8-11354

# -40 to 248°F (-40 to 120°C) Temperature Range

Stainless steel 83 series 2-way and 3-way valves with PEEK seats and low-temperature fluorocarbon FKM O-rings are available with ECE R110-type approval for use in alternative fuel service.

- Temperature rating: -40 to 248°F (-40 to 120°C)
- Pressure rating within the range: 3770 psig (260 bar)

To order, add **-21265** to a PEEK-seated, low-temperature valve ordering number.

Examples: SS-L83PS8-21265 SS-L83XPS8-21265

### **Additional Valve Materials**

Alloy 625, alloy 825, and Alloy 2507 super duplex stainless steel materials are available for 83 series valves. Refer to *Trunnion Ball Valves—Special Alloy Materials* catalog, MS-02-357.



# **Service Options**

#### 83 Series for "Fast Fill" CNG Filling Station Applications


Stainless steel 83 series 3-way manual valves are available for use in a variety of filling station applications. These valves improve performance in demanding highcycle, high-pressure applications, and prevent the need for frequent rebuilds.

Features include:

- A directional installation with 90 degree actuation for ease of operation during filling
- 3-way design with vent port for ease of venting after fill
- PEEK seats to reduce maintenance required in high-cycle applications
- Cycle life test report available upon request

Example: SS-83DXLPF4 SS-L83DXLPF4

Note: The handle set screw used in this valve is longer than the standard 83 series handle set screw and thus is not interchangeable.



#### 83DXL Valve Seal Kit

Seal kits contain components of the same materials as new components. See Materials of Construction, page 4, or Low-Temperature Service, page 9.

Seal kit contains stem, handle set screw, O-rings, backup rings, bearings, ball, seat subassemblies (PEEK seats and seat carriers), seat springs, end screw seals, lubricant, lubricant MSDS, and instructions.

Example: SS-9K-83DXLP

# 83 Series Special Cleaning and Packaging (SC-11)

To order optional cleaning and packaging in accordance with Swagelok Special Cleaning and Packaging (SC-11) catalog, MS-06-63, to ensure compliance with product cleanliness requirements stated in ASTM G93 Level C for 83 series valves, add -SC11 to the valve ordering number.

Example: SS-83KF2-SC11

# Oxygen Service Hazards

For more information about hazards and risks of oxygen-enriched systems, see the Swagelok Oxygen System Safety technical report, MS-06-13.

# **FFKM O-Ring Material**

An optional FFKM O-ring material is available for 83 and H83 Series ball valves.

- Temperature rating for 83 Series with FFKM O-ring material: 25 to 250°F (-3 to 121°C)
- Temperature rating for H83 Series with FFKM O-ring material: 36 to 250°F (3 to 121°C)

To order, add -KZ to the valve ordering number.

Example: SS-83PS4-KZ



### **Pneumatic Actuators**



Swagelok rack and pinion pneumatic actuators are compact, lightweight, easily mountable, and can be operated with standard shop air. They are available in spring-return and doubleacting modes. On-off (2-way) valves require 90° actuation; switching (3-way) valves require 180° actuation.

For technical data, including pressuretemperature ratings and materials of construction, refer to *Ball Valve Actuation Options* catalog, MS-02-343.

Actuated assemblies must be properly aligned and supported. Improper alignment or inadequate support of the actuated assembly may result in leakage or premature valve failure.

# **Pressure-Temperature Ratings**

	Actuator	Temperature		Actuator , psig (bar)
Actuator Service	Service Designator	<b>Range</b> °F (°C)	At 100°F (37°C)	At Maximum Temperature
Standard	_	-20 to 200 (-28 to 93)		165 (11.3)
High temperature	HT	0 to 400 (–17 to 204)	200 (13.7)	100 (6.8)
Low temperature	LT	-40 to 200 (-40 to 93)	200 (13.7)	165 (11.3)
Nonfluorocarbon	NF	-20 to 200 (-28 to 93)		165 (11.3)

# 83 Series Actuator Pressure at Maximum System Pressure

Based on valve performance using pressurized air or nitrogen.

					Actuatio	n Modes	
				Double	Acting	Spring	Return
Valve	Actuator	Actuator Model	System Pressure	Single	Dual	Single	Dual
Series	Model	Designator	psig (bar)	Minimu	m Actuator	Pressure,	osig (bar)
	21 (00%)	21	1500 (103)	30 (2.1)	50 (3.5)	70 (4.9)	80 (5.6)
83	31 (90°)	-31	6000 (413)	35 (2.5)	60 (4.2)	75 (5.2)	_
2-way	22 (00%)	00	1500 (103)	15 (1.1)	20 (1.4)	65 (4.5)	70 (4.9)
	33 (90°)	-33	6000 (413)	20 (1.4)	25 (1.8)	75 (5.2)	75 (5.2)
	E1 (100°)	-51	1500 (103)	35 (2.5)	60 (4.2)	75 (5.2)	
83	51 (180°)	-51	6000 (413)	45 (3.2)	85 (5.8)	-	_
3-way	EQ (4.00%)	FO	1500 (103)	15 (1.1)	25 (1.8)	70 (4.9)	75 (5.2)
	53 (180°)	-53	6000 (413)	20 (1.4)	35 (2.5)	75 (5.2)	_

# H83 Series Actuator Pressure at Maximum System Pressure

Based on valve performance using pressurized air or nitrogen.

			Actuation			n Modes	
				Double	Acting	Spring	Return
Valve	Actuator	Actuator Model	System Pressure	Single	Dual	Single	Dual
Series	Model	Designator	psig (bar)	Minimu	m Actuator	Pressure,	osig (bar)
			1 500 (103)	35 (2.5)	60 (4.2)		
	31 (90°)	-31	6 000 (413)	45 (3.2)	85 (5.9)	_	_
H83			10 000 (689)	55 (3.8)	100 (6.9)		
2-way		-33	1 500 (103)	15 (1.1)	25 (1.8)	70 (4.9)	75 (5.2)
	33 (90°)		6 000 (413)	20 (1.4)	35 (2.5)	75 (5.2)	85 (5.9)
			10 000 (689)	25 (1.8)	45 (3.2)	80 (5.6)	90 (6.3)
			1 500 (103)	35 (2.5)	60 (4.2)		
	51 (180°)	-51	6 000 (413)	45 (3.2)	85 (5.9)	_	_
H83			10 000 (689)	55 (3.8)	100 (6.9)		
3-way			1 500 (103)	15 (1.1)	25 (1.8)	70 (4.9)	
	53 (180°)	-53	6 000 (413)	20 (1.4)	35 (2.5)	75 (5.2)	_
			10 000 (689)	25 (1.8)	45 (3.2)	80 (5.6)	



#### **Pneumatic Actuators**

## **Ordering Information**

### Factory-Assembled Valves with Actuators

**Typical Ordering Number** 



# A Valve Ordering Number

# **B** Actuator Model

Based on valve series, flow pattern, and actuation mode, select an actuator designator. See Actuator Pressure at Maximum System Pressure tables, page 11.

- $-31 = 90^{\circ}$  actuation
- $-33 = 90^{\circ}$  actuation
- **-51** = 180° actuation
- $-53 = 180^{\circ}$  actuation

# C Actuation Mode

- C = Spring return, normally closed
- **D** = Double acting
- **O** = Spring return, normally open
- S = Spring return, 3-way valves

# Actuator Service

**HT** = High temperature

**LT** = Low temperature

**NF** = Nonfluorocarbon

None = Standard

For dual-mounted assemblies (two valves mounted to one actuator), add **DM** to the ordering number.

Example: SS-83KF2-31DDM

# Kits for Field Assembly

Order one actuator kit and one mounting bracket kit for each valve.

#### **Actuator Kit Typical Ordering Number**

MS-1 **31** - **DA** -HT

#### Actuator Model

Based on valve series, flow pattern, and actuation mode, select an actuator designator. See Actuator Pressure at Maximum System Pressure tables, page 11.

- $31 = 90^{\circ}$  actuation
- $33 = 90^{\circ}$  actuation
- $51 = 180^{\circ}$  actuation
- 53 = 180° actuation

#### B Actuation Mode

**DA** = Double acting

**SR** = Spring return

### Actuator Service

-HT = High temperature

**-LT** = Low temperature

-NF = Nonfluorocarbon

None = Standard

#### **Mounting Bracket Kits**

Mounting bracket kits contain:

- 316 stainless steel mounting bracket
- 316 stainless steel coupling
- stainless steel stop pin (90° actuation, 2 roll pins; 180° actuation, 1 roll pin)
- S17400 set screw
- instructions.


Valve Series	Actuator Model	Mounting Bracket Kit Ordering Number
83, H83	31 (90°)	SS-MB-83-131
2-way	33 (90°)	SS-MB-83-133
83, H83	51 (180°)	SS-MB-83-131
3-way	53 (180°)	SS-MB-83-133



# **Pneumatic Actuators**

# **Dimensions**

Dimensions, in inches (millimeters), are for reference only and are subject to change.



Actuator		Dimensions, in. (mm)							
Model	Α	В	С	D	E	F	G	Н	J
31 (90°)	4.91	4.09	0.63	1.15	3.64	1.28	2.00	1.31	3.04
51 (180°)	(125)	(104)	(16.0)	(29.2)	(92.5)	(32.5)	(50.8)	(33.3)	(77.2)
33 (90°)	7.86	5.89	0.88	1.73	4.88	1.51	2.00	1.75	4.07
53 (180°)	(200)	(150)	(22.4)	(44.0)	(124)	(38.4)	(50.8)	(44.4)	(103)



# **ISO 5211-Compliant Pneumatic Actuators**



Swagelok ISO 5211-compliant rack and pinion pneumatic actuators are suitable for general applications. They are available in spring-return and doubleacting modes. On-off (2-way) valves require 90° actuation; switching (3-way) valves require 180° actuation.

Valve-actuator assemblies on this page are based on:

- maximum valve pressure
- ambient temperature (50 to 100°F [10 to 37°C])

For technical data, including actuator materials of construction and weight, refer to Ball Valve Actuation Options catalog, MS-02-343.

For additional information on selecting and sizing ISO 5211-compliant actuators, refer to Actuated Ball Valve Selection Guide—ISO 5211-Compliant Actuator Mounting Bracket Kits catalog, MS-02-136.

**⚠** Actuated assemblies must be properly aligned and supported. Improper alignment or inadequate support of the actuated assembly may result in leakage or premature valve failure.

# **Pressure-Temperature Ratings**

Maximum actuator pressure is 116 psig (8.0 bar). See Minimum Actuator Pressure table below for minimum actuator pressures.

Actuator Service	Actuator Service Designator	Temperature Range °F (°C)
Standard	_	-40 to 176 (-40 to 80)
High temperature	HT	5 to 302 (–15 to 150)

#### 83 Series Minimum Actuator Pressure

					Actuation Mode	
		Spring Return Model Designators		Double Acting	Spring Return	Double Acting
Valve Series	Actuator Model	Normally Closed	Normally Open	Model Designator	Minimum Actuator Pressure, psig (bar)	
83 2-way	A10 (90°)		_	-A10D	-	36 (2.5)
	A15 (90°)	-A15C3	-A15O3	-A15D	43 (3.0)	36 (2.5)
83 3-way	A15 (180°)		_	-A15XD	_	36 (2.5)

#### H83 Series Minimum Actuator Pressure

					Actuation Mode	
		Spring Return Model Designators		Double Acting	Spring Return	Double Acting
Valve Series	Actuator Model	Normally Closed	Normally Open	Model Designator	Minimum Actuator Pressure, psig (bar)	
H83 2-way	A10 (90°)		_	-A10D	_	43 (3.0)
	A15 (90°)	-A15C3	-A15O3	-A15D	43 (3.0)	36 (2.5)
H83 3-way	A15 (180°)	_	_	-A15XD	_	36 (2.5)

# **ISO 5211-Compliant Pneumatic Actuators**

# **Ordering Information**

# Factory-Assembled Valves with Actuators

**Typical Ordering Number** 



A Valve Ordering Number

Based on valve series, flow pattern, and actuation mode, select an actuator designator. See Minimum Actuator Pressure tables, page 14.

Actuator Service
HT = High temperature
None = Standard

#### Kits for Field Assembly

Order one actuator kit and one mounting bracket kit for each valve.

#### **Actuator Kit Typical Ordering Number**



Actuator Model

Based on valve series, flow pattern, and actuation mode, select an actuator. See **Minimum Actuator Pressure** tables, page 14.

A10 = A10A15 = A15 **B** Actuation Mode

DA = Double acting (2-way valves)XDA = Double acting (3-way valves)3 = Spring return

Coupling Drive Type
DIN

Actuator Service

-HT = High temperature None = Standard

#### **Mounting Bracket Kits**

Swagelok ISO 5211 mounting bracket kits contain:


- 316 stainless steel mounting bracket
- four A4 stainless steel socket head cap screws (A4 is approximately equivalent to AISI 316.)
- 316 stainless steel coupling
- A4 stainless steel set screw
- instructions.

Kit ordering number: SS-MB-83-F04-11DIN-M

# **ISO 5211-Compliant Pneumatic Actuators**

### **Dimensions**

Dimensions, in inches (millimeters), are for reference only and are subject to change.



Valve	Actuator	Dimensions, in. (mm)				
Series	Model	Α	В	С	D	
83, H83	A10 (90°)	4.65 (118)	4.17 (106)	1.29 (32.8)	2.84 (72.1)	
2-way	A15 (90°)	5.33 (135)	4.17 (106)	1.29 (32.8)	3.09 (78.5)	
83, H83 3-way	A15 (180°)	7.55 (192)	4.28 (109)	1.29 (32.8)	3.09 (78.5)	

# **Options for ISO 5211-Compliant and Swagelok Pneumatic Actuators**

Swagelok offers a range of accessories to enhance instrumentation and process ball valve performance and control, including solenoid valves, limit switches, and position sensors. Factory assemblies and kits for field assembly are available.



Refer to *Ball Valve Actuation Options* catalog, <u>MS-02-343</u>, for additional information.

### **⚠** WARNING

Do not mix/interchange Swagelok products or components not governed by industrial design standards, including Swagelok tube fitting end connections, with those of other manufacturers.

#### **Electric Actuators**

Swagelok electric actuators are rugged and lightweight, and connect alternating- or direct-current power sources.

Refer to *Electric Actuators—141 and 142 Series* catalog, MS-01-35, for additional information.



#### Introduction

Since 1947, Swagelok has designed, developed, and manufactured high-quality, general-purpose and specialty fluid system products to meet the evolving needs of global industries. Our focus is on understanding our customers' needs, finding timely solutions, and adding value with our products and services.

We are pleased to provide this global edition of the book-bound *Swagelok Product Catalog*, which compiles more than 100 separate product catalogs, technical bulletins, and reference documents into one convenient, easy-to-use volume. Each product catalog is up to date at the time of printing, with its revision number shown on the last page of the individual catalog. Subsequent revisions will supersede the printed version and will be posted on the Swagelok website and in the Swagelok electronic Desktop Technical Reference (eDTR) tool.

For more information, visit your Swagelok website or contact your authorized Swagelok sales and service representative.

### **Warranty Information**

Swagelok products are backed by The Swagelok Limited Lifetime Warranty. For a copy, visit swagelok.com or contact your authorized Swagelok representative.

#### Safe Product Selection

When selecting a product, the total system design must be considered to ensure safe, trouble-free performance. Function, material compatibility, adequate ratings, proper installation, operation, and maintenance are the responsibilities of the system designer and user.

#### **⚠** WARNING

Do not mix/interchange Swagelok products or components not governed by industrial design standards, including Swagelok tube fitting end connections, with those of other manufacturers.

Not all trademarks listed below apply to this catalog. Swagelok, Cajon, Ferrule-Pak, Goop, Hinging-Colleting, IGC, Kenmac, Micro-Fit, Nupro, Snoop, Sno-Trik, SWAK, VCO, VCR, Ultra-Torr, Whitey-TM Swagelok Company 15-7 PH-TM AK Steel Corp. AccuTrak, Beacon, Westlock—TM Tyco International Services Aflas-TM Asahi Glass Co., Ltd. ASCO, El-O-Matic-TM Emerson AutoCAD-TM Autodesk, Inc. CSA-TM Canadian Standards Association Crastin, DuPont, Kalrez, Krytox, Teflon, Viton-TM E.I. duPont Nemours and Company DeviceNet-TM ODVA Dyneon, Elgiloy, TFM-TM Dyneon Elgiloy—TM Elgiloy Specialty Metals Festo—TM Festo SE & Co. KG FM-TM FM Global Grafoil—TM GrafTech International Holdings, Inc. Honeywell, MICRO SWITCH—TM Honeywell MAC-TM MAC Valves Microsoft, Windows—TM Microsoft Corp.
NACE—TM NACE International PH 15-7 Mo, 17-7 PH—TM AK Steel Corp picofast—Hans Turck KG
Pillar—TM Nippon Pillar Packing Company, Ltd. Raychem-TM Tyco Electronics Corp. Sandvik, SAF 2507-TM Sandvik AB Simriz-TM Freudenberg-NOK SolidWorks-TM SolidWorks Corporation UL-Underwriters Laboratories Inc. Xvlan-TM Whitford Corporation © 2022 Swagelok Company