

Variable Area Flowmeters



G Series and M Series

- Glass and metal (armored) tube models, including miniature armored model
- Highly accurate measurement with individually calibrated scales based on flow tests
- Flexible and adaptable to specific system requirements
- High quality, durability, and repeatability
- 1/8 to 1 1/4 in. process end connections

Contents

Variable Area Flowmeters	2
Features	2
Calibration and Testing	2
Cleaning and Packaging	2
Installation	2
Choosing the Right Flowmeter	2
G Series (Glass Tube) Flowmeters	4
G1 Model	5
G2 Model	6
G3 Model	7
G4 Model	8
GM Model	9
GP Model	10
M Series (Metal Tube) Flowmeters	11
M1 Model	12
M2 Model	14
M4 Model	16
M4H Model	18
Dimensions	20
Custom Calibration	22
Options	22
Accessories	25

Variable Area Flowmeters

Swagelok® variable area flowmeters measure the flow rate of liquids and gases by means of a tapered tube and float. The float is pushed up by increasing fluid flow and pulled down by gravity as fluid flow decreases, except for the spring-loaded M4H model. Variable area flowmeters do not require external power, but may be ordered with electrical or electronic options.

Most Swagelok models contain integral needle valves at the bottom (inlet) process connection; top mounting is available as an option.

Features

- Simple installation
- Easy to read
- No wearing parts
- Limit switches available
- 10-to-1 turndown ratio (the lowest measurement is one tenth of the full-scale reading).
- Meters are marked with the fluid media and unit of measure for which they are calibrated.

Calibration and Testing

Every Swagelok variable area flowmeter is factory calibrated to its media, flow range, and accuracy class using clean, dry air for air-flow range models and water for water-flow range models.

- G1, G2, G3, GM, and GP models are calibrated to 17.4 psia (1.2 bar) and 68°F (20°C).
- G4, M1, M2, M4, and M4H models are calibrated to 14.7 psia (1.013 bar) and 68°F (20°C).

Meters can be calibrated to user-specific applications.

Cleaning and Packaging

All Swagelok variable area flowmeters are cleaned to remove dirt, debris, and burrs and are individually boxed. Oil- and grease-free cleaning are available on request.

Installation

Variable area flowmeters must be oriented vertically, except for the M4H model, which is mounted horizontally. For complete installation information, see the Swagelok *Variable Area Flowmeters Installation Instructions, G Series and M Series*, MS-CRD-0111, available *only* on your Swagelok website.

Choosing the Right Flowmeter



Variable Area Flowmeter Selection

Model	Process Temperature Rating °F (°C)	Ambient Temperature Rating °F (°C)	Maximum Inlet Pressure at 70°F (20°C) psig (bar)
G1	23 to 212 (-5 to 100)	-4 to 212 (-20 to 100)	145 (10.0)
G2	23 to 212 (-5 to 100)	-4 to 212 (-20 to 100)	145 (10.0)
G3	23 to 212 (-5 to 100)	-4 to 212 (-20 to 100)	145 (10.0)
G4	23 to 212 (-5 to 100)	-4 to 212 (-20 to 100)	145 (10.0)
GM	23 to 212 (-5 to 100)	-4 to 212 (-20 to 100)	58.0 (4.0)
GP	23 to 212 (-5 to 100)	-4 to 212 (-20 to 100)	58.0 (4.0)
M1	-4 to 302 (-20 to 150)	-4 to 158 (-20 to 70)	1885 (130)
M2	-4 to 302 (-20 to 150)	-4 to 158 (-20 to 70)	1885 (130)
M4 (1/2 in. dia tube)	-40 to 572 (-40 to 300)	-40 to 248 (-40 to 120)	2888 (199)
M4 (1 in. dia tube)	-40 to 572 (-40 to 300)	-40 to 248 (-40 to 120)	1393 (96.0)
M4H (1/2 in. dia tube)	-40 to 572 (-40 to 300)	-40 to 248 (-40 to 120)	2888 (199)
M4H (1 in. dia tube)	-40 to 572 (-40 to 300)	-40 to 248 (-40 to 120)	1393 (96.0)

Choosing the Right Flowmeter

Variable area flowmeters are fitted with measuring tubes made of glass or metal.

- Swagelok G series models contain glass measuring tubes, which allow direct viewing of the process fluid and direct reading of the flow.
- Swagelok M series models contain metal measuring tubes, which are used for difficult operating conditions where pressure, temperature, or both are factors. Because direct readings are not possible with metal tubes, these flowmeters are equipped with mechanical or electronic displays.

See the **Variable Area Flowmeter Selection** table below for a wide selection of flowmeters.

- Standard conditions (std ft³/min and std ft³/h air flow ranges) are defined as 14.7 psia (1.013 bar) at 59°F (15°C) in accordance with ISO 13443.
- Normal conditions (NL/min and NL/h air flow ranges) are defined as 14.7 psia (1.013 bar) at 32°F (0°C) in accordance with DIN 1343.

Fluids with properties different from those of air or water, as well as systems operating at higher pressures or temperatures, may require custom-calibrated flowmeters.

See **Custom Calibration**, page 22, for more information.

Variable Area Flowmeter Selection

Air Flow Ranges				Water Flow Ranges				Accuracy Class ^①	Process End Connections	Page
NL/min	NL/h	std ft ³ /min	std ft ³ /h	L/min	L/h	U.S. gal/min	U.S. gal/h			
0.011 to 0.11 through 2.0 to 20	0.5 to 5.0 through 120 to 1200	0.0004 to 0.004 through 0.07 to 0.7	0.018 to 0.18 through 4.5 to 45	0.004 to 0.04 through 0.27 to 2.7	0.25 to 2.5 through 16 to 160	0.001 to 0.01 through 0.07 to 0.7	0.065 to 0.65 through 4.2 to 42	4.0	1/4 in. NPT	5
0.011 to 0.11 through 8.4 to 84	0.5 to 5.0 through 500 to 5000	0.0004 to 0.004 through 0.3 to 3.0	0.018 to 0.18 through 18 to 180	0.004 to 0.04 through 0.28 to 2.8	0.25 to 2.5 through 16 to 160	0.001 to 0.01 through 0.07 to 0.7	0.065 to 0.65 through 4.2 to 42	2.5	1/4 in. NPT	6
0.027 to 0.27 through 1.3 to 13	1.6 to 16 through 80 to 800	0.001 to 0.01 through 0.05 to 0.5	0.06 to 0.6 through 3.0 to 30	0.008 to 0.08 through 0.17 to 1.7	0.5 to 5.0 through 10 to 100	0.002 to 0.02 through 0.045 to 0.45	0.13 to 1.3 through 2.5 to 25	2.5	1/4 in. NPT	7
0.027 to 0.27 through 5.0 to 50	1.6 to 16 through 300 to 3000	0.001 to 0.01 through 0.18 to 1.8	0.06 to 0.6 through 11 to 110	0.0007 to 0.007 through 0.17 to 1.7	0.04 to 0.4 through 10 to 100	0.00019 to 0.0019 through 0.045 to 0.45	0.01 to 0.1 through 2.5 to 25	1.0	1/4 in. NPT	8
0.011 to 0.11 through 1.3 to 13	0.5 to 5.0 through 80 to 800	0.0004 to 0.004 through 0.05 to 0.5	0.018 to 0.18 through 3.0 to 30	0.004 to 0.04 through 0.065 to 0.65	0.25 to 2.5 through 4.0 to 40	0.001 to 0.01 through 0.017 to 0.17	0.065 to 0.65 through 1.1 to 11	4.0	G 1/8 (ISO 228)	9
0.011 to 0.11 through 8.4 to 84	0.5 to 5.0 through 500 to 5000	0.0004 to 0.004 through 0.3 to 3.0	0.018 to 0.18 through 18 to 180	0.004 to 0.04 through 0.28 to 2.8	0.25 to 2.5 through 16 to 160	0.001 to 0.01 through 0.07 to 0.7	0.065 to 0.65 through 4.2 to 42	2.5	G 1/4 (ISO 228)	10
0.08 to 0.8 through 6.0 to 60	5.0 to 50 through 340 to 3400	0.003 to 0.03 through 0.2 to 2.0	0.18 to 1.8 through 13 to 130	0.005 to 0.05 through 0.17 to 1.7	0.3 to 3.0 through 10 to 100	0.0013 to 0.013 through 0.045 to 0.45	0.08 to 0.8 through 2.5 to 25	4.0	1/4 in. NPT	12
0.08 to 0.8 through 6.0 to 60	5.0 to 50 through 340 to 3400	0.003 to 0.03 through 0.2 to 2.0	0.18 to 1.8 through 13 to 130	0.005 to 0.05 through 0.17 to 1.7	0.3 to 3.0 through 10 to 100	0.0013 to 0.013 through 0.045 to 0.45	0.08 to 0.8 through 2.5 to 25	2.5	1/4 in. NPT	14
1.1 to 11 through 50 to 500	70 to 700 through 2800 to 28 000	0.04 to 0.4 through 1.6 to 16	2.5 to 25 through 100 to 1000	0.03 to 0.3 through 1.7 to 17	1.8 to 18 through 100 to 1000	0.008 to 0.08 through 0.45 to 4.5	0.48 to 4.8 through 25 to 250	1.6	1/2 and 3/4 in. NPT; 1/2, 3/4, and 1 in. ASME flange	16
25 to 250 through 300 to 3000	1400 to 14 000 through 18 000 to 180 000	1.0 to 10 through 10 to 1000	52 to 520 through 670 to 6700	0.8 to 8.0 through 10 to 100	48 to 480 through 630 to 6300	0.2 to 2.0 through 3.0 to 30	13 to 130 through 160 to 1600	1.6	3/4 and 1 in. NPT; 3/4 and 1 in. ASME flange	16
—	—	—	—	0.11 to 1.1 through 4.0 to 40	7.0 to 70 through 240 to 2400	0.03 to 0.3 through 1.07 to 10.7	2.0 to 20 through 64 to 640	1.6	3/4 in. NPT; 1/2, 3/4, and 1 in. ASME flange	18
—	—	—	—	2.0 to 20 through 17 to 170	130 to 1300 through 1000 to 10 000	0.6 to 6.0 through 4.5 to 45	35 to 350 through 270 to 2700	1.6	1 1/4 in. NPT; 1 in. ASME flange	18

① In accordance with VDI/VDE 3513 Sheet 2: 2008, accuracy class is effectively equivalent to permissible error above $q_G = 50\%$ where:
 G = Constant permissible error in percent of measured value above q_G
 q_G = Flow limit value in percent of full scale

Above q_G , the permissible error is constant.
 Below q_G , the permissible error increases toward lower flow rates inversely proportional.
 In sizing a flowmeter, $q_G = 50\%$ allows for the greatest accuracy above 50% of the full scale.
 For assistance with variable area flowmeter selection, contact your authorized Swagelok sales and service representative.


Fluid media, temperature, pressure, viscosity, and density also must be considered in selecting a variable area flowmeter. See **Custom Calibration**, page 22.

G Series (Glass Tube) Flowmeters— G1, G2, G3, G4, GM, and GP Models

Features

- Glass tube design
- Low maintenance
- Optional factory-installed limit switches
- Polycarbonate cover for protection
- Integral needle valve for fine metering, not intended for shutoff

Reading Glass-Tube Flowmeters



Glass-tube flowmeters are read by the position of the float or ball within the flowmeter tube. The flow rate is read at the top edge of the float or ball.



Materials of Construction

G1, G2, G3, and G4 Models

Component	Material / Specification
Flowmeter	
<i>Head piece, foot piece</i>	316L stainless steel / EN 1.4404
<i>Float (G1, G2, G3)</i>	316 stainless steel / EN 1.4401
<i>Float (G4)</i>	316Ti stainless steel / EN 1.4571
<i>Measuring tube</i>	Borosilicate glass
<i>Float stops</i>	PFA with fluorocarbon (FKM) gaskets or PTFE with perfluorocarbon (FFKM) gaskets
<i>Head piece gasket, foot piece gasket</i>	Fluorocarbon (FKM), perfluorocarbon (FFKM), or EPDM
Protective cover	Polycarbonate
Mounting rail	304 stainless steel / EN 1.4301
Needle Valve	
<i>Needle</i>	316L stainless steel / EN 1.4404
<i>Gaskets</i>	PTFE
<i>O-rings</i>	Fluorocarbon (FKM), perfluorocarbon (FFKM), or EPDM
<i>Housing, spring</i>	316Ti stainless steel / EN 1.4571
<i>Spindle</i>	316L stainless steel / EN 1.4404
<i>Spindle lubricant</i>	PTFE-based
<i>Knob handle</i>	Plastic
<i>Knob handle insert</i>	Brass
<i>Knob handle set screw</i>	A2 stainless steel

Wetted components listed in *italics*.

G1 Model

This G1 model is suitable for low flow rates in fine-metering applications such as gas chromatography.

Technical Data

See **Variable Area Flowmeter Selection**, page 2.

Ordering Information

Build a G1 model variable area flowmeter ordering number by combining the designators in the sequence shown below.

4 5 6 7
VAF - G1 - 01M - 1 - 1 - A

4 Measured Flow Range

Air, NL/min

01L = 0.011 to 0.11
 02L = 0.013 to 0.13
 03L = 0.027 to 0.27
 04L = 0.07 to 0.7
 05L = 0.1 to 1.0
 06L = 0.17 to 1.7
 07L = 0.42 to 4.2
 08L = 0.83 to 8.3
 09L = 1.3 to 13
 10L = 2.0 to 20

Air, NL/h

01M = 0.5 to 5.0
 02M = 0.8 to 8.0
 03M = 1.6 to 16
 04M = 4.0 to 40
 05M = 6.0 to 60
 06M = 10 to 100
 07M = 25 to 250
 08M = 50 to 500
 09M = 80 to 800
 10M = 120 to 1200

Air, std ft³/min

01R = 0.0004 to 0.004
 02R = 0.0005 to 0.005
 03R = 0.001 to 0.01
 04R = 0.002 to 0.02
 05R = 0.0035 to 0.035
 06R = 0.006 to 0.06
 07R = 0.015 to 0.15
 08R = 0.03 to 0.3
 09R = 0.05 to 0.5
 10R = 0.07 to 0.7

Air, std ft³/h

01S = 0.022 to 0.22
 02S = 0.03 to 0.3
 03S = 0.06 to 0.6
 04S = 0.15 to 1.5
 05S = 0.22 to 2.2
 06S = 0.38 to 3.8
 07S = 0.95 to 9.5
 08S = 1.9 to 19
 09S = 3.0 to 30
 10S = 4.5 to 45

Water, L/min

A1L = 0.004 to 0.04
 A2L = 0.008 to 0.08
 A3L = 0.02 to 0.2
 A4L = 0.04 to 0.4
 A5L = 0.065 to 0.65
 A6L = 0.1 to 1.0
 A7L = 0.17 to 1.7
 A8L = 0.2 to 2.0
 A9L = 0.27 to 2.7

Water, L/h

A1M = 0.25 to 2.5
 A2M = 0.50 to 5.0
 A3M = 1.2 to 12
 A4M = 2.5 to 25
 A5M = 4.0 to 40
 A6M = 6.0 to 60
 A7M = 10 to 100
 A8M = 12 to 120
 A9M = 16 to 160

Water, U.S. gal/min

A1R = 0.001 to 0.01
 A2R = 0.002 to 0.02
 A3R = 0.005 to 0.05
 A4R = 0.01 to 0.1
 A5R = 0.017 to 0.17
 A6R = 0.025 to 0.25
 A7R = 0.045 to 0.45
 A8R = 0.055 to 0.55
 A9R = 0.07 to 0.7

Water, U.S. gal/h

A1S = 0.065 to 0.65
 A2S = 0.13 to 1.3
 A3S = 0.30 to 3.0
 A4S = 0.65 to 6.5
 A5S = 1.1 to 11
 A6S = 1.6 to 16
 A7S = 2.5 to 25
 A8S = 3.0 to 30
 A9S = 4.2 to 42

Custom

See **Custom Calibration**, page 22.

GAS = Gas

LIQ = Liquid

5 Flowmeter Gasket, Valve O-Ring Material

- 1 = Fluorocarbon (FKM) (standard)
- 2 = Perfluorocarbon (FFKM)
- 3 = EPDM

6 Limit Switches (See page 22.)

The maximum process and ambient temperatures are reduced to 149°F (65°C) if limit switches are selected. Most G1 model flowmeters can accept up to two limit switches; models with measured water flow ranges A8L, A9L, A8M, A9M, A8R, A9R, A8S, and A9S cannot accept limit switches; also see footnote below.

Limit switch amplifiers are required. Amplifiers can be ordered with the flowmeter or customer supplied.

- 0 = None
- 1 = One switch
- 2 = Two switches^①
- 3 = One switch and a one-channel isolated switch amplifier with relay output, 115 V (ac)
- 4 = Two switches and a two-channel isolated switch amplifier with relay output, 115 V (ac)^①
- 5 = One switch and a one-channel isolated switch amplifier with relay output, 230 V (ac)
- 6 = Two switches and a two-channel isolated switch amplifier with relay output, 230 V (ac)^①
- A = One switch and a one-channel isolated switch amplifier with relay output, 24 V (dc)
- B = Two switches and a two-channel isolated switch amplifier with relay output, 24 V (dc)

^① Not available with measured air flow ranges 10L, 10M, 10R, and 10S, or with measured water flow ranges A7L, A7M, A7R, and A7S.

7 Options (See page 22.)

Add multiple designators in alphabetical order; omit final dash (-) if no options are ordered.

- A = Limit switch junction box
- G = 5-point calibration record
- H = Pressure test, certificate
- J = Material certification
- T = Wall mounting
- W = Panel mounting
- X = Oil- and grease-free cleaning (required for oxygen service)
- Y = No needle valve
- Z = Top-mounted needle valve



Dimensions

See page 20 for G1 model dimensions.

G2 Model

Commonly used in analytical instrumentation applications, the G2 model is appropriate for low to medium flow rates.

Technical Data

See **Variable Area Flowmeter Selection**, page 2.

Ordering Information

Build a G2 model variable area flowmeter ordering number by combining the designators in the sequence shown below.

4 5 6 7
VAF - G2 - 01M - 1 - 1 - A

4 Measured Flow Range

<i>Air, NL/min</i>	<i>Air, NL/h</i>	<i>Water, L/min</i>	<i>Water, L/h</i>
01L = 0.011 to 0.11	01M = 0.5 to 5.0	A1L = 0.004 to 0.04	A1M = 0.25 to 2.5
02L = 0.013 to 0.13	02M = 0.8 to 8.0	A2L = 0.008 to 0.08	A2M = 0.50 to 5.0
03L = 0.027 to 0.27	03M = 1.6 to 16	A3L = 0.02 to 0.2	A3M = 1.2 to 12
04L = 0.07 to 0.7	04M = 4.0 to 40	A4L = 0.04 to 0.4	A4M = 2.5 to 25
05L = 0.1 to 1.0	05M = 6.0 to 60	A5L = 0.065 to 0.65	A5M = 4.0 to 40
06L = 0.17 to 1.7	06M = 10 to 100	A6L = 0.1 to 1.0	A6M = 6.0 to 60
07L = 0.42 to 4.2	07M = 25 to 250	A7L = 0.17 to 1.7	A7M = 10 to 100
08L = 0.83 to 8.3	08M = 50 to 500	A8L = 0.2 to 2.0	A8M = 12 to 120
09L = 1.3 to 13	09M = 80 to 800	A9L = 0.28 to 2.8	A9M = 16 to 160
10L = 1.7 to 17	10M = 100 to 1000		
11L = 3.0 to 30	11M = 180 to 1800	<i>Water, U.S. gal/min</i>	<i>Water, U.S. gal/h</i>
12L = 4.0 to 40	12M = 240 to 2400	A1R = 0.001 to 0.01	A1S = 0.065 to 0.65
13L = 5.0 to 50	13M = 300 to 3000	A2R = 0.002 to 0.02	A2S = 0.13 to 1.3
14L = 6.8 to 68	14M = 400 to 4000	A3R = 0.005 to 0.05	A3S = 0.30 to 3.0
15L = 8.4 to 84	15M = 500 to 5000	A4R = 0.01 to 0.1	A4S = 0.65 to 6.5
		A5R = 0.017 to 0.17	A5S = 1.1 to 11
<i>Air, std ft³/min</i>	<i>Air, std ft³/h</i>	A6R = 0.025 to 0.25	A6S = 1.6 to 16
01R = 0.0004 to 0.004	01S = 0.018 to 0.18	A7R = 0.045 to 0.45	A7S = 2.5 to 25
02R = 0.0005 to 0.005	02S = 0.03 to 0.3	A8R = 0.054 to 0.54	A8S = 3.0 to 30
03R = 0.001 to 0.01	03S = 0.06 to 0.6	A9R = 0.07 to 0.7	A9S = 4.2 to 42
04R = 0.002 to 0.02	04S = 0.15 to 1.5		
05R = 0.0035 to 0.035	05S = 0.22 to 2.2		
06R = 0.006 to 0.06	06S = 0.38 to 3.8		
07R = 0.015 to 0.15	07S = 0.95 to 9.5		
08R = 0.03 to 0.3	08S = 1.9 to 19		
09R = 0.05 to 0.5	09S = 3.0 to 30		
10R = 0.06 to 0.6	10S = 4.5 to 45		
11R = 0.1 to 1.0	11S = 6.5 to 65		
12R = 0.14 to 1.4	12S = 9.0 to 90		
13R = 0.18 to 1.8	13S = 11 to 110		
14R = 0.24 to 2.4	14S = 14 to 140		
15R = 0.3 to 3.0	15S = 18 to 180		

Custom

See **Custom Calibration**, page 22.

GAS = Gas **LIQ** = Liquid

5 Flowmeter Gasket, Valve O-Ring Material

- 1 = Fluorocarbon (FKM) (standard)
- 2 = Perfluorocarbon (FFKM)
- 3 = EPDM

Dimensions

See page 20 for G2 model dimensions.



6 Limit Switches (See page 22.)

The maximum process and ambient temperatures are reduced to 149°F (65°C) if limit switches are selected.

Most G2 model flowmeters can accept up to two limit switches; see footnote below.

Limit switch amplifiers are required. Amplifiers can be ordered with the flowmeter or customer supplied.

- 0 = None
- 1 = One switch
- 2 = Two switches^①
- 3 = One switch and a one-channel isolated switch amplifier with relay output, 115 V (ac)
- 4 = Two switches and a two-channel isolated switch amplifier with relay output, 115 V (ac)^①
- 5 = One switch and a one-channel isolated switch amplifier with relay output, 230 V (ac)
- 6 = Two switches and a two-channel isolated switch amplifier with relay output, 230 V (ac)^①
- A = One switch and a one-channel isolated switch amplifier with relay output, 24 V (dc)
- B = Two switches and a two-channel isolated switch amplifier with relay output, 24 V (dc)

^① Not available with measured air flow ranges 13L, 14L, 15L, 13S, 14S, 15S, 13M, 14M, 15M, 13R, 14R, and 15R, or with measured water flow ranges A7L, A8L, A9L, A7M, A8M, A9M, A7R, A8R, A9R, A7S, A8S, and A9S.

7 Options (See page 22.)

Add multiple designators in alphabetical order; omit final dash (-) if no options are ordered.

- A = Limit switch junction box
- G = 5-point calibration record
- H = Pressure test, certificate
- J = Material certification
- T = Wall mounting
- W = Panel mounting
- X = Oil- and grease-free cleaning (required for oxygen service)
- Y = No needle valve
- Z = Top-mounted needle valve

G3 Model

The G3 model provides reliable, accurate measurement over the mid ranges of air or water flow.

Technical Data

See **Variable Area Flowmeter Selection**, page 2.

Ordering Information

Build a G3 model variable area flowmeter ordering number by combining the designators in the sequence shown below.

4 5 6 7
VAF - G3 - 01M - 1 - 1 - A

4 Measured Flow Range

Air, NL/min

01L = 0.027 to 0.27
 02L = 0.07 to 0.7
 03L = 0.1 to 1.0
 04L = 0.17 to 1.7
 05L = 0.42 to 4.2
 06L = 0.83 to 8.3
 07L = 1.3 to 13

Air, NL/h

01M = 1.6 to 16
 02M = 4.0 to 40
 03M = 6.0 to 60
 04M = 10 to 100
 05M = 25 to 250
 06M = 50 to 500
 07M = 80 to 800

Air, std ft³/min

01R = 0.001 to 0.01
 02R = 0.002 to 0.02
 03R = 0.0035 to 0.035
 04R = 0.006 to 0.06
 05R = 0.015 to 0.15
 06R = 0.03 to 0.3
 07R = 0.05 to 0.5

Air, std ft³/h

01S = 0.06 to 0.6
 02S = 0.15 to 1.5
 03S = 0.21 to 2.1
 04S = 0.38 to 3.8
 05S = 0.95 to 9.5
 06S = 1.9 to 19
 07S = 3.0 to 30

Water, L/min

A1L = 0.008 to 0.08
 A2L = 0.02 to 0.2
 A3L = 0.04 to 0.4
 A4L = 0.065 to 0.65
 A5L = 0.1 to 1.0
 A6L = 0.17 to 1.7

Water, L/h

A1M = 0.5 to 5.0
 A2M = 1.2 to 12
 A3M = 2.5 to 25
 A4M = 4.0 to 40
 A5M = 6.0 to 60
 A6M = 10 to 100

Water, U.S. gal/min

A1R = 0.002 to 0.02
 A2R = 0.005 to 0.05
 A3R = 0.01 to 0.1
 A4R = 0.017 to 0.17
 A5R = 0.025 to 0.25
 A6R = 0.045 to 0.45

Water, U.S. gal/h

A1S = 0.13 to 1.3
 A2S = 0.25 to 2.5
 A3S = 0.65 to 6.5
 A4S = 1.1 to 11
 A5S = 1.6 to 16
 A6S = 2.5 to 25

Custom

See **Custom Calibration**, page 22.

GAS = Gas

LIQ = Liquid

5 Flowmeter Gasket, Valve O-Ring Material

- 1 = Fluorocarbon (FKM) (standard)
- 2 = Perfluorocarbon (FFKM)
- 3 = EPDM

6 Limit Switches (See page 22.)

The maximum process and ambient temperatures are reduced to 149°F (65°C) if limit switches are selected. Most G3 model flowmeters can accept up to two limit switches; see footnote below.

Limit switch amplifiers are required. Amplifiers can be ordered with the flowmeter or customer supplied.

- 0 = None
- 1 = One switch
- 2 = Two switches^①
- 3 = One switch and a one-channel isolated switch amplifier with relay output, 115 V (ac)
- 4 = Two switches and a two-channel isolated switch amplifier with relay output, 115 V (ac)^①
- 5 = One switch and a one-channel isolated switch amplifier with relay output, 230 V (ac)
- 6 = Two switches and a two-channel isolated switch amplifier with relay output, 230 V (ac)^①
- A = One switch and a one-channel isolated switch amplifier with relay output, 24 V (dc)
- B = Two switches and a two-channel isolated switch amplifier with relay output, 24 V (dc)

^① Not available with measured flow ranges **A6L**, **A6M**, **A6R**, and **A6S**.

7 Options (See page 22.)

Add multiple designators in alphabetical order; omit final dash (-) if no options are ordered.

- A** = Limit switch junction box
- G** = 5-point calibration record
- H** = Pressure test, certificate
- J** = Material certification
- T** = Wall mounting
- W** = Panel mounting
- X** = Oil- and grease-free cleaning (**required** for oxygen service)
- Y** = No needle valve
- Z** = Top-mounted needle valve



Dimensions

See page 20 for G3 model dimensions.

G4 Model

Suitable for laboratory applications, the large-size G4 model is highly accurate over its full measured flow range.

Technical Data

See **Variable Area Flowmeter Selection**, page 2.

Ordering Information

Build a G4 model variable area flowmeter ordering number by combining the designators in the sequence shown below.

4 5 6 7
VAF - G4 - 05M - 1 - 1 - A

4 Measured Flow Range

<i>Air, NL/min</i>	<i>Air, NL/h</i>	<i>Water, U.S. gal/min</i>	<i>Water, U.S. gal/h</i>
01L = 0.027 to 0.27	01M = 1.6 to 16	A1R = 0.00019 to 0.0019	A1S = 0.01 to 0.1
02L = 0.042 to 0.42	02M = 2.5 to 25	A2R = 0.0003 to 0.003	A2S = 0.016 to 0.16
03L = 0.068 to 0.68	03M = 4.0 to 40	A3R = 0.00045 to 0.0045	A3S = 0.025 to 0.25
04L = 0.1 to 1.0	04M = 6.0 to 60	A4R = 0.0007 to 0.007	A4S = 0.04 to 0.4
05L = 0.15 to 1.5	05M = 9.0 to 90	A5R = 0.001 to 0.01	A5S = 0.065 to 0.65
06L = 0.23 to 2.3	06M = 14 to 140	A6R = 0.0019 to 0.019	A6S = 0.1 to 1.0
07L = 0.33 to 3.3	07M = 20 to 200	A7R = 0.0025 to 0.025	A7S = 0.16 to 1.6
08L = 0.5 to 5.0	08M = 30 to 300	A8R = 0.0045 to 0.045	A8S = 0.25 to 2.5
09L = 0.83 to 8.3	09M = 50 to 500	A9R = 0.007 to 0.07	A9S = 0.4 to 4.0
10L = 1.33 to 13.3	10M = 80 to 800	B1R = 0.01 to 0.1	B1S = 0.65 to 6.5
11L = 2.0 to 20	11M = 120 to 1200	B2R = 0.017 to 0.17	B2S = 1.0 to 10
12L = 3.33 to 33.3	12M = 200 to 2000	B3R = 0.03 to 0.3	B3S = 1.6 to 16
13L = 5.0 to 50.0	13M = 300 to 3000	B4R = 0.045 to 0.45	B4S = 2.5 to 25

<i>Air, std ft³/min</i>	<i>Air, std ft³/h</i>
01R = 0.001 to 0.01	01S = 0.06 to 0.6
02R = 0.0015 to 0.015	02S = 0.095 to 0.95
03R = 0.0023 to 0.023	03S = 0.15 to 1.5
04R = 0.0035 to 0.035	04S = 0.22 to 2.2
05R = 0.0051 to 0.051	05S = 0.35 to 3.5
06R = 0.0082 to 0.082	06S = 0.50 to 5.0
07R = 0.012 to 0.12	07S = 0.75 to 7.5
08R = 0.018 to 0.18	08S = 1.1 to 11
09R = 0.03 to 0.3	09S = 1.9 to 19
10R = 0.05 to 0.5	10S = 3.0 to 30
11R = 0.072 to 0.72	11S = 4.5 to 45
12R = 0.12 to 1.2	12S = 7.5 to 75
13R = 0.18 to 1.8	13S = 11 to 110

<i>Water, L/min</i>	<i>Water, L/h</i>
A1L = 0.0007 to 0.007	A1M = 0.04 to 0.4
A2L = 0.001 to 0.01	A2M = 0.063 to 0.63
A3L = 0.0017 to 0.017	A3M = 0.1 to 1.0
A4L = 0.0025 to 0.025	A4M = 0.16 to 1.6
A5L = 0.004 to 0.04	A5M = 0.25 to 2.5
A6L = 0.007 to 0.07	A6M = 0.4 to 4.0
A7L = 0.01 to 0.1	A7M = 0.6 to 6.0
A8L = 0.017 to 0.17	A8M = 1.0 to 10
A9L = 0.025 to 0.25	A9M = 1.6 to 16
B1L = 0.04 to 0.4	B1M = 2.5 to 25
B2L = 0.065 to 0.65	B2M = 4.0 to 40
B3L = 0.1 to 1.0	B3M = 6.3 to 63
B4L = 0.17 to 1.7	B4M = 10 to 100

Custom

See **Custom Calibration**, page 22.

GAS = Gas **LIQ** = Liquid

5 Flowmeter Gasket, Valve O-Ring Material

- 1 = Fluorocarbon (FKM) (standard)
- 2 = Perfluorocarbon (FFKM)
- 3 = EPDM

Dimensions

See page 20 for G4 model dimensions.



6 Limit Switches (See page 22.)

The maximum process and ambient temperatures are reduced to 149°F (65°C) if limit switches are selected.

Most G4 model flowmeters can accept up to two limit switches; models with measured air flow ranges **01L, 02L, 03L, 11L, 12L, 13L, 01M, 02M, 03M, 11M, 12M, 13M, 01R, 02R, 03R, 11R, 12R, 13R, 01S, 02S, 03S, 11S, 12S, and 13S**, or with measured water flow ranges **A1L, A2L, A3L, B2L, B3L, B4L, A1M, A2M, A3M, B2M, B3M, B4M, A1R, A2R, A3R, B2R, B3R, B4R, A1S, A2S, A3S, B2S, B3S, and B4S** cannot accept limit switches.

Limit switch amplifiers are required. Amplifiers can be ordered with the flowmeter or customer supplied.

- 0 = None
- 1 = One switch
- 2 = Two switches
- 3 = One switch and a one-channel isolated switch amplifier with relay output, 115 V (ac)
- 4 = Two switches and a two-channel isolated switch amplifier with relay output, 115 V (ac)
- 5 = One switch and a one-channel isolated switch amplifier with relay output, 230 V (ac)
- 6 = Two switches and a two-channel isolated switch amplifier with relay output, 230 V (ac)
- A = One switch and a one-channel isolated switch amplifier with relay output, 24 V (dc)
- B = Two switches and a two-channel isolated switch amplifier with relay output, 24 V (dc)

7 Options (See page 22.)

Add multiple designators in alphabetical order; omit final dash (-) if no options are ordered.

- A = Limit switch junction box
- G = 5-point calibration record
- H = Pressure test, certificate
- J = Material certification
- W = Panel mounting
- X = Oil- and grease-free cleaning (required for oxygen service)
- Y = No needle valve
- Z = Top-mounted needle valve

GM Model

This miniature glass-tube model has a plastic head and foot piece and can be panel mounted easily.

Technical Data

See **Variable Area Flowmeter Selection**, page 2.

Materials of Construction

Component	Material / Specification
Flowmeter	
Head piece, foot piece	PVDF
Float	316 stainless steel / EN 1.4401
Measuring tube	Borosilicate glass
Float stops	PFA with fluorocarbon (FKM) gaskets or PTFE with perfluorocarbon (FFKM) gaskets
Head piece gasket, foot piece gasket	Fluorocarbon (FKM)
Protective cover	Polycarbonate
Mounting rail	Aluminum 6060
Needle Valve	
Needle	316L stainless steel / EN 1.4404
Gaskets	PTFE
O-rings	Fluorocarbon (FKM)
Housing, spring	316Ti stainless steel / EN 1.4571
Spindle	316L stainless steel / EN 1.4404
Spindle lubricant	PTFE-based
Knob handle	Aluminum 6060
Knob handle insert	Brass
Knob handle set screw	A2 stainless steel

Wetted components listed in *italics*.

Ordering Information

Build a GM model variable area flowmeter ordering number by combining the designators in the sequence shown below.

4 5
VAF - GM - 01M - Z

4 Measured Flow Range

Air, NL/min

01L = 0.011 to 0.11
02L = 0.013 to 0.13
03L = 0.027 to 0.27
04L = 0.07 to 0.7
05L = 0.1 to 1.0
06L = 0.17 to 1.7
07L = 0.42 to 4.2
08L = 0.83 to 8.3
09L = 1.3 to 13

Air, std ft³/min

01R = 0.0004 to 0.004
02R = 0.0005 to 0.005
03R = 0.001 to 0.01
04R = 0.002 to 0.02
05R = 0.0035 to 0.035
06R = 0.006 to 0.06
07R = 0.015 to 0.15
08R = 0.03 to 0.3
09R = 0.05 to 0.5

Water, L/min

A1L = 0.004 to 0.04
A2L = 0.008 to 0.08
A3L = 0.02 to 0.2
A4L = 0.04 to 0.4
A5L = 0.065 to 0.65

Water, U.S. gal/min

A1R = 0.001 to 0.01
A2R = 0.002 to 0.02
A3R = 0.005 to 0.05
A4R = 0.01 to 0.1
A5R = 0.017 to 0.17

Air, NL/h

01M = 0.5 to 5.0
02M = 0.8 to 8.0
03M = 1.6 to 16
04M = 4.0 to 40
05M = 6.0 to 60
06M = 10 to 100
07M = 25 to 250
08M = 50 to 500
09M = 80 to 800

Air, std ft³/h

01S = 0.018 to 0.18
02S = 0.03 to 0.3
03S = 0.06 to 0.6
04S = 0.15 to 1.5
05S = 0.22 to 2.2
06S = 0.38 to 3.8
07S = 0.95 to 9.5
08S = 1.9 to 19
09S = 3.0 to 30

Water, L/h

A1M = 0.25 to 2.5
A2M = 0.50 to 5.0
A3M = 1.2 to 12
A4M = 2.5 to 25
A5M = 4.0 to 40

Water, U.S. gal/h

A1S = 0.065 to 0.65
A2S = 0.13 to 1.3
A3S = 0.30 to 3.0
A4S = 0.65 to 6.5
A5S = 1.1 to 11

Custom

See **Custom Calibration**, page 22.

GAS = Gas

LIQ = Liquid

5 Options (See page 22.)

Add multiple designators in alphabetical order; omit final dash (-) if no options are ordered.

W = Panel mounting

Z = Top-mounted needle valve



Dimensions

See page 20 for GM model dimensions.

GP Model

The GP model offers a plastic head and foot piece, including end connections.

Technical Data

See **Variable Area Flowmeter Selection**, page 2.

Ordering Information

Build a GP model variable area flowmeter ordering number by combining the designators in the sequence shown below.

4 5 6 7
VAF - GP - 01M - 1 - 1 - A

4 Measured Flow Range

Air, NL/min

01L = 0.011 to 0.11
02L = 0.013 to 0.13
03L = 0.027 to 0.27
04L = 0.07 to 0.7
05L = 0.1 to 1.0
06L = 0.17 to 1.7
07L = 0.42 to 4.2
08L = 0.83 to 8.3
09L = 1.3 to 13
10L = 1.7 to 17
11L = 3.0 to 30
12L = 4.0 to 40
13L = 5 to 50
14L = 6.8 to 68
15L = 8.4 to 84

Air, std ft³/min

01R = 0.0004 to 0.004
02R = 0.0005 to 0.005
03R = 0.001 to 0.01
04R = 0.002 to 0.02
05R = 0.0035 to 0.035
06R = 0.006 to 0.06
07R = 0.015 to 0.15
08R = 0.03 to 0.3
09R = 0.05 to 0.5
10R = 0.06 to 0.6
11R = 0.1 to 1.0
12R = 0.14 to 1.4
13R = 0.18 to 1.8
14R = 0.24 to 2.4
15R = 0.3 to 3.0

Air, NL/h

01M = 0.5 to 5.0
02M = 0.8 to 8.0
03M = 1.6 to 16
04M = 4.0 to 40
05M = 6.0 to 60
06M = 10 to 100
07M = 25 to 250
08M = 50 to 500
09M = 80 to 800
10M = 100 to 1000
11M = 180 to 1800
12M = 240 to 2400
13M = 300 to 3000
14M = 400 to 4000
15M = 500 to 5000

Air, std ft³/h

01S = 0.018 to 0.18
02S = 0.03 to 0.3
03S = 0.06 to 0.6
04S = 0.15 to 1.5
05S = 0.22 to 2.2
06S = 0.38 to 3.8
07S = 0.95 to 9.5
08S = 1.9 to 19
09S = 3.0 to 30
10S = 4.5 to 45
11S = 6.5 to 65
12S = 9.0 to 90
13S = 11 to 110
14S = 14 to 140
15S = 18 to 180

Water, L/min

A1L = 0.004 to 0.04
A2L = 0.008 to 0.08
A3L = 0.02 to 0.2
A4L = 0.04 to 0.4
A5L = 0.065 to 0.65
A6L = 0.1 to 1.0
A7L = 0.17 to 1.7
A8L = 0.2 to 2.0
A9L = 0.28 to 2.8

Water, U.S. gal/min

A1R = 0.001 to 0.01
A2R = 0.002 to 0.02
A3R = 0.005 to 0.05
A4R = 0.01 to 0.1
A5R = 0.017 to 0.17
A6R = 0.025 to 0.25
A7R = 0.045 to 0.45
A8R = 0.054 to 0.54
A9R = 0.07 to 0.7

Custom

See **Custom Calibration**, page 22.

GAS = Gas

Water, L/h

A1M = 0.25 to 2.5
A2M = 0.50 to 5.0
A3M = 1.2 to 12
A4M = 2.5 to 25
A5M = 4.0 to 40
A6M = 6.0 to 60
A7M = 10 to 100
A8M = 12 to 120
A9M = 16 to 160

Water, U.S. gal/h

A1S = 0.065 to 0.65
A2S = 0.13 to 1.3
A3S = 0.30 to 3.0
A4S = 0.65 to 6.5
A5S = 1.1 to 11
A6S = 1.6 to 16
A7S = 2.5 to 25
A8S = 3.0 to 30
A9S = 4.2 to 42

5 Flowmeter Gasket, Valve O-Ring Material

- 1 = Fluorocarbon (FKM) (standard)
- 2 = Perfluorocarbon (FFKM)
- 3 = EPDM

Dimensions

See page 20 for GP model dimensions.



6 Limit Switches (See page 22.)

The maximum process and ambient temperatures are reduced to 149°F (65°C) if limit switches are selected.

Most GP model flowmeters can accept up to two limit switches; see footnote below.

Limit switch amplifiers are required. Amplifiers can be ordered with the flowmeter or customer supplied.

0 = None

1 = One switch

2 = Two switches^①

3 = One switch and a one-channel isolated switch amplifier with relay output, 115 V (ac)

4 = Two switches and a two-channel isolated switch amplifier with relay output, 115 V (ac)^①

5 = One switch and a one-channel isolated switch amplifier with relay output, 230 V (ac)

6 = Two switches and a two-channel isolated switch amplifier with relay output, 230 V (ac)^①

A = One switch and a one-channel isolated switch amplifier with relay output, 24 V (dc)

B = Two switches and a two-channel isolated switch amplifier with relay output, 24 V (dc)

^① Not available with measured air flow ranges **13L, 14L, 15L, 13M, 14M, 15M, 13R, 14R, 15R, 13S, 14S, and 15S** or with measured^o water flow ranges **A7L, A8L, A9L, A7M, A8M, A9M, A7R, A8R, A9R, A7S, A8S, and A9S**.

7 Options (See page 22.)

Add multiple designators in alphabetical order; omit final dash (-) if no options are ordered.

A = Limit switch junction box

G = 5-point calibration record

H = Pressure test, certificate

T = Wall mounting

W = Panel mounting

X = Oil- and grease-free cleaning (**required** for oxygen service)

Y = No needle valve

Z = Top-mounted needle valve

GP Model

Materials of Construction

Component	Material / Specification
Flowmeter	
<i>Head piece, foot piece</i>	<i>PVDF</i>
<i>Float</i>	<i>316 stainless steel / EN 1.4401</i>
<i>Measuring tube</i>	<i>Borosilicate glass</i>
<i>Float stops</i>	<i>PFA with fluorocarbon (FKM) gaskets, PTFE with perfluorocarbon (FFKM) gaskets, or EPDM</i>
<i>Head piece gasket, foot piece gasket</i>	<i>Fluorocarbon (FKM) or Perfluorocarbon (FFKM)</i>
Protective cover	Polycarbonate
Mounting rail	304 stainless steel / EN 1.4301
Needle Valve	
<i>Needle</i>	<i>316L stainless steel / EN 1.4404</i>
<i>Gaskets</i>	<i>PTFE</i>
<i>O-rings</i>	<i>Fluorocarbon (FKM), perfluorocarbon (FFKM), or EPDM</i>
<i>Housing, spring</i>	<i>316Ti stainless steel / EN 1.4571</i>
<i>Spindle</i>	<i>316L stainless steel / EN 1.4404</i>
<i>Spindle lubricant</i>	<i>PTFE-based</i>
<i>Knob handle</i>	<i>Plastic</i>
<i>Knob handle insert</i>	<i>Brass</i>
<i>Knob handle set screw</i>	<i>A2 stainless steel</i>

Wetted components listed in *italics*.

M Series (Metal Tube) Flowmeters—M1, M2, M4, and M4H Models

Features

- Armored design for extreme operating conditions
- Measurement in multiple flow directions
- Ideal for industrial sector applications
- Metal measuring tube for increased durability
- Horizontal mounting (M4H model) available



Materials of Construction

M1 and M2 Models

Component	Material / Specification
Flowmeter	
<i>Head piece, foot piece, float, measuring tube, upper plug</i>	<i>316L stainless steel / EN 1.4404 / Alloy C-276 / Alloy K-500</i>
<i>Upper float stop (spring)</i>	<i>316Ti stainless steel / EN 1.4571</i>
<i>Plug gasket, lower float stop</i>	<i>PTFE</i>
Indicator housing	Painted aluminum
Needle Valve	
<i>Needle</i>	<i>316L stainless steel / EN 1.4404</i>
<i>Gaskets</i>	<i>PTFE</i>
<i>O-rings</i>	<i>Fluorocarbon (FKM) or Perfluorocarbon (FFKM)</i>
<i>Housing, spring</i>	<i>316Ti stainless steel / EN 1.4571</i>
<i>Spindle</i>	<i>316L stainless steel / EN 1.4404</i>
<i>Spindle lubricant</i>	<i>PTFE-based</i>
<i>Knob handle</i>	<i>Plastic</i>
<i>Knob handle insert</i>	<i>Brass</i>
<i>Knob handle set screw</i>	<i>A2 stainless steel</i>

Wetted components listed in *italics*.

M4 and M4H Models

Component	Material / Specification
<i>Measuring tube, float, float stops, receiver, guide</i>	<i>316L stainless steel / EN 1.4404 / Alloy C-276 / Alloy K-500</i>
<i>Flange or NPT end connections</i>	<i>316L stainless steel / EN 1.4404 / Alloy C-276 / Alloy K-500</i>
Indicator housing	Painted aluminum

Wetted components listed in *italics*.

M1 Model

The miniature M1 model is compact, yet offers protection against harsh environments and higher pressures with an armored measuring tube.

Technical Data

See **Variable Area Flowmeter Selection**, page 2.

Ordering Information

Build an M1 model variable area flowmeter ordering number by combining the designators in the sequence shown below.

4 5 6 7
VAF - M1 - 01M - 1 - 1 - F

4 Measured Flow Range

Air, NL/min

01L = 0.08 to 0.8
02L = 0.17 to 1.7
03L = 0.25 to 2.5
04L = 0.67 to 6.7
05L = 1.3 to 13
06L = 2.0 to 20
07L = 3.33 to 33.3
08L = 4.2 to 42
09L = 6.0 to 60

Air, NL/h

01M = 5.0 to 50
02M = 10 to 100
03M = 15 to 150
04M = 40 to 400
05M = 80 to 800
06M = 125 to 1250
07M = 200 to 2000
08M = 250 to 2500
09M = 340 to 3400

Air, std ft³/min

01R = 0.003 to 0.03
02R = 0.006 to 0.06
03R = 0.01 to 0.1
04R = 0.025 to 0.25
05R = 0.05 to 0.5
06R = 0.075 to 0.75
07R = 0.12 to 1.2
08R = 0.15 to 1.5
09R = 0.2 to 2.0

Air, std ft³/h

01S = 0.18 to 1.8
02S = 0.37 to 3.7
03S = 0.55 to 5.5
04S = 1.5 to 15
05S = 3.0 to 30
06S = 4.5 to 45
07S = 7.5 to 75
08S = 9.5 to 95
09S = 13 to 130

Water, L/min

A1L = 0.005 to 0.05
A2L = 0.008 to 0.08
A3L = 0.018 to 0.18
A4L = 0.04 to 0.4
A5L = 0.07 to 0.7
A6L = 0.1 to 1.0
A7L = 0.13 to 1.3
A8L = 0.17 to 1.7

Water, U.S. gal/min

A1R = 0.0013 to 0.013
A2R = 0.0022 to 0.022
A3R = 0.0045 to 0.045
A4R = 0.01 to 0.1
A5R = 0.018 to 0.18
A6R = 0.025 to 0.25
A7R = 0.035 to 0.35
A8R = 0.045 to 0.45

Water, L/h

A1M = 0.3 to 3.0
A2M = 0.5 to 5.0
A3M = 1.0 to 10
A4M = 2.5 to 25
A5M = 4.0 to 40
A6M = 6.0 to 60
A7M = 8.0 to 80
A8M = 10 to 100

Water, U.S. gal/h

A1S = 0.08 to 0.8
A2S = 0.13 to 1.3
A3S = 0.25 to 2.5
A4S = 0.65 to 6.5
A5S = 1.1 to 11
A6S = 1.6 to 16
A7S = 2.0 to 20
A8S = 2.5 to 25

5 Valve O-Ring Material

1 = Fluorocarbon (FKM) (standard)
2 = Perfluorocarbon (FFKM)

Custom

See **Custom Calibration**, page 22.

GAS = Gas

LIQ = Liquid

M1 Model

Electrical Connections

- Up to two limit switches; junction box included

6 Limit Switches with Junction Box

(See page 22.)

Limit switch amplifiers are required. Amplifiers can be ordered with the flowmeter or customer supplied.

- 0 = None
- 1 = Minimum switch
- 2 = Maximum switch
- 3 = Minimum and maximum switch
- 4 = Minimum switch and a one-channel isolated switch amplifier with relay output, 115 V (ac)
- 5 = Maximum switch and a one-channel isolated switch amplifier with relay output, 115 V (ac)
- 6 = Minimum and maximum switch and a two-channel isolated switch amplifier with relay output, 115 V (ac)
- 7 = Minimum switch and a one-channel isolated switch amplifier with relay output, 230 V (ac)
- 8 = Maximum switch and a one-channel isolated switch amplifier with relay output, 230 V (ac)
- 9 = Minimum and maximum switch and a two-channel isolated switch amplifier with relay output, 230 V (ac)
- A = Minimum switch and a one-channel isolated switch amplifier with relay output, 24 V (dc)
- B = Maximum switch and a one-channel isolated switch amplifier with relay output, 24 V (dc)
- C = Minimum and maximum switch and a two-channel isolated switch amplifier with relay output, 24 V (dc)

Temperature Ranges With Limit Switches

- As ambient temperature increases, the process temperature maximum is reduced.

Process °F (°C)	Ambient °F (°C)
293 (145)	104 (40)
275 (135)	122 (50)
257 (125)	140 (60)

7 Options (See page 22.)

Add multiple designators in alphabetical order; omit final dash (-) if no options are ordered.

- B = FM Approval certificate
- F = Certificate of compliance
- G = 5-point calibration record
- H = Pressure test, certificate
- I = Silconert Coating
- J = Material certification
- X = Oil- and grease-free cleaning (**required** for oxygen service)
- Y = No needle valve
- Z = Top-mounted needle valve

Note: For non stainless steel Alloys add the prefix HC and M.

Non Stainless Steel Options

M = Alloy K-500 HC = Alloy C-276

Example: **M-VAF-M1-02M-1-0**

Dimensions

See page 20 for M1 model dimensions.



M2 Model

The M2 model offers versatility, with an integral junction box and choice of mechanical or electronic display.

Technical Data

See **Variable Area Flowmeter Selection**, page 2.

Ordering Information

Build an M2 model variable area flowmeter ordering number by combining the designators in the sequence shown below.

4 5 6 7
VAF - M2 - 01M - 1 - 1 - F

4 Measured Flow Range

Air, NL/min

01L = 0.08 to 0.8
02L = 0.17 to 1.7
03L = 0.25 to 2.5
04L = 0.67 to 6.7
05L = 1.3 to 13
06L = 2.0 to 20
07L = 3.33 to 33.3
08L = 4.2 to 42
09L = 6.0 to 60

Air, NL/h

01M = 5.0 to 50
02M = 10 to 100
03M = 15 to 150
04M = 40 to 400
05M = 80 to 800
06M = 125 to 1250
07M = 200 to 2000
08M = 250 to 2500
09M = 340 to 3400

Air, std ft³/min

01R = 0.003 to 0.03
02R = 0.006 to 0.06
03R = 0.01 to 0.1
04R = 0.025 to 0.25
05R = 0.05 to 0.5
06R = 0.075 to 0.75
07R = 0.12 to 1.2
08R = 0.15 to 1.5
09R = 0.2 to 2.0

Air, std ft³/h

01S = 0.18 to 1.8
02S = 0.37 to 3.7
03S = 0.55 to 5.5
04S = 1.5 to 15
05S = 3.0 to 30
06S = 4.5 to 45
07S = 7.5 to 75
08S = 9.5 to 95
09S = 13 to 130

Water, L/min

A1L = 0.005 to 0.05
A2L = 0.008 to 0.08
A3L = 0.018 to 0.18
A4L = 0.04 to 0.4
A5L = 0.07 to 0.7
A6L = 0.1 to 1.0
A7L = 0.13 to 1.3
A8L = 0.17 to 1.7

Water, U.S. gal/min

A1R = 0.0013 to 0.013
A2R = 0.0022 to 0.022
A3R = 0.0045 to 0.045
A4R = 0.01 to 0.1
A5R = 0.018 to 0.18
A6R = 0.025 to 0.25
A7R = 0.035 to 0.35
A8R = 0.045 to 0.45

Water, L/h

A1M = 0.3 to 3.0
A2M = 0.5 to 5.0
A3M = 1.0 to 10
A4M = 2.5 to 25
A5M = 4.0 to 40
A6M = 6.0 to 60
A7M = 8.0 to 80
A8M = 10 to 100

Water, U.S. gal/h

A1S = 0.08 to 0.8
A2S = 0.13 to 1.3
A3S = 0.25 to 2.5
A4S = 0.65 to 6.5
A5S = 1.1 to 11
A6S = 1.6 to 16
A7S = 2.0 to 20
A8S = 2.5 to 25

5 Valve O-Ring Material

- 1 = Fluorocarbon (FKM) (standard)
- 2 = Perfluorocarbon (FFKM)

Custom

See **Custom Calibration**, page 22.

GAS = Gas

LIQ = Liquid

M2 Model

Electrical Connections

- Up to two limit switches
- 2-wire, 4 to 20 mA output signal with LED display available

6 Limit Switches or Electronic Display

(See page 22.)

Limit switch amplifiers are required. Amplifiers can be ordered with the flowmeter or customer supplied.

- 0 = None
- 1 = Minimum switch
- 2 = Maximum switch
- 3 = Minimum and maximum switch
- 4 = Minimum switch and a one-channel isolated switch amplifier with relay output, 115 V (ac)
- 5 = Maximum switch and a one-channel isolated switch amplifier with relay output, 115 V (ac)
- 6 = Minimum and maximum switch and a two-channel isolated switch amplifier with relay output, 115 V (ac)
- 7 = Minimum switch and a one-channel isolated switch amplifier with relay output, 230 V (ac)
- 8 = Maximum switch and a one-channel isolated switch amplifier with relay output, 230 V (ac)
- 9 = Minimum and maximum switch and a two-channel isolated switch amplifier with relay output, 230 V (ac)
- A = Minimum switch and a one-channel isolated switch amplifier with relay output, 24 V (dc)
- B = Maximum switch and a one-channel isolated switch amplifier with relay output, 24 V (dc)
- C = Minimum and maximum switch and a two-channel isolated switch amplifier with relay output, 24 V (dc)
- E = LED display of measured flow with 4 to 20 mA output signal

Temperature Ranges

- As ambient temperature increases, the process temperature maximum is reduced.

With Limit Switches

Process °F (°C)	Ambient °F (°C)
302 (150)	104 (40)
257 (125)	122 (50)
212 (100)	140 (60)

With 4 to 20 mA Output Signal

Process °F (°C)	Ambient °F (°C)
275 (135)	104 (40)
230 (110)	122 (50)
182 (85)	140 (60)

7 Options (See page 22.)

Add multiple designators in alphabetical order; omit final dash (-) if no options are ordered.

- F = Certificate of compliance
- G = 5-point calibration record
- H = Pressure test, certificate
- I = Silconert Coating
- J = Material certification
- X = Oil- and grease-free cleaning (**required** for oxygen service)
- Y = No needle valve
- Z = Top-mounted needle valve

Note: For non stainless steel Alloys add the prefix HC and M.

Non Stainless Steel Options

M = Alloy K-500 HC = Alloy C-276
Example: HC-VAF-M2-05R-1-0

Dimensions

See page 20 for M2 model dimensions.



M4 Model

This metal-tube flowmeter, with rugged design, is suited for extreme operating conditions and high flow rates.

Technical Data

See **Variable Area Flowmeter Selection**, page 2.

Ordering Information

Build an M4 model variable area flowmeter ordering number by combining the designators in the sequence shown below. Choose end connections and measured flow range designators based on measuring tube size.

4
5
6
7
8
9

VAF - M4 - 1 - 1 - 01M - 1 A - F

4 Measuring Tube Size

- 1 = 1/2 in.
- 2 = 1 in.

5 End Connections

1/2 in. Measuring Tube

- 1 = 1/2 in. NPT
- 2 = 3/4 in. NPT
- 3 = 1/2 in. ASME class 150 flange
- 4 = 3/4 in. ASME class 150 flange
- 5 = 1 in. ASME class 150 flange

1 in. Measuring Tube

- 1 = 3/4 in. NPT
- 2 = 1 in. NPT
- 3 = 3/4 in. ASME class 150 flange
- 4 = 1 in. ASME class 150 flange

6 Measured Flow Range

1/2 in. Measuring Tube

Air, NL/min

- 01L = 1.1 to 11
- 02L = 1.7 to 17
- 03L = 2.6 to 26
- 04L = 4.0 to 40
- 05L = 6.0 to 60
- 06L = 10 to 100
- 07L = 17 to 170
- 08L = 25 to 250
- 09L = 30 to 300
- 10L = 50 to 500

Air, std ft³/min

- 01R = 0.04 to 0.4
- 02R = 0.06 to 0.6
- 03R = 0.1 to 1.0
- 04R = 0.14 to 1.4
- 05R = 0.2 to 2.0
- 06R = 0.35 to 3.5
- 07R = 0.6 to 6.0
- 08R = 0.8 to 8.0
- 09R = 1.0 to 10
- 10R = 1.6 to 16

Air, NL/h

- 01M = 70 to 700
- 02M = 100 to 1000
- 03M = 160 to 1600
- 04M = 220 to 2200
- 05M = 360 to 3600
- 06M = 550 to 5500
- 07M = 1000 to 10 000
- 08M = 1400 to 14 000
- 09M = 1800 to 18 000
- 10M = 2800 to 28 000

Air, std ft³/h

- 01S = 2.5 to 25
- 02S = 4.0 to 40
- 03S = 5.8 to 58
- 04S = 8.0 to 80
- 05S = 13 to 130
- 06S = 20 to 200
- 07S = 38 to 380
- 08S = 52 to 520
- 09S = 65 to 650
- 10S = 100 to 1000

1/2 in. Measuring Tube

Water, L/min

- A1L = 0.03 to 0.3
- A2L = 0.04 to 0.4
- A3L = 0.05 to 0.5
- A4L = 0.07 to 0.7
- A5L = 0.095 to 0.95
- A6L = 0.105 to 1.05
- A7L = 0.13 to 1.3
- A8L = 0.17 to 1.7
- A9L = 0.2 to 2.0
- B1L = 0.27 to 2.7
- B2L = 0.35 to 3.5
- B3L = 0.4 to 4.0
- B4L = 0.6 to 6.0
- B5L = 0.7 to 7.0
- B6L = 0.85 to 8.5
- B7L = 1.05 to 10.5
- B8L = 1.2 to 12
- B9L = 1.7 to 17

Water, U.S. gal/min

- A1R = 0.008 to 0.08
- A2R = 0.01 to 0.1
- A3R = 0.015 to 0.15
- A4R = 0.018 to 0.18
- A5R = 0.025 to 0.25
- A6R = 0.03 to 0.3
- A7R = 0.035 to 0.35
- A8R = 0.045 to 0.45
- A9R = 0.05 to 0.5
- B1R = 0.07 to 0.7
- B2R = 0.09 to 0.9
- B3R = 0.11 to 1.1
- B4R = 0.15 to 1.5
- B5R = 0.18 to 1.8
- B6R = 0.22 to 2.2
- B7R = 0.28 to 2.8
- B8R = 0.3 to 3.0
- B9R = 0.45 to 4.5

Water, L/h

- A1M = 1.8 to 18
- A2M = 2.5 to 25
- A3M = 3.0 to 30
- A4M = 4.0 to 40
- A5M = 5.5 to 55
- A6M = 6.3 to 63
- A7M = 8.0 to 80
- A8M = 10 to 100
- A9M = 12 to 120
- B1M = 16 to 160
- B2M = 20 to 200
- B3M = 25 to 250
- B4M = 35 to 350
- B5M = 40 to 400
- B6M = 50 to 500
- B7M = 63 to 630
- B8M = 70 to 700
- B9M = 100 to 1000

Water, U.S. gal/h

- A1S = 0.48 to 4.8
- A2S = 0.65 to 6.5
- A3S = 0.8 to 8.0
- A4S = 1.1 to 11
- A5S = 1.5 to 15
- A6S = 1.6 to 16
- A7S = 2.0 to 20
- A8S = 2.5 to 25
- A9S = 3.0 to 30
- B1S = 4.2 to 42
- B2S = 5.0 to 50
- B3S = 6.5 to 65
- B4S = 9.0 to 90
- B5S = 10 to 100
- B6S = 13 to 130
- B7S = 16 to 160
- B8S = 18 to 180
- B9S = 25 to 250

Custom

See **Custom Calibration**, page 22.

GAS = Gas

LIQ = Liquid

M4 Model

Electrical Connections

- Up to two limit switches (M20 × 1.5 cable glands standard)
- 2-wire 4 to 20 mA output signal available

6 Measured Flow Range

1 in. Measuring Tube

Air, NL/min

- 01L** = 25 to 250
- 02L** = 40 to 400
- 03L** = 60 to 600
- 04L** = 100 to 1000
- 05L** = 200 to 2000
- 06L** = 300 to 3000

Air, std ft³/min

- 01R** = 1.0 to 10
- 02R** = 1.5 to 15
- 03R** = 2.0 to 20
- 04R** = 3.0 to 30
- 05R** = 6.5 to 65
- 06R** = 10 to 100

Water, L/min

- A1L** = 0.8 to 8.0
- A2L** = 1.05 to 10.5
- A3L** = 1.5 to 15
- A4L** = 1.7 to 17
- A5L** = 2.0 to 20
- A6L** = 2.7 to 27
- A7L** = 3.0 to 30
- A8L** = 4.2 to 42
- A9L** = 5.5 to 55
- B1L** = 7.0 to 70
- B2L** = 10 to 100

Water, U.S. gal/min

- A1R** = 0.2 to 2.0
- A2R** = 0.28 to 2.8
- A3R** = 0.35 to 3.5
- A4R** = 0.45 to 4.5
- A5R** = 0.5 to 5.0
- A6R** = 0.7 to 7.0
- A7R** = 0.75 to 7.5
- A8R** = 1.0 to 10
- A9R** = 1.5 to 15
- B1R** = 1.8 to 18
- B2R** = 3.0 to 30

Air, NL/h

- 01M** = 1400 to 14 000
- 02M** = 2300 to 23 000
- 03M** = 3500 to 35 000
- 04M** = 5000 to 50 000
- 05M** = 11 000 to 110 000
- 06M** = 18 000 to 180 000

Air, std ft³/h

- 01S** = 52 to 520
- 02S** = 85 to 850
- 03S** = 130 to 1300
- 04S** = 190 to 1900
- 05S** = 400 to 4000
- 06S** = 670 to 6700

Water, L/h

- A1M** = 48 to 480
- A2M** = 63 to 630
- A3M** = 82 to 820
- A4M** = 100 to 1000
- A5M** = 120 to 1200
- A6M** = 160 to 1600
- A7M** = 170 to 1700
- A8M** = 250 to 2500
- A9M** = 320 to 3200
- B1M** = 400 to 4000
- B2M** = 630 to 6300

Water, U.S. gal/h

- A1S** = 13 to 130
- A2S** = 16 to 160
- A3S** = 22 to 220
- A4S** = 25 to 250
- A5S** = 32 to 320
- A6S** = 42 to 420
- A7S** = 45 to 450
- A8S** = 65 to 650
- A9S** = 85 to 850
- B1S** = 110 to 1100
- B2S** = 160 to 1600

Custom

See *Custom Calibration*, page 22.

GAS = Gas

LIQ = Liquid

Temperature Ranges With Limit Switches or 4 to 20 mA Output Signal

- Ambient low temperature is limited to -13°F (-25°C) with limit switches.
- As ambient temperature increases, the process temperature maximum is reduced.

Process °F (°C)	Ambient °F (°C)
392 (200)	104 (40)
356 (180)	140 (60)

7 Limit Switches (See page 22.)

Limit switch amplifiers are required.

Amplifiers can be ordered with the flowmeter or customer supplied.

- 0** = None
- 1** = Minimum switch
- 2** = Maximum switch
- 3** = Minimum and maximum switch
- 4** = Minimum switch and a one-channel isolated switch amplifier with relay output, 115 V (ac)
- 5** = Maximum switch and a one-channel isolated switch amplifier with relay output, 115 V (ac)
- 6** = Minimum and maximum switch and a two-channel isolated switch amplifier with relay output, 115 V (ac)
- 7** = Minimum switch and a one-channel isolated switch amplifier with relay output, 230 V (ac)
- 8** = Maximum switch and a one-channel isolated switch amplifier with relay output, 230 V (ac)
- 9** = Minimum and maximum switch and a two-channel isolated switch amplifier with relay output, 230 V (ac)
- A** = Minimum switch and a one-channel isolated switch amplifier with relay output, 24 V (dc)
- B** = Maximum switch and a one-channel isolated switch amplifier with relay output, 24 V (dc)
- C** = Minimum and maximum switch and a two-channel isolated switch amplifier with relay output, 24 V (dc)

8 Output Signal

Omit designator if output signal not ordered.

A = 4 to 20 mA

9 Options (See page 22.)

Add multiple designators in alphabetical order; omit final dash (-) if no options are ordered.

- B** = FM Approval Class I, Division 1 IS
- C** = FM Approval Class I, Division 1 XP
- D** = FM Approval Class I, Division 2 NI
- F** = Certificate of compliance
- G** = 5-point calibration record
- H** = Pressure test, certificate
- I** = Silconert Coating
- J** = Material certification
- L** = Dye penetration test, certificate
- N** = X-ray test, report
- P** = Hardness test, report
- R** = 1/2 in. female NPT conduit gland
- S** = M20 × 1.5 cable gland
- X** = Oil- and grease-free cleaning (**required** for oxygen service)

Note: For non stainless steel Alloys add the prefix HC and M.

Non Stainless Steel Options

M = Alloy K-500

HC = Alloy C-276

Example: **M-VAF-M4-1-1-01L-0**

Dimensions

See page 20 for M4 model dimensions.



M4H Model

This horizontal model offers liquid flow reading left-to-right or right-to-left to meet system requirements.

Technical Data

See **Variable Area Flowmeter Selection**, page 2.

Ordering Information

Build an M4H model variable area flowmeter ordering number by combining the designators in the sequence shown below. Choose end connections and measured flow range designators based on measuring tube size.

4 5 6 7 8 9 10
 VAF - M4H - 1 - 1 - A1M - 1 A - RL - F

4 Measuring Tube Size

- 1 = 1/2 in.
- 2 = 1 in.

5 End Connections

1/2 in. Measuring Tube

- 1 = 3/4 in. NPT
- 2 = 1/2 in. ASME class 150 flange
- 3 = 3/4 in. ASME class 150 flange
- 4 = 1 in. ASME class 150 flange

1 in. Measuring Tube

- 1 = 1 1/4 in. NPT
- 2 = 1 in. ASME class 150 flange

6 Measured Flow Range

1/2 in. Measuring Tube

Water, L/min

- A1L = 0.11 to 1.1
- A2L = 0.2 to 2.0
- A3L = 0.3 to 3.0
- A4L = 0.5 to 5.0
- A5L = 0.75 to 7.5
- A6L = 1.2 to 12
- A7L = 2.0 to 20
- A8L = 2.5 to 25
- A9L = 4.0 to 40

Water, U.S. gal/min

- A1R = 0.03 to 0.3
- A2R = 0.05 to 0.5
- A3R = 0.08 to 0.8
- A4R = 0.12 to 1.2
- A5R = 0.2 to 2.0
- A6R = 0.3 to 3.0
- A7R = 0.5 to 5.0
- A8R = 0.7 to 7.0
- A9R = 1.07 to 10.7

1 in. Measuring Tube

Water, L/min

- A1L = 2.0 to 20
- A2L = 3.0 to 30
- A3L = 5.0 to 50
- A4L = 8.0 to 80
- A5L = 15 to 150
- A6L = 17 to 170

Water, U.S. gal/min

- A1R = 0.6 to 6.0
- A2R = 0.9 to 9.0
- A3R = 1.4 to 14
- A4R = 2.2 to 22
- A5R = 4.0 to 40
- A6R = 4.5 to 45

Water, L/h

- A1M = 7.0 to 70
- A2M = 12 to 120
- A3M = 18 to 180
- A4M = 28 to 280
- A5M = 45 to 450
- A6M = 70 to 700
- A7M = 120 to 1200
- A8M = 160 to 1600
- A9M = 240 to 2400

Water, U.S. gal/h

- A1S = 2.0 to 20
- A2S = 3.0 to 30
- A3S = 5.0 to 50
- A4S = 8.0 to 80
- A5S = 12 to 120
- A6S = 20 to 200
- A7S = 32 to 320
- A8S = 43 to 430
- A9S = 64 to 640

Water, L/h

- A1M = 130 to 1300
- A2M = 200 to 2000
- A3M = 300 to 3000
- A4M = 500 to 5000
- A5M = 850 to 8500
- A6M = 1000 to 10 000

Water, U.S. gal/h

- A1S = 35 to 350
- A2S = 55 to 550
- A3S = 80 to 800
- A4S = 130 to 1300
- A5S = 230 to 2300
- A6S = 270 to 2700

Custom

See **Custom Calibration**, page 22.

LIQ = Liquid

7 Limit Switches (See page 22.)

Limit switch amplifiers are required. Amplifiers can be ordered with the flowmeter or customer supplied.

0 = None

1 = Minimum switch

2 = Maximum switch

3 = Minimum and maximum switch

4 = Minimum switch and a one-channel isolated switch amplifier with relay output, 115 V (ac)

5 = Maximum switch and a one-channel isolated switch amplifier with relay output, 115 V (ac)

6 = Minimum and maximum switch and a two-channel isolated switch amplifier with relay output, 115 V (ac)

7 = Minimum switch and a one-channel isolated switch amplifier with relay output, 230 V (ac)

8 = Maximum switch and a one-channel isolated switch amplifier with relay output, 230 V (ac)

9 = Minimum and maximum switch and a two-channel isolated switch amplifier with relay output, 230 V (ac)

A = Minimum switch and a one-channel isolated switch amplifier with relay output, 24 V (dc)

B = Maximum switch and a one-channel isolated switch amplifier with relay output, 24 V (dc)

C = Minimum and maximum switch and a two-channel isolated switch amplifier with relay output, 24 V (dc)

M4H Model

Electrical Connections

- Up to two limit switches (M20 × 1.5 cable glands standard)
- 2-wire 4 to 20 mA output signal available

8 Output Signal

Omit designator if output signal not ordered.

A = 4 to 20 mA

9 Flow Direction

RL = Right-to-left

LR = Left-to-right

10 Options (See page 22.)

Add multiple designators in alphabetical order; omit final dash (-) if no options are ordered.

B = FM Approval Class I, Division 1 IS

C = FM Approval Class I, Division 1 XP

D = FM Approval Class I, Division 2 NI

F = Certificate of compliance

G = 5-point calibration record

H = Pressure test, certificate

J = Material certification

L = Dye penetration test, certificate

N = X-ray test, report

P = Hardness test, report

R = 1/2 in. female NPT conduit gland

S = M20 × 1.5 cable gland

X = Oil- and grease-free cleaning (**required** for oxygen service)

Note: For non stainless steel Alloys add the prefix HC.

Non Stainless Steel Options

HC = Alloy C-276

Example: **HC-VAF-M4H-2-2-A4R-0-LR**

Temperature Ranges With Limit Switches or 4 to 20 mA Output Signal

- Ambient low temperature is limited to -13°F (-25°C) with limit switches.
- As ambient temperature increases, the process temperature maximum is reduced.

Process °F (°C)	Ambient °F (°C)
392 (200)	104 (40)
356 (180)	140 (60)

Dimensions

See page 21 for M4H model dimensions.




Left-to-Right Flow Model

Dimensions

Dimensions, in inches and (millimeters), are for reference only and are subject to change.


G1, G2, G3, G4, and GP Models



① GP model: G 1/4.


Model	Dimensions, in. (mm)			Weight lb (kg)
	A	B	C	
G1	4.37 (111)	3.54 (90.0)	1.77 (45.0)	0.80 (0.36)
G2	5.75 (146)	4.92 (125)	3.15 (80.0)	0.89 (0.40)
G3	7.72 (196)	6.89 (175)	5.12 (130)	0.98 (0.44)
G4	13.6 (346)	12.8 (325)	11.0 (280)	1.35 (0.61)
GP	5.75 (146)	4.92 (125)	3.15 (80.0)	0.44 (0.20)

M1 Model




Weight: 1.53 lb (0.7 kg)

GM Model



Weight: 0.18 lb (0.08 kg)

M2 Model




Weight: 2.2 lb (1.0 kg)


Dimensions

Dimensions, in inches and (millimeters), are for reference only and are subject to change.

M4 Model



M4H Model



**Right-to-Left
Flow Model**

M4 Model and M4H Model

Tube Size in.	Process End Connection	Dimensions, in. (mm)		Weight lb (kg)
		A	L	
1/2	NPT	11.8 (300)	4.49 (114)	4.4 (2.0)
	Flange	9.84 (250)	4.49 (114)	7.7 (3.5)
1	NPT	11.8 (300)	5.00 (127)	7.7 (3.5)
	Flange	9.84 (250)	5.00 (127)	11 (5.0)

Custom Calibration

Standard Swagelok variable area flowmeters are factory calibrated to their media, flow range, and accuracy class using clean, dry air for air-flow range models and water for water-flow range models. Standard units of measure marked on the scale are calibrated to:

- 17.4 psia (1.2 bar) and 68°F (20°C) for G1, G2, G3, GM, and GP models.
- 14.7 psia (1.013 bar) and 68°F (20°C) for G4, M1, M2, M4, and M4H models.

Custom-calibrated flowmeters are available for fluids with properties substantially different from those of air or water, as well as systems operating at higher pressures or temperatures.

Flowmeters calibrated for one fluid at a specific pressure and temperature can be used to measure other fluids and different pressures and temperatures by using a conversion factor. See the Swagelok *Variable Area Flowmeters Installation Instructions, G Series and M Series*, MS-CRD-0111, for more information.

In liquids, higher temperature can reduce viscosity and density, resulting in lower readings. In gases, higher fluid temperature can increase volume and result in higher readings. Knowing the specific fluid temperature enables us to calibrate the scale more accurately.

Increased pressure can compress gases and lead to lower meter readings. Knowing the system pressure enables us to calibrate the scale properly for your application.

To order a custom Swagelok variable area flowmeter calibrated to meet your requirements as shown below, use **GAS** or **LIQ** as the flow range designator in the desired model ordering number and contact your authorized Swagelok representative. You will need to specify:

1. Fluid to be measured
2. Fluid dynamic viscosity, typically in cP or mPa-s, or kinetic viscosity, typically in cSt or m²/s, at operating pressure and temperature
3. Fluid density in lb/ft³ or kg/m³ at operating pressure and temperature
4. Fluid temperature at operating conditions, with unit of measure
5. Fluid pressure at operating conditions, with unit of measure
6. Flow measurement range and unit of measure.

Swagelok custom-calibrated variable area flowmeters must maintain a 10-to-1 turndown ratio and are matched as closely as possible to the desired flow measurement range. Custom-calibrated flowmeters are marked with the fluid media and unit of measure for which they are calibrated.

Options

Options are specified in variable area flowmeter ordering numbers as shown in **Ordering Information** for each model.

Electrical Options

Two electrical options are available with select Swagelok variable area flowmeter models:

- discrete limit switch outputs for indicating high/low flow
- 4 to 20 mA output signal.


Limit Switches

Optional minimum or maximum limit switches available for most models are compliant with NAMUR IEC 60947-5-6 (EN 60947-5-6).

Output Signal

Some variable area flowmeter models are available with a separate two-wire 4 to 20 mA output signal. These models require auxiliary power of 14.8 to 30 V (dc).

For more information about electrical options, see the Swagelok *Variable Area Flowmeters Installation Instructions, G Series and M Series*, MS-CRD-0111, available *only* on your Swagelok website.



G Series Flowmeter with Limit Switches, Junction Box, and Isolated Switch Amplifier with Relay Output

Junction Boxes

Junction boxes, available on select Swagelok variable area flowmeter models, can be mounted to the flowmeter to facilitate electrical connections between the flowmeter and the control system. Junction boxes are suggested when limit switches are ordered.

Valve Position

An integral needle valve for fine metering is provided on some products, on the bottom (inlet) side of the flowmeter. Upon request, the valve can be mounted on the top (outlet) side or omitted from the assembly.

For gas applications, the valve is typically on the top (behind the measuring cone) to help maintain constant pressure in the measuring cone despite changes in density caused by gas compression or decompression. For liquids, the valve can be on the bottom or the top, because pressure changes do not affect liquid density.

Options

Options are specified in variable area flowmeter ordering numbers as shown in **Ordering Information** for each model.

Certificates and Test Reports

FM Approvals Certificate

Swagelok M1, M4, and M4H models are available with FM Approvals certificates of compliance.

M1 Model

- Intrinsically safe for Class I, Division 1, Groups A, B, C, and D
- Nonincendive for Class I, Division 2, Groups A, B, C, and D
- Explosion proof Class I, Division 1, Groups A, B, C, and D
- Type 4X

M4 and M4H Model

- Intrinsically safe for Class I, Division 1, Groups A, B, C, and D
- Associated apparatus nonincendive for Class I, Division 2, Groups A, B, C, and D
- Nonincendive for Class I, Division 2, Groups A, B, C, and D
- Type 4X

Certificate of Compliance

This document certifies that the products supplied to the customer by the manufacturer are in compliance with the requirements of the order, in accordance with EN 10204.

5-Point Calibration Record

The calibration record shows actual flow performance, theoretical performance, and error over the measurement range.

Pressure Test and Certificate

A hydrostatic pressure test based on EN 10204 is available.

Material Certification

This inspection certificate, in accordance with EN 10204, shows the material and heat numbers of the pressure-bearing and wetted materials, as well as the original mill material certifications of the wetted materials.

Dye Penetration Test and Certificate

A dye penetration test is available for wetted welds. For acceptance criteria, the related material standard is used.

X-Ray Test and Report

An X-ray test is available for wetted welds. The test procedure follows EN 1435-1 Class B. Acceptance criteria are in accordance with ISO 5817 group.

Hardness Test and Report

A hardness test on wetted metal components, based on ASTM A956, is available.

Oil- and Grease-Free Cleaning

An additional degreasing operation is available that meets the requirements of DIN 25410 and KWU-AVS 8/0 D. This option must be selected on flowmeters calibrated for oxygen service.

Oxygen Service Hazards

For information about hazards and risks of oxygen-enriched systems, see the Swagelok *Oxygen System Safety* technical report, (MS-06-13).

Options

Options are specified in variable area flowmeter ordering numbers as shown in **Ordering Information** for each model.

Mounting Brackets


Panel Mounting

Panel mounting is available for G1, G2, G3, G4, GM, and GP model flowmeters. The face plate is aluminum, and the rear brackets are steel.

G1, G2, G3, G4, and GP models are mounted with four nickel-plated steel fasteners, included; GM models are mounted with an anodized aluminum clamp clip and 4 mm stainless steel Allen screw.

Dimensions, in inches (millimeters) are for reference only and are subject to change.


Model	Dimensions, in. (mm)					
	A	B	C	D	E	F
G1	5.04 (128)	1.26 (32.0)	5.71 (145)	1.58 (40.0)	1.75 (44.5)	3.23 (82.0)
G2, GP	6.42 (163)	1.26 (32.0)	7.09 (180)	1.58 (40.0)	1.75 (44.5)	3.23 (82.0)
G3	8.39 (213)	1.26 (32.0)	9.06 (230)	1.58 (40.0)	1.75 (44.5)	3.23 (82.0)
G4	14.3 (363)	1.26 (32.0)	15.0 (380)	1.58 (40.0)	1.75 (44.5)	3.23 (82.0)
GM	3.70 (94.0)	0.91 (23.0)	3.82 (97.0)	0.98 (25.0)	1.38 (35.0)	2.56 (65.0)



Wall Mounting

Black anodized aluminum wall mounting brackets are available for G1, G2, G3, and GP model flowmeters.

Dimensions, in inches (millimeters) are for reference only and are subject to change.



Model	Dimensions, in. (mm)	
	A	B
G1	1.77 (45.0)	2.64 (67.0)
G2, GP	3.15 (80.0)	4.02 (102)
G3	5.12 (130)	5.98 (152)

Accessories

Damping Device

For unstable flows or low operating (inlet) pressures, particularly with gas applications, the measuring section can be fitted with a float damping device on some M4 and M4H models. This device is self-locating, with working parts of high-tech ceramic to ensure a long service life.

For more information, contact your authorized Swagelok representative.

Additional Products

Pressure Regulators

Swagelok offers a variety of pressure regulators.

- Spring-, dome-, and air-loaded models
- Pressure-reducing regulators
- Back-pressure regulators
- Gas cylinder changeover manifolds
- Electrically heated and steam-heated vaporizing regulators.

Refer to Swagelok *Pressure Regulators* catalog, [MS-02-230](#), and the Swagelok *Pressure Regulators, RHPS Series* catalog, [MS-02-430](#), for additional information.



Metering Valves

Swagelok metering valves offer:

- Low- and high-pressure service
- Repeatable vernier handles
- Brass and 316 stainless steel materials.

Refer to Swagelok *Metering Valves* catalog, [MS-01-142](#), for additional information.



⚠ WARNING

Do not mix/interchange Swagelok products or components not governed by industrial design standards, including Swagelok tube fitting end connections, with those of other manufacturers.

Introduction

Since 1947, Swagelok has designed, developed, and manufactured high-quality, general-purpose and specialty fluid system products to meet the evolving needs of global industries. Our focus is on understanding our customers' needs, finding timely solutions, and adding value with our products and services.

We are pleased to provide this global edition of the book-bound *Swagelok Product Catalog*, which compiles more than 100 separate product catalogs, technical bulletins, and reference documents into one convenient, easy-to-use volume. Each product catalog is up to date at the time of printing, with its revision number shown on the last page of the individual catalog. Subsequent revisions will supersede the printed version and will be posted on the Swagelok website and in the Swagelok electronic Desktop Technical Reference (eDTR) tool.

For more information, visit your Swagelok website or contact your authorized Swagelok sales and service representative.

Warranty Information

Swagelok products are backed by The Swagelok Limited Lifetime Warranty. For a copy, visit swagelok.com or contact your authorized Swagelok representative.

Safe Product Selection

When selecting a product, the total system design must be considered to ensure safe, trouble-free performance. Function, material compatibility, adequate ratings, proper installation, operation, and maintenance are the responsibilities of the system designer and user.

WARNING

Do not mix/interchange Swagelok products or components not governed by industrial design standards, including Swagelok tube fitting end connections, with those of other manufacturers.

Not all trademarks listed below apply to this catalog.
Swagelok, Cajon, Ferrule-Pak, Goop, Hinging-Colleting, IGC, Kenmac, Micro-Fit, Nupro, Snoop, Sno-Trik, SWAK, VCO, VCR, Ultra-Torr, Whitey—TM Swagelok Company
15-7 PH—TM AK Steel Corp.
AccuTrak, Beacon, Westlock—TM Tyco International Services
Atlas—TM Asahi Glass Co., Ltd.
ASCO, El-O-Matic—TM Emerson
AutoCAD—TM Autodesk, Inc.
CSA—TM Canadian Standards Association
Crastin, DuPont, Kalrez, Krytox, Teflon, Viton—TM E.I. duPont Nemours and Company
DeviceNet—TM ODVA
Dyneon, Elgiloy, TFM—TM Dyneon
Elgiloy—TM Elgiloy Specialty Metals
FM—TM FM Global
Grafoil—TM GrafTech International Holdings, Inc.
Honeywell, MICRO SWITCH—TM Honeywell
MAC—TM MAC Valves
Microsoft, Windows—TM Microsoft Corp.
NACE—TM NACE International
PH 15-7 Mo, 17-7 PH—TM AK Steel Corp
picofast—Hans Turck KG
Pillar—TM Nippon Pillar Packing Company, Ltd.
Raychem—TM Tyco Electronics Corp.
Sandvik, SAF 2507—TM Sandvik AB
Simriz—TM Freudenberg-NOK
SolidWorks—TM SolidWorks Corporation
UL—Underwriters Laboratories Inc.
Xylan—TM Whitford Corporation
© 2021 Swagelok Company