Pressure Regulators K Series



- Back-pressure models
- Gas cylinder changeover model
- Vaporizing models



Contents

Operation, 3

Selection, 4

Testing, 3

Cleaning and Packaging, 3

Features, 5

Pressure-Reducing



General-Purpose (KPR Series), 6



Two-Stage

(KCY Series), 8



High-Sensitivity (KLF Series), 10



High-Flow, **High-Sensitivity** (KHF Series), 12



Compact (KCP Series), 14



Medium- to **High-Pressure** (KPP Series), 16



High-Flow (KPF Series), 18



High-Pressure (KHP Series), 20



High-Pressure Hydraulic (KHR Series), 22

Back-Pressure



General-Purpose (KBP Series), 24



High-Flow, **High-Sensitivity** (KFB Series), 26



Compact (KCB Series), 28



Medium- to **High-Pressure** (KPB Series), 30



High-Pressure (KHB Series), 32



Specialty Pressure-Reducing



Gas Cylinder Changeover (KCM Series), 34





Steam-Heated Vaporizing (KSV Series), 36



Electrically Heated



Vaporizing (KEV Series), 38



Flow Data

Pressure-Reducing Regulators, 41 **Back-Pressure Regulators, 49**

Port Configurations, 52

Options and Accessories, 53

Maintenance Kits, 56



Pressure Regulator Operation

Regulators reduce the pressure of a gas or liquid from a source, such as a cylinder or compressor, to a lower value needed by a device, such as an analyzer. A pressure regulator provides better resolution and control when its inlet and control range pressures closely match the pressure requirements of the fluid handling system. *Resolution* is the number of handle turns needed to adjust a regulator from its lowest to highest outlet pressure setting. *Control* is the ability of the regulator to hold a given outlet pressure set point.

Pressure-Reducing Regulators

Pressure-reducing regulators control outlet pressure by balancing an adjustable spring force against the forces caused by inlet and outlet pressures. The spring force is adjusted by turning the stem/handle, which sets the desired outlet pressure.

As inlet pressure decreases, the force balance changes. To compensate, outlet pressure will increase. This supplypressure effect (SPE) is a function of the design and type of regulator. If a regulator is subjected to fluctuating inlet pressure, and outlet pressure variations are not desirable, a two-stage regulator is available.

Specialty Pressure-Reducing Regulators

Gas Cylinder Changeover

A two-stage gas cylinder changeover model automatically switches between two sources.

Vaporizing

Vaporization regulators are available with electric and steam heat to vaporize liquid samples or to preheat gas samples.

Supply-Pressure Effect

Supply-pressure effect (SPE) or dependency is a ratio describing the change in outlet pressure per 100 psi (6.8 bar) change in inlet pressure. In other words, for every 100 psi (6.8 bar) drop in inlet pressure, the outlet pressure will increase by X psi. X is the SPE. For standard pressure-reducing regulators, the outlet pressure increases as supply pressure decreases. The opposite is true as supply pressure increases. This effect can also be realized on system startup or shutdown.

The regulator should be set to the "off" position before turning the supply pressure on or off to prevent overpressurization of regulator diaphragms, outlet pressure gauges, or other equipment downstream. When selecting an antitamper model, it is important to make sure that SPE will not cause excessive overpressurization on opening and closing of the supply pressure.

Back-Pressure Regulators

Back-pressure regulators control inlet pressure by balancing an adjustable spring force against the force of the inlet pressure. The spring force is adjusted by turning the stem/ handle, which sets the desired inlet pressure.

When the force caused by the inlet pressure rises above the force of the spring, the regulator opens until the spring force and inlet pressure are balanced again.

- ▲ Swagelok pressure regulators are not "Safety Accessories" as defined in the Pressure Equipment Directive 2014/68/EU.
- \triangle Do not use the regulator as a shutoff device.
- ▲ Self-venting and captured-venting regulators can release system fluid to atmosphere. Position the self-vent hole or the captured vent connection away from operating personnel. See Venting Options, page 5, for more information.

Testing

Every Swagelok K series pressure regulator is pressure tested with nitrogen.

Cleaning and Packaging

Every Swagelok K series pressure regulator is cleaned and packaged in accordance with Swagelok *Standard Cleaning and Packaging (SC-10)* catalog, <u>MS-06-62</u>.

Cleaning and packaging in accordance with Swagelok Special Cleaning and Packaging (SC-11) catalog, <u>MS-06-63</u>, to ensure compliance with product cleanliness requirements stated in ASTM G93 Level C is available for select KPR, KCY, KCP, KBP, and KCB series regulators.

Oxygen Service Hazards

For more information about hazards and risks of oxygenenriched systems, refer to Swagelok *Oxygen System Safety* technical report, <u>MS-06-13</u>.

The design and operation of oxygen systems are the responsibility of the users. Qualified professional assistance should be obtained to ensure the use of oxygen.

K Series Pressure Regulator Selection

	Series																
	Pressure-Reducing Models						Specialty Regulators				l	Back-P	ressure	Model	s		
	KPR	ксү	KLF	KHF	КСР	KPP	KPF	КНР	KHR	ксм	KSV	KEV	KBP	KFB	КСВ	KPB	КНВ
Diaphragm Sensing	1	1	1	1						1	1	✓1	1	1			
Piston Sensing					1	1	1	1	1			1			1	1	1
2 Stage		1								1							
Gas Cylinder Changeover										1							
Electrical Vaporizing												1					
Steam Vaporizing											1						
Compact, MPC Platform					1										1		
Max Inlet Pressure, psig (bar)	6000	(413)	3	600 (24	-8)	6000) (413)	10 00	0 (689)	4351 (300)	3600	(248)	Equal	to pre	ssure o	control	range
Pressure Control Ranges						1											
0 to 2 (0.13)			1														
0 to 10 (0.68)	1	1	1	1	1					1	1	1	1	1	1		
0 to 25 (1.7)	1	1	1	1	1					1	1	1	1	1	1		
0 to 50 (3.4)	1	1	1	1	1					1	1	1	1	1	1		
0 to 100 (6.8)	1	1	1	1	1					1	1	1	1	1	1		
0 to 250 (17.2)	1	1	1	1	1					1	1	1	1	1	1		
0 to 375 (25.8)															1		
0 to 500 (34.4)	1	1			1			1	1	1	1	1	1				1
0 to 750 (51.6)								1	1								1
0 to 1000 (68.9)					1	1	1					1				1	
0 to 1500 (103)					1	1						1					
0 to 2000 (137)						1	1					1				1	
0 to 3000 (206)						1	1					1				1	
0 to 3600 (248)						1						1				-	
0 to 4000 (275)							1					-				1	
10 to 1500 (0.68 to 103)								1	1							-	1
15 to 2500 (1.0 to 172)								1	1								1
25 to 3600 (1.7 to 248)								1	1								
50 to 6000 (3.5 to 413)								1	1								1
100 to 10 000 (6.8 to 689)								1	1								1
Flow Coefficient (C _v)			L	1	L	1		-				1					
0.02	1		1		1	1						1					
0.06		1	1		1	·		1	1	1	1	1				1	1
0.10	ļ.	-	-		-					-	-	-			1	-	
0.20		1	1		1						1		1		· /	1	
0.25	ŀ	•	-		-			1	1		-		<u>├</u>		ŀ		1
0.50		1	1		1			-									•
1.0	ŀ	•	•	1	•		1							1			
Page	6	8	10	12	14	16	• 18	20	22	34	36	38	24	v 26	28	30	32
	Ľ	0		12	. 4	10		20	~~	04	00	00		20	20	00	<u> </u>

① Outlet pressures up to 500 psig (34.4 bar) require diaphragm sensing mechanism; outlet pressures above 500 psig (34.4 bar) require piston sensing mechanism.



Swagelok[®] K Series Pressure Regulator Features

Stem

Fine-pitch threads enable precise spring adjustment with low torque.

Stop Plate

This disc provides positive backup to the diaphragm in case of diaphragm overpressure.

Convoluted Diaphragm

The all-metal diaphragm acts as the sensing mechanism between the inlet pressure and the range spring. The convoluted, nonperforated design ensures greater sensitivity and longer life. A piston sensing mechanism (shown below) can accommodate higher pressures.

Gauze Inlet Filter

Regulators are susceptible to damage from system particles. Swagelok pressure-reducing regulators include a 25 µm press fit filter. It can be removed to use the regulator in liquid service.





Range Spring

Turning the handle compresses the spring, pushing the poppet away from the seat and increasing outlet pressure.

Two-Piece Cap

The two-piece design provides linear load on the diaphragm seal when the cap ring is tightened, eliminating torque damage to the diaphragm during assembly.

Poppet Damper

The poppet damper keeps the poppet aligned and reduces vibration and resonance.

Venting Options

The **self-vent** option allows excess outlet pressure to vent through the body cap. This can occur when downstream flow is suddenly reduced or when the handle is adjusted to a lower pressure with little or no flow downstream.

The captured-vent option includes a 1/8 in. female NPT connection and stem seal in the body cap⁽¹⁾ to allow monitoring of the diaphragm or piston sensing mechanism. It also allows containment of hazardous gas or liquid media should a diaphragm or piston rupture.

Self-vent and captured-vent options can be ordered together so that hazardous gas or liquid media can be contained if vented.

① The captured-vent port is in the bottom of the KHR series body.

Piston Sensing Mechanism

Piston sensing mechanisms typically are used to regulate higher pressures than a diaphragm can withstand. They are also more resistant to damage caused by pressure spikes and have a short stroke to maximize cycle life.



Fully-Contained Piston The piston is contained by a shoulder in the regulator body cap to prevent piston blowout if the regulator outlet is overpressurized.



General-Purpose Diaphragm-Sensing, Pressure-Reducing Regulators (KPR Series)

The KPR series is a compact regulator with excellent accuracy, sensitivity, and setpoint pressure stability.

Supply-Pressure Effect

Flow

Coefficient

(C_v)

0.02

0.06

0.20

0.50

Weight

2.4 lb (1.1 kg)

Pressure Control Range

Supply Pressure Effect, %

250 psig (17.2 bar) and Higher

0.5

1.5

2.5

3.3

Up to

100 psig

(6.8 bar)

0.3

1.0

1.7

2.3

Maximum Operating Temperature

212°F (100°C) with PEEK seat and

maximum inlet pressure greater than

176°F (80°C) with PCTFE seat

392°F (200°C) with PEEK seat

3600 psig (248 bar)

Features

- Convoluted, nonperforated diaphragm
- Metal-to-metal diaphragm seal
- Low internal volume
- Two-piece cap design provides linear load on the diaphragm seal
- High-flow, dual-gauze type filter in inlet ports

Technical Data

Maximum Inlet Pressure

- 3600 psig (248 bar)
- 6000 psig (413 bar) with PEEK seat

Pressure Control Ranges

 0 to 10 psig (0.68 bar) through 0 to 500 psig (34.4 bar)

Flow Coefficient (C_v)

- 0.06 and 0.20
- See page 41 for flow graphs.
- 0.02 and 0.50 also available

Materials of Const	ruction
	Cover
Stem nut	
Stem	Knob handle
Spring stabilizer	Spring button
Stop plate	Range spring
Cap ring	Body cap
Diaphragm	Seat retainer
Seat	Poppet
	Poppet spring
Inlet	Outlet
Filter carrier, filter	Poppet damper
Body	

Component		Material				
Knob handle, cover	1	Vylon with 3	16 SS insert			
Spring button		Zinc-pla	ted steel	ed steel		
Spring stabilizer ^①		301	SS			
Range spring			oated/plated			
Stem, stem nut, cap ring, stop plate, body cap, panel nuts [©]		316	SS			
VCR nuts ²	316 SS		—			
Nonwetted lubricant		Hydrocart	oon-based			
Seat retainer	316	SS	Alloy 400	Alloy C-276		
Seat		PCTFE	or PEEK	EEK		
Filter	316	SS	Alloy 22			
Diaphragm ³	A	lloy X-750 d	or alloy C-276			
Poppet	S1740	00 SS	Alloy 400	Alloy C-276		
Poppet spring		Alloy X-750		Alloy C-276		
Poppet damper, filter carrier		PTFE				
Self-vent seal ²	Fluorocar	bon FKM	-	-		
Body	316 SS Brass CW721R					
Tube butt weld ports, [®] VCR gland ports [®]	316L SS		_			
Wetted lubricant		PTFE-	based			

Wetted components listed in italics.

1 Not required in all configurations.

② Not shown.

③ Regulators with control ranges higher than 0 to 100 psig (0 to 6.8 bar) are assembled with two diaphragms.

Swagelot

Ports

316 SS

- 1/4 in. female NPT inlet, outlet, and gauge ports (all body materials)
- 1/4 in. tube butt weld inlet, outlet, and gauge ports (316 SS body material only)

Brass

CW721R

 1/4 in. VCR[®] inlet, outlet, and gauge ports (316 SS body material only)

Alloy 400

Alloy

C-276



Dimensions, in inches (millimeters), are for reference only and are subject to change.



Ordering Information

Build a KPR series regulator ordering number by combining the designators in the sequence shown below.

9 6 8 10 13 16 KPR 4 2 2 O O O 0

4 Body Material

- 1 = 316 SS
- 2 = Brass CW721R
- **4** = Alloy 400
- 5 = Alloy C-276
- **C** = 316 SS, SC-11–cleaned
- **D** = Brass, SC-11–cleaned

5 Pressure Control Range

- **C** = 0 to 10 psig (0 to 0.68 bar)^①
- **D** = 0 to 25 psig (0 to 1.7 bar)^①
- E = 0 to 50 psig (0 to 3.4 bar)
- **F** = 0 to 100 psig (0 to 6.8 bar)
- **G** = 0 to 250 psig (0 to 17.2 bar)
- J = 0 to 500 psig (0 to 34.4 bar)
- ① Select 0.02 or 0.06 flow coefficient if maximum inlet pressure is 4351 psig (300 bar) or 6000 psig (413 bar).

6 Maximum Inlet Pressure¹²

- F = 100 psig (6.8 bar)
- J = 500 psig (34.4 bar)
- L = 1000 psig (68.9 bar)
- P = 3000 psig (206 bar)
- R = 3600 psig (248 bar)
- **T** = 4351 psig (300 bar)³
- **W** = 6000 psig (413 bar)³⁽⁴⁾
- ① For better resolution and control, select a pressure that closely matches system pressure.
- ② Cylinder Connections and Hose accessories may limit inlet pressure ratings, see pages 53 and 56.
- ③ Available only with 316 SS body material and PEEK seat material.
- ④ Not available for regulators assembled with isolation valves.

7 Port Configuration

A, B, C, E, F, H, K, L, M, N See Port Configurations, page 52.

8 Ports

- 4 = 1/4 in, female NPT
- $\mathbf{T} = 1/4$ in. $\times 0.035$ in. tube butt weld^①
- V = 1/4 in. VCR gland, no nuts¹²
- **X** = 1/4 in. rotatable female VCR fitting^①
- **Y** = 1/4 in. rotatable male VCR fitting^①
- ① Available only with 316 SS body material in A and F port configurations; does not contain a filter. Not available with maximum inlet pressure greater than 3600 psig (248 bar).
- ② For use with VCR split-nuts, which can be ordered separately. Refer to Swagelok VCR Metal Gasket Face Seal Fittings catalog, MS-01-24.

9 Seat Material

- 1 = PCTFE
- **2** = PEEK

10 Flow Coefficient (C_{v})

1 = 0.02	5 = 0.20
2 = 0.06	7 = 0.50

11 Sensing Mechanism, Vent

- A = Alloy X-750 diaphragm, no vent
- C = Alloy X-750 diaphragm, self vent^①
- **E** = Alloy X-750 diaphragm, captured
- vent. no self vent
- \mathbf{F} = Alloy X-750 diaphragm, self and captured vent^①

H = Alloy C-276 diaphragm, no vent

① Available only with 316 SS and brass body materials and 0.06 and 0.20 Cv.

12 Handle, Mounting

Tube Butt

- **2** = Knob
- 3 = 316 SS antitamper nut
- 6 = Knob, panel mount
- 7 = 316 SS antitamper nut, panel mount

For knob handle color options, see page 56.

13 Isolation and Relief Valves 0 = No valves

For isolation and relief valve options, see page 54.

14 Cylinder Connections

0 = No connections

For cylinder connection options and pressure ratings, see page 53.

15 Gauges

0 = No gauges

For inlet and outlet gauge options, see page 54.

16 Options

- **0** = No options
- H = Inboard helium leak test to a maximum leak rate of 1 × 10⁻⁵ std cm³/s¹
- 3 = 3 ft, 1/4 in. FX series metal flexible hose, 1/4 in. female NPT inlet²
- 4 = 3 ft, 1/4 in. TH series PTFE-lined, stainless steel braided hose, 1/4 in. female NPT inlet²

For hose options and pressure ratings, see page 56.

- ① Not available with self vent.
- Not available for SC-11-cleaned regulators.
 - Swaqelok

Select KPR series regulators are available that meet the testing requirements of ASTM G175. "Standard Test Method for Evaluating the Ignition Sensitivity and Fault Tolerance of Oxygen Regulators Used for Medical and Emergency Applications." Contact your authorized Swagelok sales and service representative.

Two-Stage Diaphragm-Sensing, Pressure-Reducing Regulators (KCY Series)

The KCY series is designed for use in applications requiring constant outlet pressure even with wide variations in inlet pressure. This two-stage regulator is comparable to two single-stage regulators connected in series. The first stage is factory set to reduce the inlet pressure to 500 psig (34.4 bar). The second stage can be adjusted with the handle to achieve the required outlet pressure.

This two-stage arrangement minimizes the supply-pressure effect caused by fluctuating inlet pressure, such as with a depleting gas cylinder. As inlet pressure drops below the setting of the first stage, the regulator then functions as a single-stage regulator. The first-stage pressure setting can be reduced while monitoring the pressure at the interstage port, but lower flow may result.

Features

- Convoluted, nonperforated diaphragm
- Metal-to-metal diaphragm seal
- Excellent set-point stability
- High-flow, dual-gauze type filter in inlet ports

Technical Data

Maximum Inlet Pressure

- 3600 psig (248 bar)
- 6000 psig (413 bar) with PEEK seat

Pressure Control Ranges

 0 to 10 psig (0.68 bar) through 0 to 500 psig (34.4 bar)

Flow Coefficient (C_{ν})

- 0.06 and 0.20
- See page 42 for flow graphs.
- 0.50 also available

Supply-Pressure Effect

	Pressure Control Range						
Flow Coefficient	Up to 100 psig (6.8 bar)	250 psig (17.2 bar) and Higher					
(C _v)	Supply Press	ure Effect, %					
0.06	0.01	0.02					
0.20	0.02	0.06					
0.50	0.05	0.13					



Maximum Operating Temperature

- 176°F (80°C) with PCTFE seat
- 392°F (200°C) with PEEK seat
- 212°F (100°C) with PEEK seat and maximum inlet pressure greater than 3600 psig (248 bar)

Weight

4.2 lb (1.9 kg)

Ports

1/4 in. female NPT inlet, outlet, and gauge ports



	316 SS	Brass CW721R				
Component	Material					
Knob handle, cover	Nylon with 31	6 SS insert				
Spring buttons	316 SS (1s Zinc-plated stee					
Spring stabilizer ^①	301 \$	SS				
Range springs	316 SS or zinc coa depending on c					
Stems, stem nut, cap rings, stop plates, body caps, panel nuts, ^③ antitamper nut	316 SS					
Nonwetted lubricant	Hydrocarbo	Irocarbon-based				
Seat retainers, filter	316 SS					
Seats	PCTFE or PEEK					
Diaphragms, [@] poppet springs	Alloy X-	-750				
Poppets	S17400 SS					
Poppet dampers, filter carrier	PTFE					
Interstage port plug	316 SS with PTFE tape					
Self-vent seal ³	Fluorocarbon FKM					
Body	316 SS	Brass CW721R				
Wetted lubricant	PTFE-b	ased				

Wetted components listed in italics.

1 Not required in all configurations.

^② Regulators with control range 0 to 100 psig (0 to 6.8 bar) and 0.20 C_{ν} have zinc-plated steel range spring.

③ Not shown.

④ Regulators with control ranges higher than 0 to 100 psig (0 to 6.8 bar) are assembled with two diaphragms.



Dimensions, in inches (millimeters), are for reference only and are subject to change.



Ordering Information

Build a KCY series regulator ordering number by combining the designators in the sequence shown below.

	4	5	6	7	8	9	10	11	12	13	14	15	16
KCY													

4 Body Material

- **1** = 316 SS
- 2 = Brass CW721R
- **C** = 316 SS, SC-11–cleaned
- **D** = Brass, SC-11–cleaned

5 Pressure Control Range

- **C** = 0 to 10 psig (0 to 0.68 bar)
- D = 0 to 25 psig (0 to 1.7 bar)
- **E** = 0 to 50 psig (0 to 3.4 bar) **F** = 0 to 100 psig (0 to 6.8 bar)
- $\mathbf{F} = 0 \ 100 \ \text{psig} \ (0 \ 100 \ \text{psig})$
- **G** = 0 to 250 psig (0 to 17.2 bar) **J** = 0 to 500 psig (0 to 34.4 bar)

6 Maximum Inlet Pressure®

- P = 3000 psig (206 bar)
- R = 3600 psig (248 bar)
- **T** = 4351 psig (300 bar)²
- W = 6000 psig (413 bar)²³
- Cylinder Connections and Hose accessories may limit inlet pressure ratings, see pages 53 and 56.
- ② Available only with 316 SS body material and PEEK seat material.
- ③ Not available for regulators assembled with isolation valves.

Port Configuration A, B, C, E, F, H, K, L, M, N See Port Configurations, page 52.

8 Ports

4 = 1/4 in. female NPT

9 Seat Material

1 = PCTFE 2 = PEEK

10 Flow Coefficient (C_v)

- **2** = 0.06
- **5** = 0.20
- **7** = 0.50

11 Sensing Mechanism, Vent

- \mathbf{A} = Alloy X-750 diaphragm, no vent
- C = Alloy X-750 diaphragm, self vent¹
- **E** = Alloy X-750 diaphragm, captured
- vent, no self vent $\mathbf{F} = \text{Alloy X-750}$ diaphragm, self and
- captured vent 0 0 Available with 0.06 and 0.2 C_{ν} only. Self vent

12 Handle, Mounting¹

through second stage only.

- **2** = Knob
- **3** = Antitamper nut
- 6 = Knob, second-stage panel mount
- 7 = Antitamper nut, second-stage panel mount
- 9 = Knob, first-stage panel mount

For knob handle color options, see page 56.

1 First stage assembled with antitamper nut.

13 Isolation and Relief Valves

0 = No valves

For isolation and relief valve options, see page 54.

14 Cylinder Connections

0 = No connections

For cylinder connection options and pressure ratings, see page 53.

15 Gauges

0 = No gauges

For inlet and outlet gauge options, see page 54.

16 Options

- **0** = No options
- **3** = 3 ft, 1/4 in. FX series metal flexible hose, 1/4 in. female NPT inlet^①
- $\mathbf{4} = 3$ ft, 1/4 in. TH series PTFE-lined, stainless steel braided hose, 1/4 in. female NPT inlet^①

For hose options and pressure ratings, see page 56.

1 Not available for SC-11–cleaned regulators.

Select KCY series regulators are available that meet the testing requirements of ASTM G175, "Standard Test Method for Evaluating the Ignition Sensitivity and Fault Tolerance of Oxygen Regulators Used for Medical and Emergency Applications." Contact your authorized Swagelok representative.



High-Sensitivity Diaphragm-Sensing, Pressure-Reducing Regulators (KLF Series)

The KLF series provides high-sensitivity pressure control of gases or liquids with minimum droop in both low-flow and low-pressure applications.

Features

- Large-diameter convoluted, nonperforated diaphragm for increased pressure sensitivity
- Metal-to-metal diaphragm seal
- High-flow, dual-gauze type filter in inlet ports

Technical Data

Maximum Inlet Pressure

3600 psig (248 bar)

Pressure Control Ranges

 0 to 2.0 psig (0.13 bar) through 0 to 250 psig (17.2 bar)

Flow Coefficient (C_v)

0.02 and 0.06

See page 43 for flow graphs.

0.20 and 0.50 also available

Supply-Pressure Effect



Maximum Operating Temperature

- 176°F (80°C) with PCTFE seat
- 392°F (200°C) with PEEK seat

Weight

4.0 lb (1.8 kg)

Ports

1/4 in. female NPT inlet, outlet, and gauge ports





Component	Material
Knob handle, cover	Nylon with 316 SS insert
Spring button	Zinc-plated steel
Spring stabilizer ^①	301 SS
Range spring	316 SS or zinc coated/ plated steel, depending on configuration
Stem, stem nut, cap ring, stop plate, body cap, panel nuts ²	316 SS
Nonwetted lubricant	Hydrocarbon-based
Body, seat retainer, filter	316 SS
Seat	PCTFE or PEEK
Diaphragm, ³ poppet spring	Alloy X-750
Poppet	S17400 SS
Poppet damper, filter carrier	PTFE
Wetted lubricant	PTFE-based

Wetted components listed in italics.

① Not required in all configurations.

Not shown.

③ Regulators with control range 0 to 250 psig (0 to 17.2 bar) are assembled with two diaphragms.



Dimensions, in inches (millimeters), are for reference only and are subject to change.



Ordering Information

Build a KLF series regulator ordering number by combining the designators in the sequence shown below.

4 5 6 7 8 9 10 11 12 13 14 15 16 KLF 1 B C F 4 1 2 A 2 0 0 0 0

4 Body Material

1 = 316 SS **C** = 316 SS, SC-11–cleaned

5 Pressure Control Range

 $B = 0 \text{ to } 2.0 \text{ psig } (0 \text{ to } 0.13 \text{ bar})^{\odot}$ C = 0 to 10 psig (0 to 0.68 bar)D = 0 to 25 psig (0 to 1.7 bar)E = 0 to 50 psig (0 to 3.4 bar)F = 0 to 100 psig (0 to 6.8 bar)G = 0 to 250 psig (0 to 17.2 bar)

① Available with 15 psig (1.0 bar) maximum inlet pressure only.

6 Maximum Inlet Pressure¹³

- **C** = 15 psig (1.0 bar)²
- **F** = 100 psig (6.8 bar)
- **J** = 500 psig (34.4 bar)
- **L** = 1000 psig (68.9 bar)
- **P** = 3000 psig (206 bar)
- **R** = 3600 psig (248 bar)
- For better resolution and control, select a pressure that closely matches system pressure.
- ② Available with 0 to 2.0 psig (0 to 0.13 bar) pressure control range only.
- ③ Cylinder Connections and Hose accessories may limit inlet pressure ratings, see pages 53 and 56.

7 Port Configuration

A, B, C, E, F, H, K, L, M, N See Port Configurations, page 52.

8 Ports

4 = 1/4 in. female NPT

9 Seat Material

1 = PCTFE **2** = PEEK

10 Flow Coefficient (C_v)

- **1** = 0.02
- **2** = 0.06
- **5** = 0.20
- **7** = 0.50

11 Sensing Mechanism, Vent

A = Alloy X-750 diaphragm, no vent

E = Alloy X-750 diaphragm, captured vent, no self vent

12 Handle, Mounting

- **2** = Knob
- 3 = 316 SS antitamper nut
- 6 = Knob, panel mount
- 7 = 316 SS antitamper nut, panel mount

For knob handle color options, see page 56.

13 Isolation and Relief Valves

0 = No valves For isolation and relief valve options, see page 54.

14 Cylinder Connections

0 = No connection

For cylinder connection options and pressure ratings, see page 53.

15 Gauges

0 = No gauges

For inlet and outlet gauge options, see page 54.

16 Options

- $\mathbf{0} = No options$
- **3** = 3 ft, 1/4 in. FX series metal flexible hose, 1/4 in. female NPT inlet^①
- $\label{eq:4} \begin{array}{l} \textbf{4} = 3 \ \text{ft}, \ 1/4 \ \text{in}. \ \text{TH series PTFE-lined}, \\ \text{stainless steel braided hose, } 1/4 \ \text{in}. \\ \text{female NPT inlet} \\ \end{array}$

For hose options and pressure ratings, see page 56.

1 Not available for SC-11–cleaned regulators.



High-Flow, High-Sensitivity Diaphragm-Sensing, Pressure-Reducing Regulators (KHF Series)

The KHF series combines the high-flow capabilities $-1.0 C_v$ – of a bulk distribution regulator with the high sensitivity and accuracy of a point-of-use regulator.

Features

- Large-diameter convoluted, nonperforated diaphragm for increased pressure sensitivity
- Metal-to-metal diaphragm seal
- High-flow dual-gauze type filter in inlet ports

Technical Data

Maximum Inlet Pressure

3600 psig (248 bar)

Pressure Control Ranges

 0 to 10 psig (0.68 bar) through 0 to 250 psig (17.2 bar)

Flow Coefficient (C_v)

1.0

See page 44 for flow graphs.

Supply-Pressure Effect



Maximum Operating Temperature

- 176°F (80°C) with PCTFE seat
- 392°F (200°C) with PEEK seat

Weight

4.4 lb (2.0 kg)

Ports

1/2 in. female NPT inlet and outlet;
 1/4 in. female NPT gauge port



Stem nut	Cover	
Stem		
Spring stabilizer		- Knob handle
Stop plate		Spring button
		Range spring
Cap ring		Body cap
Diaphragm		Seat retainer
Poppet		Seat
Poppet spring		
Inlet		- Spring retainer utlet
- '''		Poppet seal retainer
Filter carrier, filter	Body	Poppet seal and spring

Component	Material
Knob handle, cover	Nylon with 316 SS insert
Spring button	316 SS (0 to 250 psig range) Zinc-plated steel (all other ranges)
Spring stabilizer ^①	301 SS
Range spring	316 SS or zinc coated/plated steel, depending on configuration
Stem, stem nut, cap ring, stop plate, body cap, panel nuts [®]	316 SS
Nonwetted lubricant	Hydrocarbon-based
Body, spring retainer, seat retainer, filter, poppet seal retainer	316 SS
Seat	PCTFE or PEEK
Diaphragm ³	Alloy X-750
Poppet	S17400 SS
Poppet spring	302 SS
Poppet seal, filter carrier	PTFE
Poppet seal spring	Elgiloy ®
Wetted lubricant	PTFE-based

Wetted components listed in italics.

① Not included in regulators with 0 to 250 psig (0 to 17.2 bar) control range.

Not shown.

③ Regulators with control range 0 to 250 psig (0 to 17.2 bar) are assembled with two diaphragms.



Dimensions, in inches (millimeters), are for reference only and are subject to change.



Panel 0.39 (10.0) thick maximum with 2 lock nuts Panel 0.63 (16.0) thick maximum with 1 lock nut Panel cutout 1.38 (35.0) dia

Ordering Information

Build a KHF series regulator ordering number by combining the designators in the sequence shown below.

4	5	6	7	8	9	10	11	12	13	14	15	16
KHF 1												

4 Body Material

1 = 316 SS **C** = 316 SS, SC-11–cleaned

5 Pressure Control Range

C = 0 to 10 psig (0 to 0.68 bar) D = 0 to 25 psig (0 to 1.7 bar) E = 0 to 50 psig (0 to 3.4 bar) F = 0 to 100 psig (0 to 6.8 bar) **G** = 0 to 250 psig (0 to 17.2 bar)

6 Maximum Inlet Pressure^①

- **F** = 100 psig (6.8 bar)
- J = 500 psig (34.4 bar)
- **L** = 1000 psig (68.9 bar)
- **R** = 3600 psig (248 bar)
- 1 For better resolution and control, select a pressure that closely matches system pressure.

7 Port Configuration

A, B, C, E, F, H, K, L, M, N See Port Configurations, page 52.

8 Ports

8 = 1/2 in. female NPT inlet and outlet; 1/4 in. female NPT gauge port

9 Seat Material

1 = PCTFE

2 = PEEK

10 Flow Coefficient (C_{v}) 8 = 1.0

11 Sensing Mechanism, Vent

- **A** = Alloy X-750 diaphragm, no vent
- E = Alloy X-750 diaphragm, captured vent, no self vent

12 Handle, Mounting

- **2** = Knob
- 3 = 316 SS antitamper nut
- 6 = Knob, panel mount
- 7 = 316 SS antitamper nut, panel mount

For knob handle color options, see page 56.

13 Isolation and Relief Valves

0 = No valves For isolation and relief valve options, see page 54.

14 Cylinder Connections

0 = No connections

15 Gauges

0 = No gauges For inlet and outlet gauge options, see page 54.

16 Options



Compact, Piston-Sensing, Pressure-Reducing Regulators (KCP Series)

The KCP series is a compact, piston-sensing pressure regulator with a short stroke to minimize wear in high-cycling applications.

Features

- Low internal volume
- Fully contained piston
- High-flow, dual-gauze type filter in inlet ports
- ANSI/ISA 76.00.02-compliant modular platform component (MPC) configuration available; MPC platform regulator does not contain a filter

Technical Data

Maximum Inlet Pressure

3600 psig (248 bar)

Pressure Control Ranges

 0 to 10 psig (0.68 bar) through 0 to 1500 psig (103 bar)

Flow Coefficient (C_v)

0.06 and 0.20

See page 45 for flow graphs. ■ 0.02 and 0.50 also available

- Supply-Pressure Effect
- Pressure Control Range 500 psig Up to 250 psig (34.4 bar) Flow (17.2 bar) and Higher Coefficient (C_v) Supply Pressure Effect, % 0.02 0.4 2.6 0.06 1.3 8.6 0.20 2.1 14.5 0.50 3.0 22.6

Maximum Operating Temperature

- 176°F (80°C) with PCTFE seat
- 392°F (200°C) with PEEK seat

Weight

1.0 lb (0.45 kg)

Ports

- 1/8 in. female NPT inlet, outlet, and gauge ports
- MPC platform



Stem nut 🔨	Thumbwheel handle
Stem —	Spring button
Spring stabilizer <	Range spring
	Body cap
	Piston seal
Piston —	Seat retainer
Seat —	Poppet
Inlet	Outlet
Filter carrie filte	Poppet spring

Component	Material
Thumbwheel handle	Anodized aluminum
Knob handle, $^{\textcircled{1}}$ cover $^{\textcircled{1}}$	Nylon with 316 SS insert
Spring button	Zinc-plated steel
Spring stabilizer	301 SS
Range spring	316 SS or zinc coated/plated steel, depending on configuration
Stem, stem nut, body cap, panel nuts $^{{\mathbb T}}$	316 SS
Nonwetted lubricant	Hydrocarbon-based
Body, seat retainer, piston, filter [®]	316 SS
Piston seal	Fluorocarbon FKM or FFKM
Seat	PCTFE or PEEK
Poppet	S17400 SS
Poppet spring	302 SS
Filter carrier [®]	PTFE
Wetted lubricant	PTFE-based

Wetted components listed in italics.

. Not shown.

② MPC platform regulator does not contain a filter.



Dimensions, in inches (millimeters), are for reference only and are subject to change.



Ordering Information

Build a KCP series regulator ordering number by combining the designators in the sequence shown below.

	4	5	6	7	8	9	10	11	12	13	14	15	16
KCP													

4 Body Material

1 = 316 SS

C = 316 SS, SC-11-cleaned

5 Pressure Control Range

 $\begin{array}{l} \textbf{C} = 0 \ \text{to} \ 10 \ \text{psig} \ (0 \ \text{to} \ 0.68 \ \text{bar}) \\ \textbf{D} = 0 \ \text{to} \ 25 \ \text{psig} \ (0 \ \text{to} \ 1.7 \ \text{bar}) \\ \textbf{E} = 0 \ \text{to} \ 50 \ \text{psig} \ (0 \ \text{to} \ 3.4 \ \text{bar}) \\ \textbf{F} = 0 \ \text{to} \ 100 \ \text{psig} \ (0 \ \text{to} \ 3.4 \ \text{bar}) \\ \textbf{G} = 0 \ \text{to} \ 250 \ \text{psig} \ (0 \ \text{to} \ 17.2 \ \text{bar}) \\ \textbf{J} = 0 \ \text{to} \ 500 \ \text{psig} \ (0 \ \text{to} \ 34.4 \ \text{bar}) \\ \textbf{L} = 0 \ \text{to} \ 1000 \ \text{psig} \ (0 \ \text{to} \ 68.9 \ \text{bar}) \\ \textbf{M} = 0 \ \text{to} \ 1500 \ \text{psig} \ (0 \ \text{to} \ 103 \ \text{bar}) \end{array}$

6 Maximum Inlet Pressure^①

- **F** = 100 psig (6.8 bar)
- **J** = 500 psig (34.4 bar)
- **L** = 1000 psig (68.9 bar)
- **R** = 3600 psig (248 bar)
- Tor better resolution and control, select a pressure that closely matches system pressure.

7 Port Configuration

A, B, C, E, F, H, K, L, M, N, 5, 6 See Port Configurations, page 52.

8 Ports

 $\mathbf{2} = 1/8$ in. female NPT $\mathbf{M} = MPC$ platform

9 Seat, Seal Material

- $\mathbf{A} = \mathsf{PCTFE}, \mathsf{fluorocarbon} \mathsf{FKM}$
- **B** = PCTFE, FFKM
- **C** = PEEK, fluorocarbon FKM
- $\mathbf{D} = \mathsf{PEEK}, \mathsf{FFKM}$

10 Flow Coefficient (C_v)

- **1** = 0.02
- **2** = 0.06
- **5** = 0.20^①
- **7** = 0.50^①

Not available with MPC platform port configuration.

11 Sensing Mechanism

P = 316 SS piston

12 Handle, Mounting

- 1 = Thumbwheel
- **2** = Knob
- 3 = 316 SS antitamper nut
- 5 = Thumbwheel, panel mount
- 6 = Knob, panel mount

7 = 316 SS antitamper nut, panel mount

For knob handle color options, see page 56.

13 Isolation Valves

0 = No valves For isolation valve options, see page 54.

14 Cylinder Connections

0 = No connections

15 Gauges

0 = No gauges

For inlet and outlet gauge options, see page 54.

16 Options



Medium- to High-Pressure Piston-Sensing, Pressure-Reducing Regulators (KPP Series)

The KPP series meets the demands of a wide range of gas or liquid applications in a lightweight, compact installation footprint. These features make the KPP pressure regulator an ideal pressure control solution within high-density OEM equipment.

Features

- Lightweight, compact design
- Live-loaded body seals
- Low internal volume
- High-flow, dual-gauze type filter in inlet ports

Technical Data

Maximum Inlet Pressure

6000 psig (413 bar)

Pressure Control Ranges

 0 to 1000 psig (68.9 bar) through 0 to 3600 psig (248 bar)

Flow Coefficient (C_v)

- 0.02 and 0.06
 - See page 48 for flow graphs.

Supply-Pressure Effect

Flow Coefficient <i>(C_v)</i>	Supply Pressure Effect, %
0.02	2.2
0.06	7.2

Maximum Operating Temperature

- 392°F (200°C) with 2000 psig (137 bar) maximum inlet pressure
- 212°F (100°C) with maximum inlet pressure greater than 2000 psig (137 bar)

Weight

2.5 lb (1.2 kg)

Ports

1/4 in. female NPT inlet, outlet, and gauge ports



		Cover
Stem nut Stem Spring		Knob handle
stabilizer		
Range spring		Piston seal and spring
Body cap		Piston seal retainer
Piston		Cap ring
Seat retainer		Piston guide
Poppet		Body seal and spring
Poppet spring		Seat
Ir	hlet	Outlet
Filter carrier, filter		Poppet damper
		Body

Component	Material
Knob handle, cover	Nylon with 316 SS insert
Spring button	316 SS (0 to 3000 and 0 to 3600 psig range) Zinc-plated steel (all other ranges) ^①
Spring stabilizer ²	301 SS
Range spring	316 SS or zinc coated/plated steel, depending on configuration
Stem, stem nut, cap ring, body cap, panel nuts ^③	316 SS
Nonwetted lubricant	Hydrocarbon-based
Body, seat retainer, filter, piston, piston guide	316 SS
Seat, piston seal retainer	PEEK
Poppet	S17400 SS
Poppet spring	Alloy X-750
Piston seal spring, body seal spring	Elgiloy
Poppet damper, filter carrier, piston seal, body seal	PTFE
Wetted lubricant	PTFE-based

Wetted components listed in italics.

① 316 SS in regulators with 0 to 2000 psig (0 to 137 bar) control range with 6000 psig (413 bar) inlet pressure and regulators with 0 to 2000 psig (0 to 137 bar) control range, 4000 psig (275 bar) inlet pressure, and 0.06 C_{v} .

2 Not included in regulators with 316 SS spring button.

Not shown.





Dimensions, in inches (millimeters), are for reference only and are subject to change.



Ordering Information

Build a KPP series regulator ordering number by combining the designators in the sequence shown below.



4 Body Material

1 = 316 SS **C** = 316 SS, SC-11–cleaned

5 Pressure Control Range

- Not available with 2000 psig (137 bar) maximum inlet pressure.

6 Maximum Inlet Pressure^①

- **N** = 2000 psig (137 bar)
- **S** = 4000 psig (275 bar)
- **W** = 6000 psig (413 bar)

 For better resolution and control, select a pressure that closely matches system pressure. 7 Port Configuration A, B, C, E, F, H, K, L, M, N See Port Configurations, page 52.

8 Ports 4 = 1/4 in. female NPT

9 Seat, Seal Material2 = PEEK, PTFE

10 Flow Coefficient (C_v) **1** = 0.02

2 = 0.06

11 Sensing Mechanism, Vent

P = 316 SS piston, no ventV = 316 SS piston, captured vent, no self vent

12 Handle, Mounting

2 = Knob

- 3 = 316 SS antitamper nut
- 6 = Knob, panel mount

7 = 316 SS antitamper nut, panel mount For knob handle color options, see page 56.

13 Isolation Valves

0 = No valves For isolation valve options, see page 54.

14 Cylinder Connections

0 = No connections

15 Gauges

0 = No gauges For inlet and outlet gauge options, see page 54.

16 Options



High-Flow Piston-Sensing, Pressure-Reducing Regulators (KPF Series)

The KPF series provides minimum droop across the flow range with high accuracy of outlet pressure.

Features

- High flow coefficient ($C_v = 1.0$)
- Balanced poppet for minimal supplypressure effect
- High-flow, dual-gauze type filter in inlet ports

Technical Data

Maximum Inlet Pressure

6000 psig (413 bar)

Pressure Control Ranges

 0 to 1000 psig (68.9 bar) through 0 to 4000 psig (275 bar)

Flow Coefficient (C_{ν})

1.0

Swagelok

See page 44 for flow graphs.

Supply-Pressure Effect



Maximum Operating Temperature

- 176°F (80°C) with PCTFE seat
- 392°F (200°C) with PEEK seat

Weight

4.5 lb (2.1 kg)

Ports

1/2 in. female NPT inlet and outlet; 1/4 in. female NPT gauge ports



Materials of Construction



Component	Material	
•		
Knob handle, cover	Nylon with 316 SS insert	
Spring button	316 SS (0 to 3000 and 0 to 4000 psig range) Zinc-plated steel (all other ranges)	
Spring stabilizer ^①	301 SS	
Range spring	316 SS or zinc coated/ plated steel, depending on configuration	
Stem, stem nut, cap ring, body cap, panel nuts ^②	316 SS	
Nonwetted lubricant	Hydrocarbon-based	
Body, spring retainer, seat retainer, filter, piston, piston guide, poppet seal retainer	316 SS	
Seat, piston seal retainer	PCTFE or PEEK	
Poppet	S17400 SS	
Poppet spring	302 SS	
Filter carrier, piston seal, poppet seal	PTFE	
Piston seal spring, poppet seal spring	Elgiloy	
Body seal	Fluorocarbon FKM	
Wetted lubricant	PTFE-based	

Wetted components listed in italics.

1 Not included in regulators with 316 SS spring button.

② Not shown.

Dimensions, in inches (millimeters), are for reference only and are subject to change.



Ordering Information

Build a KPF series regulator ordering number by combining the designators in the sequence shown below.

5 6 8 9 10 12 13 14 15 16 KPF ١٨/ 8 8 2 1 Δ Ρ 0 Δ O O 0

4 Body Material
 1 = 316 SS

C = 316 SS, SC-11–cleaned

5 Pressure Control Range

6 Maximum Inlet Pressure

W = 6000 psig (413 bar)

7 Port Configuration

A, B, C, E, F, H, K, L, M, N See Port Configurations, page 52.

8 Ports

8 = 1/2 in. female NPT inlet and outlet; 1/4 in. female NPT gauge ports

9 Seat, Body Seal Material

A = PCTFE, fluorocarbon FKM **C** = PEEK, fluorocarbon FKM

10 Flow Coefficient (C_{ν}) 8 = 1.0

11 Sensing Mechanism, Vent

P = 316 SS piston, no vent

V = 316 SS piston, captured vent, no self vent

12 Handle, Mounting

2 = Knob

- 3 = 316 SS antitamper nut
- **6** = Knob, panel mount

7 = 316 SS antitamper nut, panel mount

For knob handle color options, see page 56.

13 Isolation Valves

0 = No valves For isolation valve options, see page 54.

14 Cylinder Connections

0 = No connections

15 Gauges

0 = No gauges For inlet and outlet gauge options, see page 54.

16 Options



High-Pressure Piston-Sensing, Pressure-Reducing Regulators (KHP Series)

The KHP series provides control of supply pressures up to 10 000 psig (689 bar). The self-venting capability enables downstream pressure reduction in closed-loop systems.

Features

- Thrust roller bearing eases operation
- Panel-mounting configuration available
- High-flow, dual-gauze type filter in inlet ports

Technical Data

Maximum Inlet Pressure

10 000 psig (689 bar)

Pressure Control Ranges

 0 to 500 psig (34.4 bar) through 100 to 10 000 psig (6.8 to 689 bar)

Flow Coefficient (C_v)

0.06 and 0.25

See page 46 and 47 for flow graphs.

Supply-Pressure Effect



Maximum Operating Temperature

212°F (100°C)

Weight

5.7 lb (2.6 kg)

Ports

1/4 in. female NPT inlet, outlet, and gauge ports



Materials of Construction



Component	Material
Knob handle, cover	Nylon with 316 SS insert
Spring buttons, upper spring button set screw, knob handle retainer, vent screw, stem nuts, body cap	316 SS
Vent screw spring	302 SS
Vent rod	431 SS
Stem	CZ114 bronze
Thrust roller bearing	Hardened carbon steel
Range spring	Chrome vanadium steel
Piston seal backup ring	PTFE
Nonwetted lubricant	Hydrocarbon-based
Body, seat retainer, filter, piston, piston guide, self-vent seat retainer	316 SS
Seat, self-vent seat	PEEK
Poppet, self-vent poppet	S17400 SS
Poppet spring	Alloy X-750
Poppet damper, filter carrier	PTFE
Self-vent poppet spring	302 SS
Body seal, piston seal	Fluorocarbon FKM
Wetted lubricant	PTFE-based

Wetted components listed in italics.



Dimensions, in inches (millimeters), are for reference only and are subject to change.



Ordering Information

Build a KHP series regulator ordering number by combining the designators in the sequence shown below.



4 Body Material
 1 = 316 SS
 C = 316 SS, SC-11–cleaned

5 Pressure Control Range

J = 0 to 500 psig (0 to 34.4 bar)K = 0 to 750 psig (0 to 51.6 bar)T = 10 to 1500 psig (0.68 to 103 bar)U = 15 to 2500 psig (1.0 to 172 bar)V = 25 to 3600 psig (1.7 to 248 bar)W = 50 to 6000 psig (3.4 to 413 bar)^①X = 100 to 10 000 psig (6.8 to 689 bar)^①X = 100 to 10 000 psig (6.8 to 689 bar)^①X = 100 to 10 000 psig (6.8 to 689 bar)^①

 Not available for regulators assembled with isolation valves.

6 Maximum Inlet Pressure

X = 10 000 psig (689 bar)

Port Configuration
 A, B, C, E, F, H, K, L, M, N
 See Port Configurations, page 52.

8 Ports 4 = 1/4 in. female NPT

9 Seat, Seal Material C = PEEK, fluorocarbon FKM

10 Flow Coefficient (C_v)

2 = 0.06 **6** = 0.25

11 Sensing Mechanism, Vent

- $\mathbf{P} = 316 \text{ SS piston, no vent}$
- **S** = 316 SS piston, self vent

12 Handle, Mounting 2 = Knob

6 = Knob, panel mount For knob handle color options, see page 56.

13 Isolation Valves

0 = No valves For isolation valve options, see page 54.

14 Cylinder Connections

0 = No connections

15 Gauges

0 = No gauges For inlet and outlet gauge options, see page 54.

16 Options

High-Pressure Piston-Sensing, Hydraulic Pressure-Reducing Regulators (KHR Series)

The KHR series provides control of pressures up to 10 000 psig (689 bar) for both liquid and gas applications. Metal or polymer seats are available.

0.06

Features

Flow Coefficient (C_{ν})

0.25 also available

See page 47 for flow graphs.

- Self-venting
- Captured vent port in bottom of body
- Panel-mounting configuration available
- Thrust roller bearing eases operation
- High-flow, dual-gauze type filter in inlet ports

Technical Data

Maximum Inlet Pressure

10 000 psig (689 bar)

Pressure Control Ranges

0 to 500 psig (34.4 bar) through 100 to 10 000 psig (6.8 to 689 bar)

Supply-Pressure Effect **Pressure Control Range** 3600 and 6000 psig 10 000 Up to 2500 psig (248 and psig Flow (172 bar) 413 bar) (689 bar) Coefficient Supply Pressure Effect, % (C_v) 0.06 1.0 2.6 4.2 0.25 3.3 8.5 14.6

Maximum Operating Temperature

212°F (100°C) Weight 6.1 lb (2.75 kg)



Ports

1/4 in. female NPT inlet, outlet, vent, and gauge ports



Component	Material
Knob handle, cover	Nylon with 316 SS insert
Spring buttons, upper spring button set screw, knob handle retainer, vent screw, stem nuts, vent rod nut, body cap	316 SS
Vent screw spring	302 SS
Vent rod	431 SS
Stem	CZ114 bronze
Thrust roller bearing	Hardened carbon steel
Range spring	Chrome vanadium steel
Piston seal backup ring	PEEK
Nonwetted lubricant	Hydrocarbon-based
Body, seat retainer, filter, piston, piston guide, self-vent seat retainer	316 SS
Self-vent seat	PEEK
Seat	PEEK or 316 SS
Poppet, self-vent poppet	S17400 SS
Poppet spring	Alloy X-750
Poppet damper, filter carrier	PTFE
Self-vent poppet spring	302 SS
Body seals, piston seals	Fluorocarbon FKM
Wetted lubricant	PTFE-based

Wetted components listed in italics.

(shown off center for clarity)



Swagelok

Dimensions, in inches (millimeters), are for reference only and are subject to change.



Ordering Information

Build a KHR series regulator ordering number by combining the designators in the sequence shown below.



4 Body Material

1 = 316 SS **C** = 316 SS, SC-11–cleaned

5 Pressure Control Range

J = 0 to 500 psig (0 to 34.4 bar) **K** = 0 to 750 psig (0 to 51.6 bar)

- $\mathbf{T} = 10$ to 1500 psig (0.68 to 103 bar)
- $\mathbf{U} = 15$ to 2500 psig (0.08 to 103 bar)
- $\mathbf{V} = 25$ to 3600 psig (1.7 to 248 bar)
- W = 50 to 6000 psig (3.4 to 413 bar)^①
- $\mathbf{X} = 100 \text{ to } 10 000 \text{ psig} (6.8 \text{ to } 689 \text{ bar})^{\circ}$
- ① Not available for regulators assembled with isolation valves.

6 Maximum Inlet Pressure

X = 10 000 psig (689 bar)

Port Configuration
 A, B, C, F, M
 See Port Configurations, page 52.

8 Ports 4 = 1/4 in. female NPT

9 Seat, Seal Material

 $\mathbf{C} = \mathsf{PEEK}, \mathsf{fluorocarbon} \mathsf{FKM}$

J = 316 SS, fluorocarbon FKM⁽¹⁾

1 Not suitable for gas service.

10 Flow Coefficient (C_v)

2 = 0.06 **6** = 0.25

11 Sensing Mechanism, Vent

U = 316 SS piston, self and captured vent

12 Handle, Mounting

2 = Knob
6 = Knob, panel mount
For knob handle color options, see page 56.

13 Isolation Valves

0 = No valves For isolation valve options, see page 54.

14 Cylinder Connections

0 = No connections

15 Gauges

0 = No gauges For inlet and outlet gauge options, see page 54.

16 Options

General-Purpose Diaphragm-Sensing Back-Pressure Regulators (KBP Series)

The KBP series is a high-sensitivity, general-purpose regulator designed to control back-pressure levels in analytical or process systems upstream of the regulator. The convoluted diaphragm provides excellent sensitivity and set-point repeatability. The metal-to-metal diaphragm seal minimizes the potential for leakage.

Features

- Convoluted, nonperforated diaphragm
- Metal-to-metal diaphragm seal
- Low internal volume
- Two-piece cap design provides linear load on the seal

Technical Data

Maximum Inlet Pressure

Equal to pressure control range

Pressure Control Ranges

0 to 10 psig (0.68 bar) through 0 to 500 psig (34.4 bar)

Flow Coefficient (C_v)

- 0.20
 - See page 49 for flow graphs.

Maximum Operating Temperature

- 176°F (80°C) with PCTFE retainer seal
- 392°F (200°C) with PEEK retainer seal
 Weight
- 2.4 lb (1.1 kg)

Ports

- 1/4 in. female NPT inlet, outlet, and gauge ports (all body materials)
- 1/4 in. tube butt weld inlet, outlet, and gauge ports (316 SS body material only)
- 1/4 in. VCR inlet, outlet, and gauge ports (316 SS body material only)



	Cover
Stem nut	
Stem	Knob handle
Spring stabilizer	Spring button
Stop plate	Range spring
Cap ring	Body cap
Diaphragm	Seat
	Seat retainer
	Retainer seal
Inlet	Outlet
Body 📃 🧱	

	316 SS	Brass CW721R	
Component	Material		
Knob handle, cover	Nylon with 3	16 SS insert	
Spring button	316 SS (0 to 500 psig range) Zinc-plated steel (all other ranges)		
Spring stabilizer $^{\textcircled{1}}$	301	SS	
Range spring	316 SS or zinc coated/plated steel, depending on configuration		
Stem, stem nut, cap ring, stop plate, body cap, panel nuts ^②	316 SS		
VCR nuts ²	316 SS –		
Nonwetted lubricant	Hydrocarbon-based		
Seat retainer	316 SS		
Retainer seal	PCTFE or PEEK		
Seat	Fluorocarbon FKM or FFKM		
Diaphragm ³	Alloy X-750		
Body	316 SS Brass CW7		
Tube butt weld ports, $^{@}$ VCR gland ports $^{@}$	316L SS —		
Wetted lubricant	PTFE-based		

Wetted components listed in *italics*.

0 Not included in regulators with 0 to 500 psig (0 to 34.4 bar) control range.

② Not shown.

③ Regulators with control ranges higher than 0 to 100 psig (0 to 6.8 bar) are assembled with two diaphragms.





Dimensions, in inches (millimeters), are for reference only and are subject to change.



Ordering Information

Build a KBP series regulator ordering number by combining the designators in the sequence shown below.

4 5 6 7 8 9 10 11 12 13 14 15 16 KBP 1 F 0 D 4 A 5 A 2 0 0 0 0

4 Body Material

- **1** = 316 SS
- 2 = Brass CW721R
- C = 316 SS, SC-11-cleaned
- **D** = Brass, SC-11–cleaned

5 Pressure Control Range

- **C** = 0 to 10 psig (0 to 0.68 bar)
- **D** = 0 to 25 psig (0 to 1.7 bar)
- E = 0 to 50 psig (0 to 3.4 bar)
- F = 0 to 100 psig (0 to 6.8 bar)
- **G** = 0 to 250 psig (0 to 17.2 bar)
- **J** = 0 to 500 psig (0 to 34.4 bar)

6 Maximum Inlet Pressure

0 = Not applicable (equal to pressure control range)

7 Port Configuration

A, D, G, V

See Port Configurations, page 52.

8 Ports

- $\mathbf{4} = 1/4$ in. female NPT
- $\mathbf{T} = 1/4$ in. $\times 0.035$ in. tube butt weld⁽¹⁾
- $\mathbf{V} = 1/4$ in. VCR gland, no nuts⁽¹⁾
- $\mathbf{X} = 1/4$ in. rotatable female VCR fitting^①
- $\mathbf{Y} = 1/4$ in. rotatable male VCR fitting⁽¹⁾
- Available only with 316 SS body material in A port configuration.
- ② For use with VCR split-nuts, which can be ordered separately. Refer to Swagelok VCR Metal Gasket Face Seal Fittings catalog, <u>MS-01-24</u>.

9 Seat, Seal Material

- A = Fluorocarbon FKM, PCTFE
- **B** = FFKM, PCTFE
- **C** = Fluorocarbon FKM, PEEK
- $\mathbf{D} = FFKM, PEEK$

10 Flow Coefficient (C_v)

5 = 0.20

11 Sensing Mechanism, Vent

- A = Alloy X-750 diaphragm, no vent
- **E** = Alloy X-750 diaphragm, captured vent, no self vent

12 Handle, Mounting

Tube Butt

- **2** = Knob
- 3 = 316 SS antitamper nut
- 6 = Knob, panel mount
- **7** = 316 SS antitamper nut, panel mount *For knob handle color options, see*

page 56.

13 Valves

0 = No valves

14 Cylinder Connections

0 = No connections

15 Gauges

0 = No gauges For inlet gauge options, see page 54.

16 Options



High-Flow, High-Sensitivity Diaphragm-Sensing Back-Pressure Regulators (KFB Series)

The KFB series regulator is designed to maintain back-pressure control in high-flow applications with a C_{ν} of 1.0.

Features

- Large-diameter convoluted, nonperforated diaphragm for increased pressure sensitivity
- Metal-to-metal diaphragm seal

Technical Data

Maximum Inlet Pressure

Equal to pressure control range

Pressure Control Ranges

 0 to 10 psig (0.68 bar) through 0 to 250 psig (17.2 bar)

Flow Coefficient (C_v)

1.0

See page 49 for flow graphs.

Maximum Operating Temperature

- 176°F (80°C) with PCTFE retainer seal
- 392°F (200°C) with PEEK retainer seal

Weight

4.4 lb (2.0 kg)

Ports

1/2 in. female NPT inlet and outlet; 1/4 in. female NPT gauge port





Component	Material
Knob handle, cover	Nylon with 316 SS insert
Spring button	316 SS (0 to 250 psig range) Zinc-plated steel (all other ranges)
Spring stabilizer ^①	301 SS
Range spring	316 SS or zinc coated/plated steel, depending on configuration
Stem, stem nut, cap ring, stop plate, body cap, panel nuts [®]	316 SS
Nonwetted lubricant	Hydrocarbon-based
Body, seat retainer	316 SS
Retainer seal	PCTFE or PEEK
Seat	Fluorocarbon FKM
Diaphragm ³	Alloy X-750
Wetted lubricant	PTFE-based

Wetted components listed in *italics*.

- Not included in regulators with 0 to 250 psig (0 to 17.2 bar) control range.
- Not shown.
- ③ Regulators with control range 0 to 250 psig (0 to 17.2 bar) are assembled with two diaphragms.



Dimensions, in inches (millimeters), are for reference only and are subject to change.



Panel 0.39 (10.0) thick maximum with 2 lock nut Panel 0.63 (16.0) thick maximum with 1 lock nut Panel cutout 1.38 (35.0) dia

Ordering Information

Build a KFB series regulator ordering number by combining the designators in the sequence shown below.

4 5 6 7 8 9 10 11 12 13 14 15 16 KFB 1 F 0 D 8 A 8 A 1 0 0 0 0

4 Body Material

1 = 316 SS **C** = 316 SS, SC-11–cleaned

5 Pressure Control Range

 $\begin{array}{l} {\bm C} = 0 \mbox{ to } 10 \mbox{ psig } (0 \mbox{ to } 0.68 \mbox{ bar}) \\ {\bm D} = 0 \mbox{ to } 25 \mbox{ psig } (0 \mbox{ to } 1.7 \mbox{ bar}) \\ {\bm E} = 0 \mbox{ to } 50 \mbox{ psig } (0 \mbox{ to } 3.4 \mbox{ bar}) \\ {\bm F} = 0 \mbox{ to } 100 \mbox{ psig } (0 \mbox{ to } 6.8 \mbox{ bar}) \\ {\bm G} = 0 \mbox{ to } 250 \mbox{ psig } (0 \mbox{ to } 17.2 \mbox{ bar}) \end{array}$

6 Maximum Inlet Pressure

0 = Not applicable (equal to pressure control range)

Port Configuration
 A, D, G, V
 See Port Configurations, page 52.

8 Ports

8 = 1/2 in. female NPT inlet and outlet; 1/4 in. female NPT gauge port

9 Seat, Seal Material

A = Fluorocarbon FKM, PCTFE

C = Fluorocarbon FKM, PEEK

10 Flow Coefficient (C_v) 8 = 1.0

11 Sensing Mechanism, Vent

- **A** = Alloy X-750 diaphragm, no vent
- **E** = Alloy X-750 diaphragm, captured vent, no self vent

12 Handle, Mounting

- **2** = Knob
- 3 = 316 SS antitamper nut
- 6 = Knob, panel mount

7 = 316 SS antitamper nut, panel mount For knob handle color options, see page 56.

13 Valves

0 = No valves

14 Cylinder Connections

0 = No connections

15 Gauges

0 = No gauges For inlet gauge options, see page 54.

16 Options

Compact Piston-Sensing Back-Pressure Regulators (KCB Series)

The KCB series provides high sensitivity back-pressure control of sampling conditioning systems. It is ideally suited for use in portable or laboratory analytical systems as well as being embedded in the instrument bays of OEM equipment or sampling cabinets.

Features

- Low internal volume
- Fully contained piston
- Excellent flow characteristics with a C_v of 0.20
- ANSI/ISA 76.00.02-compliant modular platform component (MPC) configuration available

Technical Data

- Maximum Inlet Pressure
- Equal to pressure control range

Pressure Control Ranges

 0 to 10 psig (0.68 bar) through 0 to 375 psig (25.8 bar)

Flow Coefficient (C_v)

- 0.20
- See page 49 for flow graphs.
- 0.10 also available with MPC platform

Maximum Operating Temperature

- 176°F (80°C) with PCTFE retainer seal
- 392°F (200°C) with PEEK retainer seal

Weight

1.0 lb (0.5 kg)

Ports

- 1/8 in. female NPT inlet and outlet(s)
- MPC platform





Component	Material
Thumbwheel handle	Anodized aluminum
Knob handle, $^{(1)}$ cover $^{(1)}$	Nylon with 316 SS insert
Spring button	Zinc-plated steel
Spring stabilizer	301 SS
Range spring	316 SS or zinc coated/plated steel, depending on configuration
Stem, stem nut, body cap, panel nuts $^{}$	316 SS
Nonwetted lubricant	Hydrocarbon-based
Body, seat retainer, piston	316 SS
Seat, piston seal	Fluorocarbon FKM or FFKM
Retainer seal	PCTFE or PEEK
Wetted lubricant	PTFE-based

Wetted components listed in *italics*. ① Not shown.



Dimensions, in inches (millimeters), are for reference only and are subject to change.



Ordering Information

Build a KCB series regulator ordering number by combining the designators in the sequence shown below.

	4	5	6	7	8	9	10	11	12	13	14	15	16
KCB	1	F	0	D	2	Α	5	Ρ	1	0	0	0	0

4 Body Material

1 = 316 SS

C = 316 SS, SC-11-cleaned

5 Pressure Control Range

C = 0 to 10 psig (0 to 0.68 bar)

- **D** = 0 to 25 psig (0 to 1.7 bar) **E** = 0 to 50 psig (0 to 3.4 bar)
- $\mathbf{F} = 0$ to 100 psig (0 to 3.4 bar) $\mathbf{F} = 0$ to 100 psig (0 to 6.8 bar)
- $\mathbf{G} = 0$ to 250 psig (0 to 17.2 bar)
- $\mathbf{H} = 0$ to 375 psig (0 to 17.2 bar) $\mathbf{H} = 0$ to 375 psig (0 to 25.8 bar)

6 Maximum Inlet Pressure

0 = Not applicable (equal to pressure control range)

7 Port Configuration

A, D, G, V, 7, 8

See Port Configurations, page 52.

8 Ports

 $\mathbf{2} = 1/8$ in. female NPT $\mathbf{M} = MPC$ platform

9 Seat, Retainer Seal Material

- \mathbf{A} = Fluorocarbon FKM, PCTFE
- **B** = FFKM, PCTFE
- **C** = Fluorocarbon FKM, PEEK
- **D** = FFKM, PEEK

10 Flow Coefficient (C_v)

 $\mathbf{4} = 0.10$ (MPC platform only)

 $\mathbf{5} = 0.20 (1/8 \text{ in. female NPT ports only})$

11 Sensing Mechanism

P = 316 SS piston

12 Handle, Mounting

- 1 = Thumbwheel¹
- **2** = Knob
- **3** = 316 SS antitamper nut
- 5 = Thumbwheel, panel mount¹
- 6 = Knob, panel mount
- 7 = 316 SS antitamper nut, panel mount

For knob handle color options, see

page 56.

 Not available with 0 to 375 psig (0 to 25.8 bar) pressure control range.

13 Valves 0 = No valves

- 14 Cylinder Connections
- 0 = No connections

15 Gauges

0 = No gauges For inlet gauge options, see page 54.

16 Options



Medium- to High-Pressure Piston-Sensing Back-Pressure Regulators (KPB Series)

The KPB series provides back-pressure control in gas or liquid applications. This compact and lightweight regulator provides an ideal pressure-control solution within high-density compact OEM equipment, as well as other applications.

Features

- Integral high-pressure overrange protection
- Lightweight, compact design

Materials of Construction

Technical Data

Maximum Inlet Pressure

Equal to pressure control range

Pressure Control Ranges

 0 to 1000 psig (68.9 bar) through 0 to 4000 psig (275 bar)

Flow Coefficient (C_v)

0.06 and 0.2

See page 50 for flow graphs.

Maximum Operating Temperature

- 176°F (80°C) with PCTFE seat
- 392°F (200°C) with PEEK seat

Weight

2.5 lb (1.2 kg)

Ports

1/4 in. female NPT inlet, outlet, and gauge ports



Cover Stem nut Stem Knob handle Spring stabilizer Spring button Poppet Range spring retainer Body cap Piston seal and spring Poppet spring Piston seal Piston retainer Piston guide Cap ring Poppet Body seal and spring Seat retainer Seat Seat retainer Seat support seal Inlet Outlet Body

Component	Material
Knob handle, cover	Nylon with 316 SS insert
Spring button	316 SS (0 to 500 psig range) Zinc-plated steel (all other ranges)
Spring stabilizer ^①	301 SS
Range spring	316 SS or zinc coated/plated steel, depending on configuration
Stem, stem nut, cap ring, body cap, panel nuts ^②	316 SS
Nonwetted lubricant	Hydrocarbon-based
Body, seat retainer, seat support, poppet retainer, piston, piston guide	316 SS
Seat, seat retainer seal	PCTFE or PEEK
Piston seal retainer	PEEK
Poppet	S17400 SS
Poppet spring	302 SS
Piston seal, body seal	PTFE
Piston seal spring, body seal spring	Elgiloy
Wetted lubricant	PTFE-based

Wetted components listed in *italics*.

 Not included in regulators with 0 to 3000 psig (0 to 206 bar) and 0 to 4000 psig (0 to 275 bar) control ranges.

Not shown.



Dimensions, in inches (millimeters), are for reference only and are subject to change.



Panel 0.39 (10.0) thick maximum with 2 lock nuts Panel 0.63 (16.0) thick maximum with 1 lock nut Panel cutout 1.38 (35.0) dia

Ordering Information

Build a KPB series regulator ordering number by combining the designators in the sequence shown below.



4 Body Material
 1 = 316 SS
 C = 316 SS, SC-11–cleaned

5 Pressure Control Range

L = 0 to 1000 psig (0 to 68.9 bar)N = 0 to 2000 psig (0 to 137 bar)P = 0 to 3000 psig (0 to 206 bar)S = 0 to 4000 psig (0 to 275 bar)

6 Maximum Inlet Pressure

0 = Not applicable (equal to pressure control range)

7 Port Configuration

A, D, G, V See Port Configurations, page 52. 8 Ports 4 = 1/4 in. female NPT

9 Seat, Seal Material1 = PCTFE



10 Flow Coefficient (C_v) **2** = 0.06 **5** = 0.20

11 Sensing Mechanism P = 316 SS piston

12 Handle, Mounting

2 = Knob

- **3** = 316 SS antitamper nut
- 6 = Knob, panel mount

7 = 316 SS antitamper nut, panel mount

For knob handle color options, see page 56.

13 Valves 0 = No valves

-

5.00

(127)

14 Cylinder Connections0 = No connections

15 Gauges
0 = No gauges
For inlet gauge options, see page 54.

16 Options



High-Pressure Piston-Sensing Back-Pressure Regulators (KHB Series)

The KHB series provides control of back pressures up to 10 000 psig (689 bar) with high sensitivity across the control range.

Features

- Thrust roller bearing eases operation
- Panel-mounting configuration available

Technical Data

Maximum Inlet Pressure

Equal to pressure control range

Pressure Control Ranges

0 to 500 psig (34.4 bar) through
 100 to 10 000 psig (6.8 to 689 bar)

Flow Coefficient (C_v)

0.06 and 0.25

See page 51 for flow graphs.

Maximum Operating Temperature

- 212°F (100°C)
- Weight
- 5.7 lb (2.6 kg)

Ports

1/4 in. female NPT inlet, outlet, and gauge ports



Knob handle retainer Cover Knob handle Thrust roller bearing Upper spring Upper spring button button set screw Stem Range spring Stem nuts Body cap Piston Piston seal Piston seal Lower spring backup ring button Poppet retainer Piston guide seal Poppet spring Poppet retainer Body seal Seat retainer Poppet Seat Seat support Seat support seal Inlet Outlet Body

Component	Material
Knob handle, cover	Nylon with 316 SS insert
Spring buttons, upper spring button set screw, knob handle retainer, stem nuts, body cap	316 SS
Stem	CZ114 bronze
Thrust roller bearing	Hardened carbon steel
Range spring	Chrome vanadium steel
Piston seal backup ring	PEEK
Nonwetted lubricant	Hydrocarbon-based
Body, poppet retainer, seat retainer, seat support, piston, piston guide	316 SS
Seat	PEEK or 316 SS
Poppet retainer seal	PEEK
Poppet	S17400 SS
Poppet spring	302 SS
Piston seal, body seal, seat support seal	Fluorocarbon FKM
Wetted lubricant	PTFE-based

Wetted components listed in italics.



Dimensions, in inches (millimeters), are for reference only and are subject to change.



Ordering Information

Build a KHB series regulator ordering number by combining the designators in the sequence shown below.



4 Body Material

1 = 316 SS **C** = 316 SS, SC-11–cleaned

5 Pressure Control Range

J = 0 to 500 psig (0 to 34.4. bar)K = 0 to 750 psig (0 to 51.6 bar)T = 10 to 1500 psig (0.68 to 103 bar)U = 15 to 2500 psig (1.0 to 172 bar)V = 25 to 3600 psig (1.7 to 248 bar)W = 50 to 6000 psig (3.4 to 413 bar)X = 100 to 10 000 psig (6.8 to 689 bar)

6 Maximum Inlet Pressure

0 = Not applicable (equal to pressure control range)

7 Port Configuration

A, D, G, V See Port Configurations, page 52.

8 Ports

4 = 1/4 in. female NPT

 9 Seat, Piston/Body/Seat Support Seal Material
 C = PEEK, fluorocarbon FKM
 J = 316 SS, fluorocarbon FKM^①

① Not suitable for gas service.

10 Flow Coefficient (C_v)



11 Sensing Mechanism

P = 316 SS piston

12 Handle, Mounting

2 = Knob
6 = Knob, panel mount
For knob handle color options, see page 56.

13 Valves0 = No valves

- 14 Cylinder Connections
- 0 = No connections

15 Gauges

0 = No gauges For inlet gauge options, see page 54.

16 Options 0 = No options



Gas Cylinder Changeover Regulator (KCM Series)

The KCM series is a two-stage gas delivery system that ensures continuous flow of gases in critical applications. When one supply drops below the changeover pressure, the selector regulator automatically switches the gas feed from the depleted supply to an alternate supply. The automatic operation of the KCM series eliminates costly system downtime and maintenance expense of continuously monitoring the gas supply.

Features

- Convoluted, nonperforated diaphragm for strength and improved pressure response
- Metal-to-metal diaphragm seals on all stages
- Supply-pressure effect of approximately 0.01 %
- Bracket mount

Technical Data

Maximum Inlet Pressure^①

- 4351 psig (300 bar) with PEEK seat
- 3600 psig (248 bar)
- Cylinder Connections and Hose accessories may limit inlet pressure ratings, see pages 53 and 56.

Pressure Control Ranges

0 to 10 psig (0.68 bar) through
 0 to 500 psig (34.4 bar)

Operation

The KCM series can be ordered to switch from one supply to another at one of three different inlet pressures—100, 250, and 500 psig (6.8, 17.2, and 34.4 bar) called changeover pressures.

The selector regulator

(first stage) is factory-set to reduce the supply pressure to the nominal changeover pressure ordered. The line regulator (second stage) can be adjusted with the handle to achieve the required system pressure. This two-stage arrangement minimizes the supply-pressure effect caused by depleting gas supplies (cylinders, tank farm, etc.).

When one supply drops below the changeover pressure, the selector regulator automatically switches the gas feed from the depleted supply to an alternate supply. If both supplies drop below the changeover pressure, the assembly functions as a single-stage regulator, depleting both supplies at the same time. See the **Approximate Supply Depletion Pressures** table at right for pressures at which this occurs.

The Swagelok KCA series continuous gas delivery system is a panel-mounted gas changeover assembly that can be configured for many applications. For more information, see the Swagelok KCA Series Continuous Gas Delivery System catalog, <u>MS-18-01.</u>

Nominal Changeover Pressures

100, 250, and 500 psig (6.8, 17.2, and 34.4 bar)

Flow Coefficient (C_{ν})

0.06

Supply-Pressure Effect

	Pressure Control Range			
Flow Coefficient	Up to 100 psig (6.8 bar)	250 psig (17.2 bar) and Higher		
(C _v)	Supply Press	ure Effect, %		
0.06	0.01	0.02		

Maximum Operating Temperature

- 176°F (80°C) with PCTFE seat
- 392°F (200°C) with PEEK seat
- 212°F (100°C) with PEEK seat and maximum inlet pressure greater than 3600 psig (248 bar)





Shown with Swagelok tube fittings, not included.

Weight

7.25 lb (3.3 kg)

Ports

1/4 in. female NPT inlet, outlet, and gauge ports

Materials of Construction

The KCM series gas changeover uses Swagelok KPR series pressure-reducing regulators. For more information, see **General-Purpose Diaphragm Sensing, Pressure-Reducing Regulators (KPR Series),** page 6.

The table below lists additional components not shown in the KPR series section.

Component	Material		
Interstage fitting	316 SS with PTFE tape		
Line-regulator mounting block	Aluminum		
Line-regulators mounting screws, mounting bracket	316 SS		

Wetted components listed in italics.

Approximate Supply Depletion Pressures

Nominal Changeover Pressure psig (bar)	Supply 1 Depletion Pressure psig (bar)	Supply 1 (300 bar) Depletion Pressure psig (bar)	Supply 2 Depletion Pressure psig (bar)
100 (6.8)	150 (10.3)	180 (12.4)	90 (6.2)
250 (17.2)	300 (20.6)	320 (22.1)	230 (15.8)
500 (34.4)	500 (34.4)	530 (36.6)	450 (31.0)

Supply 2 can deplete below some of the available pressure control range limits. Setting the line regulator near the nominal changeover pressure will cause flow to the system to decrease or stop as the supply nears depletion.



Dimensions, in inches (millimeters), are for reference only and are subject to change.



Ordering Information

Build a KCM series regulator ordering number by combining the designators in the sequence shown below.

Q 13 5 6 8 12 14 15 16 10 KCM 1 F F В 4 1 2 D 0 0 Δ 1 0

4 Body Material

1 = 316 SS **C** = 316 SS, SC-11–cleaned

5 Pressure Control Range

- **C** = 0 to 10 psig (0 to 0.68 bar)
- D = 0 to 25 psig (0 to 1.7 bar)
- E = 0 to 50 psig (0 to 3.4 bar)
- **F** = 0 to 100 psig (0 to 6.8 bar)
- **G** = 0 to 250 psig (0 to 17.2 bar)^①
- **J** = 0 to 500 psig (0 to 34.4 bar)²
- ① Not available with 100 psig (6.8 bar) changeover pressure.
- ② Only available with 500 psig (34.4 bar) changeover pressure.

6 Nominal Changeover Pressure^①

- F = 100 psig (6.8 bar)
- **G** = 250 psig (17.2 bar) J = 500 psig (34.4 bar)
- For 4351 psig (300 bar) inlet²
 - 5 = 100 psig (6.8 bar)
 - 6 = 250 psig (17.2 bar)
 - 7 = 500 psig (34.4 bar)
- ① Inlet pressure must exceed changeover pressure for automatic switching to occur.
- Only available with PEEK seat.

Port Configurations

7 Port Configuration

B, C, L See Port Configurations, below.

8 Ports

4 = 1/4 in, female NPT

9 Seat Material

1 = PCTFE **2** = PEEK

2 = 0.06

11 Sensing Mechanism, Vent

- **A** = Alloy X-750 diaphragm, no vent
- C = Alloy X-750 diaphragm, self vent¹
- captured vent^①
- regulator only.

12 Line Regulator Handle **D** = Knob

E = 316 SS antitamper nut

Selector regulator has knob handle. For knob handle color options, see page 56.

13 Isolation and Relief Valves

0 = No valves

For isolation and relief valve options, see page 54.

14 Cylinder Connections

0 = No connections

Cylinder connections available only with hose option. For cylinder connection options and pressure ratings, see page 53.

15 Gauge Scale

- 1 = psig (bar) (North America only)
- $\mathbf{2} = bar (psig)$
- $\mathbf{3} = psiq$ (bar)
- **4** = MPa
- 5 = psig (kPa)

For more information, see page 54.

16 Options

- **0** = No options
- **3** = 3 ft, 1/4 in. FX series metal flexible hose, 1/4 in. female NPT inlet¹
- 4 = 3 ft, 1/4 in. TH series PTFE-lined, stainless steel braided hose, 1/4 in. female NPT inlet^①

For hose options and pressure ratings, see page 56.

① Not available for SC-11-cleaned regulators.

Configuration	Designator	Configuration	Designator	Configuration	Designator	
Inlet from selector regulator	В	G _o /R Inlet from selector regulator	С	R I Inlet from selector regulator	L	G _o = O G _o /R = O R = R I = Is

utlet gauge. utlet gauge relief valve. elief valve.





10 Flow Coefficient (C_v)

- F = Alloy X-750 diaphragm, self and
- ① Self and captured vent options on line

Steam-Heated Vaporizing, Diaphragm-Sensing Pressure-Reducing Regulator (KSV Series)

The KSV series is a steam-heated vaporizing regulator with a low internal volume. It can be used to vaporize liquid samples or to preheat gas samples to prevent them from condensing.

Features

- Convoluted, nonperforated diaphragm
- Metal-to-metal diaphragm seal
- Low internal volume

Technical Data

Maximum Inlet Pressure

3600 psig (248 bar)

Outlet Pressure Ranges

 0 to 10 psig (0.68 bar) through 0 to 500 psig (34.4 bar)

Flow Coefficient (C_v)

0.06 or 0.20

Supply-Pressure Effect



Maximum Steam Pressure and Temperature

650 psig (44.7 bar) and 500°F (260°C)

Maximum Regulator Operating Temperature

■ 392°F (200°C)

Weight

3.3 lb (1.5 kg)

Ports

- 1/8 in. female NPT inlet; 1/4 in. female NPT outlet(s)
- Steam tube 1/2 in. outside diameter, 0.065 in. wall





Component	Material	
Antitamper nut, stem, cap ring, stop plate, body cap, panel nuts ^①	316 SS	
Spring button	Zinc-plated steel	
Spring stabilizer [®]	301 SS	
Range spring	316 SS or zinc coated/plated steel, depending on configuration	
Nonwetted lubricant	Hydrocarbon-based	
Body, seat retainer, steam tube	316 SS	
Seat	PEEK	
Diaphragm, ³ poppet spring	Alloy X-750	
Poppet	S17400 SS	
Wetted lubricant	PTFE-based	

Wetted components listed in italics.

1 Not shown.

Not required in all configurations.

③ Regulators with control ranges higher than 0 to 100 psig (0 to 6.8 bar) are assembled with two diaphragms.


Dimensions

Dimensions, in inches (millimeters), are for reference only and are subject to change.



Ordering Information

Build a KSV series regulator ordering number by combining the designators in the sequence shown below.



4 Body Material

1 = 316 SS **C** = 316 SS, SC-11–cleaned

5 Pressure Control Range

- **C** = 0 to 10 psig (0 to 0.68 bar) **D** = 0 to 25 psig (0 to 1.7 bar)
- E = 0 to 50 psig (0 to 3.4 bar)
- $\mathbf{F} = 0$ to 100 psig (0 to 6.8 bar)
- G = 0 to 250 psig (0 to 17.2 bar)
- J = 0 to 500 psig (0 to 34.4 bar)

6 Maximum Inlet Pressure^①

- **F** = 100 psig (6.8 bar)
- **J** = 500 psig (34.4 bar)
- **L** = 1000 psig (68.9 bar)
- R = 3600 psig (248 bar)

0 For better resolution and control, select a pressure that closely matches system pressure.

7 Port Configuration

1, 4

See Port Configurations, right.

8 Ports

3 = 1/8 in. female NPT inlet; 1/4 in. female NPT outlet(s)

9 Seat Material
 2 = PEEK

10 Flow Coefficient (C_v)

2 = 0.06 **5** = 0.20

11 Sensing Mechanism, Vent

- A = Alloy X-750 diaphragm, no vent
- **E** = Alloy X-750 diaphragm, captured vent, no self vent

12 Handle, Mounting

- **3** = Antitamper nut
- 7 = Antitamper nut, panel mount
- 13 Valves 0 = No valves
- **14 Cylinder Connections** 0 = No connections

15 Gauges

- 0 = No gauges
- 16 Options
- 0 = No options

Port Configurations





Electrically Heated Vaporizing Pressure-Reducing Regulator (KEV Series)



Technical Data

Maximum Inlet Pressure

3600 psig (248 bar)

Pressure Control Ranges

0 to 10 psig (0.68 bar) through
 0 to 3600 psig (248 bar)

Flow Coefficient (C_v)

0.02 or 0.06

Supply-Pressure Effect

	Pressu	re Control	Range
Flow Coefficient	Up to 100 psig (6.8 bar)	250 and 500 psig (17.2 and 34.4 bar)	1000 psig (68.9 bar) and Higher
(C _v)	Supply Pressure Effect, %		ffect, %
0.02	0.3	0.5	2.2
0.06	1.0	1.5	7.2

Weight

- Side mounted—8.8 lb (4.0 kg)
- Base mounted—7.7 lb (3.5 kg)

Ports

1/8 in. female NPT inlet; 1/4 in. female NPT outlet The KEV series is an electrically heated vaporizing regulator with a low internal volume. It can be used to vaporize liquid samples or to preheat gas samples to prevent them from condensing. It features a heating element that is in direct contact with the process fluid for maximum thermal efficiency and is removable for easy cleaning. The KEV regulator has an integral temperature controller and is rated for use in hazardous areas, as identified below.



Electrical

- Supply—120 and 240 V (ac) (± 10 %), 50/60 Hz
- Heater ratings—50, 100, 150, and 200 W
- Control temperature range 75 to 380°F (23 to 193°C)
- Explosive atmosphere/hazardous location certification:
 - ATEX (Europe), UKEX (Great Britain), and IECEx (international), and Japan—Group II, Category 2G, Ex db IIB+H₂ T3 Gb Ambient temperatures: -4 to 140°F (-20 to 60°C)
 - CSA (Canada and U.S.A.)— Class I, Div 1, Groups B, C, and D; T3; CSA Encl Type 4 Ambient temperatures: –58 to 122°F (–50 to 50°C)

\land WARNING

Certification and hazardous type protection may be impaired if the KEV regulator is used in a manner not specified by Swagelok. Refer to KEV Series Electrically Heated Vaporizing Pressure Reducing Regulators Instructions for Use, MS-CRD-KEV1, for correct method of installation, operation, and use.

Features

- Convoluted, nonperforated diaphragm for control ranges up to 500 psig (34.4 bar)
- Stainless steel piston for control ranges from 1000 to 3600 psig (68.9 to 248 bar)
- ATEX, IECEx, UKEX, and CSA certified for critical/hazardous environments
- T3 temperature classification for all heater ranges
- CE conformity: 89/336/EEC (EMC)
- Horizontally or vertically mounted
- One-piece body eliminates potential leak paths
- Low-volume vapor chamber for fast response
- Heater in direct contact with process media for maximum thermal efficiency
- Removable heater simplifies cleaning
- Side and base inlet options

A WARNING

Do not alter or disassemble any of the flameproof joints within the KEV series regulator. Damage to the regulator resulting in affected performance and product safety is possible.

A WARNING

There is a potential for air to become trapped within the piping system, creating the possibility of a combustible mixture. This could occur during system startup or shutdown. In order to allow the KEV heater tube to stabilize at ambient temperature, turn off the power to the regulator during system startup and shutdown. The amount of time needed for the system to reach ambient conditions depends on several system parameters including, but not limited to, set point, flow rate, ambient temperature, and the thermal properties of the system and fluid.

Contact your authorized sales and service representative for any maintenance or repair beyond the maintenance of the heater sheath.



Materials of Construction



Component	Material
Antitamper nut, stem, cap ring, stop plate, body cap, retainer nut, flange, flange bolts, lock nut, connector tube, panel nuts [®]	316 SS
Spring button	Zinc-plated steel
Spring stabilizer ³	301 SS
Range spring	316 SS or zinc coated/plated steel, depending on configuration
Connector tube seal	Nitrile
Nonwetted lubricant	Hydrocarbon-based
Body, seat retainer, heater sheath	316 SS
Heater sheath seal	Alloy 718
Seat	PEEK
Diaphragm ^{①④}	Alloy X-750
Poppet	S17400 SS
Poppet spring	302 SS
Wetted lubricant	PTFE-based
Piston Sensing	g Components
Piston seal, body seal	PTFE
Piston, piston guide	316 SS
Piston seal retainer	PEEK
Piston seal spring, body seal spring	Elgiloy

Wetted components listed in *italics*.

 Not included in regulators with piston sensing mechanism.

2 Not shown.

③ Not required in all configurations.

④ Regulators with control ranges 0 to 250 psig (0 to 17.2 bar) and 0 to 500 psig (0 to 34.4 bar) are assembled with two diaphragms.

Piston Sensing Mechanism



Dimensions

Dimensions, in inches (millimeters), are for reference only and are subject to change.







Ordering Information

Build a KEV series regulator ordering number by combining the designators in the sequence shown below.



4 Body Material

1 = 316 SS **C** = 316 SS, SC-11–cleaned

5 Pressure Control Range

 $\begin{array}{l} \textbf{Diaphragm Sensing} \\ \textbf{C} = 0 \ to \ 10 \ psig \ (0 \ to \ 0.68 \ bar) \\ \textbf{D} = 0 \ to \ 25 \ psig \ (0 \ to \ 1.7 \ bar) \\ \textbf{E} = 0 \ to \ 50 \ psig \ (0 \ to \ 3.4 \ bar) \\ \textbf{F} = 0 \ to \ 100 \ psig \ (0 \ to \ 6.8 \ bar) \\ \textbf{G} = 0 \ to \ 250 \ psig \ (0 \ to \ 17.2 \ bar) \\ \textbf{J} = 0 \ to \ 500 \ psig \ (0 \ to \ 34.4 \ bar) \end{array}$

Piston Sensing

L= 0 to 1000 psig (0 to 68.9 bar)**M**= 0 to 1500 psig (0 to 103 bar)**N**= 0 to 2000 psig (0 to 137 bar)**P**= 0 to 3000 psig (0 to 206 bar)**R**= 0 to 3600 psig (0 to 248 bar)

6 Maximum Inlet Pressure^①

- F = 100 psig (6.8 bar)²
- **J** = 500 psig (34.4 bar)²
- L = 1000 psig (68.9 bar)²
- **R** = 3600 psig (248 bar)
- ① For better resolution and control, select a
- pressure that closely matches system pressure. ② Available with diaphragm sensing mechanism
- only.

7 Port Configuration

Side Mount-A, X, 1, 2

Base Mount–A, B, X, Y, Z

See Port Configurations, below.

8 Ports

3 = 1/8 in. female NPT inlet; 1/4 in. female NPT outlet(s)

9 Seat Material

2 = PEEK

10 Flow Coefficient (C_v)

- **1** = 0.02
- **2** = 0.06

11 Sensing Mechanism

- A = Alloy X-750 diaphragm (outlet pressures up to 500 psig [34.4 bar])
- **P** = 316 SS piston (outlet pressures above 500 psig [34.4 bar])

12 Handle, Mounting

- **W** = Antitamper nut, side mount
- **X** = Antitamper nut, base mount

- 13 Valves
- 0 = No valves

14 Cylinder Connections

0 = No connections

15 Gauges

0 = No gauges

16 Heater, Controller

75 to 380°F (23 to 193°C), 240 V
6 = 50 W
7 = 100 W
8 = 150 W
9 = 200 W



->> Outlet and auxiliary ports on the same face.





The graphs illustrate the change or "droop" in outlet pressures as the flow rate increases. Refer to Swagelok Pressure-Reducing Regulator Flow Curves Technical Bulletin, MS-06-114, for an overview of how to read regulator flow curves and for additional inlet pressures and flow coefficients

Flow Coefficient 0.20;

KPR Series

0

20

15

10

5.0

0

0

80

60

40

20 -

0

0

400

300

200

100

0

Outlet Pressure, psig

Outlet Pressure, psig

Outlet Pressure, psig

40

80

100 psig (6.8 bar)

2.0

200

100 psig

(6.8 bar)

100 psig

(6.8 bar)

5.0

10

400

500 psig

500 psig (34.4 bar)

10

20

(34.4 bar)







42 Pressure Regulators and Filters

K Series Pressure-Reducing Regulator Flow Data

The graphs illustrate the change or "droop" in outlet pressures as the flow rate increases.

KCY Series



Swagelok

The graphs illustrate the change or "droop" in outlet pressures as the flow rate increases.

KLF Series





The graphs illustrate the change or "droop" in outlet pressures as the flow rate increases.

KPF Series

Flow Coefficient 1.0;

KHF Series





Swagelok

The graphs illustrate the change or "droop" in outlet pressures as the flow rate increases.

KCP Series

Flow Coefficient 0.06; Maximum Inlet Pressure 3600 psig (248 bar)











The graphs illustrate the change or "droop" in outlet pressures as the flow rate increases.

KHP Series

Flow Coefficient 0.06; Maximum Inlet Pressure 10 000 psig (689 bar)



The graphs illustrate the change or "droop" in outlet pressures as the flow rate increases.

KHP Series



KHR Series

Flow Coefficient 0.06; Maximum Inlet Pressure 10 000 psig (689 bar)





The graphs illustrate the change or "droop" in outlet pressures as the flow rate increases.

KPP Series



Flow Coefficient 0.02; Maximum Inlet Pressure 4000 psig (275 bar)



Flow Coefficient 0.06; Maximum Inlet Pressure 2000 psig (137 bar)



Flow Coefficient 0.06; Maximum Inlet Pressure 6000 psig (413 bar)





K Series Back-Pressure Regulator Flow Data

The graphs illustrate the change in inlet pressure as the flow rate increases.

KBP Series



KCB Series

Flow Coefficient 0.20



K Series Back-Pressure Regulator Flow Data

The graphs illustrate the change in inlet pressure as the flow rate increases.

KPB Series

Flow Coefficient 0.06



Flow Coefficient 0.20





Inlet Pressure, bar

bar

Pressure,

Inlet I

K Series Back-Pressure Regulator Flow Data

The graphs illustrate the change in inlet pressure as the flow rate increases.

25

30

35

KHB Series

4500

0

5.0

10

15

20

Nitrogen Flow, std ft3/min

Flow Coefficient 0.06



Flow Coefficient 0.25

Pressure Regulators and Filters 52

Port Configurations

Outlet

Port configurations are available as shown in the regulator ordering information pages. The symbols indicate the port location of *factory-assembled* accessories. For alternative accessory locations, contact your authorized Swagelok representative.



G_i Inlet gauge

- R Relief valve Go/R Outlet gauge or relief
- valve

Select regulators are available on special order with additional port configurations. Contact your authorized Swagelok representative for more information.

Factory-assembled cylinder connections are placed on a filtered main inlet port; isolation valves are placed on an outlet port 180° from the cylinder connection.

Pressure-Reducing Regulators



Left-to-Right Flow



Back-Pressure Regulators

Right-to-Left Flow



Left-to-Right Flow



MPC Port Configurations

Pressure Reducing



Back Pressure

Configuration	(+) (+) Outlet Inlet (+) (+) (+) (+)	(+) (+) Inlet Inlet (+) (+) (+) (+) (+) (+) (+) (+) (+) (+) (+) (+) (+) (+) (+) (+) (+) (+) (+)
	2-Port	3-Port
Designator	7	8



Regulator accessories are available separately or mounted on Swagelok regulators. Some accessories limit regulator pressure or temperature ratings. Additional materials, options, and accessories are available. Contact your authorized Swagelok representative for more information.



Cylinder Connections

- Available in a variety of 4 in (100 mm) long CGA, BS or DIN connections
- Stainless steel construction

Insert a designator into the ordering number as shown in the appropriate regulator ordering information pages.



Cylinder Gases and Connections

Cylinder Connection	Typical Gases (others may be applicable)	Rated Pressure psig (bar)	Connection Designator
CGA 320	Carbon Dioxide	3000 (206)	В
CGA 347	High pressure Air	5500 (379)	1
CGA 350	Hydrogen, Natural Gas	3000 (206)	D
CGA 540	Oxygen	3000 (206)	F ^①
CGA 580	Helium, Nitrogen	3000 (206)	G
CGA 590	Sulfur Hexafluoride	3000 (206)	Н
CGA 660	Nitrogen Dioxide, Phosgene	3000 (206)	J
CGA 680	High pressure inert gas	5500 (379)	2
CGA 695	High pressure flammable gas	5500 (379)	3
BS 3	Argon, Helium	3600 (250)	R
BS 4	Hydrogen, Natural Gas	3600 (250)	S
BS 8	Carbon Dioxide	3600 (250)	V
BS/ISO 30	High pressure inert gas	4351 (300)	4
BS/ISO 31	High pressure Air	4351 (300)	5
BS/ISO 32	High pressure oxidising gas	4351 (300)	6
BS/ISO 38	High pressure flammable gas	4351 (300)	8
DIN 1	Ethane, Hydrogen	4351 (300)	К
DIN 5	Carbon monoxide, Hydrogen sulfide	4351 (300)	L
DIN 6	Ammonia, Xenon	4351 (300)	М
DIN 8	Chlorine, Hydrogen chloride	4351 (300)	N
DIN 10	Nitrogen	4351 (300)	Р
DIN 13	Air	4351 (300)	Z

Regulator inlet pressures and any optional accessories must be rated to the Cylinder connectors pressure. See the ordering information for each regulator for details.

 Available only on select KPR and KCY series regulators. Contact your authorized Swagelok representative.

Other cylinder connections are also available. Contact your authorized Swagelok representative for more information.





Pressure Gauges

- Provides measure of inlet pressure, outlet pressure, or both
- 2 1/2 in. (63 mm) dial size with 1/4 in. male NPT connection
- 1 1/2 in. (40 mm) dial size with 1/8 in. male NPT connection
- Stainless steel cases and wetted components

Refer to Swagelok Pressure Gauges, Industrial and Process catalog, <u>MS-02-170</u>, for additional information.

Cleaning

Gauges assembled to SC-11–cleaned regulators are cleaned in accordance with ASME B40.100 level IV.

Ordering Information

To order a regulator assembled with gauges, insert a designator from the table below into the ordering number as shown in the appropriate regulator ordering information pages. The maximum gauge pressures are appropriate for the maximum inlet pressure and/or control pressure ordered.

Gauge Scale	Gauge Designator			
primary unit (secondary unit)	Inlet and Outlet	Inlet Only	Outlet Only	Gauge Model ^{①③}
psig (bar) (North America only) ^②	1	А	G	С
psig (bar)	3	С	J	В
psig (kPa)	5	E	L	С
bar (psig)	2	В	Н	В
MPa	4	D	K	В

① KCP and KCB series regulators are assembled with M model gauges.

② Not available for KCP and KCB series regulators.

③ For pressure control range 0 to 2.0 psig, Gauge model L will be used on the outlet. Secondary units may vary.

Isolation Valves

- Allow isolation from downstream equipment
- Working pressures up to 5000 psig (344 bar)
- 316 stainless steel construction
- Swagelok integral-bonnet needle valve (1 series)
- Used in conjunction with an adjustable regulator relief valve

Refer to Swagelok Integral-Bonnet Needle Valves catalog, <u>MS-01-164</u>, for additional information.

Isolation Valve and Relief Valve Ordering Information

Isolation valves are available factory assembled on KCP, KPP, KPF, KHP, KHR, and KHB series regulators. Isolation and adjustable regulator relief valves are available factory assembled on KPR, KCY, KCM, KLF, and KHF series regulators.

To order a regulator factory assembled with an isolation valve or isolation valve and adjustable regulator relief valve, insert a designator from the table below into the ordering number as shown in the appropriate regulator ordering information pages.

	Val	ve Designa	tor
Description	Relief Only	Isolation Only ^①	Isolation and Relief
Kenmac [®] KVV series adjustable regulator relief valve	1	-	_
1/4 in. male NPT inlet 1/4 in. Swagelok tube fitting outlet angle pattern isolation valve		A	2
1/4 in. male NPT inlet6 mm Swagelok tube fitting outlet angle pattern isolation valve		В	3
1/4 in. male NPT inlet 1/4 in. female NPT outlet angle pattern isolation valve		С	4
1/4 in. Swagelok tube fitting inlet [®] and outlet straight pattern isolation valve	_	E	6
6 mm Swagelok tube fitting inlet and outlet straight pattern isolation valve		F	7
3/8 in. Swagelok tube fitting inlet [®] 1/4 in. female NPT outlet straight pattern isolation valve		G	8

0 Not available on KPR, KCY, KCM, KLF, and KHF series regulators, because a relief valve is needed to protect the diaphragm sensing mechanism.

② Includes male NPT to Swagelok tube adapter fitting (required for regulators with 1/8 and 1/2 in. female NPT ports).





Kenmac Adjustable Regulator Relief Valves (KVV Series)

 Provide non-safety related pressure protection for Swagelok regulators



Technical Data

Relief Pressure Ranges

Based on the regulator control range

Regulator Control Range psig (bar)	Relief Pressure Range psig (bar)
0 to 10 (0 to 0.68) 0 to 25 (0 to 1.7) 0 to 50 (0 to 3.4)	0 to 100 (0 to 6.8)
0 to 100 (0 to 6.8)	50 to 200 (3.4 to 13.7)
0 to 250 (0 to 17.2) 0 to 500 (0 to 34.4)	150 to 500 (10.3 to 34.4)

Maximum Operating Temperature

■ 392°F (200°C)

Weight

0.26 lb (0.12 kg)

Ports

■ 1/4 in. NPT male inlet and female outlet

Materials of Construction

Component	Material
Body, poppet, spring button, adjusting screw	316 SS
Seal	Fluorocarbon FKM
Range spring	302 SS
Lubricant	PTFE Based
Seal Bond	ECA Adhesive

Wetted components listed in *italics*.

Testing

Every KVV series regulator relief valve is factory tested at its maximum rated pressure, then set to zero when assembled to the regulator.

Reset relief pressure to the desired value before pressurizing the system.

The specification for materials used in equipment for oxygen service is the responsibility of the system designer.

Flow Data

The graph illustrates the discharge characteristics of the Kenmac adjustable regulator relief valve.



Ordering Information

To order a KVV adjustable regulator relief valve separately, select an ordering number from the table below.

Relief Pressure Range psig (bar)	Ordering Number
0 to 100 (0 to 6.8)	KVV11DE1
50 to 200 (3.4 to 13.7)	KVV11DG1
150 to 500 (10.3 to 34.4)	KVV11DI1

Special Cleaned KVVs

To order a specially-cleaned and packaged KVV in accordance with Swagelok *Special Cleaning and Packaging* (SC-11), select an ordering number from the table below.

Relief Pressure Range psig (bar)	Ordering Number
0 to 100 (0 to 6.8)	KVVC1DE1
50 to 200 (3.4 to 13.7)	KVVC1DG1
150 to 500 (10.3 to 34.4)	KVVC1DI1

- For valves not actuated for a period of time, initial relief pressure may be higher than the set pressure.
- Some system applications require relief valves to meet specific safety codes. The system designer and user must determine when such codes apply and whether these relief valves conform to them.
- Kenmac adjustable regulator relief valves should never be used as ASME Boiler and Pressure Vessel Code safety relief devices.
- Kenmac adjustable regulator relief valves are not "Safety Accessories" as defined in the Pressure Equipment Directive 2014/68/EU.



Hoses

Hoses are available assembled to the inlet of the regulator to allow connection to remote gas cylinders.

Hose options include:

- 3 ft long Swagelok 1/4 in. high-pressure, metal flexible hose (FX series), 1/4 in. female NPT inlet, 1/4 in. male NPT outlet connected to regulator: SS-FX4PM4PF4-36 Rated to 6000 psig (413 bar) at 100°F (37°C)
- 3 ft long Swagelok 1/4 in. PTFE-lined, stainless steel braided hose (TH series), 1/4 in. female NPT inlet, 1/4 in. male NPT outlet connected to regulator: SS-TH4PM4PF4-36 Rated to 3100 psig (213 bar) at 100°F (37°C)

Refer to Swagelok Hose and Flexible Tubing catalog, <u>MS-01-180</u>, for additional information.

Cleaning

Hoses are not available assembled to SC-11 speciallycleaned regulators.

Handles

Knob, thumbwheel, and antitamper handles are available.

The green plastic knob handle is standard for most Swagelok regulators. Other colors are available; add a handle color designator to a regulator ordering number.



Thumbwheel

Color	Designator
Black	BK
Blue	BL
Orange	OG
Red	RD
Yellow	YW

Example: KPR1FRF412A20000BK

The metal thumbwheel handle is available for the compact KCB and KCP series regulators.

The metal antitamper nut is available to prevent inadvertent pressure adjustment.



Wall Mounting Brackets

Stainless steel wall mounting brackets are available for many Swagelok regulators.





KPR, KLF, KHF, KCP, KPP, KPF, KHP, KBP, KFB, KCB,

KPB, and KHB Series

Mounting Bracket

KCY Series Mounting Bracket Requires 1st stage panel-

mount option. See page 9.

Wall Mounting Bracket Kits

Regulator Series	Ordering Number
KPR, KLF, KHF, KCP, KPP, KPF, KHP, KBP, KFB, KCB, KPB, KHB	9R0079
KCY	9R0149

Maintenance Kits

Filter Replacement Kits

Filter replacement kits are available for KPR, KCM, KCP, KCY, KPP, KHP, KLF, KHR, KHF, and KPF series regulators.

Filter replacement kits include:

- five sets of filters and carrier assemblies
- instructions.

Regulator Series	Inlet Size	Ordering Number
KCP	1/8 in. NPT	REG-FILTER-2-KIT5
KPR, KCM, KCY, KPP, KHP, KLF, KHR	1/4 in. NPT	REG-FILTER-4-KIT5
KHF, KPF	1/2 in. NPT	REG-FILTER-8-KIT5



Maintenance Kits

KPR, KCP, AND KBP Series Maintenance Kits

Maintenance kits include:

- all wetted components, except for the regulator body and piston, if applicable
- wetted lubricant with MSDS
- instructions.

Maintenance Kits for Other Regulator Series

Maintenance kits for KLF, KHF, KPP, KPF, KHP, KHR, KFB, KCB, KCY, KPB, KHB, KSV, and KEV series regulators are available.

To order, contact your authorized Swagelok representative; to ensure correct kit contents, please provide the original regulator ordering number.

Maintenance Instructions

Maintenance instructions for all Swagelok regulators are available from your Swagelok website.

Maintenance Tools

Specially designed tools and tool kits are available to assist in the service and repair of Swagelok regulators. Contact your authorized Swagelok representative for more information.

Ordering Information

Build a maintenance kit ordering number by combining the designators in the sequence shown below.



123 Regulator Series

KPR = KPR **KCP** = KCP **KBP** = KBP

4 Body Material, Cleaning

- $\mathbf{1}$ = 316 SS and brass
- **C** = 316 SS and brass, SC-11 cleaned

5 Pressure Control Range KPR and KBP Series

- D = 0 to 10 psig (0 to 0.68 bar) and 0 to 25 psig (0 to 1.7 bar)
- **F** = 0 to 50 psig (0 to 3.4 bar) and 0 to 100 psig (0 to 6.8 bar)
- J = 0 to 250 psig (0 to 17.2 bar) and 0 to 500 psig (0 to 34.4 bar)

KCP Series

- G = 0 to 10 psig (0 to 0.68 bar), 0 to 25 psig (0 to 1.7 bar), 0 to 50 psig (0 to 3.4 bar), 0 to 100 psig (0 to 6.8 bar), and 0 to 250 psig (0 to 17.2 bar)
 M = 0 to 500 psig (0 to 34.4 bar),
- 0 to 1000 psig (0 to 68.9 bar), and 0 to 1500 psig (0 to 103 bar) $^{\odot}$
- ① Not available with MPC platform port configuration.

6 Maximum Inlet Pressure 0 = Not applicable

7 Port Configuration

0 = Not applicable

8 Ports (Filter Size)

KPR Series

4 = 1/4 in. female NPT0 = All other end connections

KBP Series

0 = Not applicable

KCP Series

2 = 1/8 in. female NPT M = MPC platform

9 Seat, Seal Material

KPR Series

1 = PCTFE **2** = PEEK

KBP and KCP Series

- A = Fluorocarbon FKM, PCTFE
- **B** = FFKM, PCTFE
- C = Fluorocarbon FKM, PEEK
- **D** = FFKM, PEEK

10 Flow Coefficient (C_v)

- **1** = 0.02 **2** = 0.06
- $\mathbf{2} = 0.00$ $\mathbf{5} = 0.20^{12}$
- **7** = 0.20[®]
- Not available for KCP series with MPC platform port configuration.
- Required for KBP series.

11 Sensing Mechanism, Vent *KPR Series*

- A = Alloy X-750 diaphragm, no-vent models and captured-vent models
- **C** = Alloy X-750 diaphragm, self-vent models and self- and capturedvent models

KBP Series

A = Alloy X-750 diaphragm, all models

KCP Series

P = 316 SS piston

12 Handle, Mounting

0 = Not applicable



58 Pressure Regulators and Filters

Additional Products

Filters

Swagelok offers a variety of filters, filter elements, and sizes.

- 316 SS and brass materials
- Sintered and strainer elements
- Tee type, inline, and all-welded models

Refer to Swagelok filters, see the *Filters*—*FW*, *F*, and *TF* Series catalog, <u>MS-01-92</u>, for additional information.

Transducers

Swagelok industrial pressure transducers electronically monitor fluid system pressure in a variety of analytical and process applications.

- Accurate and repeatable readings
- Swagelok tube adapter end connections available for ease of installation and maintenance
- CE compliant

Refer to Swagelok industrial pressure transducers, see the *Industrial Pressure Transducers* catalog, <u>MS-02-225</u>, for additional information.





- ▲ Swagelok pressure regulators are not "Safety Accessories" as defined in the Pressure Equipment Directive 2014/68/EU.
- Δ Do not use the regulator as a shutoff device.

Do not mix/interchange Swagelok products or components not governed by industrial design standards, including Swagelok tube fitting end connections, with those of other manufacturers.

Introduction

Since 1947, Swagelok has designed, developed, and manufactured high-quality, general-purpose and specialty fluid system products to meet the evolving needs of global industries. Our focus is on understanding our customers' needs, finding timely solutions, and adding value with our products and services.

We are pleased to provide this global edition of the book-bound *Swagelok Product Catalog,* which compiles more than 100 separate product catalogs, technical bulletins, and reference documents into one convenient, easy-to-use volume. Each product catalog is up to date at the time of printing, with its revision number shown on the last page of the individual catalog. Subsequent revisions will supersede the printed version and will be posted on the Swagelok website and in the Swagelok electronic Desktop Technical Reference (eDTR) tool.

For more information, visit your Swagelok website or contact your authorized Swagelok sales and service representative.

Warranty Information

Swagelok products are backed by The Swagelok Limited Lifetime Warranty. For a copy, visit swagelok.com or contact your authorized Swagelok representative.

Safe Product Selection

When selecting a product, the total system design must be considered to ensure safe, trouble-free performance. Function, material compatibility, adequate ratings, proper installation, operation, and maintenance are the responsibilities of the system designer and user.

Do not mix/interchange Swagelok products or components not governed by industrial design standards, including Swagelok tube fitting end connections, with those of other manufacturers. Not all trademarks listed below apply to this catalog. Swagelok, Cajon, Ferrule-Pak, Goop, Hinging-Colleting, IGC, Kenmac, Micro-Fit, Nupro, Snoop, Sno-Trik, SWAK, VCO, VCR, Ultra-Torr, Whitey-TM Swagelok Company 15-7 PH-TM AK Steel Corp. AccuTrak, Beacon, Westlock-TM Tyco International Services Aflas-TM Asahi Glass Co., Ltd. Alleima-TM Alleima ASCO, EI-O-Matic-TM Emersor AutoCAD-TM Autodesk, Inc. CSA-TM Canadian Standards Association Crastin, DuPont, Kalrez, Krytox, Teflon, Viton-TM E.I. duPont Nemours and Company DeviceNet-TM ODVA Dyneon, Elgiloy, TFM-TM Dyneon Elgiloy–TM Elgiloy Specialty Metals Festo–TM Festo SE & Co. KG FM – TM FM Global Grafoil-TM GrafTech International Holdings, Inc. Honeywell, MICRO SWITCH-TM Honeywell MAC-TM MAC Valves Microsoft, Windows-TM Microsoft Corp. NACE-TM NACE International PH 15-7 Mo, 17-7 PH-TM AK Steel Corp picofast-Hans Turck KG Pillar-TM Nippon Pillar Packing Company, Ltd. Raychem-TM Tyco Electronics Corp. Sandvik, SAF 2507-TM Sandvik AB Simriz-TM Freudenberg-NOK SolidWorks-TM SolidWorks Corporation UL-Underwriters Laboratories Inc. Xylan-TM Whitford Corporation © 2022 Swagelok Company